

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192338

Luminaire Tested: **LDA6A45950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3858.7 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67747	67747	67747
5°	108447	66899	43374
10°	158464	64250	29236
15°	216653	60931	22083
20°	271046	57691	22291
25°	313101	57499	34575
30°	342983	54432	32157
35°	354164	46143	24828
40°	346628	35996	19551
45°	315971	26569	15002
50°	253953	19599	10055
55°	154632	13868	5687
60°	80235	9166	2215
65°	39109	4838	1038
70°	17936	2100	962
75°	7477	1504	1059
80°	3852	1578	1294
85°	2579	3145	1887



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	3.3
10°-20°	449.1	11.6
20°-30°	850.3	22.0
30°-40°	1029.8	26.7
40°-50°	861.9	22.3
50°-60°	417.7	10.8
60°-70°	102.4	2.7
70°-80°	16.6	0.4
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1426.2	37.0
0°-40°	2456.0	63.6
0°-60°	3735.6	96.8
0°-90°	3858.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3858.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1236	1236	1236	1236	1236	
5°	1971	1698	1216	889	788	215
15°	3817	2654	1074	491	389	1102
25°	5176	3127	951	560	572	2384
35°	5292	2763	690	398	371	3280
45°	4076	1864	343	209	194	3092
55°	1618	764	145	79	60	1516
65°	302	167	37	12	8	340
75°	35	18	7	6	5	48
85°	4	3	5	4	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1568.4	1532.2	1540.3	1546.4	1519.1	1536.3	1507.1	1497.0	1472.7	1478.8	1460.7
5°	1970.7	1920.4	1905.2	1905.2	1859.8	1875.0	1848.7	1802.3	1755.0	1740.9	1697.6
7.5°	2403.2	2347.8	2323.5	2313.4	2246.9	2237.9	2215.7	2144.2	2066.5	2025.1	1948.5
10°	2846.7	2796.4	2762.0	2738.8	2647.1	2631.0	2591.6	2490.8	2393.1	2304.3	2178.4
12.5°	3335.7	3268.1	3222.8	3184.4	3066.5	3041.3	2982.7	2847.7	2693.5	2586.6	2420.3
15°	3817.4	3748.9	3689.5	3634.1	3490.9	3454.6	3375.9	3204.6	3024.1	2864.9	2654.2
17.5°	4276.2	4189.4	4116.8	4042.3	3873.9	3828.6	3725.8	3535.2	3283.2	3102.8	2848.8
20°	4646.1	4561.4	4477.7	4383.0	4190.5	4136.1	4011.0	3785.2	3498.9	3282.1	2985.8
22.5°	4948.4	4852.7	4770.0	4646.1	4429.4	4365.8	4221.7	3965.6	3656.1	3403.1	3077.6
25°	5176.3	5074.5	4989.8	4850.8	4610.8	4537.1	4368.9	4091.6	3754.0	3475.8	3127.0
27.5°	5355.8	5238.8	5143.0	4988.8	4724.6	4642.0	4457.5	4158.1	3793.2	3489.8	3124.9
30°	5418.3	5304.3	5196.5	5030.2	4745.8	4654.1	4462.5	4138.0	3757.9	3431.4	3055.4
32.5°	5391.0	5273.0	5156.1	4979.7	4679.3	4580.6	4387.0	4040.3	3650.2	3306.4	2927.3
35°	5292.1	5172.2	5047.3	4864.8	4550.3	4443.5	4249.9	3891.1	3485.8	3142.0	2763.1
37.5°	5112.8	4992.7	4874.9	4678.3	4356.8	4245.9	4055.4	3683.4	3288.3	2941.4	2572.5
40°	4843.7	4724.6	4615.8	4417.2	4093.6	3981.7	3801.4	3432.3	3051.4	2708.6	2353.7
42.5°	4496.9	4383.0	4285.2	4090.7	3774.1	3667.2	3497.9	3141.1	2785.2	2453.6	2119.9
45°	4075.6	3971.7	3882.0	3698.6	3406.2	3303.4	3153.2	2815.4	2483.8	2173.3	1863.9
47.5°	3589.6	3494.8	3416.3	3246.9	2975.8	2881.9	2753.0	2439.4	2143.1	1859.8	1584.6
50°	2977.7	2895.2	2840.7	2694.4	2452.5	2373.9	2274.2	2010.0	1767.1	1523.1	1295.3
52.5°	2272.2	2207.6	2182.3	2072.5	1885.0	1830.6	1766.0	1563.4	1386.0	1193.5	1016.1
55°	1617.9	1575.6	1559.4	1487.8	1364.9	1329.6	1274.1	1149.2	1031.2	895.1	764.1
57.5°	1101.9	1079.6	1067.5	1023.2	947.5	923.4	892.1	811.5	735.9	647.1	553.5
60°	731.8	722.7	712.6	685.5	641.1	623.0	607.9	554.4	508.0	452.6	387.1
62.5°	474.8	470.7	463.6	446.6	429.4	417.4	401.2	366.0	338.7	310.5	261.0
65°	301.5	297.3	294.3	283.3	272.2	260.1	254.1	233.9	216.7	198.6	167.3
67.5°	186.5	183.5	182.4	175.3	167.3	160.3	156.2	143.2	133.1	122.0	101.8
70°	111.9	110.9	108.9	104.8	99.7	94.7	92.8	83.6	77.7	70.5	57.5
72.5°	64.5	63.4	62.5	59.5	56.5	54.4	52.4	49.4	42.3	38.3	32.3
75°	35.3	35.3	34.2	32.3	31.3	29.2	28.2	26.2	23.1	21.2	18.1
77.5°	20.2	19.1	19.1	18.1	17.2	17.2	16.1	15.1	13.1	13.1	11.1
80°	12.2	12.2	12.2	11.1	11.1	11.1	10.1	10.1	9.0	8.0	8.0
82.5°	8.0	7.1	7.1	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.0
85°	4.1	4.1	4.1	4.1	3.0	4.1	3.0	3.0	3.0	3.0	3.0
87.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1413.3	1403.2	1383.0	1354.8	1344.8	1338.7	1305.4	1275.1	1253.9	1226.8	1200.6
5°	1618.9	1581.6	1533.2	1474.8	1451.5	1431.4	1370.0	1313.5	1267.1	1215.7	1167.4
7.5°	1831.5	1762.1	1680.3	1587.7	1549.4	1514.0	1421.3	1337.6	1266.1	1192.6	1122.9
10°	2031.2	1925.4	1807.4	1683.4	1625.9	1574.6	1451.5	1343.8	1248.9	1154.2	1068.5
12.5°	2226.7	2082.6	1926.4	1767.1	1692.5	1625.9	1473.8	1341.7	1224.7	1113.8	1015.1
15°	2415.2	2228.8	2036.2	1840.7	1750.9	1669.3	1488.9	1334.7	1199.5	1073.6	963.7
17.5°	2567.4	2347.8	2114.9	1885.0	1784.2	1689.6	1486.9	1314.6	1165.3	1028.2	911.2
20°	2674.4	2421.3	2162.3	1905.2	1795.4	1690.4	1471.7	1287.3	1130.1	988.9	870.9
22.5°	2734.8	2455.5	2178.4	1905.2	1787.2	1677.4	1450.6	1262.0	1103.8	965.6	852.8
25°	2760.0	2461.6	2171.3	1889.1	1767.1	1654.1	1426.4	1237.9	1082.6	950.6	845.7
27.5°	2739.9	2426.3	2132.0	1844.8	1719.7	1606.8	1380.1	1195.6	1045.4	919.4	819.5
30°	2659.2	2337.7	2044.2	1759.1	1633.1	1523.1	1303.4	1125.0	980.8	859.9	765.1
32.5°	2528.1	2208.6	1920.4	1642.2	1517.2	1411.2	1201.6	1032.2	894.2	779.2	691.6
35°	2368.8	2055.4	1777.2	1506.0	1386.0	1285.2	1087.6	922.4	795.4	689.5	608.9
37.5°	2189.5	1886.0	1610.9	1361.9	1247.0	1151.2	966.7	811.5	694.5	596.8	525.2
40°	1987.9	1701.5	1442.5	1206.6	1097.7	1009.1	834.6	697.5	590.6	503.0	442.5
42.5°	1775.2	1508.0	1267.1	1046.3	943.6	862.9	704.6	582.6	488.8	417.4	368.9
45°	1547.4	1300.3	1079.6	882.0	796.3	715.7	581.6	470.7	397.2	342.7	306.5
47.5°	1304.5	1085.7	891.1	718.7	644.2	573.6	460.6	376.1	322.5	281.2	254.1
50°	1060.5	876.0	710.7	563.5	499.9	443.5	356.9	299.4	260.1	229.8	207.7
52.5°	828.6	679.4	544.4	424.3	377.1	336.8	277.2	236.9	207.7	184.5	168.4
55°	621.9	504.1	398.1	308.5	280.3	255.1	215.7	183.5	163.3	145.1	133.1
57.5°	450.6	359.8	283.3	226.8	208.7	191.5	163.3	141.1	125.9	111.9	102.9
60°	316.6	250.0	200.5	166.3	152.3	142.2	119.9	105.9	93.7	83.6	74.6
62.5°	212.7	169.4	140.1	117.9	108.9	101.8	87.8	75.6	66.6	58.4	50.4
65°	136.0	114.0	94.7	79.6	73.5	68.5	59.5	49.4	43.3	37.3	31.3
67.5°	83.6	71.6	59.5	49.4	45.3	42.3	36.3	30.3	26.2	22.3	19.1
70°	48.4	41.4	34.2	29.2	27.2	25.2	21.2	18.1	16.1	13.1	11.1
72.5°	27.2	24.1	20.2	17.2	16.1	15.1	13.1	11.1	10.1	9.0	8.0
75°	16.1	14.0	12.2	11.1	10.1	10.1	9.0	8.0	7.1	7.1	6.0
77.5°	10.1	9.0	8.0	8.0	7.1	7.1	7.1	6.0	6.0	6.0	6.0
80°	7.1	7.1	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0	5.0
82.5°	5.0	5.0	5.0	4.1	4.1	4.1	4.1	4.1	5.0	5.0	5.0
85°	3.0	3.0	4.1	4.1	4.1	4.1	4.1	4.1	5.0	5.0	5.0
87.5°	3.0	3.0	3.0	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1172.4	1160.2	1138.1	1117.9	1114.9	1086.7	1057.4	1051.3	1041.2	1025.2	1006.0
5°	1118.9	1086.7	1048.3	1020.1	1008.1	967.7	927.4	909.3	889.2	857.9	839.7
7.5°	1056.3	1009.1	955.6	923.4	906.3	855.8	809.4	783.2	756.1	722.7	700.6
10°	987.9	928.4	865.9	829.6	809.4	755.0	705.6	675.4	646.2	612.9	589.8
12.5°	923.4	855.8	787.3	749.0	726.9	670.4	619.9	587.7	558.5	531.2	504.1
15°	865.9	790.3	718.7	680.5	657.2	599.9	551.4	519.2	490.9	464.7	440.5
17.5°	810.5	731.8	661.2	624.0	600.7	547.4	501.0	471.7	444.5	420.4	399.2
20°	772.2	697.5	631.0	595.7	575.5	528.2	488.8	465.7	446.6	425.4	407.3
22.5°	762.1	695.6	638.0	608.9	593.7	556.4	528.2	514.2	508.0	494.9	484.8
25°	762.1	703.6	655.3	631.0	619.0	590.6	568.6	563.5	559.5	551.4	546.3
27.5°	742.9	688.5	645.2	624.0	613.9	588.7	569.6	563.5	558.5	552.4	546.3
30°	692.5	642.1	601.7	582.6	572.5	548.4	528.2	521.1	516.2	507.1	502.0
32.5°	625.0	576.6	543.4	521.1	512.1	488.8	469.7	461.7	457.7	449.6	440.5
35°	549.4	507.1	474.8	456.7	447.6	427.4	410.3	402.3	398.1	389.1	377.9
37.5°	472.8	434.4	408.2	391.1	384.1	367.8	352.8	346.8	342.7	335.7	326.7
40°	397.2	369.9	346.8	333.6	327.6	314.5	301.5	295.4	292.3	286.2	279.2
42.5°	334.7	312.4	294.3	283.3	278.2	268.1	257.0	251.0	247.9	241.9	236.9
45°	280.3	263.1	249.0	238.9	234.9	225.8	216.7	211.6	208.7	203.6	198.6
47.5°	234.9	219.8	207.7	200.5	196.6	189.6	181.4	176.4	174.4	170.4	165.3
50°	192.5	181.4	171.4	165.3	162.3	155.2	148.2	144.2	142.2	138.1	133.1
52.5°	155.2	147.2	138.1	132.1	129.1	124.1	116.9	112.9	109.8	105.9	99.7
55°	122.0	114.9	107.8	101.8	99.7	93.7	87.8	81.6	78.6	74.6	69.5
57.5°	94.7	86.7	79.6	74.6	72.6	66.6	60.4	54.4	51.4	46.4	43.3
60°	67.6	60.4	53.4	50.4	48.4	42.3	37.3	32.3	30.3	27.2	25.2
62.5°	44.3	39.3	33.2	30.3	29.2	25.2	21.2	20.2	18.1	17.2	16.1
65°	27.2	24.1	20.2	18.1	17.2	16.1	14.0	13.1	12.2	11.1	11.1
67.5°	16.1	15.1	13.1	12.2	11.1	10.1	10.1	9.0	9.0	8.0	8.0
70°	11.1	10.1	9.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1
72.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
75°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
77.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.0	5.0
80°	5.0	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0	5.0	5.0
82.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
85°	5.0	5.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1	4.1	3.0
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	3.0	3.0	3.0	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192338

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1004.0	995.0	985.8	1000.1	999.0	984.9	995.0	978.8
5°	829.6	816.5	806.4	815.5	810.5	796.3	802.5	788.2
7.5°	687.4	672.4	660.3	667.3	659.3	646.2	644.2	638.0
10°	574.6	558.5	547.4	552.4	544.4	532.3	529.3	525.2
12.5°	488.8	473.7	463.6	467.8	459.7	448.6	446.6	449.6
15°	422.4	411.3	403.2	406.2	395.2	389.1	387.1	389.1
17.5°	384.1	372.0	366.0	368.9	360.9	354.8	353.8	352.8
20°	400.2	391.1	389.1	394.2	388.0	383.0	386.2	382.1
22.5°	488.0	486.9	488.0	499.9	497.0	494.9	497.0	497.0
25°	549.4	553.5	554.4	567.5	568.6	566.5	571.6	571.6
27.5°	547.4	548.4	547.4	560.5	562.5	558.5	563.5	564.5
30°	499.0	499.0	496.0	507.1	507.1	505.0	507.1	508.0
32.5°	435.4	434.4	433.4	438.5	438.5	435.4	437.5	437.5
35°	376.1	372.0	372.0	375.0	374.0	371.0	372.0	371.0
37.5°	324.6	319.6	319.6	321.6	318.6	315.5	316.6	316.6
40°	277.2	273.2	273.2	276.1	274.2	271.1	273.2	273.2
42.5°	232.9	231.8	231.8	233.9	233.9	231.8	234.9	235.9
45°	196.6	193.5	193.5	195.5	195.5	193.5	194.6	193.5
47.5°	163.3	160.3	160.3	160.3	158.3	155.2	155.2	154.2
50°	130.0	125.0	124.1	124.1	122.0	119.0	119.0	117.9
52.5°	96.8	91.7	91.7	90.7	88.6	87.8	86.7	86.7
55°	66.6	62.5	63.4	61.5	61.5	59.5	60.4	59.5
57.5°	41.4	39.3	39.3	38.3	36.3	35.3	35.3	34.2
60°	24.1	22.3	22.3	22.3	21.2	20.2	20.2	20.2
62.5°	16.1	15.1	15.1	15.1	13.1	13.1	12.2	12.2
65°	10.1	9.0	9.0	9.0	8.0	8.0	8.0	8.0
67.5°	8.0	8.0	7.1	7.1	7.1	7.1	7.1	7.1
70°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	6.0
72.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
75°	6.0	6.0	5.0	6.0	5.0	5.0	5.0	5.0
77.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
80°	5.0	5.0	5.0	5.0	5.0	4.1	4.1	4.1
82.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
85°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
87.5°	3.0	2.1	2.1	2.1	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)