

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192775

Luminaire Tested: **LDA6A75927D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6726.2 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69106	69106	69106
5°	189687	63675	25979
10°	415663	52109	9903
15°	634930	39660	11618
20°	735630	29508	18050
25°	802468	24268	29119
30°	896113	22016	29739
35°	911740	15098	20391
40°	927760	7163	10319
45°	929275	2977	4504
50°	785603	1288	1390
55°	252971	889	220
60°	50226	1020	0
65°	5124	1206	0
70°	545	1667	0
75°	0	2203	0
80°	0	3694	347
85°	0	7359	692



TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.1	2.5
10°-20°	885.0	13.2
20°-30°	1694.6	25.2
30°-40°	1996.5	29.7
40°-50°	1568.2	23.3
50°-60°	382.1	5.7
60°-70°	16.4	0.2
70°-80°	6.1	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2750.7	40.9
0°-40°	4747.2	70.6
0°-60°	6697.5	99.6
0°-90°	6726.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6726.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1261	1261	1261	1261	1261	
5°	3447	2494	1157	606	472	456
15°	11187	5746	699	200	205	3123
25°	13267	6987	401	420	481	6184
35°	13624	4417	226	291	305	8543
45°	11986	1365	38	54	58	9006
55°	2647	50	9	6	2	3150
65°	40	6	9	6	0	105
75°	0	6	10	7	0	0
85°	0	7	12	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6
2.5°	2160.7	2156.1	2124.7	2153.7	2065.3	2061.9	2022.4	2004.8	1953.7	1904.9	1835.1
5°	3447.0	3371.3	3309.8	3312.1	3142.2	3110.8	3022.4	2932.9	2795.7	2667.8	2494.5
7.5°	5254.2	5164.5	5034.3	4979.7	4655.2	4559.8	4377.2	4138.8	3840.0	3542.2	3221.3
10°	7467.1	7481.1	7312.5	7156.6	6665.8	6472.8	6177.4	5707.6	5141.3	4581.9	4013.3
12.5°	9694.2	9684.8	9483.8	9247.5	8642.9	8370.8	7977.7	7391.6	6641.4	5774.0	4884.3
15°	11187.4	11253.6	11168.8	10980.4	10464.0	10152.3	9709.2	8913.9	7999.8	6946.2	5746.0
17.5°	12124.7	12187.5	12157.3	12009.5	11553.7	11221.2	10851.3	10200.0	9143.0	7818.3	6425.1
20°	12609.7	12708.5	12694.5	12534.0	12189.8	11914.3	11506.0	10902.4	9987.3	8424.2	6864.8
22.5°	12932.9	13008.6	13029.4	12848.1	12492.2	12230.5	11931.7	11320.0	10459.4	8794.1	7039.3
25°	13266.7	13400.4	13269.1	13045.7	12718.9	12467.8	12149.1	11563.0	10685.0	8945.3	6986.9
27.5°	13676.1	13740.1	13442.3	13238.8	12875.9	12603.8	12265.5	11703.7	10724.5	8824.4	6688.1
30°	14156.4	13891.1	13683.0	13279.5	12867.8	12602.7	12258.5	11615.3	10516.4	8423.1	6108.9
32.5°	14077.3	13834.3	13598.2	13171.3	12764.3	12501.5	12117.7	11321.1	10024.4	7752.1	5310.0
35°	13623.7	13676.1	13421.3	13067.8	12607.3	12336.3	11917.7	10902.4	9189.4	6826.4	4416.9
37.5°	13241.1	13356.2	13190.0	12863.1	12395.7	12029.4	11464.2	10230.3	8099.7	5651.8	3570.2
40°	12964.3	13001.6	12911.9	12545.7	11984.0	11454.9	10801.3	9023.1	6776.3	4436.6	2817.8
42.5°	12535.2	12634.1	12475.9	12075.9	11224.6	10625.7	9679.1	7628.9	5263.5	3388.7	2121.2
45°	11986.4	12080.5	11885.2	11219.9	10036.1	9158.0	8003.2	5948.3	3893.5	2497.9	1365.2
47.5°	11090.9	11149.1	10771.1	9851.1	8130.0	7303.1	6119.3	4147.1	2508.5	1396.6	664.0
50°	9211.5	9183.7	8404.5	7273.0	5437.8	4570.2	3642.3	2247.9	1126.8	661.7	415.2
52.5°	5936.7	5872.8	5101.7	4072.6	2753.9	2101.4	1579.2	969.9	587.3	369.9	163.9
55°	2646.8	2622.4	2146.7	1667.6	1126.8	969.9	740.8	475.7	312.8	129.1	50.0
57.5°	981.5	959.5	845.4	709.4	544.2	452.4	359.3	228.0	80.2	43.0	26.7
60°	458.1	457.0	402.3	331.5	230.3	174.4	101.2	53.5	33.7	23.3	15.1
62.5°	146.5	143.0	100.1	73.2	52.4	45.4	36.1	26.7	17.4	12.7	9.3
65°	39.5	39.5	36.1	30.3	24.4	21.0	17.4	12.7	8.1	7.0	5.7
67.5°	15.1	15.1	14.0	12.7	9.3	8.1	7.0	5.7	4.7	5.7	5.7
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.7	4.7	5.7
72.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
75°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
77.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
80°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
82.5°	0.0	0.0	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7	7.0
85°	0.0	0.0	1.1	2.3	2.3	3.4	3.4	4.7	4.7	5.7	7.0
87.5°	0.0	0.0	1.1	2.3	2.3	3.4	3.4	4.7	4.7	5.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6
2.5°	1783.9	1707.3	1601.4	1539.7	1524.7	1492.0	1435.0	1350.1	1280.4	1212.9	1173.4
5°	2348.0	2166.5	1963.0	1819.9	1761.8	1683.9	1545.5	1402.5	1271.0	1157.1	1067.6
7.5°	2945.7	2646.8	2317.7	2052.6	1957.1	1833.9	1608.3	1395.5	1215.2	1057.0	937.4
10°	3539.9	3058.5	2612.0	2228.2	2072.3	1904.9	1607.2	1331.5	1119.8	936.1	803.6
12.5°	4134.2	3442.3	2828.2	2334.0	2131.7	1920.0	1559.5	1233.9	998.9	811.7	685.0
15°	4683.1	3748.2	2974.7	2370.0	2125.9	1875.9	1463.0	1115.3	872.1	698.8	581.5
17.5°	5092.5	3908.5	3008.4	2315.3	2033.9	1757.1	1315.3	975.8	751.2	598.9	479.1
20°	5293.6	3934.2	2928.3	2159.6	1875.9	1588.5	1153.6	842.0	647.7	505.8	404.7
22.5°	5293.6	3813.3	2753.9	1964.1	1678.0	1394.4	997.8	731.5	566.3	440.7	355.9
25°	5092.5	3572.6	2520.0	1738.6	1460.6	1202.5	863.0	649.0	503.5	401.2	330.2
27.5°	4701.7	3240.0	2220.1	1487.4	1246.6	1031.6	755.9	573.3	455.8	361.6	362.9
30°	4164.5	2831.7	1875.9	1222.2	1026.9	847.7	636.1	480.3	365.2	347.8	358.2
32.5°	3543.5	2343.3	1486.3	947.8	795.5	667.5	483.8	339.6	290.8	293.1	304.7
35°	2906.2	1844.5	1118.7	702.4	591.9	483.8	317.5	223.3	221.0	225.6	233.7
37.5°	2294.5	1380.4	809.3	514.1	397.7	297.8	170.9	153.5	153.5	158.2	162.9
40°	1718.8	979.2	557.1	304.7	193.0	136.1	108.2	100.1	98.8	100.1	105.8
42.5°	1180.4	619.9	331.5	122.1	93.1	79.1	68.7	62.8	61.7	62.8	66.4
45°	662.8	381.5	129.1	65.1	55.8	50.0	43.0	39.5	38.4	38.4	40.7
47.5°	415.2	151.2	58.1	40.7	34.8	32.6	28.0	25.6	24.4	24.4	25.6
50°	159.3	59.4	36.1	26.7	23.3	21.0	18.6	16.3	15.1	15.1	16.3
52.5°	54.7	34.8	23.3	17.4	15.1	14.0	11.7	10.4	10.4	10.4	10.4
55°	30.3	21.0	14.0	10.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3
57.5°	18.6	12.7	9.3	8.1	8.1	8.1	8.1	8.1	8.1	9.3	9.3
60°	10.4	8.1	7.0	7.0	7.0	7.0	8.1	8.1	8.1	9.3	9.3
62.5°	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	9.3	9.3	9.3
65°	5.7	5.7	5.7	7.0	7.0	7.0	8.1	8.1	9.3	9.3	9.3
67.5°	5.7	5.7	7.0	7.0	7.0	8.1	8.1	9.3	9.3	9.3	9.3
70°	5.7	7.0	7.0	8.1	8.1	8.1	9.3	9.3	9.3	10.4	10.4
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4
75°	7.0	7.0	7.0	8.1	8.1	8.1	9.3	10.4	10.4	10.4	10.4
77.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4	10.4
80°	7.0	7.0	8.1	8.1	9.3	9.3	10.4	10.4	10.4	11.7	11.7
82.5°	7.0	7.0	8.1	9.3	9.3	9.3	10.4	10.4	11.7	11.7	11.7
85°	7.0	8.1	8.1	9.3	9.3	9.3	10.4	10.4	11.7	11.7	11.7
87.5°	7.0	8.1	8.1	9.3	9.3	9.3	10.4	10.4	11.7	11.7	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6
2.5°	1121.1	1072.3	1023.3	987.3	969.9	952.5	914.1	864.0	843.1	812.9	795.5
5°	976.9	894.3	829.2	786.2	760.5	726.8	682.7	633.7	605.9	574.5	553.5
7.5°	828.0	731.5	668.7	629.1	603.6	561.6	505.8	447.7	414.0	379.2	354.6
10°	697.8	605.9	534.9	489.5	457.0	408.2	352.3	311.7	282.5	252.4	228.0
12.5°	582.6	483.8	408.2	369.9	347.8	301.2	254.7	209.3	191.9	186.0	186.0
15°	472.1	382.6	318.6	286.1	262.8	212.7	203.6	201.2	200.0	198.9	201.2
17.5°	384.9	309.4	242.0	225.6	223.3	222.1	223.3	223.3	224.4	228.0	233.7
20°	323.2	253.5	248.8	250.0	250.0	254.7	260.5	265.1	269.8	275.7	286.1
22.5°	287.2	286.1	294.2	295.4	301.2	308.2	318.6	325.6	337.2	343.1	358.2
25°	331.5	339.6	354.6	359.3	368.6	380.3	396.6	405.9	419.7	426.7	444.3
27.5°	375.6	388.4	407.0	412.9	421.0	439.6	451.3	459.4	466.4	471.0	481.4
30°	372.2	383.7	402.3	403.6	415.2	428.0	435.0	442.0	446.6	445.4	451.3
32.5°	315.2	325.6	343.1	343.1	355.9	366.3	369.9	375.6	375.6	375.6	377.9
35°	242.0	248.8	260.5	264.0	274.4	281.4	283.8	290.8	290.8	288.4	288.4
37.5°	167.5	176.7	184.9	187.3	194.3	198.9	204.7	205.9	203.6	204.7	204.7
40°	109.2	115.2	120.9	122.1	127.9	131.5	137.2	137.2	138.5	137.2	139.6
42.5°	67.4	72.1	75.5	77.9	80.2	82.5	86.1	87.2	88.4	87.2	89.5
45°	41.8	44.1	46.5	47.7	48.8	50.0	53.5	53.5	53.5	53.5	54.7
47.5°	25.6	26.7	28.0	28.0	29.1	30.3	31.4	31.4	31.4	31.4	32.6
50°	15.1	16.3	16.3	16.3	17.4	17.4	18.6	18.6	18.6	17.4	18.6
52.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.3	10.4
55°	9.3	9.3	8.1	8.1	8.1	8.1	8.1	7.0	5.7	5.7	4.7
57.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
60°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
62.5°	9.3	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
65°	9.3	9.3	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
67.5°	9.3	9.3	9.3	8.1	9.3	8.1	7.0	7.0	5.7	4.7	4.7
70°	10.4	9.3	9.3	9.3	9.3	8.1	8.1	7.0	5.7	4.7	4.7
72.5°	10.4	10.4	9.3	9.3	9.3	8.1	8.1	7.0	5.7	5.7	4.7
75°	10.4	10.4	9.3	9.3	9.3	8.1	8.1	7.0	7.0	5.7	4.7
77.5°	10.4	10.4	10.4	9.3	9.3	9.3	8.1	8.1	7.0	5.7	4.7
80°	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	4.7
82.5°	11.7	10.4	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	5.7
85°	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1	7.0	7.0	5.7
87.5°	11.7	10.4	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192775

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6	1260.6
2.5°	777.9	768.6	768.6	752.5	750.1	737.2	747.8	740.8
5°	530.2	515.2	510.5	494.2	488.4	473.4	478.0	472.1
7.5°	333.8	318.6	313.9	302.4	295.4	283.8	284.9	281.4
10°	203.6	189.6	186.0	182.6	179.0	177.9	179.0	177.9
12.5°	184.9	183.7	181.4	182.6	180.3	181.4	182.6	181.4
15°	201.2	203.6	201.2	202.3	201.2	203.6	204.7	204.7
17.5°	236.1	240.7	238.4	242.0	240.7	246.5	246.5	246.5
20°	289.5	297.8	295.4	300.1	300.1	307.1	307.1	309.4
22.5°	364.0	374.5	373.3	383.7	381.5	389.6	389.6	391.9
25°	453.5	464.0	465.1	472.1	471.0	479.1	479.1	481.4
27.5°	490.8	496.5	495.4	498.8	500.1	504.7	508.2	505.8
30°	460.5	465.1	464.0	466.4	466.4	469.8	473.4	469.8
32.5°	387.3	390.7	390.7	395.3	391.9	393.0	398.9	395.3
35°	296.5	298.8	296.5	298.8	300.1	300.1	305.8	304.7
37.5°	211.7	212.7	212.7	216.3	212.7	212.7	218.7	219.7
40°	141.9	143.0	141.9	146.5	144.2	144.2	147.6	144.2
42.5°	90.8	91.8	90.8	94.2	91.8	94.2	95.4	96.5
45°	55.8	55.8	54.7	57.0	55.8	57.0	58.1	58.1
47.5°	32.6	32.6	31.4	33.7	32.6	32.6	32.6	33.7
50°	17.4	17.4	17.4	18.6	17.4	17.4	17.4	16.3
52.5°	9.3	9.3	8.1	9.3	8.1	8.1	8.1	8.1
55°	4.7	3.4	3.4	3.4	2.3	2.3	2.3	2.3
57.5°	3.4	2.3	2.3	1.1	1.1	1.1	0.0	0.0
60°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.3	2.3	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
70°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
72.5°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
75°	3.4	3.4	2.3	2.3	1.1	1.1	0.0	0.0
77.5°	4.7	3.4	2.3	2.3	1.1	1.1	0.0	0.0
80°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
82.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
85°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
87.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)