

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192780

Luminaire Tested: **LDA6A75927D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5072.6 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	97		98	96	94		95	93	92
2	104	98	92	88	102	96	91	87		92	88	85		89	86	83		86	84	81
3	96	88	81	76	94	86	80	76		84	78	74		81	77	73		79	75	72
4	89	79	72	67	87	78	71	66		76	70	65		74	69	64		72	67	64
5	83	72	64	59	81	71	64	58		69	63	58		67	61	57		65	60	57
6	77	65	58	52	75	64	57	52		63	56	51		61	55	51		60	55	51
7	72	60	52	46	70	59	51	46		57	51	46		56	50	46		55	49	45
8	67	55	47	42	65	54	47	41		53	46	41		51	45	41		50	45	41
9	62	50	43	38	61	50	42	37		48	42	37		47	41	37		46	41	37
10	58	46	39	34	57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	89768	89768	89768
5°	144260	87998	56125
10°	213323	84289	37680
15°	290688	79739	27985
20°	359528	75245	26526
25°	416528	74079	43551
30°	454456	70973	43576
35°	467076	61328	34091
40°	454852	48276	26543
45°	412423	35709	20917
50°	324936	26387	14183
55°	193752	18790	8105
60°	99082	12488	3070
65°	47372	6628	1349
70°	22376	2981	1298
75°	9108	1970	1483
80°	4420	2210	1484
85°	2139	3585	2139

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	3.3
10°-20°	593.9	11.7
20°-30°	1117.9	22.0
30°-40°	1361.3	26.8
40°-50°	1133.1	22.3
50°-60°	542.7	10.7
60°-70°	130.3	2.6
70°-80°	20.5	0.4
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.8	37.1
0°-40°	3241.1	63.9
0°-60°	4916.9	96.9
0°-90°	5072.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5072.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1638	1638	1638	1638	1638	
5°	2622	2224	1599	1163	1020	287
15°	5122	3480	1405	637	493	1468
25°	6886	4067	1225	694	720	3163
35°	6979	3572	916	534	509	4324
45°	5320	2388	461	284	270	4028
55°	2027	985	197	110	85	1910
65°	365	213	51	16	10	418
75°	43	22	9	8	7	59
85°	3	3	6	5	3	5
90°	0	0	0	0	0	

TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5
2.5°	2117.8	2043.4	2066.7	2062.0	2057.4	2033.0	2015.6	2000.3	1962.0	1962.0	1913.2
5°	2621.5	2534.3	2556.4	2540.1	2519.1	2481.9	2448.2	2409.8	2338.8	2308.7	2223.7
7.5°	3197.1	3098.3	3118.0	3085.5	3041.4	2991.3	2936.6	2864.5	2751.7	2683.0	2551.7
10°	3832.2	3691.4	3703.1	3654.3	3580.9	3513.5	3461.1	3323.9	3163.4	3049.5	2865.6
12.5°	4433.5	4310.2	4313.7	4245.0	4139.1	4056.6	3977.5	3796.2	3582.2	3419.3	3177.4
15°	5121.9	4970.7	4934.7	4841.7	4703.3	4602.1	4493.9	4264.9	3996.2	3780.9	3479.8
17.5°	5676.7	5520.8	5497.7	5410.3	5212.7	5090.5	4954.5	4696.3	4355.5	4088.0	3718.2
20°	6162.8	6008.2	5968.7	5855.9	5629.0	5489.4	5325.5	5020.7	4648.6	4319.4	3902.0
22.5°	6560.6	6390.8	6335.0	6195.4	5943.1	5786.1	5585.9	5253.4	4838.2	4470.6	4011.3
25°	6886.2	6693.2	6622.3	6464.1	6180.4	6007.1	5787.2	5415.0	4962.6	4556.7	4067.0
27.5°	7094.4	6901.4	6823.4	6642.1	6323.3	6137.3	5897.7	5495.3	5006.8	4568.4	4055.5
30°	7179.3	6979.3	6890.9	6685.1	6342.0	6145.4	5895.4	5460.4	4949.9	4484.6	3957.8
32.5°	7127.1	6930.5	6831.7	6608.3	6251.2	6039.6	5789.5	5325.5	4799.8	4318.3	3787.9
35°	6979.3	6785.0	6682.8	6444.4	6072.2	5851.2	5602.3	5121.9	4590.4	4098.4	3571.6
37.5°	6724.6	6540.9	6423.4	6187.4	5812.8	5587.2	5340.6	4855.6	4312.4	3849.6	3321.6
40°	6356.0	6181.5	6065.2	5812.8	5459.3	5231.3	4998.7	4506.7	3994.9	3543.8	3034.4
42.5°	5886.0	5725.5	5613.9	5368.5	5031.3	4806.8	4594.0	4121.7	3634.4	3205.3	2723.7
45°	5319.7	5180.2	5070.8	4867.2	4534.6	4321.7	4130.0	3701.8	3228.5	2834.2	2387.8
47.5°	4653.2	4538.1	4432.2	4247.3	3947.4	3746.1	3587.9	3196.0	2794.8	2423.8	2043.4
50°	3810.0	3727.5	3645.0	3453.0	3241.4	3065.8	2950.6	2601.8	2277.3	1986.5	1671.2
52.5°	2872.6	2822.7	2764.5	2627.2	2485.4	2383.1	2280.7	2015.6	1772.5	1556.2	1310.7
55°	2027.2	2001.6	1956.2	1900.4	1792.3	1722.5	1634.1	1499.2	1310.7	1165.4	985.1
57.5°	1370.0	1363.0	1331.6	1297.9	1238.6	1215.4	1141.0	1053.6	947.8	839.6	711.7
60°	903.7	888.6	881.6	863.0	817.6	798.9	772.2	716.4	651.3	575.8	496.7
62.5°	581.5	573.4	567.5	559.4	531.5	531.5	504.7	479.1	430.3	383.8	332.6
65°	365.2	358.2	357.1	351.2	340.8	336.1	316.4	297.8	274.4	249.0	212.9
67.5°	235.0	224.4	218.7	215.2	208.2	200.0	193.0	184.9	166.3	151.2	127.9
70°	139.6	130.2	129.1	130.2	122.1	120.9	113.9	108.2	95.4	86.1	72.1
72.5°	79.1	74.4	73.2	73.2	68.7	67.4	62.8	59.4	52.4	45.4	39.5
75°	43.0	39.5	39.5	39.5	37.1	36.1	33.7	32.6	28.0	25.6	22.1
77.5°	24.4	23.3	23.3	22.1	21.0	19.7	18.6	18.6	16.3	15.1	14.0
80°	14.0	14.0	14.0	14.0	12.7	12.7	11.7	11.7	10.4	10.4	9.3
82.5°	8.1	8.1	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0	5.7
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5
2.5°	1891.1	1856.1	1853.8	1802.7	1770.2	1743.3	1723.6	1699.2	1644.5	1614.3	1592.3
5°	2164.4	2092.3	2055.0	1962.0	1910.8	1865.5	1809.7	1751.5	1662.0	1599.1	1548.0
7.5°	2448.2	2328.4	2249.3	2110.8	2041.1	1970.2	1876.0	1781.7	1659.7	1565.4	1487.5
10°	2712.2	2542.4	2416.8	2230.6	2139.9	2047.0	1914.4	1787.6	1635.1	1514.2	1412.0
12.5°	2971.5	2748.3	2574.9	2338.8	2228.3	2113.2	1943.5	1784.0	1605.0	1459.5	1339.9
15°	3219.3	2939.0	2718.0	2433.0	2304.0	2165.5	1962.0	1773.6	1570.0	1405.0	1268.9
17.5°	3417.0	3084.3	2819.2	2491.3	2345.8	2188.8	1955.1	1743.3	1522.3	1346.7	1197.8
20°	3553.0	3177.4	2874.9	2514.4	2355.1	2186.5	1928.2	1701.5	1472.4	1289.8	1138.6
22.5°	3626.3	3219.3	2890.2	2507.4	2341.1	2164.4	1895.8	1663.1	1432.8	1250.2	1106.0
25°	3653.0	3222.7	2873.9	2477.3	2309.7	2129.5	1857.4	1627.1	1401.4	1224.7	1089.7
27.5°	3621.7	3173.9	2814.5	2414.5	2244.6	2066.7	1795.7	1575.9	1355.0	1187.4	1060.6
30°	3514.6	3059.9	2698.3	2302.8	2136.5	1965.5	1698.1	1481.8	1279.3	1121.2	1000.2
32.5°	3344.9	2892.5	2534.3	2149.2	1988.8	1824.7	1568.9	1363.0	1174.7	1025.8	917.7
35°	3134.3	2692.4	2343.5	1970.2	1819.0	1664.4	1421.2	1227.1	1050.2	916.4	810.6
37.5°	2895.9	2470.3	2133.1	1789.9	1636.4	1490.9	1254.9	1088.6	918.7	796.7	700.1
40°	2628.5	2215.6	1908.5	1574.7	1439.8	1307.2	1088.6	937.4	782.8	674.6	590.8
42.5°	2342.4	1957.3	1673.5	1373.6	1238.6	1117.7	921.1	785.1	647.9	558.2	492.0
45°	2038.7	1699.2	1427.1	1158.4	1036.2	931.6	752.5	629.2	529.1	460.6	410.6
47.5°	1721.2	1421.2	1179.4	945.5	837.3	746.7	602.5	508.2	429.2	379.2	340.8
50°	1401.4	1134.0	942.1	743.1	650.2	578.1	471.0	405.9	347.8	309.4	280.3
52.5°	1095.6	876.9	721.1	560.5	489.7	439.6	367.5	322.1	278.0	249.0	226.7
55°	809.5	660.6	526.8	407.0	365.2	333.8	282.7	250.0	218.7	196.6	180.3
57.5°	584.9	473.4	375.6	298.8	271.0	250.0	212.9	190.7	168.6	152.3	139.6
60°	410.6	326.8	265.1	218.7	198.9	184.9	158.2	144.2	127.9	113.9	101.2
62.5°	269.8	219.7	184.9	154.6	143.1	132.6	113.9	103.5	89.5	80.2	68.7
65°	175.6	144.2	123.2	103.5	94.2	89.5	76.8	68.7	59.4	51.1	44.1
67.5°	107.1	89.5	77.9	65.1	60.5	55.8	47.7	41.8	36.1	30.3	26.7
70°	59.4	52.4	45.4	38.4	35.0	32.6	28.0	25.6	21.0	18.6	15.1
72.5°	35.0	30.3	26.7	22.1	21.0	19.7	16.3	15.1	12.7	11.7	10.4
75°	21.0	17.4	16.3	14.0	12.7	12.7	11.7	10.4	9.3	9.3	8.1
77.5°	12.7	11.7	10.4	9.3	9.3	9.3	8.1	8.1	8.1	7.0	7.0
80°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	5.7	5.7	5.7	4.7	5.7	4.7	5.7	5.7	5.7	5.7	5.7
85°	3.4	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7
87.5°	3.4	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5
2.5°	1566.6	1523.6	1492.2	1468.9	1477.1	1436.4	1423.5	1379.4	1363.0	1363.0	1339.9
5°	1495.6	1427.1	1373.6	1339.9	1337.6	1279.3	1249.1	1193.3	1163.0	1141.0	1118.9
7.5°	1410.7	1322.3	1251.5	1210.7	1199.1	1130.4	1089.7	1033.9	988.5	959.5	932.7
10°	1320.0	1214.2	1134.0	1087.4	1069.9	995.5	942.1	890.9	842.0	811.8	783.9
12.5°	1232.8	1117.7	1029.2	981.5	959.5	882.7	828.1	774.5	728.1	696.7	668.7
15°	1152.6	1030.5	937.4	889.7	865.3	789.8	735.1	682.7	637.3	608.2	582.6
17.5°	1076.9	952.5	859.5	812.9	786.2	716.4	664.0	612.9	572.2	545.5	522.2
20°	1019.9	896.7	810.6	769.9	743.1	678.0	632.6	588.5	554.8	535.1	512.8
22.5°	995.5	881.6	808.2	771.1	752.5	700.1	668.7	637.3	615.2	611.8	597.8
25°	992.1	892.0	831.6	800.2	788.5	749.0	730.4	710.7	694.3	699.0	701.3
27.5°	977.0	883.9	833.9	807.2	797.8	765.2	751.4	732.7	721.1	726.8	729.1
30°	924.6	838.6	792.1	769.9	760.7	728.1	716.4	695.4	686.3	687.3	686.3
32.5°	843.2	761.8	718.7	699.0	688.4	659.4	646.6	628.0	614.2	612.9	610.6
35°	744.4	671.0	631.6	614.2	603.6	579.2	567.5	550.1	533.8	532.7	530.4
37.5°	643.2	578.1	544.2	529.1	519.8	500.1	486.1	474.4	464.0	459.4	458.3
40°	545.5	487.3	462.9	451.3	444.3	423.3	416.3	404.7	396.6	391.9	390.8
42.5°	453.6	412.9	393.2	382.6	376.9	361.8	353.5	344.2	336.1	331.5	330.2
45°	384.9	351.2	332.6	324.5	319.8	305.8	300.1	290.8	283.8	280.3	279.1
47.5°	321.1	294.2	281.4	272.1	271.0	259.4	251.3	244.3	237.3	233.7	232.6
50°	262.8	240.7	230.3	224.4	223.3	211.7	205.9	200.0	194.3	190.7	188.3
52.5°	216.3	195.3	188.3	180.3	179.2	168.6	163.9	158.2	152.3	147.6	144.2
55°	170.9	154.6	147.6	140.8	139.6	127.9	123.2	116.2	110.5	105.8	101.2
57.5°	130.2	117.5	110.5	103.5	102.4	94.2	86.1	80.2	74.4	68.7	65.1
60°	95.4	82.5	74.4	71.0	67.4	59.4	53.5	48.8	44.1	40.7	37.1
62.5°	62.8	53.5	47.7	43.0	40.7	35.0	31.4	28.0	25.6	24.4	23.3
65°	38.4	32.6	28.0	25.6	25.6	22.1	19.7	17.4	16.3	16.3	15.1
67.5°	23.3	19.7	17.4	16.3	15.1	14.0	12.7	12.7	11.7	11.7	10.4
70°	14.0	12.7	11.7	10.4	10.4	10.4	10.4	10.4	9.3	9.3	9.3
72.5°	10.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.1	8.1	8.1
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.0
77.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7
82.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
85°	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7
87.5°	5.7	4.7	4.7	4.7	4.7	4.7	3.4	3.4	3.4	3.4	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192780

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5	1637.5
2.5°	1328.2	1337.6	1323.6	1314.2	1304.9	1311.9	1279.3	1265.4
5°	1097.9	1087.4	1080.5	1072.3	1058.3	1060.6	1032.8	1019.9
7.5°	908.3	901.3	883.9	874.6	860.6	860.6	835.0	824.6
10°	758.4	747.8	731.5	723.4	710.7	700.1	687.3	676.9
12.5°	644.3	632.6	618.7	611.8	598.9	590.8	578.1	580.3
15°	559.4	547.8	535.1	528.1	517.5	509.4	499.0	493.1
17.5°	500.1	489.7	479.1	472.1	464.0	457.0	447.7	446.6
20°	495.4	487.3	481.4	476.8	469.9	465.3	460.6	454.7
22.5°	593.2	594.3	595.5	595.5	596.6	596.6	597.8	586.2
25°	700.1	713.0	713.0	716.4	726.8	726.8	724.6	720.0
27.5°	728.1	740.8	737.4	739.7	750.1	752.5	744.4	745.5
30°	681.6	693.1	686.3	687.3	694.3	694.3	683.9	688.4
32.5°	603.6	610.6	601.3	601.3	607.2	605.9	598.9	598.9
35°	521.1	524.5	516.4	519.8	519.8	516.4	509.4	509.4
37.5°	450.0	451.3	443.1	444.3	444.3	440.7	433.9	433.9
40°	382.6	386.2	379.2	381.5	379.2	375.6	372.2	370.9
42.5°	323.4	325.7	319.8	323.4	322.1	322.1	321.1	322.1
45°	272.1	274.4	269.8	272.1	273.4	272.1	268.7	269.8
47.5°	225.6	228.0	228.0	225.6	224.4	218.7	215.2	215.2
50°	182.6	181.4	180.3	176.8	173.3	169.9	166.3	166.3
52.5°	137.2	134.9	133.8	130.2	129.1	125.6	125.6	122.1
55°	94.2	93.1	93.1	89.5	89.5	86.1	84.8	84.8
57.5°	59.4	57.0	58.1	55.8	54.7	51.1	51.1	50.0
60°	33.7	32.6	32.6	31.4	30.3	28.0	28.0	28.0
62.5°	22.1	21.0	21.0	19.7	19.7	18.6	18.6	17.4
65°	14.0	12.7	12.7	11.7	11.7	10.4	10.4	10.4
67.5°	10.4	9.3	9.3	9.3	9.3	9.3	8.1	8.1
70°	9.3	9.3	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0
75°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
77.5°	7.0	5.7	5.7	5.7	5.7	5.7	5.7	5.7
80°	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7
82.5°	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
85°	4.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	2.3	2.3	2.3	2.3	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)