

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192791

Luminaire Tested: **LDA6A75930D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5130.3 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	104	97	92	88	101	96	91	87	92	88	85		89	86	83		86
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78
4	89	79	72	66	87	78	71	66	76	70	65		73	68	64		71
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65
6	77	65	57	51	75	64	57	51	62	56	51		61	55	50		59
7	71	59	51	46	70	58	51	46	57	50	45		56	50	45		54
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	36		46
10	58	46	38	33	57	45	38	33	44	38	33		43	37	33		42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80931	80931	80931
5°	128577	79941	51926
10°	192910	76708	34852
15°	276437	72691	25789
20°	364907	67970	21498
25°	437977	66258	31393
30°	489398	66422	47438
35°	503161	59475	40488
40°	484866	47296	30106
45°	427316	35135	23157
50°	333243	26003	16034
55°	192729	19039	10351
60°	90081	13234	4638
65°	42145	7251	1933
70°	19555	3190	1394
75°	8155	2097	1589
80°	3536	2368	1957
85°	755	3900	3145

TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.7	3.0
10°-20°	560.4	10.9
20°-30°	1109.4	21.6
30°-40°	1434.4	28.0
40°-50°	1178.7	23.0
50°-60°	544.9	10.6
60°-70°	124.4	2.4
70°-80°	20.3	0.4
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1822.5	35.5
0°-40°	3256.9	63.5
0°-60°	4980.5	97.1
0°-90°	5130.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5130.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1476	1476	1476	1476	1476	
5°	2336	2009	1453	1050	944	258
15°	4871	3258	1281	574	454	1423
25°	7241	4053	1095	538	519	3334
35°	7518	3710	889	590	605	4655
45°	5512	2504	453	301	299	4195
55°	2016	975	199	128	108	1895
65°	325	199	56	21	15	372
75°	38	22	10	9	8	51
85°	1	4	6	6	5	4
90°	0	0	0	0	0	

TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3
2.5°	1874.6	1846.0	1863.4	1872.1	1827.4	1837.3	1842.3	1807.5	1797.5	1778.7	1724.0
5°	2336.5	2302.9	2316.6	2316.6	2250.5	2254.3	2251.8	2185.9	2149.7	2102.4	2009.0
7.5°	2880.4	2846.8	2849.3	2836.9	2743.5	2737.3	2697.5	2616.5	2545.7	2458.5	2319.1
10°	3465.5	3445.6	3433.2	3401.9	3278.7	3257.5	3199.1	3070.9	2953.9	2820.7	2624.0
12.5°	4152.7	4112.7	4076.7	4026.8	3866.3	3826.5	3744.3	3558.9	3387.0	3200.4	2940.2
15°	4870.8	4839.7	4781.3	4702.8	4497.4	4433.9	4326.9	4077.9	3863.8	3591.2	3257.5
17.5°	5613.9	5556.7	5470.8	5360.0	5112.3	5022.8	4889.4	4570.9	4287.1	3947.2	3544.0
20°	6255.0	6210.2	6091.9	5948.8	5665.0	5545.5	5388.6	4997.7	4650.6	4247.2	3772.9
22.5°	6811.5	6751.6	6606.0	6433.0	6115.6	5967.5	5790.8	5353.8	4930.6	4462.5	3941.0
25°	7240.8	7196.1	7023.1	6821.4	6472.8	6301.1	6105.6	5610.2	5140.9	4626.8	4053.1
27.5°	7590.6	7514.8	7321.8	7094.0	6718.1	6517.7	6311.1	5768.4	5260.4	4710.3	4095.3
30°	7731.3	7653.0	7448.8	7196.1	6797.8	6577.4	6364.5	5785.8	5251.7	4681.7	4044.4
32.5°	7705.2	7616.7	7399.0	7131.4	6724.3	6489.0	6273.8	5672.5	5127.2	4552.2	3906.2
35°	7518.5	7445.0	7219.7	6939.7	6533.9	6286.2	6060.9	5465.8	4919.4	4351.7	3709.5
37.5°	7237.1	7132.7	6922.3	6641.0	6211.4	5981.1	5758.3	5170.9	4636.7	4074.2	3464.2
40°	6775.4	6649.7	6439.3	6194.0	5785.8	5556.7	5353.8	4804.9	4279.6	3754.2	3171.8
42.5°	6194.0	6095.7	5900.3	5647.6	5273.0	5053.8	4872.0	4344.3	3878.7	3392.0	2849.3
45°	5511.8	5417.3	5250.4	5022.8	4684.1	4493.6	4326.9	3857.6	3438.1	2993.7	2504.5
47.5°	4773.8	4680.4	4534.8	4334.3	4031.9	3867.5	3721.9	3337.3	2941.5	2553.1	2123.6
50°	3907.4	3779.1	3699.5	3531.4	3278.7	3139.3	3027.2	2682.6	2389.9	2077.6	1720.3
52.5°	2916.6	2875.4	2760.9	2642.6	2464.7	2361.3	2287.8	2066.4	1823.6	1597.1	1324.5
55°	2016.5	1979.2	1909.4	1837.3	1717.8	1665.4	1610.7	1476.3	1314.6	1160.1	974.7
57.5°	1274.6	1302.1	1257.2	1216.2	1143.9	1125.3	1083.0	1004.5	904.9	807.9	692.2
60°	821.6	836.5	807.9	784.2	744.4	729.5	709.6	662.2	602.5	546.4	468.1
62.5°	520.3	527.7	511.6	497.9	475.5	469.3	455.6	428.1	392.1	358.5	308.6
65°	324.9	331.2	320.0	311.3	297.4	298.7	286.3	270.1	249.0	227.8	199.2
67.5°	200.5	204.2	196.7	191.8	182.9	182.9	175.4	165.5	151.8	139.4	120.7
70°	122.0	123.2	118.3	115.8	109.6	108.3	104.6	97.1	88.4	79.7	68.5
72.5°	71.0	72.3	68.5	66.0	62.3	62.3	59.7	55.9	52.2	44.8	38.5
75°	38.5	39.8	37.3	36.1	33.6	34.8	32.3	31.1	27.4	24.9	22.4
77.5°	19.9	21.1	19.9	18.6	18.6	18.6	17.4	16.2	16.2	13.7	13.7
80°	11.2	11.2	11.2	11.2	11.2	9.9	9.9	9.9	9.9	9.9	8.7
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.0
85°	1.2	1.2	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7
87.5°	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3
2.5°	1707.9	1706.6	1649.3	1624.4	1604.5	1573.5	1551.1	1527.3	1506.2	1467.6	1435.3
5°	1961.8	1927.0	1832.4	1772.5	1735.2	1685.5	1630.6	1575.9	1522.3	1452.7	1395.4
7.5°	2228.2	2153.4	2011.5	1911.9	1854.7	1785.0	1693.0	1607.0	1519.8	1424.0	1341.9
10°	2482.1	2360.1	2179.7	2027.7	1949.4	1859.7	1732.7	1613.2	1498.7	1378.0	1275.9
12.5°	2741.0	2566.8	2331.5	2134.8	2035.2	1924.5	1761.3	1613.2	1471.4	1332.0	1211.2
15°	2997.4	2767.1	2474.6	2230.6	2109.9	1978.0	1781.2	1604.5	1437.8	1280.8	1146.4
17.5°	3216.5	2931.5	2579.2	2296.7	2154.7	2005.3	1780.0	1578.4	1392.9	1223.6	1080.5
20°	3387.0	3049.8	2652.6	2330.3	2171.0	2007.8	1760.1	1539.7	1341.9	1165.1	1018.2
22.5°	3502.8	3126.9	2690.0	2336.5	2165.8	1994.1	1729.0	1501.2	1295.7	1119.1	972.2
25°	3575.0	3165.6	2701.2	2327.8	2148.4	1970.5	1700.4	1467.6	1265.9	1095.4	958.5
27.5°	3588.7	3154.2	2678.8	2291.6	2107.4	1928.2	1659.2	1435.3	1239.8	1081.8	958.5
30°	3521.4	3082.1	2602.8	2210.8	2030.2	1854.7	1590.9	1376.7	1193.8	1049.3	937.4
32.5°	3393.2	2948.9	2477.1	2091.3	1915.6	1751.4	1497.5	1293.3	1116.6	983.4	882.5
35°	3207.8	2770.8	2314.1	1940.7	1770.0	1617.0	1366.8	1180.1	1012.0	888.7	795.4
37.5°	2982.5	2556.8	2123.6	1768.8	1607.0	1463.9	1224.9	1049.3	893.7	777.9	694.6
40°	2708.7	2325.3	1909.4	1579.7	1425.2	1295.7	1075.5	906.2	759.3	660.9	585.1
42.5°	2422.4	2066.4	1681.8	1368.0	1231.1	1107.9	912.4	760.5	629.8	548.9	489.2
45°	2127.3	1778.7	1442.8	1163.8	1060.6	922.3	741.9	618.7	512.8	453.2	405.8
47.5°	1794.9	1499.9	1190.1	944.8	836.5	743.1	592.6	492.9	424.4	372.2	336.1
50°	1437.8	1202.5	942.4	733.2	643.5	572.7	461.9	393.3	341.1	304.9	277.5
52.5°	1105.4	919.8	709.6	537.7	481.7	428.1	359.8	312.5	275.1	247.7	227.8
55°	821.6	670.9	510.3	398.3	358.5	323.7	282.5	245.2	217.9	199.2	182.9
57.5°	578.9	468.1	358.5	288.7	267.6	245.2	214.1	189.3	170.5	155.6	143.1
60°	387.1	318.7	252.7	211.7	196.7	181.7	161.8	144.4	130.7	120.7	108.3
62.5°	260.1	214.1	176.7	151.8	141.9	131.9	118.3	105.8	95.9	85.9	76.0
65°	166.7	141.9	119.5	103.3	95.9	90.9	81.0	72.3	64.8	55.9	48.5
67.5°	102.1	88.4	74.7	64.8	60.9	57.2	51.0	44.8	39.8	33.6	28.6
70°	59.7	52.2	44.8	38.5	37.3	34.8	29.8	26.1	23.6	19.9	17.4
72.5°	34.8	31.1	26.1	23.6	22.4	19.9	18.6	16.2	13.7	12.4	11.2
75°	19.9	17.4	14.9	13.7	13.7	12.4	11.2	11.2	9.9	9.9	8.7
77.5°	12.4	11.2	9.9	9.9	9.9	8.7	8.7	8.7	8.7	7.5	7.5
80°	8.7	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
82.5°	5.0	5.0	5.0	5.0	5.0	6.2	6.2	6.2	6.2	6.2	7.5
85°	3.7	5.0	5.0	5.0	5.0	5.0	6.2	6.2	6.2	6.2	6.2
87.5°	3.7	5.0	5.0	5.0	5.0	5.0	6.2	6.2	6.2	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3
2.5°	1416.5	1396.6	1335.7	1356.8	1318.3	1287.0	1284.6	1265.9	1233.6	1216.2	1207.5
5°	1351.8	1307.1	1232.3	1237.3	1192.6	1143.9	1117.8	1092.9	1050.5	1024.4	1007.0
7.5°	1272.1	1211.2	1122.8	1116.6	1069.3	1010.7	973.4	938.6	892.5	858.9	837.8
10°	1188.8	1114.1	1010.7	1003.3	953.6	890.0	847.7	807.9	760.5	727.0	704.6
12.5°	1111.6	1025.7	922.3	903.7	855.2	790.4	744.4	702.1	656.0	627.4	601.3
15°	1038.1	944.8	835.3	817.9	770.5	705.8	654.7	617.4	573.9	546.4	522.8
17.5°	964.7	868.9	760.5	740.6	695.9	633.6	588.8	548.9	509.1	483.0	461.9
20°	901.2	805.3	699.6	679.6	638.5	578.9	537.7	500.4	464.3	439.5	421.9
22.5°	860.2	766.8	670.9	653.5	614.9	561.5	522.8	490.5	459.4	435.7	421.9
25°	857.7	776.7	690.9	680.8	648.5	603.7	576.4	556.3	537.7	519.0	514.1
27.5°	872.6	806.7	734.4	731.9	705.8	675.8	663.4	657.2	647.3	641.0	649.7
30°	863.9	807.9	746.9	746.9	727.0	705.8	699.6	697.1	690.9	692.2	702.1
32.5°	817.9	766.8	708.3	709.6	697.1	673.4	669.6	668.4	660.9	659.7	667.1
35°	734.4	687.2	638.5	639.8	629.8	607.5	602.5	600.0	590.1	585.1	590.1
37.5°	638.5	600.0	553.9	553.9	543.9	526.5	521.5	516.6	510.3	505.4	505.4
40°	540.2	509.1	471.8	470.6	463.1	445.7	440.7	437.0	430.6	421.9	424.4
42.5°	456.9	428.1	398.3	395.8	390.8	375.9	370.9	366.0	359.8	352.3	352.3
45°	379.6	361.0	334.9	333.6	328.7	316.2	312.5	306.1	301.2	293.7	293.7
47.5°	316.2	301.2	280.0	278.8	275.1	263.9	260.1	255.2	250.2	245.2	245.2
50°	265.1	250.2	232.8	231.5	229.1	220.4	215.4	211.7	207.9	204.2	201.7
52.5°	217.9	205.4	191.8	190.5	188.0	179.2	175.4	173.0	169.2	163.0	163.0
55°	175.4	165.5	153.1	151.8	149.3	141.9	138.2	133.2	128.2	122.0	120.7
57.5°	136.9	128.2	118.3	117.0	113.3	107.1	100.9	95.9	90.9	85.9	83.5
60°	103.3	93.4	84.7	82.2	79.7	71.0	66.0	60.9	55.9	52.2	49.7
62.5°	69.8	63.6	53.5	52.2	49.7	44.8	38.5	36.1	33.6	31.1	29.8
65°	43.5	38.5	33.6	32.3	29.8	26.1	23.6	22.4	21.1	19.9	18.6
67.5°	26.1	23.6	19.9	19.9	18.6	17.4	14.9	14.9	13.7	13.7	12.4
70°	16.2	14.9	13.7	12.4	12.4	12.4	11.2	11.2	11.2	11.2	11.2
72.5°	11.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
75°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
77.5°	8.7	8.7	7.5	8.7	8.7	8.7	8.7	7.5	8.7	7.5	7.5
80°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
82.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.2	6.2	6.2	6.2
85°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.0
87.5°	6.2	6.2	6.2	6.2	6.2	5.0	5.0	5.0	5.0	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192791

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3	1476.3
2.5°	1210.0	1175.0	1188.8	1168.8	1162.6	1157.6	1150.1	1173.8
5°	999.5	962.3	971.0	951.1	942.4	933.7	924.8	943.6
7.5°	825.3	789.1	792.9	775.5	766.8	756.8	748.1	763.0
10°	689.7	656.0	657.2	641.0	632.3	622.4	614.9	626.1
12.5°	586.3	555.1	555.1	542.7	535.2	524.0	517.8	526.5
15°	507.9	480.5	480.5	468.1	461.9	451.9	445.7	454.4
17.5°	448.2	423.2	423.2	414.5	408.2	399.5	394.6	402.0
20°	408.2	387.1	388.4	379.6	374.7	364.7	362.2	368.5
22.5°	412.0	392.1	394.6	388.4	383.4	375.9	373.4	382.1
25°	515.3	500.4	509.1	509.1	511.6	500.4	505.4	519.0
27.5°	662.2	654.7	668.4	663.4	673.4	673.4	678.3	695.9
30°	715.8	709.6	724.5	723.2	733.2	730.7	733.2	749.4
32.5°	677.1	670.9	683.5	682.2	689.7	683.5	684.7	698.4
35°	595.0	588.8	597.5	596.3	601.3	593.8	597.5	605.0
37.5°	507.9	501.6	506.6	505.4	506.6	497.9	502.9	506.6
40°	426.9	419.4	426.9	421.9	423.2	414.5	415.7	420.7
42.5°	357.3	348.6	354.8	354.8	354.8	348.6	349.8	354.8
45°	297.4	291.2	295.0	293.7	295.0	290.0	293.7	298.7
47.5°	246.5	241.5	244.0	242.7	242.7	237.8	239.0	239.0
50°	203.0	198.0	199.2	198.0	194.3	188.0	186.8	188.0
52.5°	160.5	154.3	154.3	151.8	149.3	144.4	144.4	145.6
55°	118.3	113.3	113.3	112.0	109.6	105.8	105.8	108.3
57.5°	79.7	76.0	77.2	76.0	76.0	71.0	73.5	73.5
60°	48.5	46.0	46.0	44.8	42.3	41.0	39.8	42.3
62.5°	28.6	27.4	27.4	26.1	26.1	24.9	24.9	24.9
65°	18.6	17.4	17.4	16.2	16.2	14.9	13.7	14.9
67.5°	12.4	11.2	11.2	11.2	11.2	9.9	9.9	9.9
70°	11.2	9.9	9.9	9.9	9.9	8.7	8.7	8.7
72.5°	9.9	8.7	9.9	8.7	8.7	8.7	8.7	8.7
75°	8.7	8.7	8.7	7.5	7.5	7.5	7.5	7.5
77.5°	7.5	7.5	7.5	7.5	7.5	6.2	6.2	6.2
80°	7.5	6.2	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	6.2	6.2	6.2	6.2	6.2	5.0	5.0	5.0
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
87.5°	3.7	3.7	3.7	3.7	3.7	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)