

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192349

Luminaire Tested: **LDA6A50927D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50927D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3295.2 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79
4	90	80	72	67	87	78	72	66	76	70	66		74	69	65		72
5	83	72	65	59	81	71	64	59	69	63	58		67	62	57		66
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60
7	72	60	52	47	70	59	52	46	58	51	46		56	50	46		55
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		51
9	63	50	43	38	61	50	43	38	49	42	37		48	42	37		47
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54404	54404	54404
5°	86484	53615	34652
10°	128716	51524	23402
15°	182895	49052	17611
20°	239421	46840	18003
25°	285083	47368	31103
30°	316156	45684	29296
35°	322536	38943	21556
40°	308285	30021	15951
45°	268865	21615	12032
50°	204974	15692	8000
55°	114424	11297	4655
60°	52616	7806	1875
65°	24815	4216	817
70°	12149	2036	866
75°	5740	1334	953
80°	2841	1421	1137
85°	1698	2264	1132

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	3.1
10°-20°	374.4	11.4
20°-30°	748.8	22.7
30°-40°	919.5	27.9
40°-50°	736.6	22.4
50°-60°	324.0	9.8
60°-70°	73.1	2.2
70°-80°	13.3	0.4
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1225.5	37.2
0°-40°	2145.0	65.1
0°-60°	3205.6	97.3
0°-90°	3295.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3295.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	992	992	992	992	992	
5°	1572	1352	974	722	630	173
15°	3223	2173	864	402	310	940
25°	4713	2685	783	487	514	2169
35°	4820	2420	582	351	322	2984
45°	3468	1598	279	170	155	2637
55°	1197	592	118	68	49	1138
65°	191	121	32	11	6	219
75°	27	15	6	5	4	34
85°	3	3	4	4	2	3
90°	0	0	0	0	0	

TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4
2.5°	1265.7	1233.3	1259.4	1236.9	1229.7	1227.0	1216.1	1208.9	1206.2	1181.0	1161.2
5°	1571.6	1533.7	1560.8	1527.4	1510.2	1501.2	1482.3	1458.8	1439.9	1392.0	1352.4
7.5°	1929.8	1889.2	1914.5	1866.6	1834.2	1817.9	1787.2	1742.2	1699.7	1623.0	1556.2
10°	2312.3	2278.9	2300.6	2233.8	2183.2	2157.2	2112.0	2054.2	1967.6	1855.8	1757.4
12.5°	2758.0	2710.1	2727.3	2637.9	2565.9	2528.8	2464.8	2374.6	2251.9	2099.4	1964.9
15°	3222.6	3177.5	3188.3	3074.7	2974.6	2923.0	2840.0	2712.0	2549.6	2350.1	2173.4
17.5°	3699.0	3637.6	3635.8	3500.5	3366.9	3302.0	3198.3	3029.5	2839.2	2577.5	2359.2
20°	4104.0	4050.9	4036.4	3895.7	3713.4	3637.6	3512.2	3302.8	3069.3	2766.1	2509.9
22.5°	4451.3	4390.1	4363.9	4198.7	3992.2	3903.8	3760.4	3506.8	3247.0	2904.1	2615.4
25°	4713.1	4662.5	4624.6	4438.8	4207.8	4108.6	3951.6	3677.3	3376.0	3000.6	2684.9
27.5°	4920.5	4852.9	4805.1	4602.0	4342.2	4237.6	4068.8	3771.2	3441.8	3039.5	2705.7
30°	4994.5	4926.8	4871.8	4655.3	4380.1	4265.5	4088.6	3772.9	3423.7	3010.6	2660.6
32.5°	4959.3	4888.9	4826.7	4600.3	4315.2	4195.1	4014.7	3694.4	3329.0	2914.1	2560.4
35°	4819.5	4763.5	4693.1	4464.9	4183.5	4052.6	3873.0	3544.6	3182.0	2763.4	2419.6
37.5°	4621.9	4535.2	4470.3	4246.6	3974.1	3840.6	3668.2	3352.5	2985.4	2583.0	2250.0
40°	4307.9	4220.5	4155.4	3939.8	3692.6	3558.2	3399.4	3098.1	2743.6	2369.2	2051.5
42.5°	3916.3	3835.2	3772.0	3571.7	3353.4	3222.6	3082.8	2804.0	2474.7	2131.8	1834.2
45°	3468.0	3389.5	3335.4	3161.3	2967.3	2851.8	2725.5	2479.2	2177.8	1866.6	1597.8
47.5°	2981.7	2901.4	2855.4	2699.3	2535.1	2430.5	2322.2	2109.3	1839.6	1572.5	1338.9
50°	2403.4	2325.8	2284.3	2153.5	2037.1	1940.6	1862.1	1691.6	1470.6	1260.3	1070.0
52.5°	1760.1	1699.7	1669.0	1578.8	1509.4	1437.2	1386.6	1267.6	1106.1	957.2	813.7
55°	1197.2	1147.5	1133.1	1077.2	1039.3	1000.5	964.4	895.0	785.8	687.4	591.8
57.5°	748.8	743.4	753.3	703.8	686.5	670.3	642.4	603.5	535.0	473.6	415.8
60°	479.9	474.5	470.1	452.0	443.9	432.2	418.7	396.0	353.6	317.6	279.7
62.5°	304.0	300.5	304.9	294.1	283.3	283.3	268.9	256.2	230.0	208.5	181.3
65°	191.3	190.4	193.1	185.8	180.4	177.7	170.5	163.3	147.1	133.6	120.9
67.5°	120.9	120.0	121.8	120.0	113.7	111.9	107.4	102.8	92.0	83.9	74.9
70°	75.8	74.9	75.8	73.9	70.4	68.5	65.8	62.2	58.7	49.6	45.1
72.5°	46.0	45.1	46.0	45.1	42.4	42.4	38.9	37.0	34.3	28.9	25.2
75°	27.1	27.1	27.1	26.2	24.4	24.4	22.5	21.6	19.8	17.1	15.4
77.5°	15.4	15.4	15.4	15.4	14.4	14.4	13.5	12.7	11.7	10.0	10.0
80°	9.0	9.0	9.0	9.0	8.1	9.0	8.1	8.1	7.2	6.3	6.3
82.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	1.8	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4
2.5°	1144.8	1116.0	1110.6	1079.9	1074.5	1057.4	1048.4	1032.1	999.7	982.5	961.7
5°	1304.6	1259.4	1233.3	1178.3	1161.2	1132.3	1102.5	1062.8	1011.4	974.3	935.6
7.5°	1479.6	1405.6	1350.6	1269.4	1239.6	1197.2	1144.8	1082.6	1010.5	955.4	900.4
10°	1655.5	1540.0	1455.2	1346.0	1302.7	1246.8	1171.0	1087.1	997.0	925.6	857.0
12.5°	1817.0	1672.7	1556.2	1417.4	1359.6	1291.0	1191.8	1087.1	979.8	895.0	814.7
15°	1993.0	1802.6	1651.0	1481.4	1410.1	1328.9	1207.2	1083.6	960.8	864.3	775.8
17.5°	2136.4	1909.9	1724.1	1526.5	1441.7	1348.7	1208.9	1069.1	936.5	830.9	738.9
20°	2241.9	1991.1	1773.7	1552.7	1457.1	1356.0	1201.7	1050.1	911.2	802.9	709.2
22.5°	2318.6	2039.8	1799.0	1561.6	1457.9	1352.4	1189.1	1033.9	894.0	788.5	699.2
25°	2364.6	2064.2	1807.1	1558.1	1450.7	1340.6	1174.7	1019.5	883.2	783.1	700.9
27.5°	2369.2	2054.2	1785.5	1531.0	1420.9	1310.9	1144.8	991.6	859.7	767.7	689.3
30°	2317.7	1998.4	1728.5	1471.5	1360.5	1252.2	1089.0	938.3	812.9	721.7	650.5
32.5°	2218.4	1900.0	1633.0	1381.2	1272.1	1166.6	1007.8	866.1	743.4	659.5	589.1
35°	2086.8	1775.5	1509.4	1273.0	1166.6	1066.3	912.1	773.1	661.3	581.9	517.8
37.5°	1930.7	1630.3	1381.2	1152.9	1050.1	957.2	808.3	682.0	574.7	501.6	443.0
40°	1752.9	1466.1	1232.4	1015.9	923.8	833.6	698.2	582.9	482.6	419.5	369.8
42.5°	1560.8	1291.9	1076.3	875.1	791.2	709.2	586.4	481.8	395.2	343.8	304.9
45°	1349.7	1107.9	913.9	738.0	657.6	590.0	474.5	387.9	322.1	278.8	251.8
47.5°	1124.1	913.9	745.2	593.7	523.2	465.5	370.8	305.9	258.9	229.1	206.6
50°	897.7	722.7	581.9	451.1	397.9	349.2	286.9	242.7	206.6	184.0	169.6
52.5°	685.7	544.0	433.1	331.1	295.1	261.6	221.0	191.3	164.2	148.0	137.1
55°	497.1	392.5	308.6	242.7	218.3	199.4	169.6	148.0	130.9	118.2	109.2
57.5°	346.5	271.6	215.6	176.9	162.4	148.8	128.1	113.7	102.0	93.0	85.7
60°	234.6	184.0	150.7	128.1	119.1	110.1	96.5	86.6	77.6	71.2	64.1
62.5°	154.2	126.3	107.4	93.8	85.7	79.3	71.2	63.1	56.0	50.5	44.2
65°	100.1	83.0	73.9	63.1	59.5	55.0	47.8	43.3	37.0	32.5	27.9
67.5°	63.1	54.1	47.8	41.5	38.9	35.2	31.6	27.1	23.5	19.8	17.1
70°	37.9	33.3	28.9	25.2	23.5	21.6	18.9	16.2	13.5	12.7	10.8
72.5°	22.5	19.8	17.1	15.4	14.4	13.5	11.7	10.0	9.0	8.1	7.2
75°	13.5	12.7	10.8	9.0	9.0	8.1	8.1	7.2	6.3	6.3	5.4
77.5°	9.0	8.1	7.2	6.3	6.3	6.3	5.4	5.4	5.4	5.4	5.4
80°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.5	4.5
85°	2.7	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	2.7	2.7	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4
2.5°	952.7	925.6	914.8	898.6	882.3	881.5	862.4	852.6	845.3	832.8	820.1
5°	909.4	867.8	842.6	821.0	800.2	785.8	757.9	738.9	721.7	703.8	680.3
7.5°	858.9	805.6	769.6	742.5	718.1	695.5	661.3	636.0	614.4	597.2	568.4
10°	804.7	743.4	698.2	668.6	643.3	610.8	577.4	549.4	525.9	507.0	479.1
12.5°	754.2	686.5	636.0	605.4	579.2	544.0	509.7	480.9	455.6	437.6	412.3
15°	707.3	636.0	581.9	551.2	524.2	489.0	454.7	425.8	402.4	383.5	360.9
17.5°	665.9	591.0	537.7	509.7	481.8	449.3	415.0	387.9	364.4	347.3	329.3
20°	637.8	566.6	515.1	489.0	464.7	433.9	406.9	385.2	362.7	349.2	338.3
22.5°	633.3	570.2	525.9	504.3	485.3	462.8	446.6	435.8	420.4	414.1	414.1
25°	642.4	588.3	553.1	535.9	520.5	508.0	499.8	492.6	487.2	488.0	488.0
27.5°	637.0	588.3	559.4	543.1	529.6	521.5	513.4	508.8	503.4	506.1	506.1
30°	601.8	554.8	530.5	513.4	500.7	493.5	481.8	476.3	470.1	470.9	468.2
32.5°	543.1	498.9	475.5	459.2	445.7	438.5	425.8	419.5	411.4	411.4	406.0
35°	474.5	433.1	411.4	397.0	384.3	377.1	365.4	359.0	350.9	346.5	343.8
37.5°	402.4	366.3	346.5	335.6	325.7	318.4	307.6	303.2	295.1	291.4	287.8
40°	335.6	309.4	290.5	281.5	273.4	267.0	257.2	253.5	246.2	243.5	240.0
42.5°	277.8	258.0	242.7	235.4	226.4	222.9	215.6	212.0	205.8	202.9	199.4
45°	231.8	215.6	202.9	196.7	191.3	186.7	179.6	176.9	170.5	167.8	166.0
47.5°	191.3	178.6	168.7	163.3	160.6	155.2	148.8	146.1	141.7	139.0	136.3
50°	156.9	147.1	139.0	134.4	132.6	127.2	121.8	120.0	115.5	113.7	110.9
52.5°	128.1	120.0	112.8	109.2	105.5	102.0	97.4	95.7	91.1	88.4	84.9
55°	102.8	94.7	88.4	85.7	83.9	78.5	73.9	71.2	67.6	63.1	60.4
57.5°	79.3	72.2	66.8	63.1	62.2	56.8	53.3	48.7	44.2	41.5	38.9
60°	58.7	52.3	46.9	43.3	42.4	37.0	32.5	29.8	26.2	24.4	23.5
62.5°	38.9	34.3	29.8	27.9	26.2	22.5	19.8	18.1	16.2	15.4	14.4
65°	24.4	20.8	18.1	17.1	15.4	13.5	12.7	11.7	10.8	10.0	9.0
67.5°	14.4	12.7	10.8	10.8	10.0	9.0	9.0	8.1	7.2	7.2	7.2
70°	9.0	8.1	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3
72.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.4	5.4
75°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
77.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
80°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	3.6	3.6	3.6
85°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.7
87.5°	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7	2.7	2.7	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192349

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4
2.5°	810.2	794.8	793.0	789.4	785.8	790.3	787.6	780.4
5°	672.1	653.2	649.5	644.1	638.7	640.5	636.0	629.7
7.5°	556.7	536.7	533.2	526.9	521.5	520.5	516.1	509.7
10°	462.8	447.5	443.9	437.6	431.2	430.3	424.9	420.4
12.5°	396.0	381.6	378.1	371.7	366.3	364.4	360.0	356.3
15°	346.5	332.9	329.3	323.8	317.6	317.6	314.0	310.3
17.5°	315.7	304.0	299.5	295.1	289.6	288.7	286.9	284.2
20°	328.4	317.6	315.7	310.3	311.3	311.3	309.4	308.6
22.5°	409.6	406.0	413.1	407.7	417.7	421.4	423.1	423.1
25°	491.7	492.6	499.8	497.1	506.1	513.4	516.9	514.2
27.5°	506.1	507.0	509.7	508.8	516.1	520.5	523.2	516.9
30°	464.7	463.7	462.8	462.0	466.4	468.2	469.1	462.8
32.5°	400.6	397.9	398.7	394.3	396.0	396.0	399.7	390.6
35°	336.5	332.9	332.9	328.4	328.4	328.4	331.1	322.1
37.5°	282.4	278.8	277.8	273.4	272.4	270.7	273.4	265.3
40°	235.4	231.8	232.7	227.3	228.3	227.3	227.3	222.9
42.5°	194.8	192.1	191.3	189.4	190.4	190.4	193.1	189.4
45°	161.5	158.8	157.9	156.9	157.9	157.9	158.8	155.2
47.5°	134.4	130.9	129.9	128.1	128.1	125.4	125.4	121.8
50°	108.2	102.8	102.0	99.3	98.4	96.5	96.5	93.8
52.5°	82.0	77.6	75.8	73.9	73.1	71.2	71.2	69.5
55°	57.7	53.3	52.3	51.4	50.5	49.6	50.5	48.7
57.5°	36.0	34.3	33.3	32.5	31.6	30.6	30.6	29.8
60°	21.6	19.8	19.8	18.9	18.1	17.1	17.1	17.1
62.5°	13.5	12.7	12.7	11.7	11.7	10.8	10.8	10.8
65°	9.0	8.1	8.1	7.2	7.2	6.3	6.3	6.3
67.5°	6.3	6.3	6.3	6.3	5.4	5.4	5.4	5.4
70°	6.3	5.4	5.4	5.4	5.4	5.4	5.4	5.4
72.5°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
75°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
77.5°	4.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
80°	4.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	1.8
87.5°	1.8	1.8	1.8	1.8	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)