

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192803

Luminaire Tested: **LDA6A75935D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7307.3 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72258	72258	72258
5°	185351	65738	20471
10°	361310	50522	9836
15°	648596	34308	13195
20°	962969	26048	21784
25°	1094561	21461	34157
30°	1186512	23459	32125
35°	1249788	15205	19916
40°	1276814	6748	9697
45°	1153205	2582	3605
50°	759122	1023	1023
55°	207897	889	0
60°	41521	1020	0
65°	2919	1375	0
70°	417	1699	0
75°	0	2542	0
80°	0	3788	442
85°	0	7548	881

TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.5	2.2
10°-20°	857.8	11.7
20°-30°	1944.1	26.6
30°-40°	2333.7	31.9
40°-50°	1644.7	22.5
50°-60°	339.4	4.6
60°-70°	12.0	0.2
70°-80°	7.2	0.1
80°-90°	7.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2963.4	40.6
0°-40°	5297.1	72.5
0°-60°	7281.1	99.6
0°-90°	7307.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7307.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1318	1318	1318	1318	1318	
5°	3368	2454	1195	497	372	414
15°	11428	5028	604	215	232	3391
25°	18096	6082	355	497	565	8351
35°	18675	4258	227	298	298	11610
45°	14875	1460	33	45	46	10940
55°	2175	29	9	7	0	2866
65°	22	7	11	7	0	67
75°	0	7	12	8	0	0
85°	0	8	12	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1
2.5°	2246.8	2179.1	2205.6	2127.3	2110.1	2095.4	2110.1	2024.9	1977.2	1916.0	1866.9
5°	3368.2	3287.2	3305.9	3169.0	3106.5	3064.1	3056.0	2880.7	2749.1	2604.2	2454.1
7.5°	4689.0	4611.9	4601.3	4388.7	4259.9	4186.7	4156.2	3905.1	3677.9	3420.1	3138.4
10°	6490.7	6315.4	6260.9	5952.5	5706.9	5551.3	5360.0	4958.7	4560.1	4170.9	3812.0
12.5°	8587.4	8491.8	8356.3	7812.9	7382.2	7161.7	6876.1	6248.9	5645.6	5002.6	4401.9
15°	11428.2	11088.1	10856.9	10071.6	9378.1	9037.9	8620.7	7661.3	6749.8	5935.3	5027.9
17.5°	14204.0	14025.9	13664.4	12645.3	11577.0	11040.3	10418.3	9115.0	7827.5	6668.8	5560.6
20°	16506.6	16339.2	15927.2	14966.5	13781.4	12989.5	12206.9	10418.3	8736.3	7253.4	5916.8
22.5°	17609.3	17503.0	17166.9	16344.5	15334.7	14581.3	13740.2	11527.9	9408.5	7636.0	6078.9
25°	18095.7	18046.4	17830.0	17181.5	16230.1	15591.1	14796.5	12313.2	9827.2	7814.1	6081.5
27.5°	18588.6	18598.0	18119.6	17606.7	16704.5	16090.7	15325.3	12661.3	9902.9	7714.5	5882.1
30°	18744.0	18645.8	18434.5	17698.3	16841.3	16188.9	15367.8	12500.4	9591.9	7305.2	5484.9
32.5°	18680.3	18641.8	18409.3	17630.6	16608.8	15890.1	14957.2	11862.7	8978.1	6720.5	4921.6
35°	18675.0	18603.2	18070.4	17402.1	16143.8	15256.2	14027.1	10831.6	8109.1	5949.9	4258.5
37.5°	18337.5	18159.4	17759.6	16858.7	15200.4	14075.0	12697.2	9572.0	7046.1	5084.9	3600.8
40°	17841.9	17602.8	17076.6	15713.2	13566.0	12269.3	10924.6	8140.9	5920.7	4231.9	2901.8
42.5°	16806.8	16445.5	15701.3	13826.5	11388.4	10219.1	9100.4	6691.3	4828.5	3448.1	2215.0
45°	14874.8	14380.6	13374.7	11316.6	9200.0	8246.0	7346.3	5383.9	3865.2	2557.8	1460.3
47.5°	11955.7	11497.3	10581.8	9008.7	7214.9	6408.3	5690.8	4004.7	2620.2	1481.5	697.6
50°	8901.0	8507.7	7792.8	6260.9	4843.1	4209.4	3595.6	2274.8	1227.7	704.3	289.7
52.5°	5310.9	5115.5	4481.7	3471.9	2391.6	2060.8	1654.3	963.3	619.1	255.2	78.3
55°	2175.2	2007.6	1769.9	1420.4	1040.4	882.2	754.6	475.7	192.7	53.1	29.2
57.5°	983.2	946.1	838.4	659.1	478.3	401.2	271.0	90.3	42.6	26.6	17.2
60°	378.7	341.4	292.3	158.0	67.8	57.2	46.5	30.6	21.3	14.6	10.6
62.5°	54.5	51.7	46.5	37.1	29.2	26.6	22.5	16.0	12.0	9.3	7.9
65°	22.5	22.5	19.9	16.0	13.4	12.0	10.6	7.9	6.7	6.7	6.7
67.5°	9.3	9.3	7.9	6.7	5.3	5.3	5.3	4.0	5.3	5.3	6.7
70°	2.6	2.6	2.6	2.6	2.6	2.6	4.0	4.0	5.3	5.3	6.7
72.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
75°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
77.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
80°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	7.9
82.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	7.9
85°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	7.9
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1
2.5°	1824.3	1739.3	1715.3	1640.9	1578.6	1548.0	1509.4	1423.0	1357.9	1271.5	1219.8
5°	2349.2	2188.4	2060.8	1905.4	1803.0	1736.6	1633.0	1474.9	1347.3	1194.6	1085.5
7.5°	2916.4	2622.9	2393.0	2136.6	1989.0	1873.5	1696.7	1469.5	1282.2	1079.0	910.2
10°	3463.9	3025.5	2664.1	2296.1	2102.0	1941.3	1698.1	1412.5	1164.0	907.6	729.5
12.5°	3946.3	3380.2	2871.4	2398.3	2157.8	1957.1	1652.9	1310.0	1009.8	746.7	589.9
15°	4348.8	3655.2	3017.5	2436.9	2161.8	1922.6	1558.5	1164.0	838.4	604.5	494.3
17.5°	4654.5	3800.1	3062.7	2390.4	2084.7	1824.3	1413.7	979.2	680.4	512.8	415.9
20°	4812.5	3828.0	2997.6	2264.1	1942.5	1675.6	1223.8	794.6	576.7	446.5	348.1
22.5°	4832.6	3749.6	2842.2	2083.5	1763.2	1494.8	1013.8	662.9	514.2	394.6	306.9
25°	4714.3	3579.5	2620.2	1878.8	1566.6	1287.5	825.2	593.9	467.8	354.8	353.4
27.5°	4461.8	3287.2	2354.5	1640.9	1328.7	1046.9	700.2	536.8	417.3	376.1	400.0
30°	4105.7	2912.6	2027.5	1340.7	1037.8	805.1	589.9	442.4	366.8	370.6	390.7
32.5°	3623.4	2447.4	1643.5	982.0	742.8	605.9	442.4	301.6	304.3	305.7	322.9
35°	3017.5	1962.4	1227.7	660.3	522.2	426.6	249.7	221.9	226.0	227.2	239.2
37.5°	2418.2	1508.0	815.9	439.8	328.2	224.6	155.4	148.9	151.5	150.1	163.5
40°	1852.2	1051.0	488.9	217.9	126.2	104.9	95.7	91.7	93.1	94.3	102.3
42.5°	1311.4	570.0	241.8	82.4	66.5	61.1	57.2	54.5	55.8	55.8	61.1
45°	665.7	269.8	82.4	45.2	41.2	37.1	34.5	33.3	33.3	33.3	35.9
47.5°	288.3	89.0	38.5	28.0	25.2	23.9	21.3	19.9	19.9	19.9	21.3
50°	90.3	35.9	23.9	18.6	16.0	14.6	13.4	13.4	13.4	12.0	13.4
52.5°	33.3	22.5	16.0	12.0	10.6	10.6	10.6	9.3	10.6	9.3	10.6
55°	19.9	14.6	10.6	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
57.5°	13.4	10.6	9.3	9.3	7.9	7.9	9.3	9.3	9.3	9.3	9.3
60°	9.3	9.3	7.9	7.9	7.9	7.9	9.3	9.3	9.3	9.3	9.3
62.5°	7.9	7.9	7.9	7.9	7.9	7.9	9.3	9.3	9.3	9.3	10.6
65°	6.7	7.9	7.9	7.9	7.9	7.9	9.3	9.3	10.6	10.6	10.6
67.5°	6.7	7.9	7.9	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6
70°	7.9	7.9	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6	12.0
72.5°	7.9	7.9	9.3	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0
75°	7.9	9.3	9.3	9.3	9.3	10.6	10.6	10.6	12.0	12.0	12.0
77.5°	7.9	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	12.0	12.0
80°	7.9	9.3	9.3	10.6	10.6	10.6	12.0	12.0	12.0	12.0	13.4
82.5°	7.9	9.3	9.3	10.6	10.6	10.6	12.0	12.0	12.0	12.0	13.4
85°	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	12.0	12.0	13.4
87.5°	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	13.4	12.0	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1
2.5°	1150.6	1073.5	1020.4	1000.5	961.9	900.9	865.0	831.7	769.4	756.0	721.5
5°	960.7	837.2	749.4	716.3	672.3	620.5	570.0	536.8	497.0	481.0	457.0
7.5°	757.4	633.7	558.1	531.5	500.9	458.4	413.2	380.0	338.8	317.5	297.6
10°	595.2	503.5	439.8	413.2	381.4	336.1	289.7	245.8	209.9	187.4	183.4
12.5°	483.6	407.9	340.2	312.2	275.1	229.8	196.6	195.3	192.7	191.3	193.9
15°	396.0	322.9	251.1	220.5	209.9	208.6	212.6	216.6	215.2	219.3	221.9
17.5°	325.6	247.1	231.2	232.5	233.9	237.8	244.4	255.2	256.4	263.1	268.4
20°	265.7	261.7	268.4	273.7	277.7	285.6	300.2	313.6	317.5	326.8	337.5
22.5°	301.6	313.6	328.2	334.9	340.2	354.8	370.6	391.9	400.0	412.0	426.6
25°	364.1	384.0	406.5	414.6	422.5	446.5	465.1	490.3	497.0	511.6	526.2
27.5°	415.9	437.1	461.1	471.6	478.3	502.3	518.3	534.1	534.1	542.0	552.8
30°	407.9	425.2	445.1	453.2	455.8	473.0	488.9	494.3	491.7	495.6	503.5
32.5°	338.8	352.1	368.0	374.7	377.3	389.3	402.6	402.6	401.2	401.2	406.5
35°	251.1	260.5	268.4	275.1	279.1	287.0	299.0	297.6	297.6	295.0	299.0
37.5°	168.8	174.1	183.4	186.0	187.4	192.7	202.0	202.0	199.4	200.6	203.3
40°	102.3	108.9	114.2	115.6	118.3	122.3	128.8	128.8	128.8	128.8	130.2
42.5°	61.1	65.1	69.2	69.2	70.4	75.7	78.3	78.3	78.3	78.3	79.7
45°	35.9	37.1	39.9	41.2	41.2	43.8	45.2	45.2	45.2	45.2	46.5
47.5°	21.3	22.5	22.5	23.9	23.9	25.2	26.6	26.6	25.2	25.2	25.2
50°	13.4	13.4	13.4	13.4	14.6	14.6	14.6	14.6	14.6	14.6	13.4
52.5°	10.6	10.6	10.6	10.6	9.3	9.3	9.3	9.3	7.9	7.9	6.7
55°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	7.9	6.7	5.3	4.0
57.5°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	5.3	4.0
60°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	5.3	4.0
62.5°	10.6	10.6	9.3	9.3	9.3	7.9	7.9	6.7	6.7	5.3	4.0
65°	10.6	10.6	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	4.0
67.5°	10.6	10.6	10.6	10.6	9.3	9.3	9.3	7.9	6.7	5.3	4.0
70°	12.0	12.0	10.6	10.6	10.6	9.3	9.3	7.9	6.7	6.7	5.3
72.5°	12.0	12.0	10.6	10.6	10.6	10.6	9.3	7.9	7.9	6.7	5.3
75°	12.0	12.0	12.0	12.0	10.6	10.6	9.3	9.3	7.9	6.7	5.3
77.5°	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3	7.9	6.7	5.3
80°	12.0	12.0	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	5.3
82.5°	13.4	13.4	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	6.7
85°	13.4	13.4	12.0	12.0	12.0	10.6	10.6	9.3	7.9	7.9	6.7
87.5°	13.4	13.4	12.0	12.0	12.0	10.6	10.6	9.3	7.9	7.9	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192803

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1	1318.1
2.5°	700.2	660.3	647.1	656.4	645.7	637.8	627.2	621.8
5°	438.5	409.2	400.0	402.6	393.3	385.4	374.7	372.0
7.5°	269.8	241.8	231.2	231.2	220.5	211.2	204.7	200.6
10°	180.7	175.4	176.7	178.1	176.7	178.1	174.1	176.7
12.5°	193.9	191.3	193.9	195.3	195.3	198.0	192.7	196.6
15°	226.0	223.2	227.2	229.8	229.8	233.9	228.6	232.5
17.5°	276.3	275.1	281.7	284.4	285.6	292.3	285.6	290.9
20°	349.5	348.1	357.4	361.5	360.1	373.4	364.1	373.4
22.5°	443.8	441.2	454.4	458.4	459.7	476.9	469.0	475.7
25°	538.2	540.8	547.5	554.0	555.4	570.0	558.1	564.7
27.5°	558.1	554.0	558.1	566.0	567.4	574.1	563.3	568.6
30°	504.9	498.2	499.6	508.9	511.6	514.2	504.9	507.5
32.5°	410.6	400.0	400.0	409.2	412.0	415.9	400.0	406.5
35°	302.9	293.7	293.7	300.2	301.6	304.3	292.3	297.6
37.5°	207.3	199.4	202.0	204.7	205.9	208.6	207.3	205.9
40°	132.9	127.6	131.5	131.5	132.9	134.3	134.3	135.5
42.5°	81.1	77.1	79.7	79.7	81.1	81.1	81.1	82.4
45°	46.5	45.2	45.2	46.5	46.5	46.5	45.2	46.5
47.5°	25.2	23.9	25.2	25.2	25.2	25.2	25.2	25.2
50°	13.4	12.0	12.0	12.0	12.0	12.0	12.0	12.0
52.5°	6.7	5.3	5.3	5.3	4.0	5.3	4.0	4.0
55°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
57.5°	2.6	1.4	1.4	1.4	0.0	0.0	0.0	0.0
60°	2.6	1.4	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.6	1.4	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.6	1.4	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	4.0	2.6	1.4	1.4	1.4	0.0	0.0	0.0
70°	4.0	2.6	2.6	1.4	1.4	0.0	0.0	0.0
72.5°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
75°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
77.5°	4.0	4.0	2.6	2.6	1.4	1.4	1.4	0.0
80°	5.3	4.0	2.6	2.6	2.6	1.4	1.4	1.4
82.5°	5.3	4.0	2.6	2.6	2.6	1.4	1.4	1.4
85°	5.3	4.0	4.0	2.6	2.6	1.4	1.4	1.4
87.5°	5.3	4.0	4.0	2.6	2.6	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)