

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192352

Luminaire Tested: **LDA6A50927D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50927D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4273.9 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54047	54047	54047
5°	138438	49835	18264
10°	291934	39768	5177
15°	421024	28212	4302
20°	475190	18732	6056
25°	515933	18878	43599
30°	573854	12445	15243
35°	579761	7060	5849
40°	583608	2905	2648
45°	578828	1822	1535
50°	454348	1228	1083
55°	136731	860	516
60°	28879	789	395
65°	3269	934	350
70°	866	1154	577
75°	191	1525	763
80°	0	2557	1137
85°	0	4529	2264



TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	2.9
10°-20°	595.9	13.9
20°-30°	1123.4	26.3
30°-40°	1246.1	29.2
40°-50°	949.6	22.2
50°-60°	211.9	5.0
60°-70°	11.6	0.3
70°-80°	5.3	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1845.0	43.2
0°-40°	3091.1	72.3
0°-60°	4252.6	99.5
0°-90°	4273.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4273.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	986	986	986	986	986	
5°	2516	1864	906	435	332	326
15°	7418	4061	497	88	76	2068
25°	8530	4748	312	521	721	3970
35°	8663	2954	106	93	87	5426
45°	7466	870	24	24	20	5560
55°	1431	38	9	8	5	1766
65°	25	6	7	6	3	59
75°	1	4	7	6	4	1
85°	0	4	7	5	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9
2.5°	1692.3	1662.5	1658.8	1649.0	1571.4	1570.4	1569.5	1529.0	1491.9	1473.0	1392.7
5°	2515.7	2494.2	2467.0	2432.8	2304.7	2286.6	2271.3	2210.9	2081.0	2005.2	1863.6
7.5°	3716.3	3704.6	3568.5	3550.4	3314.9	3257.2	3200.4	3045.2	2794.5	2632.2	2381.4
10°	5244.4	5188.5	5084.8	4944.1	4637.4	4528.2	4422.7	4105.2	3677.6	3337.5	2910.8
12.5°	6625.4	6554.2	6427.9	6263.7	5877.6	5728.8	5561.9	5172.2	4650.0	4097.0	3493.6
15°	7418.4	7406.6	7260.5	7193.7	6882.6	6730.9	6593.0	6144.7	5492.5	4842.1	4060.9
17.5°	7887.4	7888.3	7780.9	7741.3	7451.7	7307.3	7191.0	6864.5	6181.6	5392.3	4491.2
20°	8145.4	8171.5	8071.4	8009.1	7807.1	7679.1	7570.7	7234.3	6639.8	5764.0	4734.8
22.5°	8337.5	8350.1	8228.4	8176.9	7950.5	7826.9	7758.4	7436.3	6855.5	5962.5	4808.7
25°	8529.6	8523.3	8386.2	8283.4	8060.5	7940.6	7856.8	7578.0	6945.6	6008.5	4748.3
27.5°	8732.6	8761.5	8507.1	8342.9	8143.6	8002.9	7909.0	7621.3	6939.4	5888.4	4529.1
30°	9065.5	8831.8	8577.4	8351.0	8121.9	7973.1	7865.7	7499.5	6765.2	5570.0	4112.4
32.5°	8925.7	8760.5	8510.6	8278.0	8032.6	7868.5	7737.6	7302.9	6399.9	5045.9	3553.1
35°	8663.1	8619.0	8371.8	8182.3	7903.6	7726.8	7574.4	6999.8	5833.5	4415.4	2954.1
37.5°	8426.8	8380.8	8233.8	8038.0	7721.4	7536.4	7256.9	6518.1	5096.5	3626.2	2323.6
40°	8155.2	8144.4	7980.2	7799.0	7418.4	7077.4	6787.9	5668.4	4218.8	2851.3	1807.6
42.5°	7854.9	7848.5	7715.1	7447.1	6888.0	6464.8	5980.4	4709.5	3243.7	2164.0	1343.1
45°	7466.1	7429.2	7199.1	6808.5	6005.7	5394.2	4820.5	3598.2	2378.7	1546.1	869.6
47.5°	6792.3	6727.4	6391.8	5723.4	4761.0	4135.8	3608.1	2474.3	1483.8	874.1	431.2
50°	5327.4	5155.1	4677.0	3974.3	2987.6	2444.5	2029.6	1227.7	658.5	433.9	276.1
52.5°	3290.6	3104.8	2652.8	2122.4	1362.9	1056.2	871.4	591.8	364.4	249.9	106.5
55°	1430.6	1343.1	1108.6	882.2	630.5	501.5	433.0	299.5	189.4	91.1	37.9
57.5°	558.3	541.2	471.7	397.8	298.6	243.5	215.6	135.3	52.3	32.5	21.6
60°	263.4	246.2	212.0	175.9	110.1	79.3	61.4	37.9	26.2	19.8	14.4
62.5°	72.2	62.2	50.5	43.3	33.3	29.8	26.2	20.8	16.2	12.7	10.0
65°	25.2	25.2	22.5	20.8	17.1	15.4	14.4	11.7	10.0	8.1	6.3
67.5°	11.7	11.7	10.8	10.0	8.1	8.1	7.2	6.3	5.4	4.5	4.5
70°	5.4	4.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6	3.6	3.6
72.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7	3.6	3.6	3.6
75°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	3.6
77.5°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	3.6
80°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	3.6
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	3.6
85°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	3.6
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9
2.5°	1358.5	1324.2	1279.1	1204.2	1170.8	1163.6	1102.2	1046.4	996.7	960.7	903.9
5°	1771.6	1672.3	1551.5	1406.2	1351.3	1312.5	1195.2	1083.3	987.7	905.6	819.0
7.5°	2181.1	1984.5	1803.2	1591.2	1488.4	1410.8	1236.6	1077.9	933.6	821.7	707.2
10°	2575.3	2295.7	1989.0	1710.2	1572.2	1454.9	1226.8	1025.6	845.2	714.4	593.5
12.5°	2949.7	2548.3	2140.5	1769.7	1604.7	1457.6	1178.1	941.7	747.8	607.0	480.8
15°	3321.3	2731.4	2228.9	1782.4	1583.1	1406.2	1089.7	829.8	638.6	497.1	386.0
17.5°	3553.1	2833.2	2229.8	1726.5	1501.9	1308.8	968.8	713.5	527.7	400.5	303.1
20°	3667.6	2820.7	2145.1	1597.5	1363.9	1169.0	826.3	594.5	426.6	321.1	239.1
22.5°	3634.3	2708.8	1996.1	1427.0	1210.6	1025.6	703.6	498.8	368.1	278.8	216.4
25°	3477.4	2527.5	1820.3	1266.4	1058.9	884.0	617.8	459.2	362.6	312.1	268.8
27.5°	3205.8	2289.3	1604.7	1097.8	911.0	771.3	560.2	445.7	375.2	336.5	340.0
30°	2805.3	1973.6	1326.0	872.3	713.5	599.9	420.3	310.3	229.1	196.6	196.6
32.5°	2357.1	1613.7	1024.7	645.0	516.0	435.7	295.9	212.0	169.6	154.2	147.1
35°	1936.6	1262.8	760.5	467.3	372.5	310.3	193.9	119.0	109.2	105.5	103.8
37.5°	1523.5	948.0	551.2	339.2	258.9	205.6	99.2	76.6	66.8	62.2	58.7
40°	1142.0	665.7	381.6	207.5	143.4	94.7	57.7	46.9	41.5	40.6	38.7
42.5°	799.2	446.5	236.4	91.1	66.8	53.2	39.7	33.3	30.6	29.8	28.9
45°	468.2	278.8	96.5	50.5	41.5	37.0	28.9	25.2	23.5	23.5	22.5
47.5°	294.0	112.8	51.4	32.5	27.9	26.2	21.6	18.9	18.1	18.1	18.1
50°	120.9	49.6	30.6	22.5	19.8	18.9	16.2	14.4	14.4	14.4	14.4
52.5°	44.2	27.9	20.8	16.2	14.4	13.5	11.7	10.8	10.8	11.7	10.8
55°	25.2	18.9	14.4	11.7	10.0	10.0	9.0	9.0	9.0	9.0	9.0
57.5°	16.2	12.7	10.0	8.1	7.2	7.2	7.2	7.2	7.2	8.1	7.2
60°	10.8	9.0	7.2	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2
62.5°	8.1	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2
65°	6.3	5.4	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1
67.5°	4.5	4.5	5.4	5.4	5.4	5.4	6.3	6.3	7.2	7.2	8.1
70°	4.5	4.5	5.4	5.4	5.4	5.4	6.3	6.3	7.2	7.2	8.1
72.5°	4.5	4.5	5.4	5.4	5.4	5.4	6.3	6.3	7.2	7.2	8.1
75°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2	8.1
77.5°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	7.2	7.2	7.2	8.1
80°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	7.2	7.2	8.1	8.1
82.5°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	7.2	7.2	8.1	8.1
85°	4.5	5.4	5.4	5.4	5.4	6.3	6.3	7.2	7.2	7.2	8.1
87.5°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9
2.5°	865.0	825.4	792.8	775.7	756.8	724.3	693.7	665.7	654.0	616.1	623.4
5°	751.4	683.7	629.6	605.3	577.4	532.2	492.5	454.6	434.7	402.4	390.6
7.5°	625.1	545.8	480.8	452.8	428.4	386.0	349.1	313.9	288.6	255.3	241.8
10°	500.6	424.9	365.4	341.0	313.9	271.5	234.5	203.9	183.1	157.9	145.2
12.5°	396.0	328.3	268.0	243.5	221.0	185.8	156.9	129.0	106.5	93.0	89.3
15°	308.5	243.5	193.9	174.1	155.2	120.9	99.2	92.0	88.4	84.7	83.9
17.5°	231.8	179.5	135.3	115.5	104.6	95.7	92.0	88.4	86.6	83.9	84.7
20°	178.6	128.1	110.1	107.4	105.5	101.1	100.1	99.2	98.4	99.2	101.1
22.5°	169.6	159.6	165.0	168.7	176.8	177.7	192.1	203.9	214.7	244.5	258.9
25°	285.9	303.1	330.2	347.3	370.8	395.1	440.1	479.9	521.4	559.3	592.6
27.5°	358.1	366.2	366.2	375.2	365.4	363.5	358.1	353.6	372.5	366.2	386.0
30°	198.5	207.5	222.8	230.9	240.8	248.0	245.3	236.4	241.8	234.5	241.8
32.5°	141.7	141.7	145.2	146.1	147.9	148.8	149.8	150.6	151.5	147.1	149.8
35°	101.1	97.4	95.7	95.7	94.7	93.0	92.0	92.0	93.0	88.4	90.3
37.5°	56.8	55.0	55.0	55.0	55.0	55.0	55.9	56.8	56.8	56.8	58.7
40°	37.9	37.9	37.9	38.7	38.7	38.7	39.7	39.7	40.6	40.6	41.5
42.5°	28.9	27.9	28.9	28.9	28.9	29.8	29.8	30.6	30.6	30.6	31.6
45°	22.5	22.5	22.5	22.5	23.5	23.5	23.5	23.5	24.4	23.5	24.4
47.5°	18.1	18.1	18.1	18.9	18.9	18.1	18.9	18.9	18.9	18.9	18.9
50°	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	15.4	14.4	15.4
52.5°	11.7	10.8	10.8	10.8	10.8	10.0	10.0	10.8	10.8	10.0	10.0
55°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3
60°	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3	6.3	5.4
62.5°	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3	5.4	5.4
65°	8.1	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	5.4	5.4
67.5°	8.1	8.1	7.2	7.2	7.2	7.2	7.2	6.3	6.3	5.4	5.4
70°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	5.4
72.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3
75°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3
77.5°	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3	5.4
80°	8.1	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	6.3	5.4
82.5°	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	5.4	5.4
85°	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	5.4	5.4	5.4
87.5°	7.2	7.2	7.2	6.3	6.3	6.3	6.3	5.4	5.4	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192352

CATALOG NUMBER: LDA6A50927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	985.9	985.9	985.9	985.9	985.9	985.9	985.9	985.9
2.5°	585.5	572.8	583.6	570.1	565.6	555.6	551.2	555.6
5°	368.9	355.4	358.1	349.1	334.6	334.6	330.2	331.9
7.5°	222.8	209.3	210.2	202.0	191.2	189.4	184.9	186.7
10°	129.0	114.6	114.6	105.5	96.5	95.7	93.0	93.0
12.5°	85.7	83.9	82.0	81.2	79.3	79.3	79.3	77.6
15°	80.3	79.3	78.5	78.5	76.6	76.6	77.6	75.8
17.5°	82.0	81.2	80.3	80.3	80.3	80.3	81.2	79.3
20°	98.4	99.2	99.2	101.9	103.8	104.6	107.4	103.8
22.5°	258.0	266.1	272.4	305.8	334.6	323.8	343.7	310.3
25°	617.0	639.6	658.5	662.1	680.2	705.4	721.6	720.8
27.5°	386.0	387.0	397.8	397.8	394.1	408.6	418.5	416.8
30°	238.1	237.2	240.8	231.8	230.9	237.2	240.8	240.8
32.5°	147.1	146.1	148.8	147.1	142.5	149.8	147.9	147.9
35°	88.4	89.3	87.4	87.4	83.9	87.4	86.6	87.4
37.5°	57.7	56.8	55.9	55.9	54.1	55.0	54.1	52.3
40°	40.6	40.6	39.7	39.7	38.7	37.9	37.9	37.0
42.5°	30.6	30.6	29.8	29.8	28.9	27.9	27.9	27.1
45°	23.5	22.5	21.6	21.6	21.6	20.8	20.8	19.8
47.5°	18.1	18.1	18.1	17.1	17.1	16.2	16.2	15.4
50°	14.4	14.4	14.4	14.4	13.5	13.5	13.5	12.7
52.5°	10.0	10.0	9.0	9.0	8.1	8.1	8.1	7.2
55°	7.2	7.2	7.2	6.3	6.3	6.3	5.4	5.4
57.5°	6.3	6.3	5.4	5.4	5.4	4.5	4.5	4.5
60°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
62.5°	4.5	4.5	4.5	3.6	3.6	3.6	3.6	2.7
65°	4.5	4.5	3.6	3.6	3.6	2.7	2.7	2.7
67.5°	4.5	4.5	4.5	3.6	3.6	3.6	3.6	2.7
70°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
72.5°	5.4	4.5	4.5	4.5	4.5	3.6	3.6	3.6
75°	5.4	5.4	4.5	4.5	4.5	4.5	4.5	3.6
77.5°	5.4	4.5	4.5	4.5	4.5	4.5	3.6	3.6
80°	5.4	4.5	4.5	4.5	4.5	3.6	3.6	3.6
82.5°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
85°	4.5	4.5	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	3.6	3.6	2.7	2.7	2.7	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)