

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192805

Luminaire Tested: **LDA6A75935D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6787.8 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68394	68394	68394
5°	176568	63394	19816
10°	334958	48368	6652
15°	598948	31442	6635
20°	892461	21399	12094
25°	1018317	26675	75942
30°	1101258	22288	22706
35°	1156805	10848	7114
40°	1175102	3900	3614
45°	1046954	2582	2171
50°	672404	1817	1467
55°	177016	1262	755
60°	39481	1316	581
65°	3788	1557	687
70°	1266	1923	850
75°	297	2542	1419
80°	0	4167	2115
85°	0	7548	3334



TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	2.2
10°-20°	790.7	11.6
20°-30°	1855.3	27.3
30°-40°	2134.0	31.4
40°-50°	1515.9	22.3
50°-60°	308.2	4.5
60°-70°	15.4	0.2
70°-80°	9.2	0.1
80°-90°	7.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2797.5	41.2
0°-40°	4931.5	72.7
0°-60°	6755.6	99.5
0°-90°	6787.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6787.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1248	1248	1248	1248	1248	
5°	3209	2321	1152	461	360	391
15°	10553	4745	554	125	117	3166
25°	16835	5714	441	963	1256	7759
35°	17286	4012	162	120	106	10738
45°	13504	1427	33	36	28	9952
55°	1852	37	13	13	8	2498
65°	29	11	12	11	5	70
75°	1	7	12	11	7	3
85°	0	7	12	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6
2.5°	2149.7	2084.6	2052.7	2051.5	1958.4	1989.0	1958.4	1934.5	1848.2	1812.3	1752.5
5°	3208.6	3128.9	3065.2	3037.3	2877.9	2843.2	2827.4	2746.3	2565.5	2460.6	2321.1
7.5°	4457.6	4374.0	4268.9	4185.1	3954.1	3889.0	3846.4	3707.0	3439.8	3228.6	2968.2
10°	6017.3	5968.2	5798.2	5644.1	5293.3	5157.8	5030.2	4704.7	4355.3	3931.4	3595.2
12.5°	8118.1	8002.5	7699.4	7391.3	6841.1	6639.3	6427.9	5907.2	5373.0	4708.7	4153.3
15°	10553.4	10455.0	9988.7	9486.6	8703.9	8371.9	8041.0	7221.1	6400.1	5544.5	4744.6
17.5°	13356.9	13170.8	12707.1	11858.2	10763.3	10241.2	9624.7	8580.4	7395.1	6232.7	5238.8
20°	15298.0	15187.7	14795.7	13981.3	12735.1	12045.4	11280.2	9846.6	8225.6	6784.1	5562.9
22.5°	16359.5	16249.4	15955.7	15236.9	14215.1	13523.0	12634.1	10870.9	8852.7	7154.7	5715.9
25°	16835.2	16763.4	16602.8	16016.7	15070.8	14447.6	13606.6	11579.0	9244.7	7323.5	5714.5
27.5°	17275.0	17293.7	16896.3	16414.1	15542.4	14916.6	14119.4	11897.9	9321.8	7238.5	5531.1
30°	17397.2	17350.7	17176.7	16497.7	15685.9	15004.3	14150.0	11729.3	9021.4	6862.4	5167.1
32.5°	17321.5	17322.9	17159.4	16438.0	15484.0	14721.3	13760.7	11124.7	8436.8	6272.5	4601.2
35°	17285.6	17273.6	16849.8	16216.1	15004.3	14107.5	12897.2	10154.8	7626.4	5519.1	4012.5
37.5°	16929.6	16857.8	16552.2	15692.6	14107.5	12960.9	11657.5	8968.3	6628.5	4735.3	3409.2
40°	16420.6	16330.3	15833.4	14600.4	12574.2	11294.8	9999.4	7625.1	5584.2	3955.3	2737.0
42.5°	15377.7	15228.8	14475.6	12840.0	10599.9	9409.5	8336.0	6280.4	4565.3	3211.4	2102.0
45°	13504.3	13261.1	12218.2	10509.6	8556.5	7622.3	6714.9	5034.3	3655.1	2391.5	1426.9
47.5°	10843.1	10577.3	9631.4	8258.9	6698.9	5941.7	5171.0	3707.0	2472.6	1393.8	716.1
50°	7884.2	7700.8	6865.1	5707.8	4429.8	3794.6	3203.3	2067.3	1186.5	673.7	293.6
52.5°	4542.6	4411.1	3829.1	3004.1	2178.9	1824.3	1466.8	902.1	604.5	267.0	94.3
55°	1852.1	1776.4	1521.2	1288.8	967.2	835.8	697.6	450.4	203.3	63.7	37.1
57.5°	906.2	896.8	748.0	599.2	441.0	356.0	268.4	90.3	49.1	31.9	23.9
60°	360.1	346.7	237.8	138.2	77.1	62.5	53.1	37.1	28.0	21.3	17.2
62.5°	62.5	61.1	51.7	43.8	35.9	31.9	29.2	22.5	18.6	14.6	13.2
65°	29.2	29.2	26.6	23.9	19.9	18.6	17.2	14.6	12.0	10.6	10.6
67.5°	14.6	14.6	13.2	12.0	10.6	10.6	9.3	9.3	7.9	7.9	7.9
70°	7.9	7.9	7.9	6.7	6.7	6.7	6.7	6.7	5.3	6.7	6.7
72.5°	5.3	5.3	5.3	4.0	2.6	4.0	4.0	4.0	5.3	6.7	6.7
75°	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7	6.7
77.5°	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
80°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
82.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
85°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6
2.5°	1725.9	1656.7	1611.7	1532.0	1498.7	1484.1	1411.1	1340.7	1272.9	1223.6	1148.0
5°	2214.8	2104.6	1935.9	1777.7	1708.7	1664.8	1521.2	1388.4	1262.2	1152.0	1020.4
7.5°	2741.0	2513.8	2249.5	1995.7	1876.0	1796.3	1574.4	1380.4	1199.7	1032.3	853.0
10°	3245.9	2888.5	2503.2	2140.5	1978.3	1858.8	1569.1	1320.6	1085.5	868.9	676.3
12.5°	3676.4	3214.0	2702.5	2232.0	2020.9	1868.1	1520.0	1217.1	931.3	698.8	531.5
15°	4039.1	3463.8	2833.9	2262.7	2008.9	1828.2	1424.3	1074.9	762.7	554.0	429.2
17.5°	4294.2	3584.7	2864.5	2210.9	1925.1	1716.6	1279.4	892.8	599.2	447.7	338.8
20°	4443.0	3600.7	2790.1	2084.6	1779.0	1558.5	1097.5	701.5	486.3	366.8	263.1
22.5°	4465.5	3522.2	2644.0	1914.6	1610.3	1397.7	914.1	587.3	442.4	342.8	257.8
25°	4356.6	3366.8	2454.0	1748.4	1457.5	1239.6	790.5	593.9	497.0	441.0	458.4
27.5°	4145.4	3110.4	2236.1	1578.4	1298.1	1077.6	746.7	621.8	542.0	551.4	583.2
30°	3821.2	2748.9	1922.5	1290.2	993.8	821.1	593.9	447.7	372.0	352.1	353.4
32.5°	3344.3	2295.9	1509.3	895.4	668.2	554.0	376.1	249.7	251.1	232.5	231.2
35°	2799.4	1848.2	1129.3	600.5	462.3	385.2	221.9	175.4	168.8	162.1	152.8
37.5°	2260.0	1428.3	752.0	410.6	295.0	213.8	111.6	91.7	85.0	79.7	79.7
40°	1720.6	999.1	465.0	215.2	119.5	87.6	66.4	55.8	54.5	54.5	53.1
42.5°	1249.0	589.9	252.4	85.0	66.4	58.4	46.5	41.2	41.2	41.2	41.2
45°	664.3	300.2	97.0	53.1	43.8	41.2	34.5	31.9	31.9	33.3	33.3
47.5°	306.9	113.0	49.1	35.9	30.6	30.6	26.6	25.2	25.2	26.6	26.6
50°	110.3	46.5	31.9	25.2	22.5	23.9	21.3	19.9	21.3	21.3	21.3
52.5°	42.6	29.2	22.5	19.9	17.2	18.6	16.0	16.0	17.2	17.2	17.2
55°	26.6	21.3	17.2	14.6	13.2	14.6	13.2	13.2	13.2	13.2	13.2
57.5°	18.6	16.0	13.2	12.0	10.6	12.0	12.0	12.0	12.0	12.0	12.0
60°	14.6	12.0	10.6	10.6	10.6	10.6	10.6	10.6	10.6	12.0	12.0
62.5°	12.0	10.6	10.6	10.6	10.6	10.6	10.6	10.6	12.0	12.0	12.0
65°	10.6	9.3	10.6	10.6	9.3	10.6	10.6	10.6	12.0	12.0	13.2
67.5°	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0
70°	7.9	7.9	9.3	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0
72.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6	12.0	12.0	12.0
75°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6	12.0	12.0	12.0
77.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0	12.0
80°	7.9	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	13.2	13.2
82.5°	7.9	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	13.2	13.2
85°	7.9	9.3	9.3	10.6	10.6	10.6	10.6	12.0	12.0	12.0	12.0
87.5°	7.9	9.3	9.3	10.6	10.6	10.6	10.6	10.6	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6
2.5°	1097.5	1032.3	967.2	935.4	907.4	867.6	817.1	775.9	732.1	709.6	657.7
5°	916.7	805.1	710.8	665.6	631.1	583.2	531.5	494.2	461.1	442.4	409.2
7.5°	709.6	603.3	520.8	486.3	461.1	413.2	374.7	336.1	301.6	276.3	243.2
10°	548.7	466.4	398.6	365.4	337.5	287.0	240.4	204.7	167.4	142.2	131.5
12.5°	435.7	358.7	289.7	256.4	227.2	175.4	140.8	134.3	127.6	124.9	120.9
15°	334.9	264.3	191.3	158.0	146.1	139.6	131.5	130.2	124.9	124.9	120.9
17.5°	251.1	172.7	146.1	143.4	142.2	139.6	135.5	134.3	132.9	132.9	131.5
20°	180.7	167.4	163.5	166.1	167.4	170.0	168.8	168.8	174.1	186.0	183.4
22.5°	253.8	275.1	297.6	305.5	334.9	364.1	390.7	423.8	502.3	592.6	613.8
25°	502.3	566.0	624.4	656.4	704.1	769.2	831.7	908.8	963.3	1008.4	1060.3
27.5°	624.4	648.3	639.0	643.1	637.8	628.4	631.1	647.1	639.0	615.1	624.4
30°	369.4	388.0	377.3	382.6	368.0	368.0	364.1	372.0	366.8	357.4	354.8
32.5°	240.4	251.1	249.7	249.7	244.4	241.8	232.5	229.8	220.5	203.3	199.2
35°	144.8	138.2	131.5	127.6	124.9	124.9	123.5	123.5	119.5	115.6	114.2
37.5°	78.3	79.7	79.7	79.7	79.7	82.4	81.1	81.1	81.1	78.3	78.3
40°	54.5	57.2	57.2	57.2	58.4	58.4	58.4	59.8	58.4	58.4	58.4
42.5°	42.6	43.8	42.6	42.6	43.8	43.8	43.8	45.2	45.2	45.2	43.8
45°	34.5	34.5	33.3	34.5	34.5	35.9	35.9	35.9	35.9	34.5	34.5
47.5°	28.0	28.0	28.0	28.0	29.2	29.2	29.2	29.2	29.2	29.2	29.2
50°	22.5	22.5	22.5	23.9	23.9	23.9	22.5	23.9	23.9	23.9	22.5
52.5°	17.2	17.2	17.2	17.2	17.2	16.0	16.0	16.0	16.0	16.0	14.6
55°	13.2	13.2	13.2	13.2	13.2	14.6	13.2	14.6	13.2	13.2	12.0
57.5°	12.0	12.0	12.0	12.0	13.2	13.2	12.0	12.0	12.0	10.6	10.6
60°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	10.6	9.3	9.3
62.5°	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3	9.3
65°	13.2	13.2	12.0	13.2	13.2	12.0	12.0	10.6	10.6	9.3	9.3
67.5°	13.2	13.2	13.2	13.2	13.2	13.2	12.0	12.0	10.6	10.6	9.3
70°	13.2	13.2	13.2	13.2	13.2	13.2	12.0	12.0	10.6	10.6	9.3
72.5°	13.2	13.2	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	9.3
75°	13.2	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	10.6	9.3
77.5°	13.2	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	10.6	9.3
80°	13.2	13.2	13.2	13.2	13.2	13.2	12.0	12.0	10.6	10.6	9.3
82.5°	13.2	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	10.6	9.3
85°	13.2	12.0	12.0	12.0	12.0	12.0	10.6	10.6	9.3	9.3	7.9
87.5°	12.0	12.0	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192805

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6	1247.6
2.5°	657.7	645.7	640.4	631.1	623.2	619.1	604.5	621.8
5°	402.6	388.0	384.0	376.1	366.8	361.5	350.7	360.1
7.5°	229.8	212.6	204.7	198.0	188.7	180.7	171.4	176.7
10°	128.8	123.5	124.9	120.9	119.5	118.3	116.9	119.5
12.5°	119.5	115.6	116.9	114.2	113.0	113.0	111.6	113.0
15°	120.9	116.9	119.5	116.9	115.6	115.6	114.2	116.9
17.5°	131.5	128.8	131.5	128.8	130.2	128.8	130.2	131.5
20°	184.6	188.7	196.6	191.3	195.3	200.6	207.3	207.3
22.5°	649.7	734.7	745.3	787.9	896.8	892.8	966.0	968.6
25°	1134.6	1140.0	1187.7	1171.9	1173.1	1228.9	1223.6	1255.5
27.5°	652.4	651.0	660.3	643.1	648.3	652.4	637.8	655.0
30°	364.1	357.4	361.5	352.1	352.1	354.8	350.7	358.7
32.5°	202.0	196.6	196.6	190.1	188.7	187.4	183.4	187.4
35°	115.6	111.6	113.0	110.3	107.7	106.3	104.9	106.3
37.5°	79.7	77.1	78.3	75.7	73.0	71.8	70.4	71.8
40°	58.4	57.2	57.2	54.5	53.1	51.7	50.5	50.5
42.5°	43.8	42.6	42.6	39.8	38.5	37.1	35.9	37.1
45°	33.3	31.9	31.9	30.6	29.2	28.0	28.0	28.0
47.5°	29.2	28.0	29.2	28.0	26.6	26.6	26.6	26.6
50°	22.5	22.5	22.5	21.3	19.9	19.9	18.6	17.2
52.5°	14.6	13.2	13.2	12.0	12.0	10.6	10.6	10.6
55°	12.0	10.6	10.6	9.3	9.3	7.9	7.9	7.9
57.5°	9.3	9.3	7.9	7.9	6.7	6.7	6.7	6.7
60°	7.9	7.9	7.9	6.7	6.7	5.3	5.3	5.3
62.5°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
65°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
67.5°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
70°	9.3	7.9	7.9	6.7	6.7	6.7	5.3	5.3
72.5°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
75°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
77.5°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
80°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
82.5°	7.9	7.9	7.9	6.7	6.7	6.7	6.7	6.7
85°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
87.5°	5.3	5.3	4.0	4.0	4.0	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)