

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192375

Luminaire Tested: **LDA6A50935D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4092.7 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63515	63515	63515
5°	127190	60417	16201
10°	213300	51652	4431
15°	325734	38723	6436
20°	466696	28312	75770
25°	693838	46987	38863
30°	810973	20775	6039
35°	815444	4330	3199
40°	675186	2419	1846
45°	505409	1535	1465
50°	354197	1100	853
55°	56935	851	659
60°	3487	877	537
65°	1038	1154	519
70°	641	1282	785
75°	424	1461	1038
80°	284	2178	1547
85°	566	4340	1824



TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.0	2.9
10°-20°	506.9	12.4
20°-30°	1219.6	29.8
30°-40°	1299.5	31.8
40°-50°	810.4	19.8
50°-60°	118.4	2.9
60°-70°	7.5	0.2
70°-80°	5.9	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.6	45.1
0°-40°	3146.1	76.9
0°-60°	4074.8	99.6
0°-90°	4092.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4092.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1159	1159	1159	1159	1159	
5°	2311	1854	1098	547	294	267
15°	5739	3190	682	105	113	1703
25°	11471	3793	777	805	642	5169
35°	12185	2814	65	60	48	7351
45°	6519	824	20	23	19	5132
55°	596	14	9	10	7	1053
65°	8	6	9	8	4	12
75°	2	4	7	7	5	2
85°	1	4	7	6	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6
2.5°	1723.5	1664.8	1684.8	1641.0	1625.0	1629.0	1597.2	1571.4	1557.4	1523.6	1488.7
5°	2311.3	2243.7	2263.5	2197.9	2157.1	2148.1	2098.4	2042.7	1993.0	1917.4	1853.8
7.5°	3024.3	2940.8	2954.7	2856.2	2773.7	2745.9	2670.3	2561.9	2461.4	2333.1	2210.8
10°	3831.8	3753.3	3749.3	3599.2	3457.9	3403.2	3292.9	3113.9	2942.7	2749.8	2549.0
12.5°	4783.6	4665.3	4645.3	4452.5	4241.6	4152.1	3997.9	3724.4	3453.9	3172.6	2883.1
15°	5739.4	5612.0	5580.2	5337.6	5043.2	4922.8	4716.9	4353.0	3980.1	3582.2	3189.5
17.5°	6757.7	6553.8	6381.9	6101.3	5761.2	5638.0	5371.4	4905.0	4435.5	3944.3	3419.2
20°	7999.8	7772.1	7530.5	7051.1	6427.5	6184.9	5892.5	5366.4	4780.7	4212.7	3589.2
22.5°	9702.5	9328.6	8815.3	8044.7	7187.4	6841.3	6389.7	5708.5	5046.2	4408.7	3702.6
25°	11470.8	10954.6	10390.7	9206.2	7882.6	7459.9	6866.1	5970.1	5257.0	4552.9	3793.1
27.5°	12489.2	12074.4	11435.0	10193.7	8446.4	7891.5	7207.2	6167.0	5391.2	4622.5	3818.9
30°	12811.4	12475.2	11894.5	10621.5	8635.4	7974.0	7239.0	6168.9	5326.6	4501.2	3669.7
32.5°	12677.1	12357.9	11715.4	10354.0	8289.3	7680.7	6967.5	5918.4	5008.4	4128.2	3286.9
35°	12184.8	11763.1	10982.5	9465.8	7700.5	7095.8	6429.5	5469.9	4519.1	3622.0	2814.5
37.5°	11079.9	10642.3	9754.2	8327.1	6941.7	6415.7	5879.6	4967.6	4026.8	3161.5	2402.7
40°	9434.9	8972.5	8242.6	7241.0	6123.3	5764.3	5311.7	4411.7	3505.7	2710.0	2021.8
42.5°	7775.2	7478.8	7046.2	6252.5	5473.9	5119.8	4680.2	3806.0	3004.5	2244.6	1535.6
45°	6519.1	6284.3	5996.9	5495.7	4760.7	4427.6	4018.8	3196.4	2342.0	1499.8	823.5
47.5°	5680.7	5394.3	5143.6	4584.7	3796.0	3391.3	2957.7	2106.4	1350.6	650.4	227.7
50°	4153.1	3808.0	3574.3	2947.8	2231.7	1894.5	1577.4	977.6	437.6	145.2	37.8
52.5°	2105.4	1844.9	1707.5	1289.9	852.4	637.4	468.4	201.9	86.5	28.9	21.8
55°	595.7	479.3	429.6	283.5	154.1	108.5	70.7	35.8	25.8	19.8	14.0
57.5°	61.6	52.7	49.8	40.7	32.9	30.9	27.8	21.8	16.9	14.0	8.9
60°	31.8	28.9	27.8	24.9	20.9	18.9	18.0	14.9	10.9	8.0	6.9
62.5°	16.9	16.0	14.0	12.9	10.9	10.9	10.0	8.0	6.9	6.9	6.0
65°	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0	6.0	6.0	6.0
67.5°	6.0	6.0	6.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
70°	4.0	4.0	4.0	4.0	2.9	2.9	2.9	2.9	2.9	4.0	4.0
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0	4.0
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0	4.0
77.5°	0.9	0.9	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0	4.0
80°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
82.5°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
85°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.0	2.9	4.0	4.0
87.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6
2.5°	1447.1	1422.2	1382.4	1342.6	1330.6	1297.9	1259.0	1213.3	1170.5	1136.7	1103.9
5°	1751.3	1684.8	1610.1	1509.6	1473.8	1418.2	1334.6	1245.1	1167.6	1097.9	1033.3
7.5°	2054.7	1929.4	1793.1	1647.9	1586.3	1503.7	1372.4	1246.1	1130.8	1028.3	931.8
10°	2323.1	2130.3	1938.3	1738.4	1651.9	1545.4	1370.4	1209.3	1062.1	927.9	806.6
12.5°	2570.8	2304.2	2049.7	1793.1	1684.8	1556.5	1340.6	1145.7	970.7	813.5	671.2
15°	2787.6	2444.5	2129.2	1818.9	1681.7	1534.5	1281.9	1058.1	863.3	682.3	528.1
17.5°	2938.8	2524.1	2152.1	1792.2	1641.0	1471.8	1192.4	953.8	739.9	550.0	373.9
20°	3029.3	2545.0	2130.3	1733.5	1566.3	1391.3	1108.9	867.3	659.4	485.3	338.1
22.5°	3079.0	2555.0	2114.3	1712.6	1542.5	1375.4	1112.9	882.2	704.1	586.7	574.9
25°	3128.8	2586.8	2142.2	1736.4	1577.4	1422.2	1171.5	935.8	814.6	776.8	789.7
27.5°	3125.7	2566.8	2116.3	1714.6	1561.4	1400.2	1120.8	873.1	789.7	731.0	682.3
30°	2948.7	2377.8	1917.4	1490.7	1315.7	1100.9	746.8	513.1	392.8	328.2	295.4
32.5°	2539.0	1939.3	1464.9	1036.3	865.3	625.6	321.2	169.0	145.2	129.3	115.4
35°	2110.3	1544.5	1102.9	653.4	434.6	237.7	110.4	71.6	66.7	64.7	63.6
37.5°	1740.4	1221.3	725.0	261.5	156.1	88.5	50.7	45.8	44.7	45.8	44.7
40°	1373.4	805.5	287.4	87.6	47.8	38.7	35.8	32.9	32.9	33.8	32.9
42.5°	822.4	300.4	87.6	32.9	30.9	27.8	26.9	25.8	24.9	25.8	25.8
45°	271.5	76.5	28.9	22.9	21.8	20.9	19.8	19.8	19.8	19.8	20.9
47.5°	61.6	26.9	19.8	16.9	16.9	16.0	16.0	14.9	16.0	16.0	16.9
50°	23.8	16.9	14.0	12.9	12.9	12.0	12.0	12.0	12.0	12.9	12.9
52.5°	14.9	12.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.9
55°	10.0	8.9	8.0	8.0	8.0	8.0	8.0	8.9	8.9	8.9	8.9
57.5°	6.9	6.9	6.9	6.9	8.0	6.9	8.0	6.9	6.9	8.0	8.9
60°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.9
62.5°	6.0	6.9	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9
65°	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9	8.9
67.5°	4.9	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9
70°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0
72.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0
75°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0
77.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0
80°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9	8.0
82.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9
85°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9
87.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6
2.5°	1060.1	1019.4	999.5	969.6	971.6	922.0	903.1	867.3	847.3	826.4	802.6
5°	954.7	883.1	832.4	792.6	770.8	706.1	662.3	605.6	547.0	490.3	443.5
7.5°	822.4	727.9	650.4	599.7	568.9	438.6	355.0	288.4	262.6	242.6	222.8
10°	675.2	557.9	420.7	351.1	308.3	246.6	221.8	184.0	157.2	132.3	117.4
12.5°	527.1	348.1	251.6	230.8	215.8	160.1	126.3	117.4	95.4	90.5	88.5
15°	331.2	228.8	178.1	153.2	133.2	111.4	102.5	101.4	105.4	106.5	105.4
17.5°	234.7	183.0	134.3	131.2	131.2	143.2	145.2	154.1	162.1	169.0	170.1
20°	301.3	270.5	315.3	335.1	370.0	412.7	475.4	562.9	639.4	717.0	776.8
22.5°	576.8	644.5	743.9	778.8	837.3	928.9	1015.4	1095.9	1177.5	1238.2	1251.1
25°	848.4	895.1	953.8	940.9	958.7	953.8	905.1	839.3	804.6	741.0	719.0
27.5°	649.4	600.7	559.9	513.1	490.3	446.5	383.9	344.1	308.3	272.5	257.6
30°	264.6	231.7	207.9	191.0	181.0	157.2	145.2	132.3	126.3	117.4	112.3
32.5°	103.4	97.4	94.5	91.6	90.5	87.6	84.5	80.5	79.6	79.6	75.6
35°	61.6	61.6	61.6	60.7	61.6	60.7	59.6	58.7	59.6	59.6	56.7
37.5°	43.8	44.7	44.7	44.7	44.7	44.7	44.7	44.7	43.8	43.8	40.7
40°	32.9	33.8	34.9	33.8	34.9	34.9	33.8	32.9	32.9	32.9	30.9
42.5°	26.9	26.9	26.9	26.9	27.8	26.9	26.9	26.9	26.9	26.9	25.8
45°	21.8	21.8	21.8	21.8	22.9	22.9	21.8	21.8	22.9	22.9	21.8
47.5°	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.0	16.0	16.0	14.9
50°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	14.0	12.9	12.9
52.5°	10.9	10.9	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	10.9
55°	10.0	10.0	10.9	10.9	10.9	10.9	10.9	10.0	10.0	10.0	8.9
57.5°	8.9	10.0	10.0	10.0	10.0	10.0	10.0	10.0	8.9	8.9	8.0
60°	8.9	8.9	10.0	10.0	10.0	10.0	8.9	8.9	8.0	8.0	6.9
62.5°	8.9	8.9	10.0	10.0	10.0	8.9	8.9	8.0	8.0	6.9	6.9
65°	8.9	10.0	10.0	10.0	10.0	8.9	8.9	8.0	8.0	6.9	6.9
67.5°	8.9	10.0	10.0	10.0	10.0	8.9	8.9	8.0	8.0	6.9	6.9
70°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.0	8.0	6.9	6.9
72.5°	8.0	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9
75°	8.0	8.0	8.0	8.0	8.9	8.0	8.0	8.0	6.9	6.9	6.0
77.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0
80°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0
82.5°	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0	6.0
85°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.9
87.5°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192375

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6
2.5°	776.8	759.9	755.9	755.9	746.8	729.0	725.9	720.1
5°	392.8	351.1	343.1	334.2	319.3	301.3	296.4	294.4
7.5°	202.9	185.0	182.0	176.1	167.0	158.1	156.1	155.2
10°	119.4	108.5	103.4	94.5	85.6	80.5	80.5	79.6
12.5°	88.5	88.5	88.5	88.5	88.5	88.5	88.5	88.5
15°	107.4	110.4	110.4	111.4	112.3	113.4	115.4	113.4
17.5°	181.0	195.9	195.0	197.0	203.9	212.8	208.8	213.9
20°	879.1	993.6	1026.3	1059.2	1158.6	1252.1	1233.2	1298.8
22.5°	1263.0	1297.9	1283.9	1275.0	1295.9	1284.9	1331.7	1300.8
25°	677.2	670.3	670.3	640.5	646.5	631.5	651.4	642.5
27.5°	249.6	227.7	225.7	211.9	220.8	199.9	205.9	201.9
30°	107.4	108.5	104.5	101.4	98.5	96.5	96.5	95.4
32.5°	73.6	73.6	71.6	69.6	67.6	65.6	64.7	63.6
35°	54.7	54.7	52.7	51.8	50.7	48.7	47.8	47.8
37.5°	39.8	39.8	38.7	37.8	35.8	34.9	33.8	33.8
40°	30.9	29.8	28.9	28.9	26.9	26.9	25.8	25.8
42.5°	24.9	24.9	24.9	23.8	22.9	21.8	21.8	21.8
45°	21.8	21.8	20.9	19.8	19.8	19.8	18.9	18.9
47.5°	14.9	14.9	14.0	14.0	12.9	12.9	12.0	12.0
50°	12.0	12.0	12.0	12.0	10.9	10.0	10.0	10.0
52.5°	10.9	10.0	10.0	10.0	8.9	8.9	8.0	8.0
55°	8.9	8.9	8.0	8.0	6.9	6.9	6.9	6.9
57.5°	8.0	6.9	6.9	6.9	6.0	6.0	6.0	6.0
60°	6.9	6.0	6.0	6.0	4.9	4.9	4.9	4.9
62.5°	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.9
65°	6.0	6.0	6.0	4.9	4.9	4.9	4.9	4.0
67.5°	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.9
70°	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.9
72.5°	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.9
75°	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.9
77.5°	6.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9
80°	6.0	4.9	4.9	4.9	4.9	4.0	4.0	4.9
82.5°	4.9	4.9	4.9	4.9	4.0	4.0	4.0	4.0
85°	4.0	4.0	4.0	4.0	2.9	2.9	2.9	2.9
87.5°	2.9	2.0	2.0	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)