

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192811

Luminaire Tested: **LDA6A75935D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7141.2 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	50	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	44	40
10	60	48	41	37	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	76266	76266	76266
5°	202388	70707	27047
10°	441781	57174	8060
15°	666843	41777	7009
20°	775679	28673	11008
25°	855449	30945	73299
30°	946462	23295	22795
35°	960513	11919	8539
40°	982612	4852	4093
45°	990847	2985	2473
50°	834693	2038	1586
55°	275699	1395	889
60°	54195	1316	581
65°	6369	1712	687
70°	1699	1923	850
75°	297	2542	1419
80°	0	4167	2115
85°	0	8303	3334



TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.1	2.6
10°-20°	934.8	13.1
20°-30°	1845.2	25.8
30°-40°	2081.3	29.1
40°-50°	1652.3	23.1
50°-60°	404.0	5.7
60°-70°	21.6	0.3
70°-80°	9.2	0.1
80°-90°	7.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2965.2	41.5
0°-40°	5046.5	70.7
0°-60°	7102.8	99.5
0°-90°	7141.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7141.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1391	1391	1391	1391	1391	
5°	3678	2756	1285	646	492	486
15°	11750	6245	736	145	124	3296
25°	14143	7570	512	926	1212	6550
35°	14352	4818	178	141	128	9026
45°	12781	1501	38	40	32	9579
55°	2885	65	15	15	9	3384
65°	49	12	13	11	5	120
75°	1	7	12	11	7	4
85°	0	7	13	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	2414.2	2367.7	2389.0	2355.7	2261.4	2232.2	2256.1	2220.2	2112.5	2071.4	2028.9
5°	3677.8	3636.6	3649.9	3574.1	3397.4	3336.3	3332.3	3223.4	3005.5	2883.2	2755.8
7.5°	5576.5	5519.4	5503.4	5321.5	4981.3	4853.7	4791.2	4522.8	4112.3	3821.4	3535.7
10°	7936.3	7992.0	7935.0	7639.9	7105.8	6866.6	6715.3	6207.7	5467.5	4913.5	4379.4
12.5°	10302.7	10337.2	10229.5	9862.9	9183.8	8897.0	8673.6	8023.9	7048.8	6107.9	5310.7
15°	11749.7	11913.0	11812.0	11555.6	11029.4	10681.3	10480.7	9678.2	8450.5	7416.7	6244.9
17.5°	12780.6	12932.1	12848.4	12638.4	12044.6	11764.3	11634.1	10973.6	9637.0	8322.9	6943.7
20°	13296.2	13480.9	13405.2	13167.3	12731.5	12497.6	12339.6	11695.1	10490.0	8996.6	7410.1
22.5°	13645.6	13850.3	13767.9	13551.3	13107.6	12835.2	12760.7	12150.9	10936.5	9400.5	7608.0
25°	14142.6	14314.0	14081.5	13814.4	13376.0	13088.9	13043.7	12420.6	11150.3	9553.2	7569.5
27.5°	14498.6	14702.0	14307.3	14036.3	13535.4	13233.8	13175.3	12589.3	11170.3	9432.3	7257.3
30°	14951.8	14820.3	14473.4	14080.1	13546.0	13224.5	13150.0	12491.0	10971.0	8987.2	6646.1
32.5°	14772.4	14740.6	14393.7	13931.4	13433.0	13108.8	13009.2	12188.1	10423.6	8219.2	5781.1
35°	14352.5	14453.5	14163.9	13876.8	13257.7	12920.2	12782.0	11741.6	9598.4	7230.7	4817.8
37.5°	14106.7	14170.5	13987.2	13636.3	13022.4	12578.8	12316.9	10990.9	8518.2	5984.4	3889.1
40°	13730.8	13892.8	13716.0	13313.5	12605.3	11996.8	11541.0	9634.3	7095.2	4718.2	3041.4
42.5°	13318.8	13463.6	13294.9	12812.5	11812.0	10996.3	10238.9	8039.9	5555.2	3604.7	2281.3
45°	12780.6	12910.9	12608.0	11857.2	10440.9	9315.5	8559.4	6314.0	4189.3	2648.1	1501.3
47.5°	11810.8	11776.3	11347.0	10180.4	8435.9	7427.3	6547.7	4522.8	2785.0	1500.1	746.7
50°	9787.1	9464.3	8833.1	7479.2	5661.5	4571.9	3971.5	2334.5	1263.6	726.8	469.0
52.5°	6339.2	5979.1	5401.2	4150.8	2718.5	2181.7	1749.8	1055.0	659.1	410.6	184.6
55°	2884.6	2629.4	2260.2	1676.8	1166.6	969.9	821.1	534.1	353.4	152.8	65.1
57.5°	1098.9	1013.8	900.9	718.9	539.4	466.4	386.6	256.4	110.3	57.2	38.5
60°	494.3	458.4	421.1	329.5	231.2	166.1	126.2	69.2	46.5	33.3	25.2
62.5°	168.8	140.8	116.9	83.8	62.5	54.5	47.9	38.5	28.0	22.5	17.2
65°	49.1	47.9	45.2	39.8	31.9	29.2	28.0	22.5	17.2	14.6	12.0
67.5°	23.9	22.5	21.3	19.9	16.0	14.6	14.6	13.2	10.6	9.3	7.9
70°	10.6	10.6	9.3	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
72.5°	5.3	5.3	5.3	4.0	4.0	4.0	4.0	5.3	5.3	6.7	6.7
75°	1.4	2.6	2.6	2.6	2.6	4.0	4.0	5.3	5.3	6.7	6.7
77.5°	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7	6.7
80°	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7	6.7
82.5°	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7	6.7
85°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1925.3	1897.3	1787.1	1702.1	1662.2	1659.5	1570.5	1516.1	1420.4	1345.9	1275.5
5°	2531.2	2407.7	2184.3	2007.6	1922.6	1878.8	1703.4	1577.2	1412.5	1284.9	1158.7
7.5°	3147.7	2912.6	2599.0	2262.8	2124.5	2039.5	1768.5	1566.5	1347.3	1169.2	1012.4
10°	3778.8	3364.3	2896.5	2452.7	2253.5	2109.9	1761.8	1488.1	1235.6	1027.1	855.6
12.5°	4436.4	3782.8	3131.7	2576.3	2313.3	2124.5	1702.1	1373.9	1098.9	876.9	713.5
15°	4990.6	4107.0	3280.5	2605.6	2294.7	2066.1	1574.5	1229.1	952.6	736.1	587.3
17.5°	5418.4	4289.0	3308.4	2533.8	2191.0	1935.9	1409.8	1069.6	798.6	607.2	459.7
20°	5633.7	4316.9	3220.7	2363.7	2003.6	1740.5	1222.4	907.6	669.6	491.5	365.4
22.5°	5649.7	4186.7	3029.4	2144.6	1797.7	1530.7	1068.2	782.6	587.3	441.2	346.9
25°	5442.4	3935.6	2773.0	1920.0	1586.5	1345.9	958.1	750.8	591.3	511.6	470.4
27.5°	5049.0	3587.5	2491.3	1695.4	1404.4	1218.4	912.8	750.8	640.4	577.9	592.6
30°	4504.2	3143.6	2099.3	1389.8	1142.7	980.6	717.5	562.1	441.2	368.0	354.8
32.5°	3797.4	2572.4	1627.7	1027.1	833.1	706.9	485.0	352.1	284.4	277.7	269.8
35°	3125.1	2031.6	1235.6	758.7	613.8	499.6	309.6	207.3	188.7	178.1	170.0
37.5°	2468.7	1520.0	887.5	551.4	421.1	317.5	159.4	134.3	116.9	106.3	97.0
40°	1856.1	1092.2	625.8	333.5	220.5	136.9	95.7	82.4	73.0	67.8	65.1
42.5°	1312.7	726.8	388.0	140.8	104.9	86.4	66.4	58.4	53.1	50.5	47.9
45°	762.7	451.8	156.8	82.4	66.4	59.8	49.1	43.8	41.2	38.5	37.1
47.5°	476.9	182.0	81.1	53.1	46.5	42.6	35.9	34.5	31.9	30.6	30.6
50°	192.7	81.1	50.5	37.1	33.3	31.9	28.0	26.6	23.9	23.9	23.9
52.5°	73.0	47.9	34.5	26.6	23.9	22.5	19.9	19.9	18.6	18.6	18.6
55°	42.6	31.9	23.9	18.6	17.2	17.2	16.0	16.0	14.6	14.6	14.6
57.5°	28.0	21.3	17.2	13.2	13.2	13.2	12.0	12.0	12.0	12.0	12.0
60°	18.6	14.6	12.0	10.6	10.6	10.6	10.6	12.0	12.0	12.0	12.0
62.5°	13.2	12.0	10.6	10.6	10.6	10.6	10.6	12.0	12.0	12.0	13.2
65°	10.6	9.3	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2	13.2
67.5°	7.9	7.9	7.9	7.9	9.3	9.3	10.6	12.0	12.0	12.0	13.2
70°	6.7	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2
72.5°	6.7	7.9	7.9	9.3	9.3	9.3	10.6	12.0	12.0	12.0	13.2
75°	6.7	7.9	7.9	9.3	9.3	9.3	10.6	12.0	12.0	12.0	13.2
77.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2	13.2
80°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2	13.2
82.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2	13.2
85°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	13.2	13.2
87.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0	13.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1241.0	1179.8	1113.5	1092.2	1070.9	1029.7	1004.5	959.3	926.0	892.9	866.4
5°	1074.9	977.9	896.8	862.3	829.1	772.0	732.1	684.2	645.7	612.6	582.0
7.5°	902.1	790.5	709.6	674.9	641.8	579.3	528.8	469.0	423.8	386.6	356.0
10°	742.7	636.4	548.7	507.5	469.0	403.9	356.0	308.3	269.8	237.8	209.9
12.5°	604.5	490.3	401.2	370.6	333.5	280.3	235.1	183.4	160.8	151.5	144.8
15°	469.0	366.8	292.3	264.3	231.2	180.7	160.8	151.5	144.8	140.8	135.5
17.5°	357.4	272.4	199.2	180.7	170.0	159.4	154.2	147.5	143.4	142.2	138.2
20°	280.3	205.9	187.4	182.0	182.0	179.3	175.4	175.4	174.1	178.1	178.1
22.5°	288.3	288.3	304.3	302.9	324.2	345.5	361.5	413.2	442.4	504.9	547.5
25°	503.5	551.4	607.2	624.4	665.7	726.8	790.5	870.3	926.0	985.9	1009.8
27.5°	628.4	636.4	628.4	648.3	621.8	605.9	611.2	620.5	620.5	624.4	640.4
30°	372.0	390.7	407.9	421.1	414.6	407.9	405.3	385.2	385.2	377.3	370.6
32.5°	252.4	249.7	247.1	252.4	247.1	247.1	243.2	244.4	236.5	231.2	228.6
35°	172.7	164.7	155.4	156.8	151.5	150.1	146.1	146.1	140.8	138.2	136.9
37.5°	95.7	95.7	91.7	92.9	91.7	91.7	91.7	92.9	91.7	91.7	92.9
40°	65.1	65.1	63.7	65.1	63.7	65.1	66.4	66.4	66.4	66.4	65.1
42.5°	49.1	49.1	47.9	49.1	47.9	49.1	50.5	50.5	50.5	50.5	50.5
45°	38.5	38.5	38.5	38.5	38.5	38.5	38.5	39.8	39.8	38.5	38.5
47.5°	30.6	31.9	30.6	30.6	30.6	30.6	31.9	31.9	30.6	30.6	30.6
50°	25.2	25.2	23.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9
52.5°	19.9	18.6	18.6	17.2	17.2	17.2	17.2	17.2	17.2	17.2	16.0
55°	14.6	14.6	13.2	13.2	13.2	14.6	14.6	14.6	14.6	13.2	13.2
57.5°	13.2	13.2	13.2	12.0	12.0	13.2	13.2	12.0	12.0	12.0	10.6
60°	12.0	13.2	12.0	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3
62.5°	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3	9.3
65°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	9.3	9.3
67.5°	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	10.6	10.6	9.3
70°	13.2	13.2	13.2	13.2	13.2	12.0	12.0	12.0	10.6	10.6	9.3
72.5°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	12.0	10.6	10.6	9.3
75°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3
77.5°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3
80°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3
82.5°	13.2	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	9.3	9.3
85°	13.2	13.2	12.0	12.0	12.0	12.0	10.6	10.6	9.3	9.3	7.9
87.5°	12.0	12.0	12.0	12.0	10.6	10.6	10.6	9.3	7.9	7.9	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192811

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	834.4	829.1	825.2	833.1	830.5	797.2	801.3	799.9
5°	547.5	535.5	526.2	530.1	519.5	504.9	494.3	491.5
7.5°	325.6	312.2	304.3	296.4	293.7	275.1	267.1	272.4
10°	179.3	160.8	159.4	155.4	150.1	146.1	143.4	144.8
12.5°	138.2	136.9	134.3	132.9	130.2	128.8	127.6	126.2
15°	131.5	130.2	128.8	127.6	126.2	124.9	123.5	123.5
17.5°	135.5	135.5	134.3	132.9	132.9	134.3	132.9	131.5
20°	176.7	176.7	179.3	183.4	183.4	187.4	192.7	188.7
22.5°	574.1	603.3	639.2	649.7	712.2	762.7	855.6	814.5
25°	1049.6	1116.1	1132.1	1154.6	1189.1	1206.4	1189.1	1211.8
27.5°	637.8	660.3	662.9	664.3	672.3	671.0	653.8	664.3
30°	370.6	378.7	376.1	374.7	372.0	357.4	354.8	360.1
32.5°	232.5	229.8	228.6	227.2	227.2	219.3	223.2	220.5
35°	132.9	136.9	135.5	134.3	130.2	128.8	128.8	127.6
37.5°	89.0	90.3	89.0	87.6	85.0	83.8	82.4	81.1
40°	63.7	65.1	63.7	62.5	61.1	59.8	58.4	57.2
42.5°	47.9	49.1	47.9	47.9	45.2	43.8	42.6	41.2
45°	37.1	35.9	35.9	35.9	34.5	33.3	31.9	31.9
47.5°	30.6	30.6	30.6	29.2	28.0	28.0	28.0	26.6
50°	22.5	23.9	22.5	22.5	21.3	19.9	19.9	18.6
52.5°	16.0	16.0	14.6	14.6	13.2	12.0	12.0	12.0
55°	12.0	12.0	12.0	10.6	10.6	9.3	9.3	9.3
57.5°	10.6	9.3	9.3	9.3	7.9	7.9	6.7	6.7
60°	9.3	7.9	7.9	6.7	6.7	5.3	5.3	5.3
62.5°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
65°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
67.5°	7.9	7.9	6.7	6.7	6.7	5.3	5.3	5.3
70°	7.9	7.9	7.9	6.7	6.7	6.7	5.3	5.3
72.5°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
75°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
77.5°	9.3	7.9	7.9	7.9	6.7	6.7	6.7	6.7
80°	7.9	7.9	7.9	6.7	6.7	6.7	6.7	6.7
82.5°	7.9	7.9	7.9	7.9	6.7	6.7	6.7	6.7
85°	7.9	6.7	6.7	6.7	5.3	5.3	5.3	5.3
87.5°	6.7	5.3	5.3	4.0	4.0	4.0	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)