

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192378

Luminaire Tested: **LDA6A50935D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.6 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40677	40677	40677
5°	107225	37057	12750
10°	216657	28846	7749
15°	398930	21623	11181
20°	618498	17292	18627
25°	726169	15340	23638
30°	787400	15426	18319
35°	830254	9182	9851
40°	851588	3914	4265
45°	797804	1535	1465
50°	557832	682	341
55°	195730	659	0
60°	39481	757	0
65°	2452	895	0
70°	465	1282	0
75°	0	1694	0
80°	0	2526	284
85°	0	5598	566

TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.1	2.0
10°-20°	530.8	11.0
20°-30°	1254.8	25.9
30°-40°	1528.6	31.6
40°-50°	1137.1	23.5
50°-60°	275.3	5.7
60°-70°	10.2	0.2
70°-80°	4.9	0.1
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1880.8	38.8
0°-40°	3409.4	70.4
0°-60°	4821.7	99.6
0°-90°	4841.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	742	742	742	742	742	
5°	1948	1457	673	314	232	245
15°	7029	3047	381	175	197	2118
25°	12005	3820	254	368	391	5513
35°	12406	2790	137	149	147	7727
45°	10291	1063	20	22	19	7559
55°	2048	23	7	5	0	2317
65°	19	5	7	5	0	63
75°	0	5	8	6	0	0
85°	0	5	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
2.5°	1294.0	1272.2	1270.2	1248.2	1240.3	1237.3	1206.5	1195.6	1154.8	1146.8	1089.1
5°	1948.5	1914.7	1907.8	1858.0	1821.1	1770.4	1743.6	1697.9	1601.4	1550.6	1457.2
7.5°	2772.1	2727.3	2717.4	2639.8	2563.2	2496.5	2440.9	2334.4	2157.4	2036.1	1845.1
10°	3892.1	3766.7	3720.9	3556.8	3398.6	3274.3	3209.7	2976.0	2709.4	2546.3	2279.7
12.5°	5314.4	5105.4	5019.9	4766.4	4487.8	4284.0	4158.6	3791.6	3357.9	3045.6	2664.6
15°	7029.1	6786.4	6633.3	6313.9	5807.7	5517.3	5295.5	4707.7	4075.0	3602.6	3046.6
17.5°	8896.1	8706.1	8477.3	7976.9	7161.4	6812.3	6409.4	5638.5	4771.3	4113.8	3387.7
20°	10601.9	10283.5	10111.5	9554.5	8609.6	8149.0	7652.8	6497.9	5386.9	4530.6	3649.3
22.5°	11525.9	11217.5	11114.1	10630.7	9764.4	9252.1	8620.5	7254.9	5859.4	4816.0	3788.5
25°	12005.3	11723.8	11730.7	11294.1	10512.3	10031.0	9388.3	7826.8	6181.6	4966.2	3820.5
27.5°	12380.3	12034.1	11973.5	11647.2	10952.0	10459.6	9840.0	8138.1	6300.1	4950.3	3733.8
30°	12439.0	12155.5	12199.3	11745.6	11111.1	10598.9	9954.3	8121.2	6178.7	4750.4	3509.1
32.5°	12399.2	12117.7	12218.2	11725.8	11042.5	10480.5	9763.3	7791.0	5822.6	4380.4	3178.9
35°	12406.1	12082.8	12008.3	11591.5	10777.9	10118.4	9253.1	7188.2	5296.4	3899.0	2789.9
37.5°	12258.0	11822.3	11835.2	11286.1	10266.6	9392.3	8412.6	6384.6	4673.7	3384.8	2399.1
40°	11899.9	11573.6	11470.2	10654.6	9293.9	8269.4	7324.5	5511.3	3953.7	2847.7	1940.5
42.5°	11389.7	10996.7	10693.4	9563.5	7915.3	6975.4	6158.9	4601.2	3273.4	2334.4	1506.8
45°	10290.6	9865.8	9278.0	7922.3	6526.8	5711.2	5029.9	3734.9	2647.7	1804.2	1063.3
47.5°	8442.4	8043.6	7438.9	6300.1	5211.0	4531.6	4000.4	2925.3	1935.6	1137.9	527.1
50°	6540.8	6237.4	5775.9	4787.2	3877.1	3241.6	2768.1	1837.1	987.7	519.3	220.8
52.5°	4263.1	4048.2	3637.4	2885.5	2191.2	1717.7	1396.5	781.8	465.5	218.8	64.7
55°	2047.9	1936.5	1639.2	1188.6	860.3	706.2	596.8	379.0	176.1	52.7	22.9
57.5°	816.6	792.7	706.2	532.2	407.7	346.1	268.5	104.5	34.9	21.8	14.0
60°	360.1	349.1	292.4	193.9	104.5	59.6	43.8	25.8	16.9	12.9	8.9
62.5°	51.8	47.8	40.7	31.8	25.8	21.8	18.9	14.0	8.9	6.9	6.0
65°	18.9	18.9	16.9	14.0	12.0	10.9	10.0	6.9	4.9	4.9	4.9
67.5°	8.0	8.0	8.0	6.0	6.0	4.9	4.0	4.0	4.0	4.0	4.9
70°	2.9	2.9	2.9	2.0	2.0	2.0	2.9	2.9	2.9	4.0	4.9
72.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.9
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.9
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.9	4.9
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
2.5°	1040.4	1026.4	979.7	933.0	926.1	906.1	865.4	817.6	755.9	717.1	678.3
5°	1335.8	1266.2	1187.6	1097.1	1069.3	1029.5	943.9	852.4	750.0	673.4	601.8
7.5°	1680.9	1525.7	1377.6	1232.4	1177.7	1116.0	985.7	854.3	714.2	602.7	513.3
10°	2004.2	1765.5	1535.7	1329.8	1248.2	1164.7	989.7	820.5	646.5	518.2	426.6
12.5°	2326.4	1984.3	1670.0	1400.5	1290.0	1182.6	967.7	759.9	562.9	440.6	367.0
15°	2580.1	2182.2	1767.5	1436.3	1299.0	1167.7	914.1	676.3	481.5	381.0	315.3
17.5°	2756.1	2295.7	1804.2	1421.4	1264.2	1116.0	829.6	578.9	415.7	334.2	270.5
20°	2877.5	2331.5	1778.4	1359.6	1189.6	1026.4	723.1	491.3	369.0	296.4	232.7
22.5°	2911.3	2296.6	1704.8	1267.1	1092.1	924.1	612.7	433.7	335.2	266.6	225.8
25°	2878.4	2208.1	1594.4	1156.8	972.8	796.7	520.2	398.8	309.3	253.6	262.6
27.5°	2759.2	2051.9	1441.2	1014.6	825.6	659.4	457.5	357.0	272.5	267.6	278.5
30°	2562.2	1828.2	1259.2	832.5	652.5	526.2	383.9	281.5	238.7	243.7	250.7
32.5°	2278.7	1553.7	1025.5	616.7	478.4	395.9	274.5	195.0	189.0	193.0	197.9
35°	1920.7	1264.2	767.8	425.7	339.2	272.5	161.2	138.3	135.2	137.2	139.2
37.5°	1558.6	976.8	522.2	286.5	205.9	138.3	96.5	90.5	88.5	89.6	90.5
40°	1209.5	679.3	328.2	137.2	80.5	68.7	59.6	56.7	54.7	54.7	55.8
42.5°	883.2	402.8	163.1	53.8	43.8	40.7	35.8	33.8	31.8	32.9	33.8
45°	494.4	179.0	55.8	29.8	26.9	24.9	21.8	20.9	19.8	19.8	19.8
47.5°	210.9	62.7	26.9	18.9	16.9	16.0	14.0	12.9	12.0	12.0	12.0
50°	69.6	24.9	16.9	12.9	10.9	10.0	8.9	8.0	8.0	8.0	8.9
52.5°	24.9	16.0	10.9	8.9	8.0	8.0	6.9	6.9	6.9	6.9	6.9
55°	14.9	10.9	8.0	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
57.5°	10.0	6.9	6.9	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9
60°	6.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9
62.5°	6.0	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9
65°	4.9	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9
67.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9	8.0
70°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0
72.5°	4.9	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0
75°	4.9	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.0
77.5°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.0
80°	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.0	8.9
82.5°	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.0	8.9
85°	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.9	8.9
87.5°	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
2.5°	638.5	608.7	566.9	553.1	524.2	503.3	480.4	454.6	449.5	423.7	420.8
5°	532.2	484.4	436.6	418.8	393.9	373.0	350.1	325.2	314.3	289.4	274.5
7.5°	438.6	392.8	350.1	332.2	308.3	281.5	254.6	228.8	213.9	190.0	178.1
10°	368.0	322.3	276.5	258.6	236.7	206.9	178.1	151.2	141.2	135.2	136.3
12.5°	307.4	261.6	215.8	195.9	173.1	149.2	148.2	146.2	150.2	149.2	150.2
15°	257.6	208.9	165.1	159.2	159.2	163.1	167.1	168.1	175.0	175.0	177.0
17.5°	211.9	178.1	180.0	180.0	184.0	191.0	198.9	202.9	213.9	214.8	218.8
20°	197.0	204.9	213.9	215.8	222.8	233.7	244.7	252.6	266.6	270.5	278.5
22.5°	233.7	247.7	261.6	265.6	274.5	290.4	310.3	317.3	334.2	334.2	345.2
25°	275.5	296.4	310.3	315.3	325.2	339.2	352.1	356.1	368.0	364.1	368.0
27.5°	292.4	307.4	316.3	321.2	323.2	335.2	341.2	339.2	347.2	341.2	341.2
30°	259.6	270.5	275.5	278.5	278.5	287.4	287.4	284.5	289.4	284.5	281.5
32.5°	203.9	211.9	215.8	215.8	214.8	220.8	218.8	214.8	216.8	213.9	206.9
35°	142.3	148.2	151.2	150.2	149.2	154.2	151.2	148.2	149.2	147.2	142.3
37.5°	93.5	94.5	96.5	98.5	97.4	101.4	99.4	97.4	98.5	96.5	93.5
40°	56.7	58.7	60.7	60.7	60.7	61.6	61.6	60.7	62.7	60.7	58.7
42.5°	33.8	35.8	35.8	35.8	36.9	36.9	37.8	35.8	37.8	35.8	34.9
45°	20.9	20.9	20.9	21.8	20.9	21.8	21.8	20.9	21.8	20.9	19.8
47.5°	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.0	12.9	12.0	10.9
50°	8.0	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0
52.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0
55°	6.9	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.9	4.0	2.9
57.5°	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.9	4.0	2.9	2.9
60°	6.9	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.0	2.9	2.9
62.5°	6.9	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.0	2.9	2.9
65°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.9	4.0	2.9
67.5°	8.0	6.9	6.9	6.9	6.9	6.9	6.0	4.9	4.9	4.0	2.9
70°	8.0	8.0	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	2.9
72.5°	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0	4.9	4.0	4.0
75°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0	4.9	4.0
77.5°	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9	4.0
80°	8.9	8.9	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9	4.0
82.5°	8.9	8.9	8.0	8.0	8.0	8.0	6.9	6.9	6.0	4.9	4.0
85°	8.9	8.9	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9	4.0
87.5°	8.9	8.9	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192378

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
2.5°	402.8	400.8	393.9	395.9	390.8	379.9	381.0	377.0
5°	264.6	258.6	251.6	251.6	244.7	234.7	234.7	231.7
7.5°	161.2	152.2	145.2	144.3	137.2	132.3	132.3	131.3
10°	136.3	137.2	137.2	138.3	137.2	137.2	138.3	139.2
12.5°	153.2	156.1	156.1	157.2	156.1	158.1	158.1	160.1
15°	183.0	188.0	189.0	191.0	190.0	193.0	195.0	197.0
17.5°	229.8	235.7	237.7	243.7	242.7	245.7	247.7	251.6
20°	289.4	298.4	301.4	309.3	308.3	311.3	316.3	319.3
22.5°	356.1	367.0	368.0	375.0	373.9	377.0	379.0	379.9
25°	373.9	381.0	379.9	383.9	383.9	385.0	385.0	390.8
27.5°	342.1	347.2	347.2	347.2	348.1	349.1	349.1	354.1
30°	281.5	283.5	284.5	281.5	283.5	284.5	284.5	289.4
32.5°	208.9	209.9	210.9	206.9	209.9	209.9	209.9	213.9
35°	144.3	144.3	145.2	142.3	144.3	145.2	144.3	147.2
37.5°	94.5	94.5	94.5	94.5	94.5	94.5	93.5	96.5
40°	58.7	59.6	58.7	58.7	57.7	57.7	57.7	59.6
42.5°	34.9	34.9	33.8	33.8	33.8	33.8	34.9	34.9
45°	19.8	19.8	18.9	18.9	18.0	18.9	18.9	18.9
47.5°	10.9	10.0	10.0	10.0	8.9	8.9	8.9	10.0
50°	4.9	4.9	4.9	4.0	4.0	4.0	2.9	4.0
52.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.9
55°	2.0	2.0	0.9	0.9	0.0	0.0	0.0	0.0
57.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.9	2.0	2.0	0.9	0.9	0.9	0.9
80°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
85°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
87.5°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)