

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192828

Luminaire Tested: **LDA6A75940D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7303.3 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	50	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	44	40
10	60	48	41	37	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	77993	77993	77993
5°	206977	72303	27663
10°	451806	58471	8244
15°	681968	42724	7168
20°	793280	29327	11259
25°	874859	31641	74962
30°	967934	23826	23314
35°	982310	12187	8727
40°	1004904	4959	4179
45°	1013345	3062	2527
50°	853635	2081	1620
55°	281949	1424	908
60°	55423	1349	592
65°	6538	1751	700
70°	1747	1971	866
75°	297	2605	1440
80°	0	4262	2147
85°	0	8491	3397

TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.3	2.6
10°-20°	956.1	13.1
20°-30°	1887.1	25.8
30°-40°	2128.6	29.1
40°-50°	1689.8	23.1
50°-60°	413.2	5.7
60°-70°	22.1	0.3
70°-80°	9.4	0.1
80°-90°	7.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3032.5	41.5
0°-40°	5161.0	70.7
0°-60°	7264.0	99.5
0°-90°	7303.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7303.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1423	1423	1423	1423	1423	
5°	3761	2818	1314	660	503	497
15°	12016	6387	753	148	126	3371
25°	14464	7741	523	947	1239	6699
35°	14678	4927	182	144	130	9231
45°	13071	1536	40	41	33	9796
55°	2950	66	15	15	10	3461
65°	50	12	14	11	5	123
75°	1	7	12	11	7	4
85°	0	7	14	10	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7
2.5°	2469.0	2421.5	2443.2	2409.2	2312.7	2282.9	2307.3	2270.6	2160.6	2118.4	2074.9
5°	3761.2	3719.1	3732.8	3655.2	3474.5	3412.0	3408.0	3296.6	3073.7	2948.8	2818.2
7.5°	5703.1	5644.7	5628.4	5442.2	5094.3	4963.9	4900.0	4625.6	4205.7	3908.1	3615.9
10°	8116.4	8173.4	8115.0	7813.3	7267.1	7022.5	6867.6	6348.5	5591.7	5024.9	4478.7
12.5°	10536.5	10571.7	10461.7	10086.7	9392.4	9098.8	8870.5	8206.0	7208.7	6246.6	5431.3
15°	12016.2	12183.4	12080.1	11817.9	11279.7	10923.7	10718.6	9897.7	8642.3	7585.0	6386.6
17.5°	13070.8	13225.5	13140.1	12925.3	12317.8	12031.1	11898.1	11222.7	9855.6	8511.7	7101.3
20°	13597.9	13786.9	13709.3	13466.1	13020.4	12781.2	12619.6	11960.6	10728.1	9200.8	7578.2
22.5°	13955.3	14164.6	14080.3	13858.8	13405.0	13126.4	13050.4	12426.6	11184.6	9613.8	7780.7
25°	14463.5	14638.8	14401.0	14128.0	13679.5	13385.9	13339.8	12702.5	11403.4	9770.0	7741.4
27.5°	14827.7	15035.7	14632.1	14354.9	13842.5	13534.0	13474.3	12875.1	11423.8	9646.5	7422.0
30°	15291.0	15156.6	14801.9	14399.6	13853.4	13524.5	13448.4	12774.4	11219.9	9191.3	6797.0
32.5°	15107.6	15075.0	14720.4	14247.5	13737.9	13406.3	13304.5	12464.7	10660.2	8405.7	5912.3
35°	14678.2	14781.4	14485.2	14191.7	13558.6	13213.4	13072.0	12008.1	9816.3	7394.8	4927.2
37.5°	14426.8	14492.1	14304.5	13945.8	13318.0	12864.2	12596.5	11240.3	8711.6	6120.2	3977.4
40°	14042.3	14208.0	14027.3	13615.6	12891.3	12269.0	11802.8	9853.0	7256.2	4825.3	3110.4
42.5°	13621.0	13769.1	13596.6	13103.4	12080.1	11245.7	10471.2	8222.4	5681.4	3686.6	2333.1
45°	13070.8	13203.9	12894.1	12126.4	10677.7	9526.8	8753.7	6457.3	4284.5	2708.2	1535.5
47.5°	12078.8	12043.4	11604.5	10411.5	8627.3	7595.9	6696.3	4625.6	2848.1	1534.1	763.6
50°	10009.2	9679.1	9033.6	7648.9	5790.0	4675.8	4061.6	2387.5	1292.3	743.3	479.7
52.5°	6483.1	6114.8	5523.6	4245.0	2780.2	2231.3	1789.6	1079.0	674.0	419.9	188.8
55°	2950.0	2689.1	2311.5	1714.9	1193.0	991.9	839.8	546.2	361.5	156.3	66.5
57.5°	1123.7	1036.8	921.2	735.2	551.7	476.9	395.5	262.3	112.8	58.4	39.5
60°	505.5	468.8	430.8	337.1	236.4	169.9	129.1	70.7	47.6	34.0	25.8
62.5°	172.5	144.1	119.5	85.6	63.9	55.8	49.0	39.5	28.6	23.2	17.7
65°	50.4	49.0	46.2	40.7	32.6	29.8	28.6	23.2	17.7	14.9	12.3
67.5°	24.4	23.2	21.8	20.4	16.3	14.9	14.9	13.5	10.9	9.5	8.1
70°	10.9	10.9	9.5	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
72.5°	5.4	5.4	5.4	4.0	4.0	4.0	4.0	5.4	5.4	6.8	6.8
75°	1.4	2.6	2.6	2.6	2.6	4.0	4.0	5.4	5.4	6.8	6.8
77.5°	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8	6.8
80°	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8	6.8
82.5°	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8	6.8
85°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7
2.5°	1969.0	1940.4	1827.7	1740.7	1699.9	1697.2	1606.1	1550.5	1452.5	1376.6	1304.4
5°	2588.5	2462.2	2233.9	2053.2	1966.3	1921.4	1742.1	1612.9	1444.5	1313.9	1184.9
7.5°	3219.2	2978.6	2657.9	2314.1	2172.8	2085.8	1808.6	1602.0	1377.8	1195.8	1035.4
10°	3864.6	3440.6	2962.3	2508.4	2304.6	2157.8	1801.9	1521.9	1263.7	1050.4	875.1
12.5°	4537.1	3868.6	3202.8	2634.9	2365.7	2172.8	1740.7	1405.0	1123.7	896.8	729.8
15°	5103.9	4200.2	3355.0	2664.7	2346.7	2113.0	1610.3	1256.9	974.2	752.8	600.6
17.5°	5541.3	4386.4	3383.6	2591.3	2240.8	1979.8	1441.7	1093.9	816.6	621.0	470.1
20°	5761.6	4414.8	3293.8	2417.4	2049.1	1780.1	1250.1	928.1	684.9	502.7	373.7
22.5°	5777.9	4281.7	3098.1	2193.2	1838.6	1565.4	1092.5	800.3	600.6	451.1	354.6
25°	5565.7	4024.9	2835.9	1963.5	1622.4	1376.6	979.7	767.7	604.7	523.1	481.0
27.5°	5163.6	3668.9	2547.8	1733.8	1436.2	1246.0	933.5	767.7	655.0	591.2	606.1
30°	4606.4	3215.0	2147.0	1421.3	1168.6	1002.8	733.8	574.8	451.1	376.4	362.9
32.5°	3883.5	2630.7	1664.5	1050.4	851.9	722.9	496.0	360.1	290.8	283.9	275.8
35°	3196.0	2077.7	1263.7	775.9	627.8	511.0	316.6	212.0	193.0	182.1	173.9
37.5°	2524.7	1554.5	907.7	564.0	430.8	324.8	163.0	137.2	119.5	108.8	99.1
40°	1898.2	1117.0	639.9	341.1	225.6	140.0	97.9	84.2	74.7	69.3	66.5
42.5°	1342.5	743.3	396.7	144.1	107.4	88.3	67.9	59.8	54.4	51.6	49.0
45°	780.0	462.0	160.4	84.2	67.9	61.1	50.4	44.9	42.1	39.5	38.1
47.5°	487.8	186.2	82.8	54.4	47.6	43.5	36.7	35.3	32.6	31.2	31.2
50°	197.1	82.8	51.6	38.1	34.0	32.6	28.6	27.2	24.4	24.4	24.4
52.5°	74.7	49.0	35.3	27.2	24.4	23.2	20.4	20.4	19.0	19.0	19.0
55°	43.5	32.6	24.4	19.0	17.7	17.7	16.3	16.3	14.9	14.9	14.9
57.5°	28.6	21.8	17.7	13.5	13.5	13.5	12.3	12.3	12.3	12.3	12.3
60°	19.0	14.9	12.3	10.9	10.9	10.9	10.9	12.3	12.3	12.3	12.3
62.5°	13.5	12.3	10.9	10.9	10.9	10.9	10.9	12.3	12.3	12.3	13.5
65°	10.9	9.5	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5	13.5
67.5°	8.1	8.1	8.1	8.1	9.5	9.5	10.9	12.3	12.3	12.3	13.5
70°	6.8	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5
72.5°	6.8	8.1	8.1	9.5	9.5	9.5	10.9	12.3	12.3	12.3	13.5
75°	6.8	8.1	8.1	9.5	9.5	9.5	10.9	12.3	12.3	12.3	13.5
77.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5	13.5
80°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5	13.5
82.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5	13.5
85°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	13.5	13.5
87.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7
2.5°	1269.2	1206.7	1138.6	1117.0	1095.3	1053.2	1027.2	981.1	947.2	913.1	886.0
5°	1099.3	1000.2	917.2	881.9	847.9	789.4	748.7	699.8	660.5	626.4	595.2
7.5°	922.6	808.6	725.6	690.3	656.3	592.4	540.8	479.7	433.4	395.5	364.1
10°	759.6	650.8	561.2	519.0	479.7	413.1	364.1	315.3	275.8	243.2	214.8
12.5°	618.3	501.5	410.4	379.2	341.1	286.7	240.6	187.6	164.4	154.9	148.1
15°	479.7	375.0	299.0	270.4	236.4	184.8	164.4	154.9	148.1	144.1	138.6
17.5°	365.5	278.6	203.9	184.8	173.9	163.0	157.6	150.9	146.7	145.5	141.3
20°	286.7	210.6	191.6	186.2	186.2	183.4	179.3	179.3	177.9	182.1	182.1
22.5°	294.8	294.8	311.1	309.9	331.6	353.2	369.5	422.5	452.5	516.4	559.9
25°	515.0	564.0	621.0	638.7	680.8	743.3	808.6	890.0	947.2	1008.3	1032.7
27.5°	642.7	650.8	642.7	663.1	635.9	619.6	625.0	634.5	634.5	638.7	655.0
30°	380.4	399.5	417.1	430.8	423.9	417.1	414.5	394.1	394.1	385.9	379.2
32.5°	258.1	255.5	252.7	258.1	252.7	252.7	248.6	250.0	241.8	236.4	233.7
35°	176.7	168.5	159.0	160.4	154.9	153.5	149.5	149.5	144.1	141.3	140.0
37.5°	97.9	97.9	93.7	95.1	93.7	93.7	93.7	95.1	93.7	93.7	95.1
40°	66.5	66.5	65.3	66.5	65.3	66.5	67.9	67.9	67.9	67.9	66.5
42.5°	50.4	50.4	49.0	50.4	49.0	50.4	51.6	51.6	51.6	51.6	51.6
45°	39.5	39.5	39.5	39.5	39.5	39.5	39.5	40.7	40.7	39.5	39.5
47.5°	31.2	32.6	31.2	31.2	31.2	31.2	32.6	32.6	31.2	31.2	31.2
50°	25.8	25.8	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
52.5°	20.4	19.0	19.0	17.7	17.7	17.7	17.7	17.7	17.7	17.7	16.3
55°	14.9	14.9	13.5	13.5	13.5	14.9	14.9	14.9	14.9	13.5	13.5
57.5°	13.5	13.5	13.5	12.3	12.3	13.5	13.5	12.3	12.3	12.3	10.9
60°	12.3	13.5	12.3	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5
62.5°	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5	9.5
65°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	9.5	9.5
67.5°	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	10.9	10.9	9.5
70°	13.5	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	10.9	9.5
72.5°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	12.3	10.9	10.9	9.5
75°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5
77.5°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5
80°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5
82.5°	13.5	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	9.5	9.5
85°	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	9.5	9.5	8.1
87.5°	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5	8.1	8.1	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192828

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7	1422.7
2.5°	853.3	847.9	843.8	851.9	849.3	815.2	819.4	818.0
5°	559.9	547.6	538.2	542.2	531.3	516.4	505.5	502.7
7.5°	332.9	319.4	311.1	303.0	300.2	281.3	273.2	278.6
10°	183.4	164.4	163.0	159.0	153.5	149.5	146.7	148.1
12.5°	141.3	140.0	137.2	135.8	133.2	131.8	130.4	129.1
15°	134.6	133.2	131.8	130.4	129.1	127.7	126.3	126.3
17.5°	138.6	138.6	137.2	135.8	135.8	137.2	135.8	134.6
20°	180.7	180.7	183.4	187.6	187.6	191.6	197.1	193.0
22.5°	587.0	616.9	653.6	664.5	728.4	780.0	875.1	833.0
25°	1073.5	1141.4	1157.7	1180.9	1216.2	1233.9	1216.2	1239.3
27.5°	652.2	675.4	678.0	679.4	687.5	686.3	668.5	679.4
30°	379.2	387.3	384.6	383.2	380.4	365.5	362.9	368.3
32.5°	237.8	235.1	233.7	232.3	232.3	224.2	228.3	225.6
35°	135.8	140.0	138.6	137.2	133.2	131.8	131.8	130.4
37.5°	91.1	92.5	91.1	89.7	87.0	85.6	84.2	82.8
40°	65.3	66.5	65.3	63.9	62.5	61.1	59.8	58.4
42.5°	49.0	50.4	49.0	49.0	46.2	44.9	43.5	42.1
45°	38.1	36.7	36.7	36.7	35.3	34.0	32.6	32.6
47.5°	31.2	31.2	31.2	29.8	28.6	28.6	28.6	27.2
50°	23.2	24.4	23.2	23.2	21.8	20.4	20.4	19.0
52.5°	16.3	16.3	14.9	14.9	13.5	12.3	12.3	12.3
55°	12.3	12.3	12.3	10.9	10.9	9.5	9.5	9.5
57.5°	10.9	9.5	9.5	9.5	8.1	8.1	6.8	6.8
60°	9.5	8.1	8.1	6.8	6.8	5.4	5.4	5.4
62.5°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
65°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
67.5°	8.1	8.1	6.8	6.8	6.8	5.4	5.4	5.4
70°	8.1	8.1	8.1	6.8	6.8	6.8	5.4	5.4
72.5°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
75°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
77.5°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
80°	8.1	8.1	8.1	6.8	6.8	6.8	6.8	6.8
82.5°	8.1	8.1	8.1	8.1	6.8	6.8	6.8	6.8
85°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
87.5°	6.8	5.4	5.4	4.0	4.0	4.0	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)