

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192395

Luminaire Tested: **LDA6A50940D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5028.6 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42250	42250	42250
5°	111363	38482	13246
10°	225013	29959	8049
15°	414327	22458	11612
20°	642364	17962	19345
25°	754199	15932	24558
30°	817784	16021	19028
35°	862304	9543	10233
40°	884450	4065	4437
45°	828582	1605	1520
50°	579350	699	350
55°	203290	698	0
60°	40995	800	0
65°	2542	947	0
70°	497	1314	0
75°	0	1737	0
80°	0	2589	347
85°	0	5850	692

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.0
10°-20°	551.3	11.0
20°-30°	1303.2	25.9
30°-40°	1587.6	31.6
40°-50°	1180.9	23.5
50°-60°	286.0	5.7
60°-70°	10.6	0.2
70°-80°	5.1	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1953.3	38.8
0°-40°	3541.0	70.4
0°-60°	5007.9	99.6
0°-90°	5028.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5028.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	771	771	771	771	771	
5°	2024	1513	699	326	241	254
15°	7300	3164	396	182	205	2200
25°	12469	3968	263	382	406	5726
35°	12885	2898	143	155	153	8025
45°	10688	1104	21	23	20	7850
55°	2127	24	7	5	0	2406
65°	20	5	7	5	0	65
75°	0	5	8	6	0	0
85°	0	5	9	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7
2.5°	1343.9	1321.3	1319.1	1296.5	1288.2	1285.1	1253.1	1241.7	1199.3	1191.1	1131.1
5°	2023.7	1988.6	1981.4	1929.7	1891.4	1838.7	1810.9	1763.4	1663.2	1610.5	1513.4
7.5°	2879.0	2832.5	2822.2	2741.7	2662.1	2592.9	2535.0	2424.6	2240.6	2114.6	1916.2
10°	4042.2	3912.1	3864.6	3694.0	3529.8	3400.7	3333.6	3090.8	2814.0	2644.5	2367.7
12.5°	5519.4	5302.5	5213.7	4950.3	4661.0	4449.2	4319.1	3937.9	3487.5	3163.2	2767.5
15°	7300.4	7048.3	6889.3	6557.7	6031.9	5730.2	5499.8	4889.4	4232.3	3741.6	3164.1
17.5°	9239.4	9042.1	8804.5	8284.8	7437.7	7075.2	6656.9	5856.3	4955.4	4272.6	3518.5
20°	11011.0	10680.5	10501.7	9923.2	8941.9	8463.6	7948.1	6748.8	5594.9	4705.4	3790.2
22.5°	11970.8	11650.5	11543.1	11040.9	10141.2	9609.2	8953.2	7534.9	6085.5	5001.9	3934.8
25°	12468.7	12176.3	12183.6	11730.0	10918.1	10418.0	9750.7	8128.8	6420.2	5157.9	3967.9
27.5°	12858.1	12498.6	12435.6	12096.7	11374.6	10863.4	10219.7	8452.2	6543.1	5141.4	3878.0
30°	12919.0	12624.6	12670.1	12199.0	11539.9	11008.0	10338.5	8434.7	6417.2	4933.7	3644.5
32.5°	12877.7	12585.3	12689.7	12178.4	11468.6	10885.0	10140.2	8091.7	6047.4	4549.5	3301.6
35°	12885.0	12549.2	12471.7	12038.8	11193.9	10509.0	9610.3	7465.7	5500.9	4049.4	2897.7
37.5°	12731.0	12278.5	12292.0	11721.7	10662.9	9754.9	8737.3	6631.0	4854.1	3515.4	2491.7
40°	12359.1	12020.3	11912.9	11065.8	9652.5	8588.6	7607.2	5724.0	4106.3	2957.5	2015.4
42.5°	11829.2	11421.1	11106.1	9932.6	8220.8	7244.7	6396.5	4778.8	3399.7	2424.6	1565.0
45°	10687.6	10246.6	9636.1	8228.0	6778.7	5931.6	5224.0	3879.0	2749.9	1874.0	1104.4
47.5°	8768.3	8354.1	7726.0	6543.1	5412.0	4706.5	4154.8	3038.2	2010.2	1181.8	547.5
50°	6793.1	6478.1	5998.8	4972.0	4026.7	3366.6	2874.9	1908.0	1025.8	539.2	229.3
52.5°	4427.5	4204.4	3777.7	2996.9	2275.7	1784.1	1450.4	812.0	483.5	227.2	67.1
55°	2127.0	2011.3	1702.5	1234.5	893.6	733.5	619.8	393.5	182.9	54.7	23.7
57.5°	848.1	823.4	733.5	552.7	423.6	359.5	278.9	108.5	36.2	22.8	14.4
60°	373.9	362.6	303.8	201.4	108.5	62.0	45.4	26.9	17.6	13.4	9.3
62.5°	53.8	49.5	42.4	33.1	26.9	22.8	19.6	14.4	9.3	7.3	6.2
65°	19.6	19.6	17.6	14.4	12.4	11.4	10.3	7.3	5.2	5.2	5.2
67.5°	8.2	8.2	8.2	6.2	6.2	5.2	4.1	4.1	4.1	4.1	5.2
70°	3.1	3.1	3.1	2.1	2.1	2.1	3.1	3.1	3.1	4.1	5.2
72.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	5.2
75°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	5.2
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
80°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	5.2	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7
2.5°	1080.5	1066.1	1017.5	969.0	961.7	941.1	898.7	849.2	785.1	744.8	704.5
5°	1387.3	1315.0	1233.5	1139.4	1110.5	1069.1	980.3	885.3	778.9	699.3	625.0
7.5°	1745.8	1584.6	1430.8	1279.9	1223.1	1159.0	1023.7	887.3	741.7	626.1	533.0
10°	2081.6	1833.6	1595.0	1381.1	1296.5	1209.6	1027.8	852.2	671.5	538.2	443.2
12.5°	2416.2	2060.9	1734.4	1454.5	1339.8	1228.3	1005.2	789.2	584.7	457.6	381.2
15°	2679.7	2266.5	1835.7	1491.7	1349.2	1212.8	949.3	702.5	500.0	395.7	327.5
17.5°	2862.5	2384.2	1874.0	1476.2	1312.9	1159.0	861.5	601.2	431.8	347.1	281.0
20°	2988.5	2421.4	1847.1	1412.1	1235.5	1066.1	751.1	510.3	383.2	307.9	241.8
22.5°	3023.6	2385.2	1770.6	1316.1	1134.3	959.6	636.4	450.4	348.1	276.9	234.5
25°	2989.6	2293.3	1655.9	1201.4	1010.3	827.5	540.3	414.2	321.2	263.4	272.8
27.5°	2865.6	2131.1	1496.8	1053.6	857.4	684.9	475.2	370.9	283.1	277.9	289.2
30°	2661.1	1898.7	1307.8	864.7	677.7	546.5	398.7	292.4	247.9	253.1	260.3
32.5°	2366.7	1613.6	1065.0	640.5	496.8	411.2	285.1	202.5	196.2	200.4	205.5
35°	1994.7	1312.9	797.5	442.1	352.2	283.1	167.4	143.5	140.5	142.6	144.6
37.5°	1618.8	1014.4	542.4	297.5	213.9	143.5	100.2	94.0	91.9	93.0	94.0
40°	1256.1	705.5	340.8	142.6	83.7	71.2	62.0	58.9	56.8	56.8	57.9
42.5°	917.4	418.4	169.4	55.8	45.4	42.4	37.2	35.1	33.1	34.0	35.1
45°	513.4	185.9	57.9	31.0	27.9	25.8	22.8	21.7	20.7	20.7	20.7
47.5°	219.0	65.0	27.9	19.6	17.6	16.5	14.4	13.4	12.4	12.4	12.4
50°	72.3	25.8	17.6	13.4	11.4	10.3	9.3	8.2	8.2	8.2	9.3
52.5°	25.8	16.5	11.4	9.3	8.2	8.2	7.3	7.3	7.3	7.3	7.3
55°	15.5	11.4	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
57.5°	10.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3
60°	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3
62.5°	6.2	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
65°	5.2	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
67.5°	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2
70°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2
72.5°	5.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2
75°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
77.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	8.2
80°	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	8.2	9.3
82.5°	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	8.2	9.3
85°	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.3	9.3
87.5°	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7
2.5°	663.2	632.2	588.9	574.4	544.4	522.7	498.9	472.1	466.9	440.0	437.0
5°	552.7	503.1	453.5	434.9	409.0	387.3	363.6	337.8	326.4	300.6	285.1
7.5°	455.5	408.1	363.6	345.1	320.2	292.4	264.4	237.6	222.1	197.3	184.9
10°	382.2	334.7	287.2	268.5	245.9	214.9	184.9	157.0	146.7	140.5	141.6
12.5°	319.3	271.7	224.2	203.5	179.7	154.9	153.9	151.9	156.0	154.9	156.0
15°	267.6	216.9	171.5	165.3	165.3	169.4	173.6	174.5	181.8	181.8	183.9
17.5°	220.1	184.9	187.0	187.0	191.1	198.4	206.6	210.7	222.1	223.1	227.2
20°	204.6	212.8	222.1	224.2	231.3	242.7	254.1	262.4	276.9	281.0	289.2
22.5°	242.7	257.3	271.7	275.8	285.1	301.6	322.3	329.6	347.1	347.1	358.5
25°	286.2	307.9	322.3	327.5	337.8	352.2	365.7	369.8	382.2	378.1	382.2
27.5°	303.8	319.3	328.5	333.7	335.7	348.1	354.3	352.2	360.6	354.3	354.3
30°	269.6	281.0	286.2	289.2	289.2	298.6	298.6	295.4	300.6	295.4	292.4
32.5°	211.7	220.1	224.2	224.2	223.1	229.3	227.2	223.1	225.2	222.1	214.9
35°	147.8	153.9	157.0	156.0	154.9	160.1	157.0	153.9	154.9	152.9	147.8
37.5°	97.1	98.1	100.2	102.2	101.3	105.4	103.3	101.3	102.2	100.2	97.1
40°	58.9	60.9	63.0	63.0	63.0	64.1	64.1	63.0	65.0	63.0	60.9
42.5°	35.1	37.2	37.2	37.2	38.3	38.3	39.2	37.2	39.2	37.2	36.2
45°	21.7	21.7	21.7	22.8	21.7	22.8	22.8	21.7	22.8	21.7	20.7
47.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	12.4	13.4	12.4	11.4
50°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	6.2
52.5°	7.3	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1
55°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	5.2	5.2	4.1	3.1
57.5°	7.3	7.3	6.2	6.2	6.2	6.2	5.2	5.2	4.1	3.1	3.1
60°	7.3	7.3	7.3	6.2	6.2	6.2	5.2	5.2	4.1	3.1	3.1
62.5°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	5.2	4.1	3.1	3.1
65°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	3.1
67.5°	8.2	7.3	7.3	7.3	7.3	7.3	6.2	5.2	5.2	4.1	3.1
70°	8.2	8.2	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	3.1
72.5°	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2	5.2	4.1	4.1
75°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	6.2	5.2	4.1
77.5°	9.3	8.2	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2	4.1
80°	9.3	9.3	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2	4.1
82.5°	9.3	9.3	8.2	8.2	8.2	8.2	7.3	7.3	6.2	5.2	4.1
85°	9.3	9.3	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2	4.1
87.5°	9.3	9.3	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192395

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	770.7	770.7	770.7	770.7	770.7	770.7	770.7	770.7
2.5°	418.4	416.3	409.0	411.2	406.0	394.6	395.7	391.6
5°	274.8	268.5	261.4	261.4	254.1	243.8	243.8	240.7
7.5°	167.4	158.1	150.8	149.8	142.6	137.4	137.4	136.4
10°	141.6	142.6	142.6	143.5	142.6	142.6	143.5	144.6
12.5°	159.0	162.2	162.2	163.3	162.2	164.2	164.2	166.3
15°	190.0	195.2	196.2	198.4	197.3	200.4	202.5	204.6
17.5°	238.6	244.8	247.0	253.1	252.1	255.2	257.3	261.4
20°	300.6	309.9	313.0	321.2	320.2	323.4	328.5	331.6
22.5°	369.8	381.2	382.2	389.4	388.4	391.6	393.5	394.6
25°	388.4	395.7	394.6	398.7	398.7	399.8	399.8	406.0
27.5°	355.4	360.6	360.6	360.6	361.5	362.6	362.6	367.7
30°	292.4	294.4	295.4	292.4	294.4	295.4	295.4	300.6
32.5°	216.9	218.0	219.0	214.9	218.0	218.0	218.0	222.1
35°	149.8	149.8	150.8	147.8	149.8	150.8	149.8	152.9
37.5°	98.1	98.1	98.1	98.1	98.1	98.1	97.1	100.2
40°	60.9	62.0	60.9	60.9	59.9	59.9	59.9	62.0
42.5°	36.2	36.2	35.1	35.1	35.1	35.1	36.2	36.2
45°	20.7	20.7	19.6	19.6	18.5	19.6	19.6	19.6
47.5°	11.4	10.3	10.3	10.3	9.3	9.3	9.3	10.3
50°	5.2	5.2	5.2	4.1	4.1	4.1	3.1	4.1
52.5°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	1.1
55°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
57.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.1	3.1	2.1	2.1	1.1	1.1	1.1	1.1
80°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
85°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
87.5°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)