

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192834

Luminaire Tested: **LDA6A75950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6552.5 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		76	72	68
5	86	76	69	64	84	75	68	63		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	51	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	61	50	43	38		49	43	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	102251	102251	102251
5°	199922	97199	35461
10°	336511	83465	7860
15°	512460	63196	12917
20°	740530	51198	144008
25°	1102098	82825	41627
30°	1272943	28359	8223
35°	1273345	6338	4450
40°	1040771	3542	2734
45°	788121	2303	1760
50°	523386	1569	1194
55°	84145	1338	946
60°	5263	1403	778
65°	1660	1816	921
70°	898	2052	1138
75°	572	2393	1504
80°	474	3567	2241
85°	943	7108	2642



TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	3.0
10°-20°	832.5	12.7
20°-30°	1959.8	29.9
30°-40°	2064.9	31.5
40°-50°	1287.6	19.6
50°-60°	185.0	2.8
60°-70°	11.8	0.2
70°-80°	9.2	0.1
80°-90°	6.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2987.1	45.6
0°-40°	5052.0	77.1
0°-60°	6524.6	99.6
0°-90°	6552.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6552.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1865	1865	1865	1865	1865	
5°	3633	2941	1766	917	644	421
15°	9030	5111	1114	194	228	2689
25°	18220	6127	1369	991	688	8199
35°	19027	4488	95	88	66	11477
45°	10166	1242	30	32	23	7956
55°	880	23	14	16	10	1582
65°	13	10	14	11	7	19
75°	3	7	11	11	7	3
85°	2	7	11	8	4	1
90°	0	0	0	0	0	

TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2
2.5°	2722.9	2704.7	2710.3	2667.8	2611.4	2636.8	2573.2	2574.6	2535.0	2434.7	2391.0
5°	3633.0	3630.1	3626.0	3548.2	3448.0	3459.2	3365.9	3330.6	3228.8	3052.2	2940.7
7.5°	4763.5	4764.9	4743.6	4554.4	4442.8	4435.6	4288.8	4182.7	3993.3	3715.0	3511.5
10°	6045.2	6084.8	6046.5	5755.4	5547.8	5550.6	5286.4	5082.9	4779.1	4373.4	4083.8
12.5°	7550.0	7555.7	7496.3	7113.5	6796.9	6772.8	6418.2	6029.7	5567.4	5037.7	4616.5
15°	9029.5	9069.1	8992.8	8520.8	8080.0	8013.5	7561.3	7048.4	6474.7	5690.5	5111.1
17.5°	10670.1	10608.0	10405.8	9730.4	9200.5	9103.0	8616.8	7945.7	7213.6	6265.6	5505.3
20°	12693.7	12714.8	12286.8	11277.8	10381.9	10001.8	9437.9	8703.1	7790.3	6688.1	5768.2
22.5°	15584.9	15470.3	14551.8	12919.8	11573.0	11065.9	10261.8	9248.6	8221.2	7008.9	5964.5
25°	18220.3	17919.2	17072.7	14827.4	12719.1	12091.7	11259.4	9713.5	8578.8	7246.2	6127.2
27.5°	19733.7	19599.3	18639.8	16374.7	13644.7	12761.4	11590.0	10055.4	8790.8	7363.5	6173.6
30°	20109.4	20133.5	19279.9	16887.7	13863.6	12854.8	11643.8	10045.6	8648.0	7154.4	5905.2
32.5°	20013.4	19883.4	18816.5	16321.0	13280.1	12361.5	11118.1	9596.3	8080.0	6531.2	5236.9
35°	19027.0	18836.4	17523.5	14847.2	12289.5	11396.4	10268.8	8860.0	7287.2	5737.2	4488.0
37.5°	17150.5	16930.1	15415.2	13078.0	11101.1	10345.1	9370.2	8040.3	6486.1	4996.6	3829.4
40°	14543.5	14269.3	13003.2	11382.3	9823.6	9295.2	8471.4	7105.0	5655.2	4295.8	3221.9
42.5°	12105.9	11974.4	11214.2	9823.6	8773.8	8263.7	7432.9	6161.1	4827.1	3579.4	2385.3
45°	10165.7	10078.0	9573.6	8690.4	7625.0	7147.3	6364.6	5123.8	3672.7	2410.7	1242.1
47.5°	8898.0	8674.8	8181.8	7254.7	6070.6	5475.6	4729.6	3375.9	2071.7	1068.3	381.6
50°	6136.9	6158.2	5601.3	4579.7	3572.3	3069.1	2535.0	1553.0	685.3	233.2	66.5
52.5°	3231.7	2992.8	2601.5	1943.0	1352.3	1031.6	753.2	311.0	124.3	46.7	35.4
55°	880.4	773.0	617.6	436.7	236.0	165.4	108.8	57.8	41.1	32.4	22.7
57.5°	86.1	82.0	74.9	60.7	52.4	48.0	43.8	35.4	28.3	19.8	14.0
60°	48.0	46.7	43.8	38.2	33.9	31.0	28.3	24.1	17.0	12.8	11.3
62.5°	26.8	25.4	24.1	21.2	18.4	17.0	17.0	14.0	11.3	9.9	9.9
65°	12.8	12.8	12.8	12.8	12.8	11.3	9.9	9.9	9.9	9.9	9.9
67.5°	9.9	9.9	9.9	8.4	8.4	8.4	8.4	8.4	8.4	7.1	8.4
70°	5.6	5.6	7.1	5.6	5.6	5.6	5.6	5.6	5.6	5.6	7.1
72.5°	2.7	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.6	5.6	7.1
75°	2.7	2.7	2.7	2.7	4.2	4.2	4.2	4.2	5.6	5.6	7.1
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	4.2	4.2	5.6	5.6	7.1
80°	1.5	1.5	1.5	2.7	2.7	2.7	2.7	4.2	5.6	5.6	7.1
82.5°	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
85°	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1
87.5°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2
2.5°	2345.7	2276.4	2207.2	2138.0	2135.1	2094.2	2033.5	1952.8	1886.5	1830.0	1774.9
5°	2829.0	2686.2	2543.5	2400.8	2358.5	2285.0	2153.5	2005.2	1878.0	1766.3	1659.0
7.5°	3313.6	3073.5	2847.4	2624.0	2535.0	2423.5	2218.5	2003.8	1820.0	1656.1	1496.5
10°	3746.0	3397.1	3079.1	2765.5	2636.8	2491.2	2215.6	1943.0	1709.8	1499.4	1295.8
12.5°	4144.5	3658.4	3255.6	2860.0	2684.8	2508.2	2171.8	1846.8	1568.5	1317.1	1082.3
15°	4495.0	3898.8	3380.1	2902.5	2687.7	2475.7	2080.0	1714.1	1401.7	1113.5	859.1
17.5°	4745.1	4018.8	3421.0	2864.4	2614.1	2376.8	1944.4	1553.0	1216.7	915.7	669.8
20°	4897.7	4068.3	3399.8	2793.5	2528.0	2282.1	1844.0	1463.9	1137.4	877.6	710.8
22.5°	4998.0	4116.2	3408.4	2792.3	2526.6	2294.9	1886.5	1530.4	1264.6	1124.9	1105.0
25°	5105.4	4184.1	3470.5	2855.8	2608.5	2393.8	1998.0	1650.5	1428.5	1369.3	1377.8
27.5°	5099.7	4154.4	3411.1	2800.7	2540.6	2323.2	1859.6	1420.1	1212.4	1045.7	984.9
30°	4796.1	3811.1	3007.1	2323.2	2016.6	1749.4	1138.9	740.4	511.5	448.0	384.3
32.5°	4085.2	3087.6	2248.3	1606.7	1261.9	942.6	448.0	237.4	202.1	169.5	154.0
35°	3397.1	2461.6	1681.5	970.8	613.4	380.1	161.1	106.0	100.4	94.7	94.7
37.5°	2807.8	1933.2	1086.7	409.9	224.6	137.1	77.7	70.6	67.9	66.5	66.5
40°	2196.0	1260.5	470.6	135.6	72.1	62.2	55.1	52.4	51.0	49.5	51.0
42.5°	1295.8	507.3	137.1	51.0	48.0	45.2	41.1	39.6	39.6	38.2	39.6
45°	440.9	131.4	45.2	36.7	33.9	33.9	31.0	31.0	31.0	29.7	32.4
47.5°	114.4	41.1	29.7	26.8	25.4	25.4	24.1	24.1	24.1	24.1	25.4
50°	39.6	26.8	21.2	19.8	18.4	19.8	18.4	18.4	18.4	18.4	19.8
52.5°	24.1	18.4	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5
55°	15.5	14.0	12.8	12.8	12.8	12.8	12.8	14.0	14.0	14.0	14.0
57.5°	12.8	11.3	11.3	11.3	11.3	11.3	12.8	11.3	11.3	12.8	14.0
60°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.8	12.8	14.0
62.5°	9.9	11.3	11.3	11.3	11.3	11.3	11.3	12.8	12.8	12.8	14.0
65°	9.9	9.9	9.9	11.3	11.3	11.3	12.8	12.8	12.8	14.0	14.0
67.5°	8.4	8.4	9.9	9.9	11.3	11.3	11.3	12.8	12.8	12.8	14.0
70°	8.4	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	12.8	12.8
72.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	11.3	12.8
75°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	12.8
77.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	11.3	12.8
80°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
82.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
85°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3
87.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2
2.5°	1698.4	1674.5	1589.6	1578.4	1564.3	1495.0	1466.8	1418.7	1351.0	1331.1	1307.2
5°	1533.1	1454.1	1329.6	1295.8	1259.0	1150.2	1083.8	1004.6	917.1	869.0	823.8
7.5°	1322.7	1212.4	1047.2	980.7	939.6	821.0	715.0	609.0	480.5	407.0	360.4
10°	1088.0	936.9	764.5	688.2	633.0	460.6	360.4	313.7	269.9	234.5	203.5
12.5°	852.1	681.1	486.2	398.5	354.7	294.0	238.9	180.9	161.1	159.6	154.0
15°	624.6	433.8	327.8	295.3	264.3	189.4	187.9	187.9	193.6	197.8	199.3
17.5°	460.6	381.6	299.6	279.8	294.0	305.3	325.0	354.7	378.7	446.6	432.3
20°	675.4	669.8	730.5	808.3	863.4	980.7	1129.0	1297.2	1472.3	1667.4	1815.7
22.5°	1158.7	1300.1	1410.2	1503.5	1553.0	1685.8	1803.0	1861.1	1895.0	1878.0	1853.9
25°	1416.0	1466.8	1432.9	1400.5	1404.6	1284.5	1196.9	1085.2	990.6	904.4	853.5
27.5°	846.4	774.3	672.7	602.1	587.8	507.3	448.0	385.7	367.3	311.0	286.8
30°	305.3	283.9	251.5	226.1	223.2	202.1	189.4	175.2	173.8	161.1	154.0
32.5°	138.5	138.5	127.2	129.9	127.2	123.0	121.6	117.3	117.3	112.9	110.2
35°	90.5	91.8	90.5	90.5	89.0	89.0	89.0	86.1	87.6	84.9	80.5
37.5°	66.5	67.9	65.0	66.5	66.5	66.5	66.5	65.0	63.5	60.7	59.3
40°	51.0	51.0	51.0	51.0	51.0	51.0	51.0	49.5	49.5	48.0	45.2
42.5°	39.6	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1	39.6	39.6
45°	32.4	33.9	32.4	33.9	33.9	33.9	32.4	32.4	32.4	31.0	29.7
47.5°	25.4	25.4	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	22.7
50°	19.8	19.8	19.8	19.8	19.8	19.8	21.2	19.8	19.8	19.8	19.8
52.5°	15.5	17.0	17.0	18.4	18.4	18.4	18.4	18.4	17.0	17.0	15.5
55°	14.0	15.5	15.5	17.0	17.0	17.0	17.0	15.5	15.5	15.5	14.0
57.5°	14.0	15.5	15.5	15.5	15.5	15.5	15.5	14.0	14.0	12.8	12.8
60°	14.0	14.0	14.0	15.5	15.5	14.0	14.0	12.8	12.8	11.3	11.3
62.5°	14.0	14.0	14.0	15.5	15.5	14.0	14.0	12.8	11.3	11.3	9.9
65°	14.0	15.5	14.0	15.5	15.5	14.0	14.0	12.8	11.3	11.3	9.9
67.5°	14.0	15.5	15.5	15.5	14.0	14.0	14.0	12.8	11.3	11.3	9.9
70°	12.8	14.0	14.0	14.0	14.0	14.0	12.8	12.8	11.3	11.3	9.9
72.5°	12.8	14.0	12.8	14.0	14.0	12.8	12.8	12.8	11.3	11.3	9.9
75°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	9.9
77.5°	12.8	12.8	12.8	12.8	12.8	12.8	11.3	11.3	11.3	9.9	9.9
80°	12.8	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	9.9	8.4
82.5°	11.3	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	9.9	8.4
85°	11.3	11.3	11.3	11.3	11.3	11.3	9.9	9.9	8.4	7.1	7.1
87.5°	9.9	11.3	9.9	9.9	9.9	9.9	8.4	7.1	5.6	5.6	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192834

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2	1865.2
2.5°	1268.9	1233.6	1235.1	1240.7	1205.4	1187.0	1182.7	1164.3
5°	763.0	722.1	715.0	709.4	659.9	640.1	624.6	644.4
7.5°	327.8	312.2	309.5	305.3	282.7	271.3	265.7	271.3
10°	162.4	152.6	154.0	155.5	148.4	144.1	142.7	141.2
12.5°	161.1	159.6	161.1	161.1	162.4	159.6	161.1	161.1
15°	209.1	209.1	213.3	216.2	223.2	221.9	224.6	227.6
17.5°	521.4	494.5	508.8	508.8	572.3	515.7	563.9	520.1
20°	2049.0	2145.0	2242.7	2324.6	2407.9	2433.3	2482.8	2468.5
22.5°	1817.2	1828.5	1814.3	1798.8	1794.6	1798.8	1722.6	1733.9
25°	780.0	774.3	751.7	727.8	734.8	740.4	713.5	688.2
27.5°	267.0	260.0	252.9	247.3	244.5	240.1	231.7	226.1
30°	151.3	147.0	144.1	142.7	140.0	137.1	132.8	129.9
32.5°	108.8	106.0	104.5	103.1	100.4	97.4	93.3	91.8
35°	80.5	77.7	76.3	74.9	72.1	69.2	67.9	66.5
37.5°	59.3	56.6	56.6	56.6	52.4	49.5	48.0	46.7
40°	45.2	43.8	43.8	43.8	41.1	39.6	38.2	38.2
42.5°	39.6	38.2	38.2	38.2	35.4	33.9	33.9	32.4
45°	29.7	28.3	28.3	26.8	25.4	25.4	24.1	22.7
47.5°	22.7	21.2	21.2	21.2	19.8	18.4	18.4	17.0
50°	18.4	18.4	17.0	18.4	15.5	15.5	15.5	14.0
52.5°	15.5	15.5	14.0	14.0	12.8	12.8	12.8	11.3
55°	14.0	12.8	12.8	12.8	11.3	11.3	11.3	9.9
57.5°	11.3	11.3	9.9	9.9	8.4	8.4	8.4	8.4
60°	9.9	9.9	8.4	8.4	7.1	7.1	7.1	7.1
62.5°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
65°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
67.5°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
70°	9.9	9.9	8.4	8.4	8.4	7.1	7.1	7.1
72.5°	9.9	9.9	8.4	8.4	8.4	8.4	7.1	7.1
75°	8.4	8.4	8.4	8.4	7.1	7.1	7.1	7.1
77.5°	8.4	8.4	8.4	8.4	7.1	7.1	7.1	7.1
80°	8.4	8.4	7.1	7.1	7.1	7.1	7.1	7.1
82.5°	8.4	7.1	7.1	7.1	7.1	5.6	5.6	5.6
85°	5.6	5.6	5.6	5.6	4.2	4.2	4.2	4.2
87.5°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)