

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192400

Luminaire Tested: **LDA6A50940D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3773.5 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79
4	90	80	72	67	87	78	72	66	76	70	66		74	69	65		72
5	83	72	65	59	81	71	64	59	69	63	58		67	62	57		66
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60
7	72	60	52	47	70	59	52	46	58	51	46		56	50	46		55
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		51
9	63	50	43	38	61	50	43	38	49	42	37		48	42	37		47
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62298	62298	62298
5°	99037	61396	39682
10°	147398	59006	26803
15°	209439	56169	20170
20°	274167	53642	20611
25°	326450	54239	35621
30°	362037	52318	33543
35°	369335	44591	24681
40°	353026	34379	18263
45°	307885	24755	13777
50°	234730	17978	9160
55°	131025	12931	5333
60°	60269	8947	2149
65°	28408	4825	947
70°	13897	2308	994
75°	6566	1546	1101
80°	3252	1642	1294
85°	1950	2579	1321

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.1	3.1
10°-20°	428.7	11.4
20°-30°	857.5	22.7
30°-40°	1053.0	27.9
40°-50°	843.5	22.4
50°-60°	371.0	9.8
60°-70°	83.7	2.2
70°-80°	15.2	0.4
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1403.3	37.2
0°-40°	2456.3	65.1
0°-60°	3670.8	97.3
0°-90°	3773.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3773.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1136	1136	1136	1136	1136	
5°	1800	1549	1116	826	721	198
15°	3690	2489	990	461	355	1076
25°	5397	3075	897	558	589	2483
35°	5519	2771	666	402	369	3417
45°	3971	1830	319	195	178	3019
55°	1371	678	135	78	56	1303
65°	219	138	37	12	7	251
75°	31	18	7	6	5	39
85°	3	3	4	4	2	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4
2.5°	1449.4	1412.2	1442.3	1416.4	1408.1	1405.1	1392.6	1384.4	1381.2	1352.4	1329.6
5°	1799.7	1756.2	1787.2	1749.1	1729.5	1719.1	1697.4	1670.6	1648.8	1594.0	1548.6
7.5°	2209.8	2163.3	2192.3	2137.5	2100.3	2081.7	2046.6	1995.0	1946.4	1858.6	1782.1
10°	2647.9	2609.6	2634.4	2558.0	2500.1	2470.2	2418.4	2352.4	2253.2	2125.1	2012.5
12.5°	3158.2	3103.4	3123.0	3020.8	2938.2	2895.8	2822.4	2719.2	2578.7	2404.0	2250.1
15°	3690.3	3638.6	3651.0	3520.8	3406.1	3347.2	3252.3	3105.5	2919.5	2691.2	2488.8
17.5°	4235.7	4165.5	4163.4	4008.5	3855.5	3781.1	3662.4	3469.2	3251.2	2951.6	2701.5
20°	4699.6	4638.7	4622.1	4461.0	4252.3	4165.5	4021.9	3782.2	3514.6	3167.5	2874.1
22.5°	5097.3	5027.2	4997.1	4808.0	4571.5	4470.2	4306.0	4015.6	3718.1	3325.6	2995.0
25°	5397.0	5339.1	5295.7	5082.9	4818.5	4704.7	4525.0	4211.0	3865.9	3436.1	3074.6
27.5°	5634.6	5557.1	5502.3	5269.9	4972.3	4852.5	4659.3	4318.3	3941.3	3480.5	3098.3
30°	5719.3	5641.8	5578.8	5330.8	5015.8	4884.5	4682.1	4320.5	3920.7	3447.4	3046.6
32.5°	5679.0	5598.4	5527.2	5267.8	4941.4	4803.9	4597.3	4230.6	3812.1	3336.9	2931.9
35°	5518.8	5454.9	5374.2	5112.8	4790.5	4640.8	4435.1	4059.1	3643.8	3164.5	2770.8
37.5°	5292.7	5193.5	5119.1	4862.8	4550.9	4397.9	4200.6	3839.0	3418.6	2957.8	2576.5
40°	4933.1	4832.9	4758.5	4511.5	4228.6	4074.6	3892.8	3547.7	3141.7	2712.9	2349.3
42.5°	4484.7	4391.7	4319.4	4090.1	3840.1	3690.3	3530.1	3210.9	2833.8	2441.2	2100.3
45°	3971.3	3881.4	3819.4	3620.0	3397.9	3265.6	3121.0	2839.0	2493.9	2137.5	1829.6
47.5°	3414.5	3322.4	3269.7	3091.1	2903.1	2783.2	2659.2	2415.4	2106.5	1800.7	1533.1
50°	2752.3	2663.4	2615.9	2466.0	2332.8	2222.2	2132.3	1937.1	1683.9	1443.2	1225.2
52.5°	2015.6	1946.4	1911.3	1807.9	1728.4	1645.8	1587.9	1451.5	1266.6	1096.1	931.8
55°	1370.9	1314.1	1297.5	1233.6	1190.2	1145.7	1104.4	1024.9	899.9	787.2	677.7
57.5°	857.5	851.3	862.7	805.9	786.2	767.6	735.6	691.2	612.7	542.4	476.3
60°	549.7	543.4	538.3	517.6	508.3	494.8	479.3	453.5	404.9	363.6	320.3
62.5°	348.1	344.0	349.2	336.7	324.4	324.4	307.9	293.4	263.5	238.6	207.6
65°	219.0	218.0	221.1	212.8	206.6	203.5	195.3	187.0	168.4	152.9	138.4
67.5°	138.4	137.4	139.4	137.4	130.2	128.1	122.9	117.7	105.4	96.1	85.8
70°	86.7	85.8	86.7	84.7	80.6	78.5	75.5	71.2	67.1	56.8	51.6
72.5°	52.7	51.6	52.7	51.6	48.6	48.6	44.4	42.4	39.2	33.1	28.9
75°	31.0	31.0	31.0	29.9	27.9	27.9	25.8	24.8	22.8	19.6	17.6
77.5°	17.6	17.6	17.6	17.6	16.5	16.5	15.5	14.4	13.4	11.4	11.4
80°	10.3	10.3	10.3	10.3	9.3	10.3	9.3	9.3	8.2	7.3	7.3
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
85°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
87.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4
2.5°	1311.0	1277.9	1271.7	1236.6	1230.4	1210.8	1200.5	1181.8	1144.7	1125.0	1101.3
5°	1493.9	1442.3	1412.2	1349.2	1329.6	1296.6	1262.5	1217.0	1158.1	1115.7	1071.4
7.5°	1694.3	1609.6	1546.6	1453.5	1419.5	1370.9	1311.0	1239.7	1157.1	1094.0	1031.0
10°	1895.8	1763.5	1666.4	1541.4	1491.8	1427.7	1341.0	1244.8	1141.6	1060.0	981.5
12.5°	2080.7	1915.4	1782.1	1623.0	1556.9	1478.4	1364.7	1244.8	1122.0	1024.9	932.9
15°	2282.2	2064.1	1890.6	1696.4	1614.8	1521.7	1382.3	1240.7	1100.2	989.7	888.5
17.5°	2446.4	2187.1	1974.3	1748.0	1651.0	1544.5	1384.4	1224.2	1072.3	951.5	846.1
20°	2567.3	2280.1	2031.1	1777.9	1668.4	1552.7	1376.1	1202.6	1043.4	919.5	812.0
22.5°	2655.1	2335.8	2060.0	1788.3	1669.5	1548.6	1361.6	1183.9	1023.8	902.9	800.7
25°	2707.8	2363.8	2069.3	1784.2	1661.3	1535.2	1345.1	1167.4	1011.4	896.7	802.7
27.5°	2712.9	2352.4	2044.5	1753.2	1627.1	1501.1	1311.0	1135.3	984.5	879.1	789.3
30°	2654.0	2288.3	1979.5	1685.0	1557.9	1433.9	1247.0	1074.4	930.9	826.5	744.8
32.5°	2540.4	2175.7	1870.0	1581.7	1456.7	1335.8	1154.0	991.8	851.3	755.2	674.7
35°	2389.6	2033.1	1728.4	1457.8	1335.8	1221.1	1044.5	885.3	757.3	666.3	593.0
37.5°	2210.8	1866.8	1581.7	1320.3	1202.6	1096.1	925.7	781.0	658.1	574.4	507.3
40°	2007.3	1678.8	1411.3	1163.3	1057.9	954.6	799.7	667.4	552.7	480.4	423.6
42.5°	1787.2	1479.4	1232.5	1002.1	906.0	812.0	671.5	551.6	452.5	393.7	349.2
45°	1545.6	1268.7	1046.5	845.1	753.2	675.7	543.4	444.3	368.8	319.3	288.3
47.5°	1287.2	1046.5	853.3	679.8	599.2	533.1	424.7	350.2	296.5	262.4	236.6
50°	1027.9	827.5	666.3	516.6	455.6	399.8	328.5	277.9	236.6	210.8	194.3
52.5°	785.2	623.0	495.9	379.1	337.8	299.7	253.1	219.0	188.0	169.5	157.0
55°	569.3	449.4	353.3	277.9	250.0	228.3	194.3	169.5	149.8	135.3	125.0
57.5°	396.7	310.9	247.0	202.5	185.9	170.4	146.7	130.2	116.8	106.5	98.1
60°	268.7	210.8	172.5	146.7	136.4	126.1	110.6	99.2	88.9	81.6	73.4
62.5°	176.6	144.6	122.9	107.4	98.1	91.0	81.6	72.3	64.1	57.9	50.6
65°	114.7	95.1	84.7	72.3	68.2	63.0	54.8	49.5	42.4	37.2	32.0
67.5°	72.3	62.0	54.8	47.5	44.4	40.3	36.2	31.0	26.9	22.8	19.6
70°	43.4	38.3	33.1	28.9	26.9	24.8	21.7	18.5	15.5	14.4	12.4
72.5°	25.8	22.8	19.6	17.6	16.5	15.5	13.4	11.4	10.3	9.3	8.2
75°	15.5	14.4	12.4	10.3	10.3	9.3	9.3	8.2	7.3	7.3	6.2
77.5°	10.3	9.3	8.2	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2
80°	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.2	5.2
85°	3.1	3.1	3.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
87.5°	3.1	3.1	3.1	3.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4
2.5°	1091.0	1060.0	1047.5	1029.0	1010.3	1009.4	987.7	976.3	968.0	953.5	939.1
5°	1041.3	993.9	964.9	940.1	916.3	899.9	867.8	846.1	826.5	805.9	779.0
7.5°	983.5	922.5	881.2	850.2	822.3	796.5	757.3	728.3	703.5	683.9	650.8
10°	921.5	851.3	799.7	765.5	736.6	699.4	661.2	629.1	602.4	580.6	548.6
12.5°	863.6	786.2	728.3	693.2	663.3	623.0	583.7	550.6	521.7	501.1	472.2
15°	810.0	728.3	666.3	631.2	600.2	560.0	520.7	487.7	460.8	439.1	413.3
17.5°	762.4	676.6	615.7	583.7	551.6	514.4	475.2	444.3	417.4	397.8	377.1
20°	730.4	648.8	589.9	560.0	532.0	497.0	466.0	441.1	415.3	399.8	387.4
22.5°	725.2	652.9	602.4	577.5	555.8	529.9	511.4	498.9	481.5	474.2	474.2
25°	735.6	673.6	633.3	613.6	596.1	581.7	572.3	564.1	557.9	558.9	558.9
27.5°	729.3	673.6	640.5	622.0	606.5	597.2	587.8	582.6	576.5	579.6	579.6
30°	689.1	635.3	607.5	587.8	573.4	565.1	551.6	545.4	538.3	539.3	536.2
32.5°	622.0	571.4	544.5	525.8	510.3	502.1	487.7	480.4	471.1	471.1	464.9
35°	543.4	495.9	471.1	454.6	440.1	431.8	418.4	411.2	401.9	396.7	393.7
37.5°	460.8	419.5	396.7	384.3	373.0	364.7	352.2	347.1	337.8	333.7	329.6
40°	384.3	354.3	332.6	322.3	313.0	305.8	294.5	290.3	282.0	279.0	274.8
42.5°	318.2	295.4	277.9	269.6	259.3	255.2	247.0	242.7	235.6	232.4	228.3
45°	265.5	247.0	232.4	225.2	219.0	213.9	205.6	202.5	195.3	192.1	190.1
47.5°	219.0	204.6	193.2	187.0	183.9	177.7	170.4	167.4	162.2	159.2	156.0
50°	179.8	168.4	159.2	153.9	151.9	145.7	139.4	137.4	132.3	130.2	127.1
52.5°	146.7	137.4	129.1	125.0	120.9	116.8	111.6	109.5	104.3	101.3	97.1
55°	117.7	108.5	101.3	98.1	96.1	89.9	84.7	81.6	77.5	72.3	69.2
57.5°	91.0	82.6	76.4	72.3	71.2	65.1	60.9	55.8	50.6	47.5	44.4
60°	67.1	60.0	53.8	49.5	48.6	42.4	37.2	34.0	29.9	27.9	26.9
62.5°	44.4	39.2	34.0	32.0	29.9	25.8	22.8	20.7	18.5	17.6	16.5
65°	27.9	23.7	20.7	19.6	17.6	15.5	14.4	13.4	12.4	11.4	10.3
67.5°	16.5	14.4	12.4	12.4	11.4	10.3	10.3	9.3	8.2	8.2	8.2
70°	10.3	9.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3
72.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	6.2	6.2
75°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
77.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
80°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1
85°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	3.1
87.5°	4.1	4.1	4.1	4.1	4.1	3.1	3.1	3.1	3.1	3.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192400

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4	1136.4
2.5°	927.7	910.2	908.1	904.0	899.9	905.1	901.9	893.7
5°	769.6	748.0	743.8	737.7	731.5	733.5	728.3	721.1
7.5°	637.4	614.7	610.6	603.3	597.2	596.1	591.0	583.7
10°	529.9	512.4	508.3	501.1	493.8	492.8	486.6	481.5
12.5°	453.5	437.0	432.9	425.6	419.5	417.4	412.2	408.1
15°	396.7	381.2	377.1	370.9	363.6	363.6	359.5	355.4
17.5°	361.6	348.1	343.0	337.8	331.6	330.6	328.5	325.5
20°	376.1	363.6	361.6	355.4	356.5	356.5	354.3	353.3
22.5°	469.0	464.9	473.1	467.0	478.3	482.5	484.5	484.5
25°	563.0	564.1	572.3	569.3	579.6	587.8	592.0	588.9
27.5°	579.6	580.6	583.7	582.6	591.0	596.1	599.2	592.0
30°	532.0	531.0	529.9	529.0	534.2	536.2	537.2	529.9
32.5°	458.7	455.6	456.6	451.4	453.5	453.5	457.6	447.3
35°	385.3	381.2	381.2	376.1	376.1	376.1	379.1	368.8
37.5°	323.4	319.3	318.2	313.0	312.0	310.0	313.0	303.8
40°	269.6	265.5	266.6	260.3	261.4	260.3	260.3	255.2
42.5°	223.1	220.1	219.0	216.9	218.0	218.0	221.1	216.9
45°	185.0	181.8	180.8	179.8	180.8	180.8	181.8	177.7
47.5°	153.9	149.8	148.7	146.7	146.7	143.5	143.5	139.4
50°	123.9	117.7	116.8	113.6	112.6	110.6	110.6	107.4
52.5°	94.0	88.9	86.7	84.7	83.7	81.6	81.6	79.6
55°	66.1	60.9	60.0	58.9	57.9	56.8	57.9	55.8
57.5°	41.3	39.2	38.3	37.2	36.2	35.1	35.1	34.0
60°	24.8	22.8	22.8	21.7	20.7	19.6	19.6	19.6
62.5°	15.5	14.4	14.4	13.4	13.4	12.4	12.4	12.4
65°	10.3	9.3	9.3	8.2	8.2	7.3	7.3	7.3
67.5°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
70°	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2
72.5°	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
75°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
77.5°	5.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
80°	5.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1
82.5°	4.1	4.1	4.1	4.1	4.1	3.1	3.1	3.1
85°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.1
87.5°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)