

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192848

Luminaire Tested: **LDA6A75950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6163.9 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	109081	109081	109081
5°	175297	106928	68209
10°	259214	102431	45780
15°	353237	96890	34007
20°	436879	91428	32238
25°	506146	90011	52914
30°	552224	86235	52964
35°	567561	74519	41425
40°	552693	58660	32253
45°	501145	43392	25421
50°	394853	32067	17236
55°	235423	22833	9854
60°	120385	15185	3717
65°	57568	8068	1660
70°	27168	3638	1587
75°	11099	2393	1779
80°	5367	2652	1768
85°	2642	4466	2642

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.3	3.3
10°-20°	721.7	11.7
20°-30°	1358.4	22.0
30°-40°	1654.1	26.8
40°-50°	1376.9	22.3
50°-60°	659.5	10.7
60°-70°	158.4	2.6
70°-80°	24.9	0.4
80°-90°	5.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2284.3	37.1
0°-40°	3938.4	63.9
0°-60°	5974.8	96.9
0°-90°	6163.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6163.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1990	1990	1990	1990	1990	
5°	3186	2702	1943	1413	1240	349
15°	6224	4228	1707	774	599	1784
25°	8368	4942	1488	844	875	3843
35°	8481	4340	1114	649	619	5255
45°	6464	2901	560	345	328	4895
55°	2463	1197	239	134	103	2320
65°	444	258	62	20	13	508
75°	52	27	11	10	8	71
85°	4	4	7	6	4	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8
2.5°	2573.5	2483.1	2511.4	2505.8	2500.1	2470.3	2449.2	2430.8	2384.2	2384.2	2324.7
5°	3185.5	3079.4	3106.3	3086.4	3061.0	3015.8	2974.9	2928.2	2842.1	2805.2	2702.1
7.5°	3885.0	3764.9	3788.8	3749.4	3695.5	3634.8	3568.3	3480.8	3343.7	3260.3	3100.7
10°	4656.6	4485.5	4499.8	4440.5	4351.5	4269.3	4205.8	4039.0	3843.9	3705.4	3482.2
12.5°	5387.2	5237.4	5241.8	5158.4	5029.8	4929.4	4833.2	4612.7	4352.7	4154.9	3860.9
15°	6224.0	6040.2	5996.3	5883.3	5715.1	5592.2	5460.7	5182.3	4855.9	4594.5	4228.4
17.5°	6898.0	6708.6	6680.3	6574.4	6334.1	6185.8	6020.5	5706.6	5292.6	4967.6	4518.1
20°	7488.7	7300.8	7252.8	7115.6	6840.1	6670.5	6471.2	6101.0	5648.8	5248.8	4741.4
22.5°	7972.0	7765.8	7697.9	7528.4	7221.7	7030.9	6787.9	6383.6	5879.0	5432.4	4874.3
25°	8367.8	8133.1	8047.0	7854.8	7509.9	7299.3	7032.2	6580.0	6030.3	5537.1	4942.2
27.5°	8620.8	8386.2	8291.5	8071.1	7683.8	7457.7	7166.5	6677.6	6084.0	5551.3	4927.9
30°	8723.8	8480.8	8373.5	8123.2	7706.5	7467.6	7163.7	6635.1	6014.8	5449.5	4809.3
32.5°	8660.3	8421.5	8301.4	8030.0	7596.1	7339.0	7035.1	6471.2	5832.5	5247.3	4602.9
35°	8480.8	8244.8	8120.5	7830.8	7378.6	7110.0	6807.5	6224.0	5578.1	4980.2	4340.1
37.5°	8171.3	7948.1	7805.4	7518.5	7063.4	6789.1	6489.6	5900.2	5240.4	4677.9	4036.2
40°	7723.2	7511.4	7370.0	7063.4	6633.8	6356.8	6074.1	5476.3	4854.5	4306.1	3687.2
42.5°	7152.4	6957.4	6821.8	6523.6	6113.7	5841.0	5582.3	5008.5	4416.4	3894.8	3309.8
45°	6464.1	6294.6	6161.7	5914.5	5510.2	5251.7	5018.4	4498.3	3923.1	3444.1	2901.4
47.5°	5654.4	5514.4	5385.7	5161.1	4796.5	4552.0	4359.8	3883.6	3395.9	2945.2	2483.1
50°	4629.8	4529.4	4429.2	4196.0	3938.7	3725.3	3585.4	3161.4	2767.0	2413.7	2030.9
52.5°	3490.7	3429.9	3359.2	3192.5	3020.2	2895.7	2771.4	2449.2	2153.7	1890.9	1592.8
55°	2463.2	2432.2	2377.1	2309.2	2177.9	2093.0	1985.7	1821.6	1592.8	1416.1	1196.9
57.5°	1664.8	1656.3	1618.1	1577.3	1505.2	1476.9	1386.3	1280.3	1151.9	1020.3	864.9
60°	1098.0	1079.7	1071.2	1048.6	993.5	970.8	938.4	870.5	791.4	699.5	603.5
62.5°	706.6	696.7	689.6	679.7	645.8	645.8	613.4	582.3	522.8	466.4	404.2
65°	443.8	435.2	433.8	426.8	414.0	408.4	384.3	361.8	333.6	302.4	258.5
67.5°	285.4	272.8	265.7	261.5	252.9	243.0	234.6	224.6	202.1	183.8	155.5
70°	169.5	158.2	156.9	158.2	148.4	147.0	138.5	131.4	115.9	104.5	87.6
72.5°	96.2	90.5	89.0	89.0	83.4	82.0	76.3	72.1	63.5	55.1	48.0
75°	52.4	48.0	48.0	48.0	45.2	43.8	41.1	39.6	33.9	31.0	26.8
77.5°	29.7	28.3	28.3	26.8	25.4	24.1	22.7	22.7	19.8	18.4	17.0
80°	17.0	17.0	17.0	17.0	15.5	15.5	14.0	14.0	12.8	12.8	11.3
82.5°	9.9	9.9	9.9	9.9	9.9	9.9	8.4	8.4	8.4	8.4	7.1
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8
2.5°	2297.9	2255.6	2252.6	2190.6	2151.0	2118.5	2094.5	2064.7	1998.3	1961.5	1934.7
5°	2630.1	2542.4	2497.1	2384.2	2322.0	2266.9	2199.0	2128.4	2019.6	1943.1	1881.0
7.5°	2974.9	2829.3	2733.1	2565.1	2480.2	2394.1	2279.7	2165.1	2016.7	1902.3	1807.5
10°	3295.8	3089.3	2936.8	2710.7	2600.3	2487.3	2326.2	2172.1	1986.9	1840.1	1715.8
12.5°	3610.9	3339.5	3128.9	2842.1	2707.7	2567.8	2361.5	2168.0	1950.2	1773.6	1628.0
15°	3911.9	3571.3	3302.7	2956.5	2799.6	2631.5	2384.2	2155.2	1907.9	1707.2	1541.8
17.5°	4152.1	3748.0	3425.7	3027.1	2850.4	2659.8	2375.7	2118.5	1849.8	1636.5	1455.7
20°	4317.5	3860.9	3493.6	3055.4	2861.8	2656.9	2343.1	2067.6	1789.1	1567.2	1383.6
22.5°	4406.6	3911.9	3512.0	3047.0	2844.8	2630.1	2303.6	2020.9	1741.2	1519.2	1344.0
25°	4439.0	3916.0	3492.1	3010.2	2806.6	2587.7	2257.0	1977.0	1703.0	1488.1	1324.1
27.5°	4400.9	3856.7	3420.0	2933.8	2727.5	2511.4	2182.0	1914.8	1646.4	1442.9	1288.9
30°	4270.8	3718.2	3278.8	2798.2	2596.0	2388.4	2063.4	1800.4	1554.6	1362.3	1215.3
32.5°	4064.5	3514.7	3079.4	2611.6	2416.6	2217.4	1906.4	1656.3	1427.4	1246.4	1115.0
35°	3808.7	3271.6	2847.7	2394.1	2210.3	2022.4	1727.0	1490.9	1276.2	1113.5	985.1
37.5°	3518.9	3001.8	2591.9	2175.0	1988.4	1811.8	1524.8	1322.9	1116.4	968.1	850.7
40°	3193.9	2692.2	2319.1	1913.6	1749.5	1588.6	1322.9	1139.1	951.1	819.7	717.9
42.5°	2846.3	2378.6	2033.6	1669.0	1505.2	1358.0	1119.2	953.9	787.3	678.3	597.8
45°	2477.5	2064.7	1734.0	1407.5	1259.1	1131.9	914.5	764.6	643.0	559.7	498.9
47.5°	2091.6	1727.0	1433.1	1149.0	1017.5	907.3	732.2	617.6	521.6	460.8	414.0
50°	1703.0	1378.0	1144.7	903.1	790.0	702.4	572.3	493.3	422.7	376.0	340.5
52.5°	1331.3	1065.6	876.1	681.2	594.9	534.1	446.6	391.5	337.8	302.4	275.6
55°	983.6	802.8	640.1	494.5	443.8	405.7	343.4	303.9	265.7	238.9	219.0
57.5°	710.8	575.2	456.5	363.2	329.3	303.9	258.5	231.7	205.0	185.0	169.5
60°	498.9	397.1	322.3	265.7	241.6	224.6	192.2	175.2	155.5	138.5	123.0
62.5°	327.9	267.2	224.6	187.9	173.9	161.1	138.5	125.7	108.8	97.4	83.4
65°	213.3	175.2	149.9	125.7	114.4	108.8	93.3	83.4	72.1	62.2	53.7
67.5°	129.9	108.8	94.7	79.1	73.5	67.9	58.0	51.0	43.8	36.7	32.4
70°	72.1	63.5	55.1	46.7	42.3	39.6	33.9	31.0	25.4	22.7	18.4
72.5°	42.3	36.7	32.4	26.8	25.4	24.1	19.8	18.4	15.5	14.0	12.8
75°	25.4	21.2	19.8	17.0	15.5	15.5	14.0	12.8	11.3	11.3	9.9
77.5°	15.5	14.0	12.8	11.3	11.3	11.3	9.9	9.9	9.9	8.4	8.4
80°	9.9	9.9	9.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
82.5°	7.1	7.1	7.1	5.6	7.1	5.6	7.1	7.1	7.1	7.1	7.1
85°	4.2	4.2	5.6	5.6	5.6	5.6	5.6	7.1	7.1	7.1	7.1
87.5°	4.2	4.2	5.6	5.6	5.6	5.6	5.6	7.1	7.1	7.1	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8
2.5°	1903.7	1851.3	1813.2	1785.0	1794.7	1745.3	1729.8	1676.2	1656.3	1656.3	1628.0
5°	1817.4	1734.0	1669.0	1628.0	1625.2	1554.6	1517.8	1450.1	1413.2	1386.3	1359.5
7.5°	1714.3	1606.8	1520.7	1471.2	1457.0	1373.6	1324.1	1256.4	1201.3	1165.9	1133.4
10°	1604.1	1475.4	1378.0	1321.4	1300.2	1209.7	1144.7	1082.5	1023.3	986.5	952.5
12.5°	1498.0	1358.0	1250.8	1192.8	1165.9	1072.7	1006.2	941.3	884.7	846.6	812.7
15°	1400.6	1252.1	1139.1	1081.1	1051.4	959.5	893.2	829.6	774.5	739.1	708.0
17.5°	1308.6	1157.5	1044.4	987.8	955.3	870.5	806.9	744.7	695.2	662.8	634.5
20°	1239.5	1089.6	985.1	935.6	903.1	823.9	768.9	715.2	674.1	650.0	623.2
22.5°	1209.7	1071.2	982.2	936.9	914.5	850.7	812.7	774.5	747.7	743.3	726.4
25°	1205.5	1084.0	1010.5	972.3	958.3	910.1	887.4	863.5	843.6	849.3	852.2
27.5°	1187.1	1074.1	1013.4	980.8	969.6	930.0	913.0	890.3	876.1	883.3	886.2
30°	1123.6	1019.0	962.4	935.6	924.2	884.7	870.5	845.1	833.8	835.2	833.8
32.5°	1024.7	925.6	873.4	849.3	836.7	801.3	785.8	763.2	746.2	744.7	742.0
35°	904.4	815.4	767.4	746.2	733.4	703.9	689.6	668.4	648.8	647.3	644.4
37.5°	781.6	702.4	661.3	643.0	631.8	607.7	590.7	576.7	563.9	558.3	556.8
40°	662.8	592.2	562.4	548.4	539.8	514.4	505.9	491.8	481.9	476.3	474.9
42.5°	551.1	501.7	477.8	465.0	457.9	439.4	429.6	418.3	408.4	402.8	401.3
45°	467.7	426.8	404.2	394.4	388.6	371.7	364.6	353.3	344.9	340.5	339.2
47.5°	390.0	357.6	342.0	330.7	329.3	315.1	305.3	296.7	288.3	284.1	282.7
50°	319.4	292.6	279.8	272.8	271.3	257.1	250.2	243.0	236.0	231.7	229.0
52.5°	262.8	237.4	229.0	219.0	217.7	205.0	199.3	192.2	185.0	179.6	175.2
55°	207.7	187.9	179.6	171.0	169.5	155.5	149.9	141.2	134.3	128.6	123.0
57.5°	158.2	142.7	134.3	125.7	124.3	114.4	104.5	97.4	90.5	83.4	79.1
60°	115.9	100.4	90.5	86.1	82.0	72.1	65.0	59.3	53.7	49.5	45.2
62.5°	76.3	65.0	58.0	52.4	49.5	42.3	38.2	33.9	31.0	29.7	28.3
65°	46.7	39.6	33.9	31.0	31.0	26.8	24.1	21.2	19.8	19.8	18.4
67.5°	28.3	24.1	21.2	19.8	18.4	17.0	15.5	15.5	14.0	14.0	12.8
70°	17.0	15.5	14.0	12.8	12.8	12.8	12.8	12.8	11.3	11.3	11.3
72.5°	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3	9.9	9.9	9.9
75°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	8.4
77.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
80°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	7.1	7.1	7.1
82.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
85°	7.1	7.1	7.1	7.1	7.1	7.1	5.6	5.6	5.6	5.6	5.6
87.5°	7.1	5.6	5.6	5.6	5.6	5.6	4.2	4.2	4.2	4.2	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192848

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8	1989.8
2.5°	1614.0	1625.2	1608.3	1596.9	1585.7	1594.2	1554.6	1537.6
5°	1334.1	1321.4	1312.8	1303.0	1286.0	1288.9	1255.0	1239.5
7.5°	1103.6	1095.3	1074.1	1062.8	1045.8	1045.8	1014.6	1002.0
10°	921.4	908.8	888.9	879.0	863.5	850.7	835.2	822.4
12.5°	782.9	768.9	751.8	743.3	727.8	717.9	702.4	705.1
15°	679.7	665.7	650.0	641.6	628.9	619.0	606.2	599.2
17.5°	607.7	594.9	582.3	573.8	563.9	555.4	544.1	542.7
20°	602.1	592.2	585.1	579.4	571.0	565.3	559.7	552.6
22.5°	720.8	722.1	723.5	723.5	725.0	725.0	726.4	712.3
25°	850.7	866.3	866.3	870.5	883.3	883.3	880.5	874.8
27.5°	884.7	900.2	896.1	898.8	911.6	914.5	904.4	905.8
30°	828.2	842.4	833.8	835.2	843.6	843.6	831.1	836.7
32.5°	733.4	742.0	730.7	730.7	737.8	736.3	727.8	727.8
35°	633.0	637.4	627.4	631.8	631.8	627.4	619.0	619.0
37.5°	546.9	548.4	538.5	539.8	539.8	535.6	527.2	527.2
40°	465.0	469.1	460.8	463.5	460.8	456.5	452.2	450.7
42.5°	392.9	395.6	388.6	392.9	391.5	391.5	390.0	391.5
45°	330.7	333.6	327.9	330.7	332.2	330.7	326.5	327.9
47.5°	274.1	277.1	277.1	274.1	272.8	265.7	261.5	261.5
50°	221.9	220.5	219.0	214.8	210.6	206.3	202.1	202.1
52.5°	166.8	163.9	162.6	158.2	156.9	152.6	152.6	148.4
55°	114.4	113.2	113.2	108.8	108.8	104.5	103.1	103.1
57.5°	72.1	69.2	70.6	67.9	66.5	62.2	62.2	60.7
60°	41.1	39.6	39.6	38.2	36.7	33.9	33.9	33.9
62.5°	26.8	25.4	25.4	24.1	24.1	22.7	22.7	21.2
65°	17.0	15.5	15.5	14.0	14.0	12.8	12.8	12.8
67.5°	12.8	11.3	11.3	11.3	11.3	11.3	9.9	9.9
70°	11.3	11.3	9.9	9.9	9.9	9.9	9.9	9.9
72.5°	9.9	9.9	9.9	9.9	8.4	8.4	8.4	8.4
75°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
77.5°	8.4	7.1	7.1	7.1	7.1	7.1	7.1	7.1
80°	7.1	7.1	7.1	7.1	7.1	7.1	5.6	5.6
82.5°	7.1	5.6	5.6	5.6	5.6	5.6	5.6	5.6
85°	5.6	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	2.7	2.7	2.7	2.7	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)