

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192401

Luminaire Tested: **LDA6A50940D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5245.5 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64551	64551	64551
5°	165067	59514	21715
10°	354753	48006	7988
15°	517506	35114	9149
20°	586003	25249	14100
25°	635262	20306	21866
30°	708818	16673	21054
35°	719443	10788	14027
40°	724758	5174	7099
45°	720222	2163	2969
50°	576638	972	972
55°	171970	698	105
60°	35107	800	0
65°	3347	947	0
70°	337	1314	0
75°	0	1737	0
80°	0	2936	347
85°	0	5850	692

TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	2.9
10°-20°	735.7	14.0
20°-30°	1352.1	25.8
30°-40°	1551.3	29.6
40°-50°	1173.7	22.4
50°-60°	260.1	5.0
60°-70°	11.0	0.2
70°-80°	4.9	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2239.8	42.7
0°-40°	3791.1	72.3
0°-60°	5224.8	99.6
0°-90°	5245.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5245.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1178	1178	1178	1178	1178	
5°	3000	2240	1082	529	395	397
15°	9118	4946	619	160	161	2541
25°	10502	5815	336	325	362	4900
35°	10750	3589	161	201	210	6734
45°	9290	1015	28	36	38	6933
55°	1799	38	7	5	1	2227
65°	26	5	7	4	0	69
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5
2.5°	1994.5	1974.9	1980.1	2004.8	1902.6	1899.4	1852.0	1845.8	1798.3	1711.5	1668.1
5°	2999.6	2987.1	2965.4	2973.7	2856.9	2778.4	2695.8	2635.9	2514.1	2349.8	2240.4
7.5°	4602.5	4468.2	4403.2	4278.2	4129.5	3977.6	3824.8	3647.1	3391.0	3104.8	2873.5
10°	6372.9	6314.0	6180.8	6101.3	5771.8	5548.6	5311.1	4947.6	4478.6	3960.1	3528.3
12.5°	8108.2	8039.0	7837.6	7668.1	7229.2	7029.9	6721.1	6262.4	5667.4	4928.9	4246.2
15°	9118.4	9133.9	8905.6	8897.4	8519.3	8260.0	7992.6	7450.3	6695.2	5847.2	4945.5
17.5°	9710.2	9748.4	9522.3	9586.2	9209.2	8940.7	8741.4	8344.7	7542.2	6524.8	5485.7
20°	10044.9	10105.8	9865.1	9914.8	9592.5	9410.6	9208.2	8815.7	8107.1	6984.4	5792.4
22.5°	10300.0	10323.8	10056.2	10122.4	9770.2	9588.3	9444.8	9077.1	8377.8	7227.2	5888.5
25°	10502.4	10562.3	10256.7	10261.8	9911.6	9729.8	9570.7	9236.1	8493.5	7291.1	5815.2
27.5°	10793.8	10842.2	10392.9	10353.7	10014.9	9814.5	9642.0	9312.5	8488.3	7148.7	5538.3
30°	11197.6	10927.0	10467.3	10366.1	9984.9	9781.4	9596.6	9169.0	8298.2	6764.4	5035.4
32.5°	11081.9	10862.9	10409.5	10248.3	9870.3	9652.3	9440.6	8920.0	7857.2	6169.4	4349.4
35°	10750.3	10680.1	10204.0	10153.4	9695.7	9467.5	9254.7	8543.0	7180.7	5391.7	3589.3
37.5°	10470.4	10350.6	10043.9	9964.3	9484.0	9232.0	8893.2	7980.1	6286.2	4400.2	2866.2
40°	10127.6	10046.9	9750.4	9665.8	9110.1	8725.9	8311.7	6959.6	5205.8	3425.0	2213.5
42.5°	9762.9	9690.6	9410.6	9233.1	8492.4	7984.2	7340.8	5724.2	4007.7	2581.2	1658.8
45°	9289.9	9187.5	8837.4	8506.9	7445.1	6717.9	5993.8	4368.1	2933.4	1837.5	1015.4
47.5°	8476.9	8314.7	7890.2	7226.1	5921.5	5223.3	4469.3	2962.3	1811.6	946.1	511.3
50°	6761.3	6478.3	5913.3	5123.2	3792.8	3123.5	2532.7	1506.0	777.8	487.6	300.6
52.5°	4166.7	3907.4	3426.1	2663.9	1748.7	1346.8	1060.8	701.3	428.6	275.8	111.5
55°	1799.3	1637.1	1406.8	1073.1	762.3	627.0	504.0	350.1	221.0	84.7	38.3
57.5°	679.7	631.1	572.2	470.0	351.2	293.3	246.8	154.9	53.8	32.0	21.7
60°	320.2	290.3	256.1	203.5	134.3	97.1	60.9	39.2	25.8	17.6	12.4
62.5°	87.8	66.1	54.7	44.4	34.0	29.9	25.8	19.6	14.4	9.3	7.3
65°	25.8	22.8	21.7	18.5	15.5	13.4	11.4	9.3	7.3	5.2	5.2
67.5°	9.3	9.3	8.2	7.3	6.2	5.2	5.2	4.1	4.1	4.1	4.1
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1	4.1	4.1
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	4.1
75°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	4.1
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
80°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5
2.5°	1631.9	1572.1	1487.3	1444.0	1405.8	1395.4	1316.9	1266.3	1206.5	1144.5	1079.4
5°	2138.0	1985.2	1823.0	1686.8	1617.5	1577.2	1424.3	1309.8	1199.2	1081.5	981.2
7.5°	2640.0	2366.3	2129.8	1909.8	1789.0	1698.0	1479.1	1306.6	1139.3	986.4	851.1
10°	3125.5	2731.0	2354.0	2056.5	1890.2	1754.8	1471.8	1247.8	1038.0	862.4	721.0
12.5°	3617.2	3041.8	2540.9	2135.0	1936.6	1763.2	1422.3	1149.7	927.6	741.7	595.0
15°	4056.1	3283.6	2657.7	2153.5	1914.0	1709.4	1325.2	1024.7	803.6	618.7	490.6
17.5°	4360.8	3413.8	2664.8	2085.5	1818.9	1599.0	1189.9	893.4	678.6	515.4	402.8
20°	4499.2	3409.5	2566.7	1943.9	1665.0	1435.7	1029.8	759.2	566.0	432.8	336.7
22.5°	4457.9	3279.4	2393.2	1743.6	1477.0	1247.8	881.1	640.4	486.5	371.8	295.4
25°	4251.3	3052.1	2189.7	1543.1	1274.5	1060.8	746.8	547.4	422.4	335.7	268.5
27.5°	3913.6	2742.3	1916.0	1308.7	1062.8	896.6	629.0	473.0	371.8	296.5	279.9
30°	3419.9	2366.3	1594.7	1055.6	858.3	709.6	510.2	381.1	297.4	263.4	264.4
32.5°	2875.6	1952.1	1253.9	806.7	646.6	547.4	377.0	266.4	218.0	215.8	216.9
35°	2333.4	1520.4	932.8	589.8	474.1	394.6	242.7	167.4	162.2	161.2	163.1
37.5°	1852.0	1131.0	672.4	412.1	314.0	240.6	131.2	113.6	109.5	111.5	112.6
40°	1383.0	793.3	454.5	243.8	152.8	110.6	79.6	73.4	71.2	72.3	72.3
42.5°	951.3	495.8	270.7	101.2	73.4	60.9	50.6	47.5	45.4	44.4	45.4
45°	512.3	308.8	105.4	51.6	43.4	39.2	32.0	29.9	28.9	27.9	27.9
47.5°	327.5	114.7	47.5	32.0	27.9	25.8	21.7	19.6	18.5	17.6	17.6
50°	122.9	44.4	28.9	20.7	17.6	16.5	13.4	12.4	11.4	11.4	11.4
52.5°	42.4	26.9	18.5	13.4	11.4	10.3	9.3	8.2	8.2	8.2	8.2
55°	23.7	16.5	11.4	8.2	8.2	7.3	7.3	7.3	7.3	7.3	7.3
57.5°	14.4	9.3	7.3	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
60°	8.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
62.5°	5.2	5.2	5.2	5.2	5.2	6.2	6.2	7.3	7.3	7.3	7.3
65°	5.2	5.2	5.2	5.2	5.2	6.2	6.2	7.3	7.3	7.3	7.3
67.5°	4.1	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	8.2	7.3
70°	5.2	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2
72.5°	5.2	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2
75°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2	8.2
77.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3	8.2
80°	5.2	5.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2	9.3	9.3
82.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	9.3	9.3	9.3
85°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	9.3	9.3	9.3
87.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5
2.5°	1044.3	984.4	935.8	936.9	896.6	865.6	826.3	804.6	787.1	758.1	731.3
5°	907.9	816.0	746.8	733.3	686.9	639.3	590.9	554.7	528.9	500.9	475.1
7.5°	760.2	654.8	575.4	556.7	517.5	473.0	428.6	392.5	361.5	331.6	300.6
10°	616.7	520.5	448.2	429.7	390.4	343.9	301.6	269.6	245.8	222.1	198.4
12.5°	498.8	414.2	346.0	322.3	290.3	254.1	220.0	189.0	163.1	152.8	149.8
15°	403.9	323.2	269.6	250.0	223.1	185.9	166.3	161.2	160.1	160.1	160.1
17.5°	326.4	263.4	214.8	194.1	180.8	178.6	178.6	178.6	179.7	181.8	185.9
20°	273.7	218.0	199.3	201.4	201.4	203.5	207.6	210.7	214.8	220.0	226.2
22.5°	242.7	231.3	229.3	235.4	236.5	242.7	250.9	257.2	264.4	272.7	277.8
25°	265.5	269.6	272.7	281.9	285.1	295.4	307.7	317.1	325.4	334.6	340.8
27.5°	289.2	296.5	302.6	312.0	314.0	327.5	337.8	343.9	350.1	354.2	358.5
30°	272.7	279.9	286.2	294.4	294.4	308.8	314.0	319.1	324.3	326.4	330.5
32.5°	224.2	231.3	237.6	243.8	244.8	255.2	261.3	263.4	267.5	268.5	271.6
35°	168.3	171.5	177.7	182.9	183.8	191.1	196.2	198.4	201.4	201.4	203.5
37.5°	115.7	117.7	122.9	126.1	128.1	133.2	136.4	138.4	140.5	141.6	142.5
40°	75.4	76.4	79.6	82.6	84.7	87.8	89.9	91.9	93.0	95.1	95.1
42.5°	46.5	47.5	49.5	51.6	51.6	54.7	55.8	57.9	58.9	59.9	59.9
45°	28.9	29.9	29.9	31.0	32.0	33.1	35.1	35.1	36.2	36.2	36.2
47.5°	17.6	18.5	17.6	18.5	18.5	19.6	20.7	20.7	20.7	20.7	20.7
50°	11.4	11.4	11.4	11.4	11.4	11.4	12.4	12.4	12.4	12.4	11.4
52.5°	8.2	8.2	7.3	8.2	7.3	7.3	7.3	7.3	7.3	7.3	6.2
55°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	5.2	4.1	4.1
57.5°	7.3	7.3	6.2	6.2	6.2	5.2	5.2	5.2	4.1	4.1	3.1
60°	7.3	7.3	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1	3.1
62.5°	7.3	7.3	6.2	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1
65°	7.3	7.3	7.3	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1
67.5°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	4.1	4.1	3.1
70°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	3.1
72.5°	8.2	8.2	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	4.1
75°	8.2	8.2	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	4.1
77.5°	8.2	8.2	8.2	8.2	7.3	7.3	6.2	6.2	5.2	5.2	4.1
80°	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2	5.2	5.2	4.1
82.5°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	5.2	5.2	4.1
85°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	5.2	5.2	4.1
87.5°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	5.2	5.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192401

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5
2.5°	706.5	693.1	692.0	680.6	658.0	669.4	654.8	644.5
5°	452.4	437.9	423.5	425.6	409.0	412.1	400.7	394.6
7.5°	287.1	271.6	267.5	267.5	248.9	248.9	241.7	237.6
10°	180.8	168.3	164.2	157.0	148.7	147.7	144.6	143.5
12.5°	146.7	146.7	143.5	144.6	144.6	144.6	143.5	143.5
15°	160.1	161.2	158.0	159.0	161.2	160.1	161.2	161.2
17.5°	184.9	190.0	185.9	188.0	192.1	191.1	192.1	193.2
20°	226.2	234.5	229.3	233.5	238.6	237.6	240.6	241.7
22.5°	281.9	292.3	287.1	291.3	299.5	297.4	301.6	303.6
25°	343.9	354.2	348.1	353.3	358.5	360.4	360.4	361.5
27.5°	358.5	364.6	360.4	365.6	367.7	369.7	367.7	368.8
30°	328.4	333.6	329.5	334.6	334.6	336.7	334.6	332.6
32.5°	270.7	274.8	269.6	275.8	274.8	275.8	276.8	277.8
35°	204.5	206.6	203.5	204.5	205.5	206.6	209.6	209.6
37.5°	142.5	145.7	142.5	143.5	143.5	145.7	147.7	147.7
40°	95.1	98.1	95.1	97.1	96.0	97.1	99.2	99.2
42.5°	59.9	62.0	59.9	60.9	60.9	60.9	62.0	63.0
45°	36.2	37.2	36.2	37.2	37.2	37.2	38.3	38.3
47.5°	20.7	21.7	20.7	20.7	21.7	20.7	21.7	21.7
50°	11.4	11.4	11.4	11.4	11.4	10.3	10.3	11.4
52.5°	6.2	6.2	5.2	5.2	5.2	5.2	5.2	5.2
55°	3.1	3.1	2.1	2.1	2.1	1.1	2.1	1.1
57.5°	2.1	2.1	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	3.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.1	3.1	2.1	2.1	1.1	1.1	1.1	0.0
80°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
85°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
87.5°	3.1	3.1	2.1	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)