

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192412

Luminaire Tested: **LDA6A50950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5229.7 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	43938	43938	43938
5°	115815	40023	13774
10°	234014	31156	8372
15°	430899	23354	12077
20°	668056	18680	20121
25°	784364	16567	25538
30°	850498	16661	19788
35°	896796	9925	10641
40°	919831	4229	4616
45°	861725	1667	1582
50°	602522	725	367
55°	211424	726	0
60°	42639	833	0
65°	2646	986	0
70°	513	1362	0
75°	0	1800	0
80°	0	2683	347
85°	0	6101	692

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	2.0
10°-20°	573.4	11.0
20°-30°	1355.4	25.9
30°-40°	1651.1	31.6
40°-50°	1228.2	23.5
50°-60°	297.4	5.7
60°-70°	11.0	0.2
70°-80°	5.3	0.1
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2031.5	38.8
0°-40°	3682.6	70.4
0°-60°	5208.2	99.6
0°-90°	5229.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5229.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	802	802	802	802	802	
5°	2105	1574	727	340	250	264
15°	7592	3291	412	189	213	2288
25°	12967	4127	274	398	422	5955
35°	13400	3014	148	161	159	8346
45°	11115	1149	22	24	20	8164
55°	2212	25	8	5	0	2502
65°	20	5	8	5	0	68
75°	0	5	8	6	0	0
85°	0	5	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5
2.5°	1397.7	1374.2	1371.9	1348.4	1339.7	1336.5	1303.2	1291.4	1247.3	1238.7	1176.3
5°	2104.6	2068.1	2060.7	2006.9	1967.1	1912.2	1883.3	1833.9	1729.7	1674.9	1573.9
7.5°	2994.2	2945.8	2935.1	2851.4	2768.6	2696.6	2636.4	2521.6	2330.2	2199.2	1992.8
10°	4203.9	4068.6	4019.2	3841.8	3671.0	3536.7	3466.9	3214.4	2926.6	2750.3	2462.4
12.5°	5740.2	5514.6	5422.2	5148.3	4847.4	4627.2	4491.9	4095.4	3627.0	3289.7	2878.2
15°	7592.4	7330.2	7164.9	6820.0	6273.2	5959.4	5719.8	5085.0	4401.6	3891.3	3290.7
17.5°	9609.0	9403.8	9156.7	8616.2	7735.2	7358.2	6923.2	6090.6	5153.6	4443.5	3659.2
20°	11451.4	11107.7	10921.8	10320.1	9299.6	8802.1	8266.0	7018.8	5818.7	4893.6	3941.8
22.5°	12449.6	12116.5	12004.8	11482.5	10546.8	9993.6	9311.3	7836.3	6328.9	5202.0	4092.2
25°	12967.4	12663.4	12670.9	12199.2	11354.8	10834.7	10140.7	8454.0	6677.0	5364.2	4126.6
27.5°	13372.4	12998.5	12933.0	12580.6	11829.6	11297.9	10628.5	8790.3	6804.8	5347.1	4033.1
30°	13435.8	13129.6	13176.9	12687.0	12001.5	11448.3	10752.0	8772.1	6673.9	5131.0	3790.3
32.5°	13392.8	13088.7	13197.3	12665.5	11927.3	11320.4	10545.8	8415.4	6289.3	4731.5	3433.7
35°	13400.4	13051.2	12970.6	12520.4	11641.7	10929.4	9994.7	7764.3	5720.9	4211.4	3013.6
37.5°	13240.2	12769.6	12783.7	12190.6	11089.4	10145.1	9086.8	6896.2	5048.3	3656.0	2591.4
40°	12853.5	12501.1	12389.4	11508.4	10038.6	8932.1	7911.5	5953.0	4270.6	3075.8	2096.0
42.5°	12302.4	11877.9	11550.3	10329.9	8549.6	7534.5	6652.4	4970.0	3535.7	2521.6	1627.6
45°	11115.1	10656.5	10021.5	8557.1	7049.8	6168.9	5433.0	4034.2	2859.9	1949.0	1148.6
47.5°	9119.0	8688.3	8035.0	6804.8	5628.5	4894.8	4321.0	3159.7	2090.6	1229.1	569.4
50°	7064.8	6737.2	6238.8	5170.9	4187.8	3501.3	2989.9	1984.3	1066.8	560.8	238.5
52.5°	4604.6	4372.6	3928.8	3116.8	2366.7	1855.5	1508.4	844.5	502.8	236.3	69.8
55°	2212.1	2091.8	1770.6	1283.9	929.3	762.8	644.6	409.2	190.2	56.9	24.6
57.5°	882.0	856.3	762.8	574.8	440.5	373.9	290.1	112.8	37.6	23.7	15.0
60°	388.9	377.1	316.0	209.5	112.8	64.5	47.2	28.0	18.3	13.9	9.7
62.5°	56.0	51.5	44.1	34.4	28.0	23.7	20.4	15.0	9.7	7.6	6.4
65°	20.4	20.4	18.3	15.0	12.9	11.9	10.7	7.6	5.4	5.4	5.4
67.5°	8.5	8.5	8.5	6.4	6.4	5.4	4.3	4.3	4.3	4.3	5.4
70°	3.2	3.2	3.2	2.2	2.2	2.2	3.2	3.2	3.2	4.3	5.4
72.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	5.4
75°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	5.4
77.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
80°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	5.4	5.4
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5
2.5°	1123.7	1108.7	1058.2	1007.8	1000.2	978.7	934.6	883.2	816.5	774.6	732.7
5°	1442.8	1367.6	1282.8	1185.0	1154.9	1111.9	1019.5	920.7	810.1	727.3	650.0
7.5°	1815.6	1648.0	1488.0	1331.1	1272.0	1205.4	1064.6	922.8	771.4	651.1	554.3
10°	2164.9	1906.9	1658.8	1436.3	1348.4	1258.0	1068.9	886.3	698.4	559.7	460.9
12.5°	2512.8	2143.3	1803.8	1512.7	1393.4	1277.4	1045.4	820.8	608.1	475.9	396.4
15°	2786.9	2357.2	1909.1	1551.4	1403.2	1261.3	987.3	730.6	520.0	411.5	340.6
17.5°	2977.0	2479.6	1949.0	1535.2	1365.4	1205.4	896.0	625.2	449.1	361.0	292.2
20°	3108.0	2518.3	1921.0	1468.6	1284.9	1108.7	781.1	530.7	398.5	320.2	251.5
22.5°	3144.5	2480.6	1841.4	1368.7	1179.7	998.0	661.9	468.4	362.0	288.0	243.9
25°	3109.2	2385.0	1722.1	1249.5	1050.7	860.6	561.9	430.8	334.0	273.9	283.7
27.5°	2980.2	2216.3	1556.7	1095.7	891.7	712.3	494.2	385.7	294.4	289.0	300.8
30°	2767.5	1974.6	1360.1	899.3	704.8	568.4	414.6	304.1	257.8	263.2	270.7
32.5°	2461.4	1678.1	1107.6	666.1	516.7	427.6	296.5	210.6	204.0	208.4	213.7
35°	2074.5	1365.4	829.4	459.8	366.3	294.4	174.1	149.2	146.1	148.3	150.4
37.5°	1683.6	1055.0	564.1	309.4	222.5	149.2	104.2	97.8	95.6	96.7	97.8
40°	1306.3	733.7	354.4	148.3	87.0	74.0	64.5	61.3	59.1	59.1	60.2
42.5°	954.1	435.1	176.2	58.0	47.2	44.1	38.7	36.5	34.4	35.4	36.5
45°	533.9	193.3	60.2	32.2	29.0	26.8	23.7	22.6	21.5	21.5	21.5
47.5°	227.8	67.6	29.0	20.4	18.3	17.2	15.0	13.9	12.9	12.9	12.9
50°	75.2	26.8	18.3	13.9	11.9	10.7	9.7	8.5	8.5	8.5	9.7
52.5°	26.8	17.2	11.9	9.7	8.5	8.5	7.6	7.6	7.6	7.6	7.6
55°	16.1	11.9	8.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
57.5°	10.7	7.6	7.6	6.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6
60°	7.6	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6
62.5°	6.4	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6
65°	5.4	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6
67.5°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5
70°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5
72.5°	5.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5
75°	5.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5	8.5
77.5°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	8.5
80°	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	8.5	9.7
82.5°	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	8.5	9.7
85°	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	9.7	9.7
87.5°	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5
2.5°	689.7	657.5	612.5	597.4	566.2	543.6	518.9	491.0	485.6	457.6	454.5
5°	574.8	523.2	471.6	452.3	425.4	402.8	378.1	351.3	339.5	312.6	296.5
7.5°	473.7	424.4	378.1	358.9	333.0	304.1	275.0	247.1	231.0	205.2	192.3
10°	397.5	348.1	298.7	279.2	255.7	223.5	192.3	163.3	152.6	146.1	147.3
12.5°	332.1	282.6	233.2	211.6	186.9	161.1	160.1	158.0	162.2	161.1	162.2
15°	278.3	225.6	178.4	171.9	171.9	176.2	180.5	181.5	189.1	189.1	191.3
17.5°	228.9	192.3	194.5	194.5	198.7	206.3	214.9	219.1	231.0	232.0	236.3
20°	212.8	221.3	231.0	233.2	240.6	252.4	264.3	272.9	288.0	292.2	300.8
22.5°	252.4	267.6	282.6	286.8	296.5	313.7	335.2	342.8	361.0	361.0	372.8
25°	297.6	320.2	335.2	340.6	351.3	366.3	380.3	384.6	397.5	393.2	397.5
27.5°	316.0	332.1	341.6	347.0	349.1	362.0	368.5	366.3	375.0	368.5	368.5
30°	280.4	292.2	297.6	300.8	300.8	310.5	310.5	307.2	312.6	307.2	304.1
32.5°	220.2	228.9	233.2	233.2	232.0	238.5	236.3	232.0	234.2	231.0	223.5
35°	153.7	160.1	163.3	162.2	161.1	166.5	163.3	160.1	161.1	159.0	153.7
37.5°	101.0	102.0	104.2	106.3	105.4	109.6	107.4	105.4	106.3	104.2	101.0
40°	61.3	63.3	65.5	65.5	65.5	66.7	66.7	65.5	67.6	65.5	63.3
42.5°	36.5	38.7	38.7	38.7	39.8	39.8	40.8	38.7	40.8	38.7	37.6
45°	22.6	22.6	22.6	23.7	22.6	23.7	23.7	22.6	23.7	22.6	21.5
47.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	12.9	13.9	12.9	11.9
50°	8.5	9.7	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4
52.5°	7.6	7.6	7.6	7.6	7.6	7.6	6.4	6.4	5.4	4.3	4.3
55°	7.6	7.6	7.6	6.4	6.4	6.4	6.4	5.4	5.4	4.3	3.2
57.5°	7.6	7.6	6.4	6.4	6.4	6.4	5.4	5.4	4.3	3.2	3.2
60°	7.6	7.6	7.6	6.4	6.4	6.4	5.4	5.4	4.3	3.2	3.2
62.5°	7.6	7.6	7.6	6.4	6.4	6.4	6.4	5.4	4.3	3.2	3.2
65°	7.6	7.6	7.6	7.6	7.6	6.4	6.4	5.4	5.4	4.3	3.2
67.5°	8.5	7.6	7.6	7.6	7.6	7.6	6.4	5.4	5.4	4.3	3.2
70°	8.5	8.5	7.6	7.6	7.6	7.6	6.4	6.4	5.4	4.3	3.2
72.5°	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4	5.4	4.3	4.3
75°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4	5.4	4.3
77.5°	9.7	8.5	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4	4.3
80°	9.7	9.7	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4	4.3
82.5°	9.7	9.7	8.5	8.5	8.5	8.5	7.6	7.6	6.4	5.4	4.3
85°	9.7	9.7	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4	4.3
87.5°	9.7	9.7	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192412

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	801.5	801.5	801.5	801.5	801.5	801.5	801.5	801.5
2.5°	435.1	433.0	425.4	427.6	422.2	410.4	411.5	407.3
5°	285.8	279.2	271.9	271.9	264.3	253.6	253.6	250.3
7.5°	174.1	164.4	156.8	155.8	148.3	142.9	142.9	141.9
10°	147.3	148.3	148.3	149.2	148.3	148.3	149.2	150.4
12.5°	165.4	168.7	168.7	169.8	168.7	170.8	170.8	173.0
15°	197.6	203.0	204.0	206.3	205.2	208.4	210.6	212.8
17.5°	248.1	254.6	256.9	263.2	262.2	265.4	267.6	271.9
20°	312.6	322.3	325.5	334.0	333.0	336.3	341.6	344.9
22.5°	384.6	396.4	397.5	405.0	403.9	407.3	409.2	410.4
25°	403.9	411.5	410.4	414.6	414.6	415.8	415.8	422.2
27.5°	369.6	375.0	375.0	375.0	376.0	377.1	377.1	382.4
30°	304.1	306.2	307.2	304.1	306.2	307.2	307.2	312.6
32.5°	225.6	226.7	227.8	223.5	226.7	226.7	226.7	231.0
35°	155.8	155.8	156.8	153.7	155.8	156.8	155.8	159.0
37.5°	102.0	102.0	102.0	102.0	102.0	102.0	101.0	104.2
40°	63.3	64.5	63.3	63.3	62.3	62.3	62.3	64.5
42.5°	37.6	37.6	36.5	36.5	36.5	36.5	37.6	37.6
45°	21.5	21.5	20.4	20.4	19.2	20.4	20.4	20.4
47.5°	11.9	10.7	10.7	10.7	9.7	9.7	9.7	10.7
50°	5.4	5.4	5.4	4.3	4.3	4.3	3.2	4.3
52.5°	3.2	2.2	2.2	2.2	1.1	1.1	0.0	1.1
55°	2.2	2.2	1.1	1.1	0.0	0.0	0.0	0.0
57.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.2	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.2	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.2	3.2	2.2	2.2	1.1	1.1	1.1	1.1
80°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
82.5°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
85°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
87.5°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)