

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192414

Luminaire Tested: **LDA6A50950D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4861.1 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	101		102	100	98		99	97	95		95	94	92
2	105	99	94	89	102	97	92	88		94	90	86		90	87	85		88	85	83
3	98	89	83	78	95	88	82	78		85	80	76		83	79	75		80	77	74
4	91	81	74	69	89	80	73	68		78	72	67		75	71	67		73	69	66
5	84	74	66	61	82	73	66	61		71	65	60		69	64	59		67	63	59
6	78	67	59	54	77	66	59	54		65	58	53		63	57	53		61	57	53
7	73	61	54	48	71	60	53	48		59	53	48		58	52	47		56	51	47
8	68	56	48	43	66	55	48	43		54	48	43		53	47	43		52	46	42
9	63	51	44	39	62	51	44	39		50	43	39		49	43	39		48	42	38
10	59	47	40	35	58	47	40	35		46	39	35		45	39	35		44	39	35

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41992	41992	41992
5°	110659	38312	12349
10°	220960	29364	4904
15°	402267	20613	5358
20°	618550	14795	33842
25°	725419	22090	28006
30°	789830	13869	8159
35°	831292	5749	3380
40°	852397	2533	1918
45°	791276	1667	1419
50°	555009	1279	648
55°	202994	927	411
60°	42858	932	241
65°	3632	1103	285
70°	1218	1362	513
75°	233	1800	911
80°	347	2683	1357
85°	0	5346	1384



TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	2.0
10°-20°	529.9	10.9
20°-30°	1280.7	26.3
30°-40°	1505.6	31.0
40°-50°	1137.4	23.4
50°-60°	285.3	5.9
60°-70°	13.8	0.3
70°-80°	6.6	0.1
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1907.0	39.2
0°-40°	3412.7	70.2
0°-60°	4835.4	99.5
0°-90°	4861.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4861.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	766	766	766	766	766	
5°	2011	1460	696	295	224	251
15°	7088	3074	363	98	94	2145
25°	11993	3825	365	507	463	5517
35°	12422	2819	86	61	50	7735
45°	10206	1108	22	23	18	7520
55°	2124	31	10	8	4	2349
65°	28	8	8	8	2	75
75°	1	5	8	8	4	3
85°	0	5	8	6	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0
2.5°	1336.4	1314.9	1299.9	1274.0	1261.2	1266.6	1239.7	1203.2	1192.5	1160.2	1104.4
5°	2010.9	1988.5	1952.9	1898.1	1857.3	1850.9	1798.3	1710.2	1654.3	1571.6	1460.0
7.5°	2839.3	2819.9	2760.8	2679.1	2610.4	2584.6	2507.2	2352.6	2229.0	2063.7	1871.3
10°	3969.4	3894.2	3783.4	3618.1	3460.1	3387.1	3250.6	2995.0	2794.1	2567.4	2306.4
12.5°	5386.4	5253.0	5073.7	4825.5	4553.7	4417.4	4200.4	3809.2	3458.0	3069.1	2688.9
15°	7087.9	6953.5	6693.6	6309.1	5871.7	5652.7	5332.6	4715.9	4192.8	3622.3	3074.4
17.5°	9095.6	8876.4	8530.6	7973.1	7296.3	6952.6	6499.2	5645.1	4865.2	4120.9	3411.7
20°	10602.8	10442.6	10115.0	9531.8	8725.0	8282.5	7673.3	6497.0	5490.5	4519.4	3667.5
22.5°	11527.8	11383.8	11083.0	10595.3	9854.1	9363.1	8676.6	7244.6	5976.0	4795.4	3795.3
25°	11992.9	11889.8	11680.3	11254.9	10607.1	10114.0	9420.0	7798.0	6304.8	4944.8	3825.3
27.5°	12402.1	12229.3	11888.7	11598.7	11024.9	10523.2	9866.0	8073.0	6419.7	4927.6	3749.2
30°	12477.4	12378.5	12110.0	11695.3	11161.4	10654.4	9961.5	8033.2	6289.7	4727.7	3541.7
32.5°	12412.8	12326.9	12123.9	11671.6	11074.3	10514.7	9754.2	7706.7	5908.4	4357.2	3191.6
35°	12421.6	12285.0	11929.4	11542.8	10797.3	10139.8	9247.1	7109.4	5374.5	3875.9	2818.8
37.5°	12257.1	12032.6	11739.4	11240.8	10234.3	9419.1	8398.4	6339.2	4732.0	3384.9	2383.7
40°	11911.2	11740.4	11350.5	10584.5	9275.0	8250.2	7307.0	5455.0	4030.5	2848.9	1943.3
42.5°	11346.2	11142.1	10597.5	9442.6	7886.0	6992.2	6143.6	4550.5	3340.9	2330.0	1525.5
45°	10206.4	9894.9	9182.6	7805.4	6477.7	5719.3	5027.5	3710.5	2708.2	1822.9	1107.5
47.5°	8385.6	8120.2	7367.3	6217.7	5172.4	4585.9	3996.2	2926.1	2015.3	1172.0	569.3
50°	6507.7	6298.2	5723.6	4714.8	3842.5	3273.2	2809.1	1868.2	1074.2	539.2	255.7
52.5°	4282.0	4149.8	3656.7	2943.4	2206.5	1800.4	1462.0	811.0	500.6	239.6	88.1
55°	2123.9	1954.1	1718.8	1274.0	921.8	745.6	632.6	399.7	207.3	68.7	31.1
57.5°	865.8	828.3	745.6	575.7	442.6	373.9	298.7	124.6	46.2	28.0	19.2
60°	390.9	373.9	324.5	227.8	123.6	76.3	53.7	34.4	23.7	17.2	12.9
62.5°	68.7	63.3	56.0	43.0	34.4	30.1	25.8	19.2	15.0	11.9	9.7
65°	28.0	28.0	25.8	22.6	18.3	17.2	15.0	11.9	9.7	8.5	7.6
67.5°	15.0	13.9	13.9	11.9	10.7	9.7	8.5	7.6	7.6	6.4	6.4
70°	7.6	7.6	7.6	6.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
72.5°	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	4.3	4.3
75°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
77.5°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
80°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	5.4
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	5.4
87.5°	0.0	0.0	1.1	1.1	1.1	2.2	2.2	3.2	3.2	4.3	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0
2.5°	1102.2	1046.3	1003.4	962.5	952.8	919.6	888.4	834.7	786.3	741.2	689.7
5°	1417.0	1307.4	1216.1	1126.9	1097.8	1042.0	966.8	870.1	779.9	696.2	608.0
7.5°	1759.6	1573.8	1411.6	1261.2	1208.6	1129.0	1007.7	870.1	740.2	619.8	512.4
10°	2095.9	1818.6	1573.8	1356.8	1277.3	1174.2	1007.7	832.5	667.1	527.5	421.1
12.5°	2420.2	2040.0	1709.1	1422.3	1318.1	1189.1	980.8	767.1	574.7	437.2	348.0
15°	2673.7	2226.8	1804.7	1448.1	1318.1	1168.8	918.4	675.7	481.3	363.2	283.6
17.5°	2864.0	2337.6	1837.0	1423.4	1273.1	1105.4	824.0	568.3	396.3	300.8	224.4
20°	2974.6	2365.5	1803.7	1351.4	1187.1	1009.7	706.9	468.4	336.3	253.6	181.5
22.5°	3000.4	2326.8	1726.3	1259.0	1089.3	909.9	603.7	418.9	324.5	258.9	226.7
25°	2971.4	2248.4	1624.3	1165.6	996.9	819.7	566.2	451.2	388.9	365.2	390.9
27.5°	2856.4	2102.4	1498.6	1061.3	891.6	726.1	537.1	454.5	390.9	380.2	368.5
30°	2651.3	1882.0	1305.3	868.0	688.6	551.1	381.4	270.7	215.9	219.1	217.0
32.5°	2330.0	1562.0	1021.6	606.9	473.7	372.8	252.4	160.1	150.4	150.4	148.2
35°	1976.6	1268.6	768.0	426.5	329.8	262.1	150.4	117.1	98.9	85.9	77.4
37.5°	1616.8	987.3	529.7	288.0	209.5	134.3	72.0	59.1	52.6	49.4	48.4
40°	1251.5	695.0	338.4	158.0	92.5	59.1	46.2	39.8	36.5	35.4	35.4
42.5°	926.0	448.0	182.6	62.3	49.4	40.8	33.3	29.0	28.0	28.0	26.8
45°	557.4	224.4	68.7	38.7	32.2	29.0	24.6	22.6	21.5	21.5	22.6
47.5°	257.8	83.7	37.6	25.8	23.7	21.5	19.2	18.3	18.3	18.3	19.2
50°	93.5	36.5	23.7	18.3	17.2	16.1	15.0	13.9	13.9	15.0	15.0
52.5°	35.4	22.6	17.2	13.9	12.9	12.9	11.9	11.9	11.9	11.9	11.9
55°	21.5	16.1	12.9	10.7	10.7	9.7	9.7	9.7	9.7	9.7	9.7
57.5°	13.9	11.9	9.7	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
60°	10.7	8.5	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5	8.5
62.5°	8.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5
65°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7
67.5°	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5
70°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5
72.5°	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5
75°	5.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5
77.5°	5.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	9.7
80°	5.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7
82.5°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	9.7	9.7
85°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	8.5	8.5	9.7
87.5°	5.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0
2.5°	661.8	617.7	586.6	558.6	547.9	523.2	496.3	465.2	439.3	437.2	415.8
5°	548.9	487.7	443.7	415.8	401.8	376.0	344.9	324.5	295.4	286.8	265.4
7.5°	443.7	386.7	345.9	320.2	304.1	272.8	237.4	214.9	191.2	173.0	149.2
10°	361.0	306.2	262.1	236.3	220.2	186.9	150.4	124.6	103.2	98.9	96.7
12.5°	290.1	234.2	190.2	162.2	145.0	113.9	104.2	99.8	96.7	93.5	93.5
15°	225.6	168.7	121.4	110.6	107.4	104.2	102.0	99.8	97.8	96.7	97.8
17.5°	164.3	119.3	113.9	112.8	110.6	110.6	112.8	113.9	116.0	118.1	121.4
20°	145.0	146.1	158.0	166.5	163.3	179.4	201.9	220.2	264.3	291.1	327.6
22.5°	260.0	298.7	353.4	386.7	405.0	458.7	517.8	606.9	652.1	716.6	774.5
25°	444.7	489.8	537.1	550.1	559.7	565.0	557.4	516.7	507.1	488.8	483.4
27.5°	333.0	311.5	319.1	322.3	319.1	314.8	301.9	279.2	273.9	265.4	267.5
30°	196.6	190.2	198.7	197.6	197.6	197.6	193.3	175.0	166.5	156.8	150.4
32.5°	145.0	133.2	123.6	115.0	111.7	106.3	103.2	95.6	92.5	88.1	88.1
35°	72.0	68.7	68.7	66.7	65.5	66.7	66.7	63.3	61.3	60.2	60.2
37.5°	47.2	47.2	48.4	47.2	47.2	47.2	47.2	46.2	45.1	44.1	44.1
40°	35.4	35.4	36.5	36.5	35.4	35.4	35.4	34.4	34.4	34.4	34.4
42.5°	28.0	28.0	28.0	28.0	26.8	28.0	28.0	28.0	26.8	26.8	25.8
45°	23.7	22.6	22.6	22.6	22.6	22.6	23.7	22.6	22.6	21.5	21.5
47.5°	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	18.3	18.3
50°	15.0	15.0	15.0	15.0	15.0	13.9	13.9	12.9	12.9	11.9	11.9
52.5°	11.9	11.9	10.7	10.7	10.7	10.7	10.7	10.7	9.7	9.7	9.7
55°	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	8.5	7.6	7.6
57.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4
60°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	6.4	6.4	6.4
62.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4
65°	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4	6.4
67.5°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
70°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
72.5°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
75°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
77.5°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
80°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
82.5°	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6	6.4
85°	9.7	9.7	8.5	8.5	8.5	8.5	8.5	7.6	6.4	6.4	5.4
87.5°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	5.4	5.4	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192414

CATALOG NUMBER: LDA6A50950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	766.0	766.0	766.0	766.0	766.0	766.0	766.0	766.0
2.5°	411.5	396.3	393.2	397.5	380.2	380.2	380.2	387.8
5°	256.7	241.7	237.4	238.5	224.4	214.9	220.2	224.4
7.5°	139.7	123.6	118.1	118.1	104.2	98.9	99.8	102.0
10°	93.5	91.3	91.3	90.2	88.1	87.0	88.1	88.1
12.5°	90.2	89.1	89.1	88.1	88.1	87.0	87.0	88.1
15°	94.4	94.4	94.4	93.5	93.5	92.5	94.4	94.4
17.5°	120.3	122.4	126.7	128.9	133.2	128.9	136.4	135.4
20°	353.4	388.9	454.5	479.1	550.1	515.6	589.7	580.1
22.5°	800.3	826.2	836.9	842.3	843.2	877.7	883.1	894.9
25°	472.7	466.1	460.8	460.8	441.5	464.0	459.8	463.0
27.5°	252.4	250.3	245.0	247.1	237.4	245.0	247.1	247.1
30°	142.8	138.5	134.3	134.3	125.7	130.0	128.9	128.9
32.5°	82.8	80.6	78.4	77.4	75.2	75.2	74.0	74.0
35°	56.9	56.0	54.8	53.7	51.5	50.5	50.5	50.5
37.5°	41.9	40.8	39.8	39.8	38.7	36.5	36.5	36.5
40°	32.2	31.1	30.1	30.1	29.0	26.8	26.8	26.8
42.5°	24.6	23.7	22.6	21.5	21.5	20.4	19.2	19.2
45°	20.4	20.4	19.2	19.2	18.3	18.3	18.3	18.3
47.5°	17.2	17.2	16.1	16.1	16.1	15.0	15.0	13.9
50°	10.7	9.7	9.7	8.5	8.5	7.6	7.6	7.6
52.5°	8.5	7.6	7.6	6.4	6.4	5.4	5.4	5.4
55°	6.4	6.4	5.4	5.4	5.4	4.3	4.3	4.3
57.5°	5.4	5.4	4.3	4.3	4.3	3.2	3.2	3.2
60°	5.4	4.3	4.3	3.2	3.2	3.2	2.2	2.2
62.5°	5.4	4.3	4.3	3.2	3.2	2.2	2.2	2.2
65°	5.4	4.3	4.3	3.2	3.2	3.2	3.2	2.2
67.5°	5.4	5.4	4.3	4.3	4.3	3.2	3.2	3.2
70°	6.4	5.4	5.4	4.3	4.3	4.3	4.3	3.2
72.5°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
75°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
77.5°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
80°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
82.5°	5.4	5.4	5.4	4.3	4.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	3.2	3.2	3.2	3.2	2.2
87.5°	3.2	3.2	2.2	2.2	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)