

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192418

Luminaire Tested: **LDA6A50950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5455.3 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	101	99			99	97	96			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	89	83	79		86	81	77			84	80	76			81
4	92	82	75	70	90	81	75	70		79	73	69			77	72	68			75
5	85	75	68	62	83	74	67	62		72	66	62			70	65	61			69
6	80	69	61	56	78	68	61	56		66	60	55			64	59	55			63
7	74	63	55	50	73	62	55	50		61	54	50			59	54	49			58
8	69	58	50	45	68	57	50	45		56	49	45			55	49	45			54
9	65	53	46	41	64	53	46	41		52	45	41			51	45	41			50
10	61	49	42	37	60	49	42	37		48	41	37			47	41	37			46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67133	67133	67133
5°	171670	61897	22584
10°	368942	49927	8305
15°	538204	36516	9512
20°	609444	26258	14666
25°	660673	21116	22743
30°	737170	17338	21896
35°	748220	11216	14589
40°	753748	5382	7385
45°	749031	2248	3086
50°	599707	1015	1015
55°	178851	726	105
60°	36510	833	0
65°	3476	986	0
70°	353	1362	0
75°	0	1800	0
80°	0	3062	347
85°	0	6101	692



TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.1	2.9
10°-20°	765.1	14.0
20°-30°	1406.2	25.8
30°-40°	1613.3	29.6
40°-50°	1220.6	22.4
50°-60°	270.5	5.0
60°-70°	11.5	0.2
70°-80°	5.0	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2329.4	42.7
0°-40°	3942.7	72.3
0°-60°	5433.8	99.6
0°-90°	5455.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5455.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1225	1225	1225	1225	1225	
5°	3120	2330	1125	550	410	412
15°	9483	5143	643	166	168	2643
25°	10922	6048	349	338	376	5096
35°	11180	3733	168	210	218	7003
45°	9662	1056	29	38	40	7210
55°	1871	40	8	5	1	2316
65°	27	5	8	4	0	72
75°	0	4	8	5	0	0
85°	0	5	10	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6
2.5°	2074.3	2053.9	2059.3	2085.0	1978.7	1975.4	1926.1	1919.6	1870.2	1780.0	1734.8
5°	3119.6	3106.6	3084.0	3092.6	2971.2	2889.5	2803.6	2741.3	2614.7	2443.8	2330.0
7.5°	4786.6	4646.9	4579.3	4449.3	4294.7	4136.7	3977.8	3793.0	3526.6	3229.0	2988.4
10°	6627.8	6566.6	6428.0	6345.4	6002.7	5770.5	5523.5	5145.5	4657.7	4118.5	3669.4
12.5°	8432.5	8360.6	8151.1	7974.8	7518.4	7311.1	6989.9	6512.9	5894.1	5126.1	4416.0
15°	9483.1	9499.3	9261.8	9253.3	8860.1	8590.4	8312.3	7748.3	6963.0	6081.1	5143.3
17.5°	10098.6	10138.3	9903.2	9969.6	9577.6	9298.3	9091.1	8678.5	7843.9	6785.8	5705.1
20°	10446.7	10510.0	10259.7	10311.4	9976.2	9787.0	9576.5	9168.3	8431.4	7263.8	6024.1
22.5°	10712.0	10736.8	10458.4	10527.3	10161.0	9971.8	9822.6	9440.2	8712.9	7516.3	6124.0
25°	10922.5	10984.8	10667.0	10672.3	10308.1	10119.0	9953.5	9605.5	8833.2	7582.7	6047.8
27.5°	11225.6	11275.9	10808.6	10767.8	10415.5	10207.1	10027.7	9685.0	8827.8	7434.6	5759.8
30°	11645.5	11364.1	10886.0	10780.7	10384.3	10172.7	9980.5	9535.8	8630.1	7035.0	5236.8
32.5°	11525.2	11297.4	10825.9	10658.2	10265.1	10038.4	9818.2	9276.8	8171.5	6416.2	4523.4
35°	11180.3	11107.3	10612.2	10559.5	10083.5	9846.2	9624.9	8884.7	7467.9	5607.4	3732.9
37.5°	10889.2	10764.6	10445.7	10362.9	9863.4	9601.3	9248.9	8299.3	6537.6	4576.2	2980.8
40°	10532.7	10448.8	10140.4	10052.4	9474.5	9074.9	8644.2	7238.0	5414.0	3562.0	2302.0
42.5°	10153.4	10078.2	9787.0	9602.4	8832.1	8303.6	7634.4	5953.2	4168.0	2684.4	1725.2
45°	9661.5	9555.0	9190.9	8847.2	7742.9	6986.6	6233.6	4542.8	3050.7	1911.0	1056.0
47.5°	8816.0	8647.3	8205.8	7515.1	6158.4	5432.2	4648.1	3080.8	1884.1	983.9	531.8
50°	7031.8	6737.4	6149.8	5328.1	3944.5	3248.4	2634.0	1566.2	808.9	507.1	312.6
52.5°	4333.4	4063.7	3563.1	2770.5	1818.6	1400.7	1103.2	729.4	445.7	286.8	116.0
55°	1871.3	1702.6	1463.1	1116.0	792.8	652.1	524.2	364.1	229.8	88.1	39.8
57.5°	706.9	656.3	595.1	488.8	365.2	305.0	256.7	161.1	56.0	33.3	22.6
60°	333.0	301.9	266.3	211.6	139.7	101.0	63.3	40.8	26.8	18.3	12.9
62.5°	91.3	68.7	56.9	46.2	35.4	31.1	26.8	20.4	15.0	9.7	7.6
65°	26.8	23.7	22.6	19.2	16.1	13.9	11.9	9.7	7.6	5.4	5.4
67.5°	9.7	9.7	8.5	7.6	6.4	5.4	5.4	4.3	4.3	4.3	4.3
70°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3
72.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
75°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
77.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
80°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6
2.5°	1697.2	1635.0	1546.8	1501.8	1462.0	1451.2	1369.6	1317.0	1254.8	1190.3	1122.6
5°	2223.5	2064.6	1895.9	1754.3	1682.2	1640.3	1481.3	1362.2	1247.2	1124.8	1020.4
7.5°	2745.6	2461.0	2215.0	1986.2	1860.6	1765.9	1538.3	1358.9	1184.9	1025.9	885.1
10°	3250.5	2840.2	2448.2	2138.8	1965.8	1825.0	1530.7	1297.7	1079.5	896.9	749.8
12.5°	3761.9	3163.5	2642.5	2220.4	2014.1	1833.7	1479.2	1195.7	964.7	771.4	618.8
15°	4218.3	3414.9	2764.0	2239.6	1990.6	1777.8	1378.2	1065.7	835.7	643.4	510.2
17.5°	4535.2	3550.4	2771.4	2168.9	1891.7	1663.0	1237.5	929.1	705.7	536.0	418.9
20°	4679.2	3545.9	2669.4	2021.7	1731.6	1493.1	1071.0	789.6	588.6	450.1	350.2
22.5°	4636.2	3410.6	2488.9	1813.3	1536.1	1297.7	916.3	666.0	506.0	386.7	307.2
25°	4421.4	3174.2	2277.3	1604.8	1325.5	1103.2	776.7	569.3	439.3	349.1	279.2
27.5°	4070.1	2852.0	1992.6	1361.0	1105.3	932.5	654.2	491.9	386.7	308.4	291.1
30°	3556.7	2461.0	1658.5	1097.8	892.6	738.0	530.6	396.3	309.3	273.9	275.0
32.5°	2990.6	2030.2	1304.1	839.0	672.5	569.3	392.1	277.1	226.7	224.4	225.6
35°	2426.7	1581.2	970.1	613.4	493.1	410.4	252.4	174.1	168.7	167.6	169.6
37.5°	1926.1	1176.2	699.3	428.6	326.6	250.2	136.4	118.1	113.9	116.0	117.1
40°	1438.3	825.0	472.7	253.6	158.9	115.0	82.8	76.3	74.0	75.2	75.2
42.5°	989.4	515.6	281.5	105.2	76.3	63.3	52.6	49.4	47.2	46.2	47.2
45°	532.8	321.2	109.6	53.7	45.1	40.8	33.3	31.1	30.1	29.0	29.0
47.5°	340.6	119.3	49.4	33.3	29.0	26.8	22.6	20.4	19.2	18.3	18.3
50°	127.8	46.2	30.1	21.5	18.3	17.2	13.9	12.9	11.9	11.9	11.9
52.5°	44.1	28.0	19.2	13.9	11.9	10.7	9.7	8.5	8.5	8.5	8.5
55°	24.6	17.2	11.9	8.5	8.5	7.6	7.6	7.6	7.6	7.6	7.6
57.5°	15.0	9.7	7.6	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6
60°	8.5	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6
62.5°	5.4	5.4	5.4	5.4	5.4	6.4	6.4	7.6	7.6	7.6	7.6
65°	5.4	5.4	5.4	5.4	5.4	6.4	6.4	7.6	7.6	7.6	7.6
67.5°	4.3	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	8.5	7.6
70°	5.4	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5
72.5°	5.4	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5
75°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5	8.5
77.5°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7	8.5
80°	5.4	5.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	9.7	9.7
82.5°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	9.7	9.7	9.7
85°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	9.7	9.7	9.7
87.5°	5.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6
2.5°	1086.1	1023.8	973.2	974.4	932.5	900.2	859.4	836.8	818.6	788.4	760.6
5°	944.2	848.6	776.7	762.6	714.4	664.9	614.5	576.9	550.1	520.9	494.1
7.5°	790.6	681.0	598.4	579.0	538.2	491.9	445.7	408.2	376.0	344.9	312.6
10°	641.4	541.3	466.1	446.9	406.0	357.7	313.7	280.4	255.6	231.0	206.3
12.5°	518.8	430.8	359.8	335.2	301.9	264.3	228.8	196.6	169.6	158.9	155.8
15°	420.1	336.1	280.4	260.0	232.0	193.3	173.0	167.6	166.5	166.5	166.5
17.5°	339.5	273.9	223.4	201.9	188.0	185.7	185.7	185.7	186.9	189.1	193.3
20°	284.6	226.7	207.3	209.5	209.5	211.6	215.9	219.1	223.4	228.8	235.2
22.5°	252.4	240.6	238.5	244.8	246.0	252.4	260.9	267.5	275.0	283.6	288.9
25°	276.1	280.4	283.6	293.2	296.5	307.2	320.0	329.8	338.4	348.0	354.4
27.5°	300.8	308.4	314.7	324.5	326.6	340.6	351.3	357.7	364.1	368.4	372.8
30°	283.6	291.1	297.6	306.2	306.2	321.2	326.6	331.9	337.3	339.5	343.7
32.5°	233.2	240.6	247.1	253.6	254.6	265.4	271.8	273.9	278.2	279.2	282.5
35°	175.0	178.4	184.8	190.2	191.2	198.7	204.0	206.3	209.5	209.5	211.6
37.5°	120.3	122.4	127.8	131.1	133.2	138.5	141.9	143.9	146.1	147.3	148.2
40°	78.4	79.5	82.8	85.9	88.1	91.3	93.5	95.6	96.7	98.9	98.9
42.5°	48.4	49.4	51.5	53.7	53.7	56.9	58.0	60.2	61.3	62.3	62.3
45°	30.1	31.1	31.1	32.2	33.3	34.4	36.5	36.5	37.6	37.6	37.6
47.5°	18.3	19.2	18.3	19.2	19.2	20.4	21.5	21.5	21.5	21.5	21.5
50°	11.9	11.9	11.9	11.9	11.9	11.9	12.9	12.9	12.9	12.9	11.9
52.5°	8.5	8.5	7.6	8.5	7.6	7.6	7.6	7.6	7.6	7.6	6.4
55°	7.6	7.6	7.6	7.6	6.4	6.4	6.4	5.4	5.4	4.3	4.3
57.5°	7.6	7.6	6.4	6.4	6.4	5.4	5.4	5.4	4.3	4.3	3.2
60°	7.6	7.6	6.4	6.4	6.4	5.4	5.4	4.3	4.3	3.2	3.2
62.5°	7.6	7.6	6.4	6.4	6.4	6.4	5.4	5.4	4.3	4.3	3.2
65°	7.6	7.6	7.6	6.4	6.4	6.4	5.4	5.4	4.3	4.3	3.2
67.5°	7.6	7.6	7.6	7.6	6.4	6.4	6.4	5.4	4.3	4.3	3.2
70°	7.6	7.6	7.6	7.6	7.6	6.4	6.4	5.4	5.4	4.3	3.2
72.5°	8.5	8.5	7.6	7.6	7.6	6.4	6.4	5.4	5.4	4.3	4.3
75°	8.5	8.5	7.6	7.6	7.6	6.4	6.4	5.4	5.4	4.3	4.3
77.5°	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4	5.4	5.4	4.3
80°	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4	5.4	5.4	4.3
82.5°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	5.4	5.4	4.3
85°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	5.4	5.4	4.3
87.5°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	5.4	5.4	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192418

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6	1224.6
2.5°	734.8	720.8	719.7	707.8	684.3	696.2	681.0	670.3
5°	470.5	455.4	440.4	442.6	425.4	428.6	416.7	410.4
7.5°	298.6	282.5	278.2	278.2	258.9	258.9	251.4	247.1
10°	188.0	175.0	170.8	163.3	154.6	153.6	150.4	149.2
12.5°	152.6	152.6	149.2	150.4	150.4	150.4	149.2	149.2
15°	166.5	167.6	164.3	165.4	167.6	166.5	167.6	167.6
17.5°	192.3	197.6	193.3	195.5	199.8	198.7	199.8	200.9
20°	235.2	243.9	238.5	242.8	248.1	247.1	250.2	251.4
22.5°	293.2	304.0	298.6	303.0	311.5	309.3	313.7	315.7
25°	357.7	368.4	362.0	367.4	372.8	374.8	374.8	376.0
27.5°	372.8	379.2	374.8	380.2	382.4	384.5	382.4	383.6
30°	341.5	346.9	342.7	348.0	348.0	350.2	348.0	345.9
32.5°	281.5	285.8	280.4	286.8	285.8	286.8	287.9	288.9
35°	212.7	214.9	211.6	212.7	213.7	214.9	218.0	218.0
37.5°	148.2	151.5	148.2	149.2	149.2	151.5	153.6	153.6
40°	98.9	102.0	98.9	101.0	99.8	101.0	103.2	103.2
42.5°	62.3	64.5	62.3	63.3	63.3	63.3	64.5	65.5
45°	37.6	38.7	37.6	38.7	38.7	38.7	39.8	39.8
47.5°	21.5	22.6	21.5	21.5	22.6	21.5	22.6	22.6
50°	11.9	11.9	11.9	11.9	11.9	10.7	10.7	11.9
52.5°	6.4	6.4	5.4	5.4	5.4	5.4	5.4	5.4
55°	3.2	3.2	2.2	2.2	2.2	1.1	2.2	1.1
57.5°	2.2	2.2	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	3.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.2	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.2	3.2	2.2	2.2	1.1	1.1	1.1	0.0
80°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
82.5°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
85°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
87.5°	3.2	3.2	2.2	2.2	2.2	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)