

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192420

Luminaire Tested: **LDA6A50950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5090.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64370	64370	64370
5°	164874	59355	21759
10°	347667	47361	6157
15°	501399	33593	5119
20°	565912	22309	7211
25°	614443	22483	51922
30°	683409	14825	18155
35°	690452	8412	6973
40°	695045	3464	3156
45°	689343	2171	1837
50°	541091	1467	1279
55°	162842	1023	612
60°	34394	932	471
65°	3904	1103	415
70°	1026	1362	689
75°	233	1800	911
80°	0	3062	1357
85°	0	5346	2705

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.7	2.9
10°-20°	709.6	13.9
20°-30°	1337.9	26.3
30°-40°	1484.0	29.2
40°-50°	1130.9	22.2
50°-60°	252.3	5.0
60°-70°	13.8	0.3
70°-80°	6.3	0.1
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2197.2	43.2
0°-40°	3681.2	72.3
0°-60°	5064.5	99.5
0°-90°	5090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5090.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1174	1174	1174	1174	1174	
5°	2996	2220	1079	518	395	388
15°	8835	4836	592	105	90	2463
25°	10158	5655	372	621	858	4728
35°	10317	3518	126	111	104	6462
45°	8892	1036	28	29	24	6621
55°	1704	45	11	10	6	2103
65°	30	8	8	8	3	70
75°	1	4	8	8	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2
2.5°	2015.3	1979.8	1975.5	1963.7	1871.4	1870.3	1869.2	1820.8	1776.8	1754.3	1658.6
5°	2996.1	2970.2	2938.0	2897.2	2744.7	2723.1	2705.0	2633.0	2478.3	2388.2	2219.5
7.5°	4425.9	4412.0	4249.8	4228.2	3947.8	3879.2	3811.4	3626.7	3328.0	3134.7	2836.0
10°	6245.6	6179.2	6055.6	5888.1	5522.7	5392.8	5267.1	4888.9	4379.8	3974.8	3466.5
12.5°	7890.4	7805.5	7655.1	7459.6	6999.8	6822.5	6623.9	6159.7	5537.8	4879.3	4160.5
15°	8834.6	8820.7	8646.6	8567.1	8196.6	8016.1	7851.7	7317.8	6541.1	5766.6	4836.3
17.5°	9393.3	9394.4	9266.5	9219.2	8874.4	8702.5	8564.0	8175.0	7361.8	6421.9	5348.7
20°	9700.5	9731.7	9612.4	9538.3	9297.7	9145.1	9016.2	8615.5	7907.6	6864.4	5638.8
22.5°	9929.3	9944.3	9799.3	9738.1	9468.5	9321.3	9239.6	8856.2	8164.3	7100.7	5726.9
25°	10158.2	10150.6	9987.2	9864.8	9599.4	9456.6	9356.8	9024.8	8271.7	7155.5	5654.9
27.5°	10399.8	10434.1	10131.3	9935.7	9698.3	9530.8	9419.1	9076.4	8264.2	7012.7	5393.8
30°	10796.2	10518.0	10215.0	9945.4	9672.5	9495.3	9367.5	8931.4	8056.9	6633.4	4897.6
32.5°	10629.7	10433.2	10135.5	9858.4	9566.2	9370.7	9214.9	8697.1	7621.8	6009.3	4231.4
35°	10317.1	10264.5	9970.2	9744.6	9412.5	9202.0	9020.4	8336.2	6947.2	5258.6	3518.2
37.5°	10035.6	9980.9	9805.7	9572.6	9195.6	8975.3	8642.3	7762.6	6069.5	4318.5	2767.2
40°	9712.4	9699.5	9503.8	9287.9	8834.6	8428.6	8083.7	6750.5	5024.2	3395.7	2152.8
42.5°	9354.6	9347.0	9188.1	8869.0	8203.0	7699.1	7122.2	5608.7	3863.1	2577.1	1599.5
45°	8891.6	8847.5	8573.6	8108.4	7152.4	6424.0	5740.8	4285.1	2832.8	1841.2	1035.6
47.5°	8089.1	8011.7	7612.2	6816.1	5669.9	4925.4	4297.0	2946.7	1767.2	1040.9	513.6
50°	6344.5	6139.3	5570.0	4733.1	3557.8	2911.2	2417.1	1462.1	784.2	516.7	328.7
52.5°	3918.8	3697.5	3159.3	2527.7	1623.2	1257.9	1037.7	704.7	434.0	297.6	126.7
55°	1703.8	1599.5	1320.3	1050.6	751.0	597.3	515.6	356.7	225.6	108.5	45.1
57.5°	665.0	644.5	561.9	473.7	355.6	290.1	256.7	161.1	62.3	38.7	25.8
60°	313.7	293.3	252.4	209.5	131.1	94.4	73.0	45.1	31.1	23.7	17.2
62.5°	85.9	74.0	60.2	51.5	39.8	35.4	31.1	24.6	19.2	15.0	11.9
65°	30.1	30.1	26.8	24.6	20.4	18.3	17.2	13.9	11.9	9.7	7.6
67.5°	13.9	13.9	12.9	11.9	9.7	9.7	8.5	7.6	6.4	5.4	5.4
70°	6.4	5.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3	4.3	4.3
72.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.2	4.3	4.3	4.3
75°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	4.3
77.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	4.3
80°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	4.3
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3	4.3
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2
2.5°	1617.8	1577.0	1523.3	1434.2	1394.3	1385.8	1312.7	1246.1	1187.1	1144.1	1076.4
5°	2109.8	1991.6	1847.8	1674.7	1609.2	1563.0	1423.4	1290.1	1176.3	1078.6	975.4
7.5°	2597.6	2363.3	2147.4	1895.0	1772.6	1680.1	1472.8	1283.8	1111.9	978.6	842.3
10°	3067.0	2734.0	2368.7	2036.8	1872.4	1732.7	1461.0	1221.4	1006.5	850.8	706.9
12.5°	3512.8	3034.7	2549.2	2107.8	1911.1	1736.1	1403.0	1121.5	890.6	723.0	572.6
15°	3955.4	3252.8	2654.5	2122.7	1885.3	1674.7	1297.7	988.2	760.6	591.9	459.8
17.5°	4231.4	3374.2	2655.5	2056.1	1788.7	1558.8	1153.8	849.7	628.4	476.9	361.0
20°	4367.9	3359.2	2554.7	1902.6	1624.3	1392.1	983.9	708.0	508.1	382.4	284.6
22.5°	4328.2	3226.0	2377.3	1699.5	1441.6	1221.4	837.8	594.0	438.4	331.9	257.8
25°	4141.3	3010.1	2167.8	1508.2	1261.2	1052.8	735.8	546.7	431.9	371.7	320.2
27.5°	3817.8	2726.5	1911.1	1307.4	1085.0	918.4	667.1	530.6	446.9	400.7	405.0
30°	3341.0	2350.5	1579.1	1038.8	849.7	714.4	500.6	369.5	272.8	234.2	234.2
32.5°	2807.1	1921.8	1220.3	768.0	614.5	518.9	352.5	252.4	201.9	183.7	175.0
35°	2306.4	1503.9	905.6	556.5	443.7	369.5	231.0	141.9	130.0	125.7	123.6
37.5°	1814.4	1129.0	656.3	403.9	308.4	245.0	118.1	91.3	79.5	74.0	69.8
40°	1359.9	792.8	454.5	247.1	170.8	112.8	68.7	56.0	49.4	48.4	46.2
42.5°	951.7	531.8	281.5	108.5	79.5	63.3	47.2	39.8	36.5	35.4	34.4
45°	557.4	331.9	115.0	60.2	49.4	44.1	34.4	30.1	28.0	28.0	26.8
47.5°	350.2	134.3	61.3	38.7	33.3	31.1	25.8	22.6	21.5	21.5	21.5
50°	143.9	59.1	36.5	26.8	23.7	22.6	19.2	17.2	17.2	17.2	17.2
52.5°	52.6	33.3	24.6	19.2	17.2	16.1	13.9	12.9	12.9	13.9	12.9
55°	30.1	22.6	17.2	13.9	11.9	11.9	10.7	10.7	10.7	10.7	10.7
57.5°	19.2	15.0	11.9	9.7	8.5	8.5	8.5	8.5	8.5	9.7	8.5
60°	12.9	10.7	8.5	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5
62.5°	9.7	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5
65°	7.6	6.4	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7
67.5°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7
70°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7
72.5°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7
75°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5	9.7
77.5°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5	9.7
80°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7	9.7
82.5°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	9.7	9.7
85°	5.4	6.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5	9.7
87.5°	5.4	5.4	6.4	6.4	6.4	7.6	7.6	8.5	8.5	8.5	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2
2.5°	1030.2	982.9	944.3	923.8	901.4	862.7	826.2	792.8	778.8	733.7	742.2
5°	894.9	814.3	749.8	720.8	687.4	633.8	586.6	541.3	517.8	479.1	465.2
7.5°	744.5	649.9	572.6	539.2	510.2	459.8	415.8	373.9	343.7	304.1	288.0
10°	596.1	506.0	435.0	406.1	373.9	323.3	279.2	242.8	218.1	188.0	173.0
12.5°	471.5	390.9	319.1	290.1	263.2	221.3	186.9	153.6	126.7	110.6	106.3
15°	367.4	290.1	231.0	207.4	184.8	143.9	118.1	109.6	105.2	101.0	99.8
17.5°	276.1	213.7	161.1	137.5	124.6	113.9	109.6	105.2	103.2	99.8	101.0
20°	212.8	152.6	131.1	127.8	125.7	120.3	119.3	118.1	117.1	118.1	120.3
22.5°	201.9	190.2	196.6	200.9	210.6	211.6	228.9	242.8	255.7	291.1	308.4
25°	340.6	361.0	393.2	413.6	441.5	470.6	524.3	571.5	621.0	666.0	705.7
27.5°	426.5	436.2	436.2	446.9	435.0	433.0	426.5	421.1	443.7	436.2	459.8
30°	236.3	247.1	265.4	275.0	286.8	295.4	292.2	281.5	288.0	279.2	288.0
32.5°	168.7	168.7	173.0	174.1	176.2	177.2	178.4	179.4	180.4	175.0	178.4
35°	120.3	116.0	113.9	113.9	112.8	110.6	109.6	109.6	110.6	105.2	107.4
37.5°	67.6	65.5	65.5	65.5	65.5	65.5	66.7	67.6	67.6	67.6	69.8
40°	45.1	45.1	45.1	46.2	46.2	46.2	47.2	47.2	48.4	48.4	49.4
42.5°	34.4	33.3	34.4	34.4	34.4	35.4	35.4	36.5	36.5	36.5	37.6
45°	26.8	26.8	26.8	26.8	28.0	28.0	28.0	28.0	29.0	28.0	29.0
47.5°	21.5	21.5	21.5	22.6	22.6	21.5	22.6	22.6	22.6	22.6	22.6
50°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	18.3	17.2	18.3
52.5°	13.9	12.9	12.9	12.9	12.9	11.9	11.9	12.9	12.9	11.9	11.9
55°	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7	9.7
57.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6
60°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6	7.6	6.4
62.5°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6	6.4	6.4
65°	9.7	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4	6.4
67.5°	9.7	9.7	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4
70°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4
72.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6
75°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6
77.5°	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6	6.4
80°	9.7	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	7.6	6.4
82.5°	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4	6.4
85°	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4	6.4	6.4
87.5°	8.5	8.5	8.5	7.6	7.6	7.6	7.6	6.4	6.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192420

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2	1174.2
2.5°	697.2	682.1	695.0	678.9	673.6	661.8	656.3	661.8
5°	439.3	423.2	426.5	415.8	398.5	398.5	393.2	395.4
7.5°	265.4	249.3	250.3	240.6	227.8	225.6	220.2	222.5
10°	153.6	136.4	136.4	125.7	115.0	113.9	110.6	110.6
12.5°	102.0	99.8	97.8	96.7	94.4	94.4	94.4	92.5
15°	95.6	94.4	93.5	93.5	91.3	91.3	92.5	90.2
17.5°	97.8	96.7	95.6	95.6	95.6	95.6	96.7	94.4
20°	117.1	118.1	118.1	121.4	123.6	124.6	127.8	123.6
22.5°	307.2	316.9	324.5	364.1	398.5	385.6	409.2	369.5
25°	734.9	761.7	784.2	788.5	810.1	840.1	859.4	858.4
27.5°	459.8	460.8	473.7	473.7	469.5	486.7	498.4	496.3
30°	283.6	282.6	286.8	276.1	275.0	282.6	286.8	286.8
32.5°	175.0	174.1	177.2	175.0	169.6	178.4	176.2	176.2
35°	105.2	106.3	104.2	104.2	99.8	104.2	103.2	104.2
37.5°	68.7	67.6	66.7	66.7	64.5	65.5	64.5	62.3
40°	48.4	48.4	47.2	47.2	46.2	45.1	45.1	44.1
42.5°	36.5	36.5	35.4	35.4	34.4	33.3	33.3	32.2
45°	28.0	26.8	25.8	25.8	25.8	24.6	24.6	23.7
47.5°	21.5	21.5	21.5	20.4	20.4	19.2	19.2	18.3
50°	17.2	17.2	17.2	17.2	16.1	16.1	16.1	15.0
52.5°	11.9	11.9	10.7	10.7	9.7	9.7	9.7	8.5
55°	8.5	8.5	8.5	7.6	7.6	7.6	6.4	6.4
57.5°	7.6	7.6	6.4	6.4	6.4	5.4	5.4	5.4
60°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
62.5°	5.4	5.4	5.4	4.3	4.3	4.3	4.3	3.2
65°	5.4	5.4	4.3	4.3	4.3	3.2	3.2	3.2
67.5°	5.4	5.4	5.4	4.3	4.3	4.3	4.3	3.2
70°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
72.5°	6.4	5.4	5.4	5.4	5.4	4.3	4.3	4.3
75°	6.4	6.4	5.4	5.4	5.4	5.4	5.4	4.3
77.5°	6.4	5.4	5.4	5.4	5.4	5.4	4.3	4.3
80°	6.4	5.4	5.4	5.4	5.4	4.3	4.3	4.3
82.5°	6.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
85°	5.4	5.4	4.3	4.3	4.3	4.3	4.3	4.3
87.5°	4.3	4.3	3.2	3.2	3.2	2.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)