

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179716

Luminaire Tested: **LDA6A55827D010TE LARH40FL 6LA1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55827D010TE LARH40FL 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5358.4 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179716

CATALOG NUMBER: LDA6A55827D010TE LARH40FL 6LA1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179716

CATALOG NUMBER: LDA6A55827D010TE LARH40FL 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	115	112	110	109		112	110	108	107		106	105	104			103	101	100			99
2	110	107	103	101		108	105	102	100		102	99	97			99	97	95			96
3	107	101	98	94		105	100	97	94		98	95	92			95	93	91			93
4	103	97	93	89		101	96	92	89		94	90	88			92	89	87			90
5	99	93	88	85		98	92	88	84		90	87	84			89	85	83			87
6	96	89	84	81		94	88	84	81		87	83	80			85	82	80			84
7	92	85	81	77		91	85	80	77		84	80	77			82	79	76			81
8	89	82	77	74		88	82	77	74		81	77	74			80	76	74			79
9	86	79	74	71		85	79	74	71		78	74	71			77	73	71			76
10	84	76	72	69		83	76	71	69		75	71	68			74	71	68			74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	760274
5°	661890
10°	598041
15°	546445
20°	400143
25°	197449
30°	43842
35°	8881
40°	1481
45°	434
50°	77
55°	86
60°	99
65°	117
70°	144
75°	0
80°	0
85°	0



TEST NUMBER: P179716

CATALOG NUMBER: LDA6A55827D010TE LARH40FL 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1115.0	20.8
10°-20°	2587.1	48.3
20°-30°	1517.5	28.3
30°-40°	131.3	2.5
40°-50°	5.7	0.1
50°-60°	0.8	0.0
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5219.5	97.4
0°-40°	5350.8	99.9
0°-60°	5357.4	100.0
0°-90°	5358.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5358.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13868	
5°	12028	###
15°	9628	2587
25°	3264	1518
35°	133	131
45°	6	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P179716

CATALOG NUMBER: LDA6A55827D010TE LARH40FL 6LA1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13868.5
2.5°	13031.9
5°	12027.9
7.5°	11359.8
10°	10743.4
12.5°	10230.6
15°	9628.3
17.5°	8587.6
20°	6859.0
22.5°	4960.0
25°	3264.3
27.5°	1839.7
30°	692.6
32.5°	357.6
35°	132.7
37.5°	40.5
40°	20.7
42.5°	11.3
45°	5.6
47.5°	2.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)