

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205168

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.7 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205168

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBWL11

Luminous Intensity Polar Plot






TEST NUMBER: P205168

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	93	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	43	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205168

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	6.0
10°-20°	249.2	18.1
20°-30°	375.7	27.3
30°-40°	384.5	28.0
40°-50°	224.0	16.3
50°-60°	51.5	3.7
60°-70°	6.3	0.5
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.8	51.5
0°-40°	1092.4	79.4
0°-60°	1367.9	99.4
0°-90°	1375.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	860	
5°	864	83
15°	883	249
25°	824	376
35°	624	385
45°	289	224
55°	50	51
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205168

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	859.5
2.5°	858.0
5°	864.2
7.5°	870.5
10°	878.2
12.5°	879.8
15°	882.9
17.5°	879.8
20°	872.0
22.5°	847.0
25°	823.6
27.5°	786.2
30°	737.9
32.5°	687.9
35°	624.0
37.5°	552.2
40°	472.6
42.5°	383.8
45°	288.6
47.5°	201.2
50°	132.6
52.5°	84.2
55°	49.9
57.5°	26.5
60°	14.0
62.5°	7.8
65°	4.6
67.5°	4.6
70°	3.1
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)