

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203526

Luminaire Tested: **LE_6B10D010 EC6B10209035 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209035 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 923.7 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203526

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203526

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203526

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	6.9
10°-20°	170.5	18.5
20°-30°	229.0	24.8
30°-40°	187.8	20.3
40°-50°	112.8	12.2
50°-60°	75.0	8.1
60°-70°	50.3	5.4
70°-80°	27.1	2.9
80°-90°	7.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	463.2	50.1
0°-40°	651.0	70.5
0°-60°	838.7	90.8
0°-90°	923.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	689	
5°	678	64
15°	608	171
25°	504	229
35°	298	188
45°	143	113
55°	83	75
65°	51	50
75°	26	27
85°	6	8
90°	0	



TEST NUMBER: P203526

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	689.2
2.5°	684.1
5°	677.8
7.5°	663.8
10°	647.1
12.5°	626.8
15°	607.6
17.5°	584.8
20°	561.8
22.5°	536.4
25°	504.5
27.5°	466.2
30°	415.2
32.5°	358.0
35°	298.1
37.5°	247.1
40°	203.9
42.5°	169.4
45°	142.6
47.5°	121.0
50°	105.8
52.5°	93.0
55°	82.8
57.5°	73.9
60°	66.2
62.5°	57.4
65°	51.0
67.5°	43.4
70°	37.0
72.5°	30.6
75°	25.5
77.5°	20.4
80°	15.2
82.5°	11.5
85°	6.4
87.5°	2.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)