

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203320

Luminaire Tested: **LE_6B10D010 EC6B10209035 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209035 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 909.1 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203320

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203320

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203320

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.7	11.4
10°-20°	254.5	28.0
20°-30°	294.5	32.4
30°-40°	188.3	20.7
40°-50°	53.4	5.9
50°-60°	9.5	1.0
60°-70°	3.9	0.4
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.7	71.8
0°-40°	841.0	92.5
0°-60°	903.9	99.4
0°-90°	909.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1134	
5°	1114	104
15°	913	255
25°	650	295
35°	297	188
45°	62	53
55°	9	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203320

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1134.1
2.5°	1132.9
5°	1114.0
7.5°	1079.8
10°	1031.8
12.5°	976.1
15°	912.9
17.5°	847.1
20°	782.6
22.5°	719.5
25°	649.9
27.5°	574.0
30°	489.4
32.5°	394.5
35°	297.1
37.5°	215.0
40°	149.2
42.5°	98.6
45°	62.0
47.5°	36.6
50°	21.5
52.5°	12.6
55°	8.9
57.5°	7.6
60°	6.4
62.5°	5.0
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)