

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204661

Luminaire Tested: **LE_6B10D010 EC6B10209035 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209035 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1250.8 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204661

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204661

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204661

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	3.8
10°-20°	136.1	10.9
20°-30°	205.0	16.4
30°-40°	243.9	19.5
40°-50°	243.5	19.5
50°-60°	198.0	15.8
60°-70°	121.8	9.7
70°-80°	47.2	3.8
80°-90°	7.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.9	31.1
0°-40°	632.8	50.6
0°-60°	1074.3	85.9
0°-90°	1250.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1250.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	504	
5°	502	48
15°	483	136
25°	446	205
35°	391	244
45°	316	243
55°	222	198
65°	122	122
75°	43	47
85°	6	8
90°	0	



TEST NUMBER: P204661

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	504.0
2.5°	504.8
5°	502.5
7.5°	499.5
10°	495.9
12.5°	489.1
15°	483.2
17.5°	474.4
20°	464.8
22.5°	455.8
25°	446.1
27.5°	432.9
30°	419.5
32.5°	406.9
35°	390.6
37.5°	372.8
40°	356.5
42.5°	336.5
45°	316.5
47.5°	295.0
50°	272.0
52.5°	248.2
55°	221.6
57.5°	195.6
60°	170.5
62.5°	146.0
65°	122.2
67.5°	100.0
70°	79.2
72.5°	60.0
75°	43.0
77.5°	28.1
80°	17.0
82.5°	10.4
85°	5.9
87.5°	3.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)