

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204453

Luminaire Tested: **LE_6B10D010 EC6B10209035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1054.3 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204453

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204453

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	101	98	100	98	95		97	94	93		93
2	102	95	89	84	100	93	88	83	90	85	81		86	83	79		84
3	94	84	77	72	91	83	76	71	80	74	70		77	73	68		75
4	86	76	68	62	84	74	67	61	72	65	60		70	64	60		68
5	80	68	60	54	78	67	59	53	65	58	53		63	57	52		61
6	74	62	53	47	72	61	53	47	59	52	47		57	51	46		56
7	69	56	48	42	67	55	48	42	54	47	42		52	46	41		51
8	64	51	43	38	63	51	43	38	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		45	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204453

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	4.2
10°-20°	124.6	11.8
20°-30°	185.3	17.6
30°-40°	215.6	20.4
40°-50°	210.1	19.9
50°-60°	161.6	15.3
60°-70°	89.3	8.5
70°-80°	23.7	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.7	33.6
0°-40°	569.3	54.0
0°-60°	941.1	89.3
0°-90°	1054.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	465	
5°	462	44
15°	441	125
25°	402	185
35°	346	216
45°	273	210
55°	180	162
65°	90	89
75°	20	24
85°	0	0
90°	0	



TEST NUMBER: P204453

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	465.1
2.5°	465.1
5°	462.4
7.5°	458.4
10°	455.8
12.5°	447.8
15°	441.0
17.5°	434.4
20°	425.0
22.5°	415.6
25°	402.2
27.5°	388.9
30°	375.5
32.5°	360.9
35°	346.1
37.5°	327.4
40°	311.4
42.5°	294.0
45°	272.6
47.5°	252.6
50°	229.9
52.5°	205.8
55°	180.4
57.5°	156.4
60°	133.6
62.5°	110.9
65°	89.5
67.5°	69.5
70°	50.8
72.5°	34.8
75°	20.0
77.5°	9.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)