

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204038

Luminaire Tested: **LE_6B10D010 EC6B10208050 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208050 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 993.6 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204038

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204038

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103	109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90	102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79	96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	64	85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59	80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54	75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50	71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46	67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43	64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204038

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	7.6
10°-20°	200.6	20.2
20°-30°	267.8	26.9
30°-40°	216.0	21.7
40°-50°	103.5	10.4
50°-60°	61.4	6.2
60°-70°	40.8	4.1
70°-80°	21.8	2.2
80°-90°	6.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.0	54.8
0°-40°	760.0	76.5
0°-60°	924.9	93.1
0°-90°	993.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	993.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	815	
5°	805	76
15°	714	201
25°	586	268
35°	346	216
45°	128	104
55°	68	61
65°	41	41
75°	20	22
85°	5	6
90°	0	



TEST NUMBER: P204038

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	814.8
2.5°	814.8
5°	805.4
7.5°	789.5
10°	767.4
12.5°	743.8
15°	713.8
17.5°	685.4
20°	653.8
22.5°	620.6
25°	585.9
27.5°	549.5
30°	497.4
32.5°	424.8
35°	345.9
37.5°	273.1
40°	211.6
42.5°	164.2
45°	127.9
47.5°	101.0
50°	85.2
52.5°	75.8
55°	67.9
57.5°	61.6
60°	53.8
62.5°	47.4
65°	41.0
67.5°	34.8
70°	30.0
72.5°	25.2
75°	20.5
77.5°	15.8
80°	12.6
82.5°	9.5
85°	4.8
87.5°	1.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)