

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204450

Luminaire Tested: **LE_6B10D010 EC6B10208050 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208050 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1260.1 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204450

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204450

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204450

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	4.2
10°-20°	148.9	11.8
20°-30°	221.4	17.6
30°-40°	257.7	20.4
40°-50°	251.2	19.9
50°-60°	193.2	15.3
60°-70°	106.8	8.5
70°-80°	28.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.8	33.5
0°-40°	680.4	54.0
0°-60°	1124.8	89.3
0°-90°	1260.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1260.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	553	52
15°	527	149
25°	481	221
35°	414	258
45°	326	251
55°	216	193
65°	107	107
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P204450

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	555.9
2.5°	555.9
5°	552.6
7.5°	547.9
10°	544.6
12.5°	535.1
15°	527.1
17.5°	519.1
20°	507.9
22.5°	496.8
25°	480.8
27.5°	464.8
30°	448.9
32.5°	431.2
35°	413.8
37.5°	391.4
40°	372.1
42.5°	351.4
45°	325.9
47.5°	301.9
50°	274.8
52.5°	246.0
55°	215.6
57.5°	186.9
60°	159.8
62.5°	132.6
65°	107.0
67.5°	83.0
70°	60.8
72.5°	41.5
75°	24.0
77.5°	11.1
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)