

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202493

Luminaire Tested: **LE_6B10D010 EC6B10208050 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208050 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1446.6 lumens
Efficiency: N/A
Efficacy: 146.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202493

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202493

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	82		87	84	81		84	81	79
3	95	86	79	73	92	84	78	73		81	76	71		79	74	70		76	72	69
4	88	77	70	64	86	76	69	63		74	67	62		71	66	62		69	65	61
5	81	70	62	56	79	69	61	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		59	53	49		58	53	48
7	70	58	50	45	69	57	50	45		56	49	44		55	48	44		53	48	44
8	66	54	46	40	64	53	45	40		52	45	40		50	44	40		49	44	40
9	62	49	42	37	61	49	42	37		48	41	37		47	41	36		46	40	36
10	58	46	39	34	57	45	38	34		45	38	34		44	38	33		43	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202493

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	5.4
10°-20°	202.3	14.0
20°-30°	268.3	18.5
30°-40°	286.1	19.8
40°-50°	267.5	18.5
50°-60°	204.0	14.1
60°-70°	110.9	7.7
70°-80°	29.8	2.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.0	37.9
0°-40°	834.1	57.7
0°-60°	1305.5	90.2
0°-90°	1446.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	836	
5°	825	77
15°	721	202
25°	584	268
35°	457	286
45°	348	267
55°	230	204
65°	111	111
75°	26	30
85°	0	0
90°	0	



TEST NUMBER: P202493

CATALOG NUMBER: LE_6B10D010 EC6B10208050 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	836.5
2.5°	833.9
5°	825.0
7.5°	806.4
10°	785.1
12.5°	755.0
15°	721.2
17.5°	687.6
20°	651.2
22.5°	616.8
25°	584.0
27.5°	549.4
30°	516.6
32.5°	484.8
35°	457.2
37.5°	429.8
40°	401.4
42.5°	375.8
45°	348.2
47.5°	318.1
50°	289.8
52.5°	259.6
55°	229.5
57.5°	196.8
60°	166.6
62.5°	138.2
65°	110.8
67.5°	86.0
70°	62.9
72.5°	43.4
75°	25.8
77.5°	11.5
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)