

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179705

Luminaire Tested: **LDA6A55930D010TE LARH30NF 6LA1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26623)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55930D010TE LARH30NF 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4417.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.55
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179705

CATALOG NUMBER: LDA6A55930D010TE LARH30NF 6LA1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179705

CATALOG NUMBER: LDA6A55930D010TE LARH30NF 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	95	93		96	94	92		94
4	103	98	94	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	99	93	89	86	91	88	85		90	87	84		88
6	97	90	86	82	95	89	85	82	88	84	82		87	84	81		86
7	94	87	82	79	93	86	82	79	85	81	79		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	84	78	74	71	77	73	71		76	73	70		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	714214
5°	661538
10°	589334
15°	449707
20°	269611
25°	148587
30°	36759
35°	2844
40°	802
45°	310
50°	136
55°	153
60°	175
65°	104
70°	128
75°	169
80°	253
85°	0



TEST NUMBER: P179705

CATALOG NUMBER: LDA6A55930D010TE LARH30NF 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1106.0	25.0
10°-20°	2120.2	48.0
20°-30°	1095.0	24.8
30°-40°	88.7	2.0
40°-50°	3.6	0.1
50°-60°	1.4	0.0
60°-70°	1.1	0.0
70°-80°	0.8	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4321.2	97.8
0°-40°	4409.9	99.8
0°-60°	4415.0	100.0
0°-90°	4417.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4417.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13028	
5°	12022	###
15°	7924	2120
25°	2456	1095
35°	42	89
45°	4	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179705

CATALOG NUMBER: LDA6A55930D010TE LARH30NF 6LA1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	13028.3
2.5°	12731.1
5°	12021.5
7.5°	11375.1
10°	10587.0
12.5°	9527.3
15°	7923.8
17.5°	6143.3
20°	4621.5
22.5°	3388.0
25°	2456.5
27.5°	1479.4
30°	580.7
32.5°	246.7
35°	42.5
37.5°	20.8
40°	11.2
42.5°	6.4
45°	4.0
47.5°	2.4
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)