

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204249

Luminaire Tested: **LE_6B10D010 EC6B10209050 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209050 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1212.3 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204249

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204249

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204249

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	5.5
10°-20°	172.6	14.2
20°-30°	225.8	18.6
30°-40°	239.0	19.7
40°-50°	223.0	18.4
50°-60°	168.9	13.9
60°-70°	91.4	7.5
70°-80°	24.5	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.1	38.4
0°-40°	704.1	58.1
0°-60°	1095.9	90.4
0°-90°	1212.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1212.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	723	
5°	712	67
15°	617	173
25°	491	226
35°	382	239
45°	290	223
55°	190	169
65°	92	91
75°	21	25
85°	0	0
90°	0	



TEST NUMBER: P204249

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	723.0
2.5°	720.4
5°	712.4
7.5°	695.1
10°	672.6
12.5°	646.0
15°	616.9
17.5°	583.8
20°	554.5
22.5°	521.4
25°	490.9
27.5°	460.4
30°	431.1
32.5°	406.0
35°	382.0
37.5°	358.1
40°	335.6
42.5°	313.1
45°	290.5
47.5°	265.4
50°	240.1
52.5°	214.9
55°	189.8
57.5°	163.1
60°	138.0
62.5°	114.1
65°	91.5
67.5°	70.2
70°	51.8
72.5°	35.9
75°	21.2
77.5°	9.2
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)