

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179735

Luminaire Tested: **LDA6A55840D010TE LARH20SP 6LAL1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26678)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55840D010TE LARH20SP 6LAL1LI
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4555.7 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.45
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179735

CATALOG NUMBER: LDA6A55840D010TE LARH20SP 6LAL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179735

CATALOG NUMBER: LDA6A55840D010TE LARH20SP 6LAL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	94	90	87	99	94	90	87	92	89	86		91	88	85		89
6	97	91	87	84	96	90	86	83	89	85	83		88	85	82		87
7	95	88	84	80	93	87	83	80	86	83	80		85	82	80		84
8	92	85	81	78	91	84	80	78	83	80	77		83	79	77		82
9	89	82	78	75	88	82	78	75	81	77	75		80	77	75		80
10	87	80	75	73	86	79	75	73	79	75	72		78	75	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1102050
5°	892618
10°	578864
15°	400655
20°	279890
25°	168221
30°	17737
35°	1720
40°	1031
45°	636
50°	614
55°	879
60°	1009
65°	804
70°	657
75°	657
80°	663
85°	629



TEST NUMBER: P179735

CATALOG NUMBER: LDA6A55840D010TE LARH20SP 6LAL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1370.7	30.1
10°-20°	1985.7	43.6
20°-30°	1140.0	25.0
30°-40°	33.4	0.7
40°-50°	7.2	0.2
50°-60°	7.8	0.2
60°-70°	6.5	0.1
70°-80°	3.5	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4496.5	98.7
0°-40°	4529.9	99.4
0°-60°	4544.9	99.8
0°-90°	4555.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4555.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20103	
5°	16221	###
15°	7060	1986
25°	2781	1140
35°	26	33
45°	8	7
55°	9	8
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P179735

CATALOG NUMBER: LDA6A55840D010TE LARH20SP 6LAL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	20103.0
2.5°	19004.9
5°	16220.7
7.5°	13393.4
10°	10398.9
12.5°	8487.0
15°	7059.5
17.5°	5970.6
20°	4797.7
22.5°	3761.2
25°	2781.1
27.5°	1316.7
30°	280.2
32.5°	34.9
35°	25.7
37.5°	18.5
40°	14.4
42.5°	11.3
45°	8.2
47.5°	7.2
50°	7.2
52.5°	8.2
55°	9.2
57.5°	9.2
60°	9.2
62.5°	8.2
65°	6.2
67.5°	5.1
70°	4.1
72.5°	4.1
75°	3.1
77.5°	3.1
80°	2.1
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)