

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202499

Luminaire Tested: **LE_6B10D010 EC6B10209050 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209050 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1216.6 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202499

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202499

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	82		87	84	81		84	81	79
3	95	86	79	73		92	84	78	73		81	76	71		79	74	70		76	72	69
4	88	77	70	64		86	76	69	63		74	67	62		71	66	62		69	65	61
5	81	70	62	56		79	69	61	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		59	53	49		58	53	48
7	70	58	50	45		69	57	50	45		56	49	44		55	48	44		53	48	44
8	66	54	46	40		64	53	45	40		52	45	40		50	44	40		49	44	40
9	62	49	42	37		61	49	42	37		48	41	37		47	41	36		46	40	36
10	58	46	39	34		57	45	38	34		45	38	34		44	38	33		43	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202499

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	5.4
10°-20°	170.2	14.0
20°-30°	225.6	18.5
30°-40°	240.6	19.8
40°-50°	225.0	18.5
50°-60°	171.5	14.1
60°-70°	93.2	7.7
70°-80°	25.0	2.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.9	37.9
0°-40°	701.5	57.7
0°-60°	1098.0	90.3
0°-90°	1216.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	704	
5°	694	65
15°	607	170
25°	491	226
35°	384	241
45°	293	225
55°	193	172
65°	93	93
75°	22	25
85°	0	0
90°	0	



TEST NUMBER: P202499

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	703.5
2.5°	701.2
5°	693.9
7.5°	678.2
10°	660.2
12.5°	635.0
15°	606.6
17.5°	578.4
20°	547.8
22.5°	518.8
25°	491.1
27.5°	462.0
30°	434.5
32.5°	407.6
35°	384.5
37.5°	361.5
40°	337.6
42.5°	316.0
45°	292.9
47.5°	267.5
50°	243.8
52.5°	218.4
55°	193.0
57.5°	165.5
60°	140.1
62.5°	116.2
65°	93.1
67.5°	72.2
70°	52.9
72.5°	36.5
75°	21.6
77.5°	9.8
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)