

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202704

Luminaire Tested: **LE_6B10D010 EC6B10209050 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209050 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1023.9 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202704

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202704

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		51
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202704

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	5.8
10°-20°	169.3	16.5
20°-30°	248.2	24.2
30°-40°	258.3	25.2
40°-50°	178.7	17.5
50°-60°	77.8	7.6
60°-70°	23.8	2.3
70°-80°	7.1	0.7
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.1	46.6
0°-40°	735.4	71.8
0°-60°	991.9	96.9
0°-90°	1023.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1023.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	632	
5°	629	60
15°	601	169
25°	543	248
35°	418	258
45°	231	179
55°	84	78
65°	22	24
75°	7	7
85°	1	1
90°	0	



TEST NUMBER: P202704

CATALOG NUMBER: LE_6B10D010 EC6B10209050 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	631.5
2.5°	632.9
5°	628.9
7.5°	623.6
10°	617.0
12.5°	610.4
15°	601.0
17.5°	589.1
20°	575.9
22.5°	561.2
25°	542.6
27.5°	518.8
30°	488.2
32.5°	456.4
35°	418.0
37.5°	375.5
40°	326.4
42.5°	277.2
45°	230.9
47.5°	187.1
50°	148.6
52.5°	112.8
55°	83.6
57.5°	59.8
60°	41.1
62.5°	30.5
65°	22.5
67.5°	17.2
70°	12.0
72.5°	9.2
75°	6.6
77.5°	4.0
80°	2.6
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)