

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203634

Luminaire Tested: **LE_6B15D010 EC6B10208027 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208027 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1102.9 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203634

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203634

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203634

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.1	11.5
10°-20°	303.2	27.5
20°-30°	347.4	31.5
30°-40°	233.4	21.2
40°-50°	66.6	6.0
50°-60°	16.3	1.5
60°-70°	6.2	0.6
70°-80°	2.4	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.7	70.5
0°-40°	1011.2	91.7
0°-60°	1094.1	99.2
0°-90°	1102.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1414	
5°	1374	127
15°	1088	303
25°	758	347
35°	372	233
45°	76	67
55°	18	16
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203634

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1413.9
2.5°	1403.9
5°	1373.6
7.5°	1319.4
10°	1253.0
12.5°	1168.5
15°	1088.1
17.5°	1003.6
20°	919.1
22.5°	838.8
25°	758.2
27.5°	683.9
30°	597.4
32.5°	482.8
35°	372.1
37.5°	271.5
40°	187.0
42.5°	122.6
45°	76.4
47.5°	46.2
50°	28.1
52.5°	22.1
55°	18.1
57.5°	14.1
60°	10.0
62.5°	8.0
65°	6.0
67.5°	4.0
70°	4.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)