

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204666

Luminaire Tested: **LE_6B15D010 EC6B10208027 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208027 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1968.0 lumens
Efficiency: N/A
Efficacy: 137.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204666

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204666

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	65	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204666

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	3.8
10°-20°	214.1	10.9
20°-30°	322.5	16.4
30°-40°	383.8	19.5
40°-50°	383.1	19.5
50°-60°	311.5	15.8
60°-70°	191.7	9.7
70°-80°	74.2	3.8
80°-90°	11.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.8	31.1
0°-40°	995.6	50.6
0°-60°	1690.2	85.9
0°-90°	1968.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1968.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	793	
5°	791	75
15°	760	214
25°	702	323
35°	614	384
45°	498	383
55°	349	312
65°	192	192
75°	68	74
85°	9	12
90°	0	



TEST NUMBER: P204666

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	792.9
2.5°	794.1
5°	790.6
7.5°	785.9
10°	780.1
12.5°	769.6
15°	760.2
17.5°	746.2
20°	731.1
22.5°	717.1
25°	702.0
27.5°	681.0
30°	660.0
32.5°	640.1
35°	614.5
37.5°	586.5
40°	560.9
42.5°	529.4
45°	497.9
47.5°	464.1
50°	428.0
52.5°	390.6
55°	348.6
57.5°	307.9
60°	268.2
62.5°	229.8
65°	192.4
67.5°	157.4
70°	124.8
72.5°	94.5
75°	67.6
77.5°	44.2
80°	26.9
82.5°	16.4
85°	9.4
87.5°	4.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)