

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179787

Luminaire Tested: **LDA6A55940D010TE LARH20SP 6LFC1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26681)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55940D010TE LARH20SP 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4217.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179787

CATALOG NUMBER: LDA6A55940D010TE LARH20SP 6LFC1H

Luminous Intensity Polar Plot





TEST NUMBER: P179787

CATALOG NUMBER: LDA6A55940D010TE LARH20SP 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	113	111	109	113	111	109	107		107	105	104			103	102	101			96
2	111	107	104	102	109	106	103	101		103	100	98			100	98	96			93
3	107	103	99	96	106	101	98	95		99	96	94			96	94	92			90
4	104	98	94	91	102	97	94	91		95	92	90			93	91	89			86
5	101	94	90	87	99	94	90	87		92	89	86			91	88	85			83
6	97	91	87	84	96	90	86	83		89	85	83			88	85	82			81
7	94	88	83	80	93	87	83	80		86	82	80			85	82	79			78
8	92	85	81	78	91	84	80	77		83	80	77			83	79	77			76
9	89	82	78	75	88	82	78	75		81	77	75			80	77	74			73
10	87	80	75	73	86	79	75	73		79	75	72			78	75	72			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	867162
5°	785707
10°	553981
15°	391296
20°	269506
25°	145266
30°	10236
35°	2456
40°	1567
45°	1085
50°	895
55°	583
60°	482
65°	454
70°	272
75°	191
80°	284
85°	0



TEST NUMBER: P179787

CATALOG NUMBER: LDA6A55940D010TE LARH20SP 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1221.7	29.0
10°-20°	1926.2	45.7
20°-30°	1016.1	24.1
30°-40°	31.0	0.7
40°-50°	11.3	0.3
50°-60°	5.9	0.1
60°-70°	3.3	0.1
70°-80°	1.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4164.0	98.7
0°-40°	4195.0	99.5
0°-60°	4212.2	99.9
0°-90°	4217.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4217.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15818	
5°	14278	###
15°	6895	1926
25°	2402	1016
35°	37	31
45°	14	11
55°	6	6
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179787

CATALOG NUMBER: LDA6A55940D010TE LARH20SP 6LFC1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	15818.3
2.5°	15438.9
5°	14277.9
7.5°	12334.3
10°	9951.9
12.5°	8268.9
15°	6894.6
17.5°	5787.7
20°	4619.7
22.5°	3609.9
25°	2401.6
27.5°	941.6
30°	161.7
32.5°	49.8
35°	36.7
37.5°	27.1
40°	21.9
42.5°	17.5
45°	14.0
47.5°	11.4
50°	10.5
52.5°	7.9
55°	6.1
57.5°	5.2
60°	4.4
62.5°	4.4
65°	3.5
67.5°	2.6
70°	1.7
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)