

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203119

Luminaire Tested: **LE_6B15D010 EC6B10208027 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208027 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1657.4 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203119

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P203119

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68		
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60		
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44		
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37		
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203119

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	5.3
10°-20°	245.8	14.8
20°-30°	354.2	21.4
30°-40°	367.7	22.2
40°-50°	271.9	16.4
50°-60°	162.4	9.8
60°-70°	98.7	6.0
70°-80°	54.1	3.3
80°-90°	15.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.7	41.5
0°-40°	1055.4	63.7
0°-60°	1489.7	89.9
0°-90°	1657.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1657.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	931	
5°	925	88
15°	872	246
25°	772	354
35°	593	368
45°	350	272
55°	177	162
65°	98	99
75°	50	54
85°	12	15
90°	0	



TEST NUMBER: P203119

CATALOG NUMBER: LE_6B15D010 EC6B10208027 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	930.8
2.5°	930.8
5°	924.8
7.5°	916.8
10°	904.6
12.5°	890.6
15°	872.5
17.5°	852.4
20°	832.2
22.5°	804.1
25°	772.0
27.5°	737.8
30°	693.5
32.5°	649.4
35°	593.0
37.5°	534.8
40°	470.4
42.5°	408.1
45°	349.8
47.5°	297.5
50°	251.2
52.5°	211.1
55°	176.9
57.5°	150.8
60°	128.6
62.5°	112.6
65°	98.5
67.5°	86.5
70°	74.4
72.5°	62.4
75°	50.2
77.5°	40.2
80°	30.1
82.5°	22.1
85°	12.0
87.5°	6.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)