

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179803

Luminaire Tested: **LDA6A55940D010TE LARH30NF 6LFC1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26682)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55940D010TE LARH30NF 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4712.7 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.55
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 61
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179803

CATALOG NUMBER: LDA6A55940D010TE LARH30NF 6LFC1H

Luminous Intensity Polar Plot





TEST NUMBER: P179803

CATALOG NUMBER: LDA6A55940D010TE LARH30NF 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	95	93		96	94	92		94
4	103	98	94	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	99	93	89	86	91	88	85		90	87	84		88
6	97	90	86	83	96	89	85	82	88	84	82		87	84	81		86
7	94	87	82	79	93	86	82	79	85	81	79		84	81	78		83
8	91	84	79	76	90	83	79	76	82	79	76		81	78	76		81
9	88	81	77	74	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	746574
5°	712088
10°	639578
15°	484407
20°	288139
25°	157443
30°	35809
35°	3393
40°	1374
45°	674
50°	443
55°	421
60°	285
65°	337
70°	272
75°	191
80°	284
85°	0



TEST NUMBER: P179803

CATALOG NUMBER: LDA6A55940D010TE LARH30NF 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1187.5	25.2
10°-20°	2285.7	48.5
20°-30°	1136.8	24.1
30°-40°	87.9	1.9
40°-50°	7.8	0.2
50°-60°	3.6	0.1
60°-70°	2.2	0.0
70°-80°	1.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4610.0	97.8
0°-40°	4697.9	99.7
0°-60°	4709.3	99.9
0°-90°	4712.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13619	
5°	12940	###
15°	8535	2286
25°	2603	1137
35°	51	88
45°	9	8
55°	4	4
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179803

CATALOG NUMBER: LDA6A55940D010TE LARH30NF 6LFC1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13618.6
2.5°	13349.3
5°	12940.1
7.5°	12259.0
10°	11489.6
12.5°	10319.7
15°	8535.2
17.5°	6591.6
20°	4939.1
22.5°	3623.2
25°	2602.9
27.5°	1364.0
30°	565.7
32.5°	224.7
35°	50.7
37.5°	29.7
40°	19.2
42.5°	13.1
45°	8.7
47.5°	7.0
50°	5.2
52.5°	4.4
55°	4.4
57.5°	3.5
60°	2.6
62.5°	2.6
65°	2.6
67.5°	1.7
70°	1.7
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)