

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192494

Luminaire Tested: **LDA6A55950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4688.6 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		76	72	68
5	86	76	69	64	84	75	68	63		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	51	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	61	50	43	38		49	43	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73163	73163	73163
5°	143055	69552	25369
10°	240788	59724	5628
15°	366682	45216	9245
20°	529870	36637	103043
25°	788580	59259	29784
30°	910830	20288	5887
35°	911117	4537	3179
40°	744695	2533	1947
45°	563927	1651	1256
50°	374504	1126	861
55°	60203	965	679
60°	3761	1009	559
65°	1193	1310	662
70°	657	1475	817
75°	424	1716	1080
80°	316	2557	1610
85°	629	5095	1887

TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	3.0
10°-20°	595.7	12.7
20°-30°	1402.3	29.9
30°-40°	1477.5	31.5
40°-50°	921.3	19.6
50°-60°	132.4	2.8
60°-70°	8.5	0.2
70°-80°	6.6	0.1
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2137.3	45.6
0°-40°	3614.9	77.1
0°-60°	4668.5	99.6
0°-90°	4688.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4688.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1335	1335	1335	1335	1335	
5°	2600	2104	1264	656	461	302
15°	6461	3657	797	138	163	1924
25°	13037	4384	980	709	492	5866
35°	13614	3211	68	63	48	8212
45°	7274	889	21	23	16	5693
55°	630	16	10	11	7	1132
65°	9	7	10	8	5	13
75°	2	5	8	8	5	2
85°	1	5	8	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1948.3	1935.3	1939.3	1908.9	1868.6	1886.8	1841.1	1842.2	1813.9	1742.2	1710.8
5°	2599.6	2597.5	2594.5	2538.8	2467.1	2475.2	2408.4	2383.2	2310.4	2183.9	2104.1
7.5°	3408.5	3409.4	3394.2	3258.8	3179.0	3173.9	3068.7	2992.8	2857.3	2658.1	2512.5
10°	4325.6	4353.9	4326.4	4118.2	3969.6	3971.7	3782.6	3637.0	3419.6	3129.4	2922.1
12.5°	5402.3	5406.3	5363.9	5090.0	4863.4	4846.2	4592.4	4314.4	3983.7	3604.6	3303.2
15°	6460.9	6489.2	6434.6	6097.0	5781.5	5733.9	5410.4	5043.3	4632.9	4071.7	3657.1
17.5°	7634.7	7590.3	7445.7	6962.4	6583.2	6513.5	6165.6	5685.4	5161.6	4483.2	3939.3
20°	9082.7	9097.9	8791.5	8069.6	7428.6	7156.6	6753.1	6227.4	5574.2	4785.6	4127.3
22.5°	11151.5	11069.6	10412.3	9244.6	8280.9	7917.9	7342.7	6617.7	5882.6	5015.1	4267.8
25°	13037.1	12821.7	12216.2	10609.5	9100.9	8652.0	8056.5	6950.3	6138.4	5184.9	4384.1
27.5°	14120.1	14024.0	13337.4	11716.6	9763.2	9131.2	8293.1	7195.0	6290.0	5268.8	4417.5
30°	14388.9	14406.2	13795.5	12083.7	9919.9	9198.1	8331.5	7188.0	6188.0	5119.2	4225.4
32.5°	14320.3	14227.3	13463.7	11678.3	9502.3	8845.1	7955.4	6866.4	5781.5	4673.2	3747.2
35°	13614.4	13478.0	12538.7	10623.7	8793.5	8154.4	7347.6	6339.5	5214.2	4105.1	3211.3
37.5°	12271.7	12114.0	11030.0	9357.7	7943.2	7402.2	6704.7	5753.2	4641.0	3575.2	2740.1
40°	10406.2	10210.2	9304.3	8144.4	7029.2	6651.0	6061.5	5083.8	4046.4	3073.8	2305.4
42.5°	8662.2	8568.0	8024.1	7029.2	6278.0	5912.9	5318.5	4408.5	3453.9	2561.1	1706.7
45°	7273.9	7211.2	6850.3	6218.3	5455.9	5114.1	4554.1	3666.2	2627.9	1724.9	888.7
47.5°	6366.9	6207.1	5854.4	5191.0	4343.7	3918.0	3384.2	2415.6	1482.3	764.4	273.0
50°	4391.2	4406.4	4008.0	3276.9	2556.1	2196.1	1813.9	1111.2	490.4	166.9	47.5
52.5°	2312.4	2141.5	1861.4	1390.3	967.6	738.2	538.9	222.5	88.9	33.4	25.4
55°	629.9	553.1	441.9	312.5	168.8	118.4	77.8	41.4	29.3	23.3	16.2
57.5°	61.7	58.7	53.6	43.5	37.4	34.3	31.3	25.4	20.3	14.1	10.1
60°	34.3	33.4	31.3	27.2	24.3	22.2	20.3	17.3	12.2	9.2	8.1
62.5°	19.2	18.2	17.3	15.2	13.2	12.2	12.2	10.1	8.1	7.1	7.1
65°	9.2	9.2	9.2	9.2	9.2	8.1	7.1	7.1	7.1	7.1	7.1
67.5°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	6.0	6.0	5.1	6.0
70°	4.1	4.1	5.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.1
72.5°	2.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	4.1	4.1	5.1
75°	2.0	2.0	2.0	2.0	3.0	3.0	3.0	3.0	4.1	4.1	5.1
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	3.0	3.0	4.1	4.1	5.1
80°	1.0	1.0	1.0	2.0	2.0	2.0	2.0	3.0	4.1	4.1	5.1
82.5°	1.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.1
85°	1.0	1.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.1
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	3.0	4.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1678.5	1628.8	1579.3	1529.8	1527.8	1498.5	1455.1	1397.3	1349.8	1309.5	1269.9
5°	2024.3	1922.1	1820.0	1717.9	1687.6	1635.0	1541.0	1434.8	1343.8	1263.9	1187.1
7.5°	2371.0	2199.2	2037.4	1877.6	1813.9	1734.1	1587.5	1433.7	1302.3	1185.0	1070.8
10°	2680.4	2430.7	2203.2	1978.8	1886.8	1782.6	1585.4	1390.3	1223.4	1072.9	927.3
12.5°	2965.6	2617.7	2329.5	2046.4	1921.1	1794.6	1554.0	1321.4	1122.4	942.3	774.5
15°	3216.3	2789.7	2418.5	2076.9	1923.2	1771.4	1488.3	1226.5	1003.0	796.7	614.7
17.5°	3395.3	2875.6	2447.8	2049.5	1870.5	1700.6	1391.3	1111.2	870.6	655.2	479.2
20°	3504.5	2911.0	2432.7	1998.9	1808.9	1632.9	1319.4	1047.5	813.9	628.0	508.6
22.5°	3576.2	2945.3	2438.8	1997.9	1807.8	1642.1	1349.8	1095.0	904.9	804.9	790.6
25°	3653.1	2993.8	2483.2	2043.4	1866.5	1712.8	1429.7	1180.9	1022.2	979.7	985.8
27.5°	3649.0	2972.6	2440.8	2004.0	1817.9	1662.2	1330.6	1016.2	867.6	748.2	704.7
30°	3431.7	2727.0	2151.7	1662.2	1442.9	1251.7	814.9	529.8	366.0	320.5	275.0
32.5°	2923.1	2209.3	1608.7	1149.6	902.9	674.4	320.5	169.8	144.6	121.3	110.2
35°	2430.7	1761.3	1203.2	694.7	438.9	272.0	115.3	75.8	71.9	67.8	67.8
37.5°	2009.1	1383.2	777.6	293.3	160.8	98.1	55.6	50.5	48.6	47.5	47.5
40°	1571.2	901.9	336.8	97.0	51.6	44.5	39.4	37.4	36.4	35.4	36.4
42.5°	927.3	363.0	98.1	36.4	34.3	32.3	29.3	28.3	28.3	27.2	28.3
45°	315.4	94.0	32.3	26.2	24.3	24.3	22.2	22.2	22.2	21.3	23.3
47.5°	81.8	29.3	21.3	19.2	18.2	18.2	17.3	17.3	17.3	17.3	18.2
50°	28.3	19.2	15.2	14.1	13.2	14.1	13.2	13.2	13.2	13.2	14.1
52.5°	17.3	13.2	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1
55°	11.1	10.1	9.2	9.2	9.2	9.2	9.2	10.1	10.1	10.1	10.1
57.5°	9.2	8.1	8.1	8.1	8.1	8.1	9.2	8.1	8.1	9.2	10.1
60°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2	10.1
62.5°	7.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	10.1
65°	7.1	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2	10.1	10.1
67.5°	6.0	6.0	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2	10.1
70°	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	9.2	9.2
72.5°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	9.2
75°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	7.1	8.1	8.1	9.2
77.5°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	9.2
80°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	8.1
82.5°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	8.1
85°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	7.1	8.1	8.1	8.1
87.5°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1215.3	1198.2	1137.4	1129.3	1119.4	1069.7	1049.6	1015.1	966.7	952.4	935.3
5°	1097.0	1040.4	951.4	927.3	900.8	823.1	775.5	718.8	656.1	621.8	589.5
7.5°	946.4	867.6	749.2	701.7	672.4	587.5	511.6	435.8	343.8	291.2	257.9
10°	778.5	670.4	547.0	492.4	453.0	329.6	257.9	224.4	193.1	167.8	145.6
12.5°	609.6	487.3	347.9	285.2	253.9	210.4	170.9	129.4	115.3	114.3	110.2
15°	447.0	310.3	234.5	211.3	189.1	135.5	134.5	134.5	138.5	141.5	142.6
17.5°	329.6	273.0	214.4	200.2	210.4	218.4	232.5	253.9	270.9	319.5	309.3
20°	483.3	479.2	522.7	578.3	617.8	701.7	807.9	928.2	1053.5	1193.1	1299.3
22.5°	829.1	930.3	1009.1	1075.9	1111.2	1206.3	1290.1	1331.6	1356.0	1343.8	1326.5
25°	1013.2	1049.6	1025.3	1002.0	1005.1	919.2	856.4	776.6	708.8	647.2	610.7
27.5°	605.6	554.0	481.3	430.8	420.6	363.0	320.5	276.0	262.8	222.5	205.3
30°	218.4	203.2	179.9	161.8	159.7	144.6	135.5	125.3	124.3	115.3	110.2
32.5°	99.1	99.1	91.0	93.0	91.0	88.0	86.9	83.9	83.9	80.8	78.8
35°	64.8	65.7	64.8	64.8	63.8	63.8	63.8	61.7	62.7	60.7	57.6
37.5°	47.5	48.6	46.5	47.5	47.5	47.5	47.5	46.5	45.4	43.5	42.4
40°	36.4	36.4	36.4	36.4	36.4	36.4	36.4	35.4	35.4	34.3	32.3
42.5°	28.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	28.3	28.3
45°	23.3	24.3	23.3	24.3	24.3	24.3	23.3	23.3	23.3	22.2	21.3
47.5°	18.2	18.2	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	16.2
50°	14.1	14.1	14.1	14.1	14.1	14.1	15.2	14.1	14.1	14.1	14.1
52.5°	11.1	12.2	12.2	13.2	13.2	13.2	13.2	13.2	12.2	12.2	11.1
55°	10.1	11.1	11.1	12.2	12.2	12.2	12.2	11.1	11.1	11.1	10.1
57.5°	10.1	11.1	11.1	11.1	11.1	11.1	11.1	10.1	10.1	9.2	9.2
60°	10.1	10.1	10.1	11.1	11.1	10.1	10.1	9.2	9.2	8.1	8.1
62.5°	10.1	10.1	10.1	11.1	11.1	10.1	10.1	9.2	8.1	8.1	7.1
65°	10.1	11.1	10.1	11.1	11.1	10.1	10.1	9.2	8.1	8.1	7.1
67.5°	10.1	11.1	11.1	11.1	10.1	10.1	10.1	9.2	8.1	8.1	7.1
70°	9.2	10.1	10.1	10.1	10.1	10.1	9.2	9.2	8.1	8.1	7.1
72.5°	9.2	10.1	9.2	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1
75°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1
77.5°	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1	7.1
80°	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.0
82.5°	8.1	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.0
85°	8.1	8.1	8.1	8.1	8.1	8.1	7.1	7.1	6.0	5.1	5.1
87.5°	7.1	8.1	7.1	7.1	7.1	7.1	6.0	5.1	4.1	4.1	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192494

CATALOG NUMBER: LDA6A55950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	907.9	882.8	883.8	887.7	862.5	849.3	846.2	833.1
5°	546.0	516.7	511.6	507.5	472.2	458.0	447.0	461.0
7.5°	234.5	223.4	221.4	218.4	202.3	194.2	190.1	194.2
10°	116.3	109.2	110.2	111.3	106.2	103.2	102.1	101.1
12.5°	115.3	114.3	115.3	115.3	116.3	114.3	115.3	115.3
15°	149.7	149.7	152.7	154.8	159.7	158.8	160.8	162.9
17.5°	373.0	353.9	364.0	364.0	409.4	369.0	403.5	372.1
20°	1466.1	1534.8	1604.6	1663.3	1723.0	1741.2	1776.5	1766.3
22.5°	1300.3	1308.4	1298.2	1287.1	1284.1	1287.1	1232.5	1240.6
25°	558.1	554.0	537.9	520.7	525.7	529.8	510.5	492.4
27.5°	191.0	186.1	181.0	176.9	174.9	171.8	165.9	161.8
30°	108.3	105.1	103.2	102.1	100.2	98.1	95.1	93.0
32.5°	77.8	75.8	74.8	73.7	71.9	69.8	66.8	65.7
35°	57.6	55.6	54.6	53.6	51.6	49.5	48.6	47.5
37.5°	42.4	40.5	40.5	40.5	37.4	35.4	34.3	33.4
40°	32.3	31.3	31.3	31.3	29.3	28.3	27.2	27.2
42.5°	28.3	27.2	27.2	27.2	25.4	24.3	24.3	23.3
45°	21.3	20.3	20.3	19.2	18.2	18.2	17.3	16.2
47.5°	16.2	15.2	15.2	15.2	14.1	13.2	13.2	12.2
50°	13.2	13.2	12.2	13.2	11.1	11.1	11.1	10.1
52.5°	11.1	11.1	10.1	10.1	9.2	9.2	9.2	8.1
55°	10.1	9.2	9.2	9.2	8.1	8.1	8.1	7.1
57.5°	8.1	8.1	7.1	7.1	6.0	6.0	6.0	6.0
60°	7.1	7.1	6.0	6.0	5.1	5.1	5.1	5.1
62.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
65°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
67.5°	7.1	6.0	6.0	6.0	5.1	5.1	5.1	5.1
70°	7.1	7.1	6.0	6.0	6.0	5.1	5.1	5.1
72.5°	7.1	7.1	6.0	6.0	6.0	6.0	5.1	5.1
75°	6.0	6.0	6.0	6.0	5.1	5.1	5.1	5.1
77.5°	6.0	6.0	6.0	6.0	5.1	5.1	5.1	5.1
80°	6.0	6.0	5.1	5.1	5.1	5.1	5.1	5.1
82.5°	6.0	5.1	5.1	5.1	5.1	4.1	4.1	4.1
85°	4.1	4.1	4.1	4.1	3.0	3.0	3.0	3.0
87.5°	3.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)