

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192503

Luminaire Tested: **LDA6A55950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5848.4 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60088	60088	60088
5°	164924	55365	22590
10°	361405	45312	8617
15°	552052	34489	10097
20°	639605	25657	15687
25°	697722	21104	25320
30°	779139	19136	25852
35°	792737	13124	17728
40°	806661	6219	8967
45°	807968	2589	3915
50°	683065	1126	1203
55°	219949	774	191
60°	43681	888	0
65°	4449	1051	0
70°	481	1475	0
75°	0	1949	0
80°	0	3189	316
85°	0	6353	629

TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.8	2.5
10°-20°	769.5	13.2
20°-30°	1473.4	25.2
30°-40°	1735.9	29.7
40°-50°	1363.5	23.3
50°-60°	332.3	5.7
60°-70°	14.3	0.2
70°-80°	5.4	0.1
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2391.7	40.9
0°-40°	4127.6	70.6
0°-60°	5823.3	99.6
0°-90°	5848.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5848.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1096	1096	1096	1096	1096	
5°	2997	2169	1006	527	410	396
15°	9727	4996	608	174	178	2715
25°	11535	6075	349	365	419	5376
35°	11846	3840	196	253	265	7428
45°	10422	1187	33	46	50	7830
55°	2301	44	8	5	2	2739
65°	34	5	8	5	0	91
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1
2.5°	1878.8	1874.7	1847.2	1872.6	1795.9	1792.8	1758.3	1743.2	1698.7	1656.2	1595.6
5°	2997.0	2931.3	2877.7	2879.8	2732.1	2704.8	2627.9	2550.1	2430.7	2319.6	2168.9
7.5°	4568.3	4490.4	4377.3	4329.7	4047.5	3964.6	3806.0	3598.6	3338.7	3080.0	2800.9
10°	6492.4	6504.6	6357.9	6222.5	5795.8	5628.1	5371.2	4962.6	4470.2	3983.9	3489.4
12.5°	8428.8	8420.7	8245.8	8040.6	7514.7	7278.1	6936.4	6426.8	5774.5	5020.3	4246.7
15°	9727.1	9784.7	9710.9	9547.2	9098.1	8827.2	8442.0	7750.3	6955.6	6039.5	4996.1
17.5°	10542.1	10596.7	10570.4	10442.0	10045.6	9756.3	9434.9	8868.7	7949.6	6797.9	5586.5
20°	10963.7	11049.6	11037.6	10898.0	10598.7	10359.1	10004.2	9479.4	8683.7	7324.6	5968.7
22.5°	11244.8	11310.5	11328.8	11171.1	10861.6	10634.1	10374.2	9842.5	9094.1	7646.2	6120.4
25°	11535.0	11651.3	11537.0	11342.9	11058.7	10840.4	10563.3	10053.7	9290.3	7777.6	6074.8
27.5°	11890.9	11946.6	11687.7	11510.8	11195.3	10958.7	10664.4	10176.1	9324.6	7672.5	5815.1
30°	12308.5	12078.0	11897.1	11546.2	11188.1	10957.6	10658.4	10099.2	9143.7	7323.7	5311.5
32.5°	12239.8	12028.4	11823.1	11452.1	11098.2	10869.7	10536.0	9843.3	8715.9	6740.1	4616.9
35°	11845.5	11890.9	11669.4	11362.1	10961.7	10726.1	10362.1	9479.4	7990.0	5935.4	3840.3
37.5°	11512.8	11613.0	11468.3	11184.1	10777.6	10459.2	9967.8	8894.9	7042.6	4914.1	3104.2
40°	11272.1	11304.5	11226.7	10908.0	10419.7	9959.7	9391.4	7845.3	5891.9	3857.6	2450.0
42.5°	10899.0	10985.0	10847.5	10499.6	9759.5	9238.7	8415.7	6633.1	4576.3	2946.5	1844.2
45°	10421.7	10503.7	10333.8	9755.4	8726.1	7962.7	6958.6	5171.9	3385.2	2171.9	1187.1
47.5°	9643.2	9693.7	9365.2	8565.3	7068.8	6349.8	5320.6	3605.7	2181.0	1214.4	577.4
50°	8009.2	7984.9	7307.5	6323.6	4728.0	3973.7	3166.9	1954.5	979.7	575.3	360.9
52.5°	5161.8	5106.2	4435.8	3541.0	2394.4	1827.2	1373.1	843.2	510.5	321.5	142.6
55°	2301.3	2280.1	1866.6	1450.0	979.7	843.2	644.2	413.5	272.0	112.3	43.5
57.5°	853.4	834.2	735.2	616.8	473.2	393.3	312.5	198.2	69.8	37.4	23.3
60°	398.4	397.4	349.9	288.2	200.2	151.7	88.0	46.5	29.3	20.3	13.2
62.5°	127.4	124.3	86.9	63.8	45.4	39.4	31.3	23.3	15.2	11.1	8.1
65°	34.3	34.3	31.3	26.2	21.3	18.2	15.2	11.1	7.1	6.0	5.1
67.5°	13.2	13.2	12.2	11.1	8.1	7.1	6.0	5.1	4.1	5.1	5.1
70°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	4.1	4.1	5.1
72.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
75°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
77.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
80°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
82.5°	0.0	0.0	1.0	2.0	2.0	2.0	3.0	4.1	4.1	5.1	6.0
85°	0.0	0.0	1.0	2.0	2.0	3.0	3.0	4.1	4.1	5.1	6.0
87.5°	0.0	0.0	1.0	2.0	2.0	3.0	3.0	4.1	4.1	5.1	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1
2.5°	1551.2	1484.4	1392.4	1338.7	1325.6	1297.3	1247.8	1173.8	1113.3	1054.7	1020.2
5°	2041.4	1883.8	1706.7	1582.5	1531.8	1464.1	1343.8	1219.5	1105.2	1006.1	928.3
7.5°	2561.1	2301.3	2015.2	1784.6	1701.6	1594.6	1398.4	1213.4	1056.6	919.2	814.9
10°	3077.9	2659.4	2271.0	1937.4	1801.8	1656.2	1397.4	1157.7	973.8	814.0	698.7
12.5°	3594.6	2993.0	2459.1	2029.4	1853.4	1669.4	1356.0	1072.9	868.6	705.7	595.6
15°	4071.8	3258.8	2586.5	2060.7	1848.3	1630.9	1271.9	969.7	758.4	607.7	505.5
17.5°	4427.8	3398.4	2615.8	2013.1	1768.4	1527.8	1143.6	848.3	653.1	520.7	416.5
20°	4602.7	3420.7	2546.0	1877.7	1630.9	1381.2	1003.1	732.1	563.2	439.8	351.9
22.5°	4602.7	3315.5	2394.4	1707.8	1459.1	1212.4	867.6	636.1	492.4	383.2	309.5
25°	4427.8	3106.2	2191.1	1511.6	1269.9	1045.5	750.3	564.2	437.8	348.9	287.1
27.5°	4088.0	2817.0	1930.2	1293.2	1083.9	896.9	657.2	498.6	396.3	314.4	315.4
30°	3620.9	2462.2	1630.9	1062.7	892.8	737.2	553.1	417.6	317.4	302.3	311.4
32.5°	3081.0	2037.4	1292.2	824.1	691.7	580.4	420.6	295.3	252.8	254.8	264.9
35°	2526.8	1603.6	972.7	610.7	514.6	420.6	276.0	194.2	192.1	196.1	203.2
37.5°	1994.9	1200.3	703.8	447.0	345.8	258.9	148.6	133.4	133.4	137.5	141.5
40°	1494.5	851.3	484.3	264.9	167.8	118.4	94.0	86.9	85.9	86.9	92.0
42.5°	1026.4	538.9	288.2	106.2	80.8	68.8	59.7	54.6	53.6	54.6	57.6
45°	576.4	331.7	112.3	56.7	48.6	43.5	37.4	34.3	33.4	33.4	35.4
47.5°	360.9	131.5	50.5	35.4	30.3	28.3	24.3	22.2	21.3	21.3	22.2
50°	138.5	51.6	31.3	23.3	20.3	18.2	16.2	14.1	13.2	13.2	14.1
52.5°	47.5	30.3	20.3	15.2	13.2	12.2	10.1	9.2	9.2	9.2	9.2
55°	26.2	18.2	12.2	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	16.2	11.1	8.1	7.1	7.1	7.1	7.1	7.1	7.1	8.1	8.1
60°	9.2	7.1	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.1	8.1
62.5°	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	8.1	8.1	8.1
65°	5.1	5.1	5.1	6.0	6.0	6.0	7.1	7.1	8.1	8.1	8.1
67.5°	5.1	5.1	6.0	6.0	6.0	7.1	7.1	8.1	8.1	8.1	8.1
70°	5.1	6.0	6.0	7.1	7.1	7.1	8.1	8.1	8.1	9.2	9.2
72.5°	5.1	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2
75°	6.0	6.0	6.0	7.1	7.1	7.1	8.1	9.2	9.2	9.2	9.2
77.5°	6.0	6.0	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2	9.2
80°	6.0	6.0	7.1	7.1	8.1	8.1	9.2	9.2	9.2	10.1	10.1
82.5°	6.0	6.0	7.1	8.1	8.1	8.1	9.2	9.2	10.1	10.1	10.1
85°	6.0	7.1	7.1	8.1	8.1	8.1	9.2	9.2	10.1	10.1	10.1
87.5°	6.0	7.1	7.1	8.1	8.1	8.1	9.2	9.2	10.1	10.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1
2.5°	974.8	932.4	889.7	858.4	843.2	828.2	794.7	751.2	733.1	706.8	691.7
5°	849.4	777.6	720.9	683.6	661.2	632.0	593.5	551.0	526.8	499.5	481.3
7.5°	719.9	636.1	581.5	547.0	524.8	488.4	439.8	389.3	360.0	329.6	308.5
10°	606.6	526.8	465.1	425.7	397.4	355.0	306.4	270.9	245.8	219.3	198.2
12.5°	506.6	420.6	355.0	321.5	302.3	262.0	221.4	182.0	166.9	161.8	161.8
15°	410.5	332.7	277.1	248.8	228.5	185.0	176.9	174.9	173.9	172.8	174.9
17.5°	334.7	268.9	210.4	196.1	194.2	193.1	194.2	194.2	195.2	198.2	203.2
20°	281.1	220.4	216.3	217.4	217.4	221.4	226.5	230.6	234.6	239.6	248.8
22.5°	249.8	248.8	255.8	256.9	262.0	267.9	277.1	283.1	293.3	298.3	311.4
25°	288.2	295.3	308.5	312.5	320.5	330.6	344.9	352.9	364.9	371.1	386.3
27.5°	326.6	337.7	353.9	359.0	366.0	382.2	392.3	399.5	405.5	409.4	418.6
30°	323.5	333.6	349.9	350.9	360.9	372.1	378.1	384.3	388.3	387.3	392.3
32.5°	274.0	283.1	298.3	298.3	309.5	318.4	321.5	326.6	326.6	326.6	328.6
35°	210.4	216.3	226.5	229.5	238.6	244.7	246.7	252.8	252.8	250.7	250.7
37.5°	145.6	153.7	160.8	162.9	168.8	172.8	177.9	179.0	176.9	177.9	177.9
40°	95.1	100.2	105.1	106.2	111.3	114.3	119.4	119.4	120.2	119.4	121.3
42.5°	58.7	62.7	65.7	67.8	69.8	71.9	74.8	75.8	76.9	75.8	77.8
45°	36.4	38.4	40.5	41.4	42.4	43.5	46.5	46.5	46.5	46.5	47.5
47.5°	22.2	23.3	24.3	24.3	25.4	26.2	27.2	27.2	27.2	27.2	28.3
50°	13.2	14.1	14.1	14.1	15.2	15.2	16.2	16.2	16.2	15.2	16.2
52.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.1	9.2
55°	8.1	8.1	7.1	7.1	7.1	7.1	7.1	6.0	5.1	5.1	4.1
57.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	5.1	4.1	3.0
60°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	4.1	4.1	3.0
62.5°	8.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	4.1	4.1	3.0
65°	8.1	8.1	7.1	7.1	7.1	6.0	6.0	5.1	5.1	4.1	3.0
67.5°	8.1	8.1	8.1	7.1	8.1	7.1	6.0	6.0	5.1	4.1	4.1
70°	9.2	8.1	8.1	8.1	8.1	7.1	7.1	6.0	5.1	4.1	4.1
72.5°	9.2	9.2	8.1	8.1	8.1	7.1	7.1	6.0	5.1	5.1	4.1
75°	9.2	9.2	8.1	8.1	8.1	7.1	7.1	6.0	6.0	5.1	4.1
77.5°	9.2	9.2	9.2	8.1	8.1	8.1	7.1	7.1	6.0	5.1	4.1
80°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	4.1
82.5°	10.1	9.2	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	5.1
85°	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1	6.0	6.0	5.1
87.5°	10.1	9.2	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192503

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1	1096.1
2.5°	676.4	668.3	668.3	654.2	652.2	641.1	650.1	644.2
5°	461.0	447.9	443.9	429.7	424.6	411.5	415.6	410.5
7.5°	290.2	277.1	273.0	262.8	256.9	246.7	247.7	244.7
10°	176.9	164.8	161.8	158.8	155.8	154.8	155.8	154.8
12.5°	160.8	159.7	157.8	158.8	156.7	157.8	158.8	157.8
15°	174.9	176.9	174.9	175.9	174.9	176.9	177.9	177.9
17.5°	205.3	209.4	207.3	210.4	209.4	214.4	214.4	214.4
20°	251.8	258.9	256.9	260.9	260.9	266.9	266.9	268.9
22.5°	316.5	325.5	324.6	333.6	331.7	338.7	338.7	340.8
25°	394.4	403.5	404.5	410.5	409.4	416.5	416.5	418.6
27.5°	426.7	431.7	430.8	433.8	434.8	438.9	441.9	439.8
30°	400.4	404.5	403.5	405.5	405.5	408.4	411.5	408.4
32.5°	336.8	339.8	339.8	343.8	340.8	341.7	346.8	343.8
35°	257.9	259.9	257.9	259.9	260.9	260.9	265.9	264.9
37.5°	184.0	185.0	185.0	188.0	185.0	185.0	190.1	191.2
40°	123.3	124.3	123.3	127.4	125.3	125.3	128.3	125.3
42.5°	78.8	79.9	78.8	81.8	79.9	81.8	82.9	83.9
45°	48.6	48.6	47.5	49.5	48.6	49.5	50.5	50.5
47.5°	28.3	28.3	27.2	29.3	28.3	28.3	28.3	29.3
50°	15.2	15.2	15.2	16.2	15.2	15.2	15.2	14.1
52.5°	8.1	8.1	7.1	8.1	7.1	7.1	7.1	7.1
55°	4.1	3.0	3.0	3.0	2.0	2.0	2.0	2.0
57.5°	3.0	2.0	2.0	1.0	1.0	1.0	0.0	0.0
60°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.0	2.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.0	2.0	2.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.0	2.0	1.0	1.0	0.0	0.0	0.0
72.5°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
75°	3.0	3.0	2.0	2.0	1.0	1.0	0.0	0.0
77.5°	4.1	3.0	2.0	2.0	1.0	1.0	0.0	0.0
80°	4.1	3.0	2.0	2.0	2.0	1.0	1.0	1.0
82.5°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
85°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
87.5°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)