

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192514

Luminaire Tested: **LDA6A60927D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5015.3 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49596	49596	49596
5°	127223	45119	14049
10°	247980	34669	6747
15°	445161	23547	9058
20°	660933	17881	14952
25°	751247	14729	23445
30°	814359	16104	22054
35°	857786	10440	13666
40°	876342	4630	6655
45°	791501	1768	2473
50°	521023	699	699
55°	142685	602	0
60°	28496	691	0
65°	2011	947	0
70°	289	1170	0
75°	0	1737	0
80°	0	2589	284
85°	0	5158	566

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.8	2.2
10°-20°	588.7	11.7
20°-30°	1334.4	26.6
30°-40°	1601.7	31.9
40°-50°	1128.8	22.5
50°-60°	232.9	4.6
60°-70°	8.2	0.2
70°-80°	4.9	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2033.9	40.6
0°-40°	3635.6	72.5
0°-60°	4997.4	99.6
0°-90°	5015.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5015.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	905	905	905	905	905	
5°	2312	1684	820	341	255	284
15°	7844	3451	415	148	160	2328
25°	12420	4174	244	341	388	5732
35°	12818	2923	156	204	204	7968
45°	10209	1002	23	31	32	7509
55°	1493	20	6	4	0	1967
65°	16	4	7	4	0	46
75°	0	4	8	6	0	0
85°	0	6	8	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7
2.5°	1542.1	1495.6	1513.8	1460.1	1448.1	1438.2	1448.1	1389.8	1357.0	1315.1	1281.3
5°	2311.9	2256.2	2269.0	2175.0	2132.1	2103.0	2097.5	1977.1	1886.8	1787.4	1684.4
7.5°	3218.2	3165.4	3158.0	3012.2	2923.7	2873.6	2852.6	2680.2	2524.3	2347.3	2154.1
10°	4454.8	4334.6	4297.2	4085.6	3916.9	3810.1	3678.9	3403.5	3129.8	2862.7	2616.4
12.5°	5894.0	5828.3	5735.3	5362.3	5066.8	4915.5	4719.4	4288.9	3874.9	3433.6	3021.3
15°	7843.7	7610.3	7451.6	6912.6	6436.6	6203.1	5916.8	5258.4	4632.8	4073.7	3450.9
17.5°	9748.8	9626.6	9378.6	8679.1	7945.9	7577.4	7150.7	6256.0	5372.3	4577.1	3816.6
20°	11329.3	11214.4	10931.7	10272.3	9458.8	8915.3	8378.2	7150.7	5996.1	4978.3	4060.9
22.5°	12086.1	12013.2	11782.5	11218.0	10524.9	10007.9	9430.5	7912.2	6457.6	5241.1	4172.3
25°	12419.9	12386.2	12237.5	11792.5	11139.6	10700.9	10155.6	8451.2	6744.8	5363.2	4174.0
27.5°	12758.3	12764.6	12436.4	12084.3	11465.2	11043.8	10518.5	8690.0	6796.8	5294.8	4037.2
30°	12864.9	12797.5	12652.5	12147.3	11559.1	11111.3	10547.7	8579.7	6583.4	5013.9	3764.5
32.5°	12821.2	12794.7	12635.1	12100.8	11399.5	10906.1	10265.8	8142.0	6162.1	4612.7	3377.9
35°	12817.5	12768.3	12402.6	11943.9	11080.3	10471.1	9627.6	7434.3	5565.7	4083.8	2922.9
37.5°	12585.9	12463.7	12189.2	11570.9	10432.8	9660.3	8714.6	6569.7	4836.1	3490.1	2471.4
40°	12245.8	12081.6	11720.5	10784.8	9311.1	8421.1	7498.1	5587.5	4063.7	2904.6	1991.8
42.5°	11535.4	11287.3	10776.5	9489.9	7816.4	7013.8	6246.0	4592.7	3314.0	2366.6	1520.3
45°	10209.3	9870.1	9179.7	7767.2	6314.4	5659.6	5042.2	3695.2	2652.8	1755.5	1002.3
47.5°	8205.7	7891.2	7262.8	6183.0	4951.9	4398.4	3905.9	2748.6	1798.4	1016.8	478.8
50°	6109.2	5839.3	5348.7	4297.2	3324.1	2889.1	2467.7	1561.2	842.6	483.3	198.7
52.5°	3645.1	3511.1	3076.0	2382.9	1641.5	1414.4	1135.3	661.2	424.9	175.1	53.9
55°	1492.9	1378.0	1214.7	974.9	714.1	605.5	518.0	326.5	132.2	36.4	20.1
57.5°	674.8	649.3	575.4	452.3	328.3	275.4	186.1	62.0	29.1	18.3	11.8
60°	259.9	234.3	200.6	108.6	46.5	39.2	31.9	21.0	14.6	10.0	7.3
62.5°	37.4	35.6	31.9	25.6	20.1	18.3	15.5	11.0	8.2	6.3	5.5
65°	15.5	15.5	13.6	11.0	9.1	8.2	7.3	5.5	4.5	4.5	4.5
67.5°	6.3	6.3	5.5	4.5	3.7	3.7	3.7	2.7	3.7	3.7	4.5
70°	1.8	1.8	1.8	1.8	1.8	1.8	2.7	2.7	3.7	3.7	4.5
72.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
75°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
77.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
80°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	5.5
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	5.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	5.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7
2.5°	1252.1	1193.7	1177.4	1126.3	1083.4	1062.5	1036.0	976.7	932.0	872.7	837.2
5°	1612.3	1502.0	1414.4	1307.8	1237.6	1191.9	1120.8	1012.3	924.8	819.9	745.0
7.5°	2001.7	1800.2	1642.4	1466.4	1365.2	1285.8	1164.6	1008.6	880.1	740.5	624.6
10°	2377.4	2076.6	1828.5	1575.9	1442.7	1332.4	1165.4	969.4	798.9	622.8	500.7
12.5°	2708.5	2320.0	1970.8	1646.0	1481.1	1343.4	1134.5	899.2	693.1	512.5	404.9
15°	2984.9	2508.8	2071.1	1672.5	1483.7	1319.6	1069.8	798.9	575.4	414.9	339.2
17.5°	3194.6	2608.2	2102.0	1640.6	1430.8	1252.1	970.3	672.2	467.0	352.0	285.4
20°	3303.1	2627.4	2057.4	1553.9	1333.2	1150.0	840.0	545.3	395.8	306.5	239.0
22.5°	3316.8	2573.5	1950.7	1430.0	1210.2	1025.9	695.8	455.0	352.9	270.9	210.7
25°	3235.7	2456.8	1798.4	1289.5	1075.1	883.7	566.3	407.6	321.0	243.5	242.6
27.5°	3062.4	2256.2	1615.9	1126.3	912.0	718.6	480.6	368.4	286.4	258.1	274.5
30°	2817.9	1999.1	1391.6	920.1	712.3	552.6	404.9	303.7	251.8	254.4	268.1
32.5°	2486.9	1679.8	1128.0	674.0	509.7	415.9	303.7	207.0	208.9	209.7	221.7
35°	2071.1	1347.0	842.6	453.2	358.4	292.7	171.5	152.3	155.0	156.0	164.1
37.5°	1659.8	1035.1	559.9	301.8	225.3	154.1	106.7	102.1	103.9	103.1	112.2
40°	1271.2	721.4	335.6	149.5	86.6	72.0	65.7	62.9	63.9	64.7	70.2
42.5°	900.2	391.3	166.0	56.5	45.6	41.9	39.2	37.4	38.3	38.3	41.9
45°	456.8	185.1	56.5	31.0	28.3	25.6	23.8	22.8	22.8	22.8	24.6
47.5°	197.9	61.1	26.4	19.1	17.3	16.5	14.6	13.6	13.6	13.6	14.6
50°	62.0	24.6	16.5	12.8	11.0	10.0	9.1	9.1	9.1	8.2	9.1
52.5°	22.8	15.5	11.0	8.2	7.3	7.3	7.3	6.3	7.3	6.3	7.3
55°	13.6	10.0	7.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
57.5°	9.1	7.3	6.3	6.3	5.5	5.5	6.3	6.3	6.3	6.3	6.3
60°	6.3	6.3	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3
65°	4.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	7.3	7.3	7.3
67.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
70°	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3	8.2
72.5°	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2
75°	5.5	6.3	6.3	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2
77.5°	5.5	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
80°	5.5	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.1
82.5°	5.5	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.1
85°	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.1
87.5°	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	9.1	8.2	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7
2.5°	789.8	736.9	700.4	686.7	660.2	618.3	593.7	570.9	528.0	518.9	495.2
5°	659.4	574.6	514.4	491.6	461.5	425.9	391.3	368.4	341.1	330.1	313.7
7.5°	519.8	435.0	383.0	364.8	343.8	314.6	283.6	260.8	232.5	218.0	204.2
10°	408.6	345.6	301.8	283.6	261.7	230.7	198.7	168.8	144.0	128.6	125.9
12.5°	331.9	280.0	233.5	214.3	188.8	157.8	135.0	134.0	132.2	131.4	133.2
15°	271.7	221.7	172.3	151.3	144.0	143.2	145.9	148.7	147.7	150.5	152.3
17.5°	223.5	169.6	158.7	159.6	160.5	163.3	167.8	175.1	176.0	180.6	184.2
20°	182.4	179.6	184.2	187.9	190.6	196.1	206.1	215.2	218.0	224.3	231.7
22.5°	207.0	215.2	225.3	229.8	233.5	243.5	254.4	269.1	274.5	282.7	292.7
25°	249.9	263.6	279.1	284.5	290.0	306.5	319.1	336.6	341.1	351.1	361.2
27.5°	285.4	300.0	316.5	323.8	328.3	344.7	355.7	366.5	366.5	372.0	379.3
30°	280.0	291.8	305.5	311.0	312.8	324.6	335.6	339.2	337.4	340.1	345.6
32.5°	232.5	241.6	252.6	257.1	258.9	267.2	276.4	276.4	275.4	275.4	279.1
35°	172.3	178.8	184.2	188.8	191.6	197.0	205.2	204.2	204.2	202.4	205.2
37.5°	115.8	119.4	125.9	127.7	128.6	132.2	138.7	138.7	136.8	137.7	139.5
40°	70.2	74.8	78.5	79.3	81.2	84.0	88.5	88.5	88.5	88.5	89.3
42.5°	41.9	44.7	47.4	47.4	48.4	52.0	53.9	53.9	53.9	53.9	54.7
45°	24.6	25.6	27.4	28.3	28.3	30.1	31.0	31.0	31.0	31.0	31.9
47.5°	14.6	15.5	15.5	16.5	16.5	17.3	18.3	18.3	17.3	17.3	17.3
50°	9.1	9.1	9.1	9.1	10.0	10.0	10.0	10.0	10.0	10.0	9.1
52.5°	7.3	7.3	7.3	7.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5
55°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	5.5	4.5	3.7	2.7
57.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	3.7	2.7
60°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	3.7	2.7
62.5°	7.3	7.3	6.3	6.3	6.3	5.5	5.5	4.5	4.5	3.7	2.7
65°	7.3	7.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7
67.5°	7.3	7.3	7.3	7.3	6.3	6.3	6.3	5.5	4.5	3.7	2.7
70°	8.2	8.2	7.3	7.3	7.3	6.3	6.3	5.5	4.5	4.5	3.7
72.5°	8.2	8.2	7.3	7.3	7.3	7.3	6.3	5.5	5.5	4.5	3.7
75°	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3	5.5	4.5	3.7
77.5°	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3	5.5	4.5	3.7
80°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	3.7
82.5°	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	4.5
85°	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3	5.5	5.5	4.5
87.5°	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3	5.5	5.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192514

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	904.7	904.7	904.7	904.7	904.7	904.7	904.7	904.7
2.5°	480.6	453.2	444.2	450.5	443.2	437.7	430.4	426.7
5°	301.0	280.9	274.5	276.4	269.9	264.4	257.1	255.3
7.5°	185.1	166.0	158.7	158.7	151.3	145.0	140.5	137.7
10°	124.1	120.4	121.2	122.2	121.2	122.2	119.4	121.2
12.5°	133.2	131.4	133.2	134.0	134.0	135.9	132.2	135.0
15°	155.0	153.2	156.0	157.8	157.8	160.5	156.8	159.6
17.5°	189.7	188.8	193.4	195.2	196.1	200.6	196.1	199.7
20°	239.8	239.0	245.3	248.1	247.1	256.3	249.9	256.3
22.5°	304.6	302.8	311.8	314.6	315.5	327.4	321.9	326.5
25°	369.3	371.2	375.7	380.3	381.2	391.3	383.0	387.6
27.5°	383.0	380.3	383.0	388.5	389.5	394.0	386.7	390.3
30°	346.6	341.9	342.9	349.2	351.1	352.9	346.6	348.4
32.5°	281.9	274.5	274.5	280.9	282.7	285.4	274.5	279.1
35°	207.9	201.6	201.6	206.1	207.0	208.9	200.6	204.2
37.5°	142.2	136.8	138.7	140.5	141.4	143.2	142.2	141.4
40°	91.1	87.5	90.3	90.3	91.1	92.1	92.1	93.0
42.5°	55.7	52.9	54.7	54.7	55.7	55.7	55.7	56.5
45°	31.9	31.0	31.0	31.9	31.9	31.9	31.0	31.9
47.5°	17.3	16.5	17.3	17.3	17.3	17.3	17.3	17.3
50°	9.1	8.2	8.2	8.2	8.2	8.2	8.2	8.2
52.5°	4.5	3.7	3.7	3.7	2.7	3.7	2.7	2.7
55°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
57.5°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.7	1.8	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.7	1.8	1.8	0.9	0.9	0.0	0.0	0.0
72.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
75°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
77.5°	2.7	2.7	1.8	1.8	0.9	0.9	0.9	0.0
80°	3.7	2.7	1.8	1.8	1.8	0.9	0.9	0.9
82.5°	3.7	2.7	1.8	1.8	1.8	0.9	0.9	0.9
85°	3.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
87.5°	3.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)