

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192516

Luminaire Tested: **LDA6A60927D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4658.8 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	46943	46943	46943
5°	121192	43506	13598
10°	229906	33199	4570
15°	411086	21584	4557
20°	612542	14678	8296
25°	698919	18316	52128
30°	755844	15293	15591
35°	793975	7449	4885
40°	806533	2676	2476
45°	718578	1768	1481
50°	461503	1245	1006
55°	121496	870	526
60°	27092	899	406
65°	2607	1064	480
70°	882	1314	593
75°	191	1737	953
80°	0	2873	1421
85°	0	5158	2327



TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.0	2.2
10°-20°	542.7	11.6
20°-30°	1273.4	27.3
30°-40°	1464.7	31.4
40°-50°	1040.4	22.3
50°-60°	211.5	4.5
60°-70°	10.6	0.2
70°-80°	6.3	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1920.1	41.2
0°-40°	3384.7	72.7
0°-60°	4636.7	99.5
0°-90°	4658.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4658.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	856	856	856	856	856	
5°	2202	1593	791	316	247	268
15°	7243	3256	380	86	80	2173
25°	11555	3922	303	661	862	5325
35°	11864	2754	111	82	73	7370
45°	9269	979	23	25	19	6830
55°	1271	26	9	9	6	1714
65°	20	7	8	7	4	48
75°	1	4	8	7	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3
2.5°	1475.4	1430.8	1408.9	1407.9	1344.2	1365.2	1344.2	1327.8	1268.4	1243.8	1202.9
5°	2202.3	2147.6	2103.7	2084.6	1975.2	1951.5	1940.6	1884.9	1761.0	1688.8	1593.2
7.5°	3059.5	3002.1	2929.9	2872.5	2713.9	2669.2	2640.0	2544.3	2361.0	2216.0	2037.2
10°	4130.1	4096.3	3979.6	3873.8	3633.0	3540.1	3452.5	3229.1	2989.3	2698.4	2467.6
12.5°	5571.8	5492.5	5284.6	5072.9	4695.4	4556.8	4411.8	4054.3	3687.8	3231.8	2850.6
15°	7243.3	7175.8	6855.8	6511.1	5973.9	5745.9	5518.9	4956.3	4392.7	3805.4	3256.4
17.5°	9167.4	9039.8	8721.6	8138.8	7387.5	7029.1	6605.9	5889.1	5075.7	4277.8	3595.6
20°	10499.8	10424.0	10155.1	9596.0	8740.7	8267.4	7742.2	6758.2	5645.6	4656.3	3818.1
22.5°	11228.4	11152.7	10951.2	10457.8	9756.6	9281.5	8671.3	7461.3	6076.0	4910.6	3923.1
25°	11554.8	11505.6	11395.2	10993.1	10343.8	9916.1	9338.9	7947.3	6345.1	5026.5	3922.1
27.5°	11856.7	11869.5	11596.8	11265.8	10667.6	10238.1	9690.9	8166.1	6398.0	4968.1	3796.3
30°	11940.5	11908.6	11789.2	11323.2	10766.1	10298.3	9711.9	8050.4	6191.9	4710.0	3546.4
32.5°	11888.6	11889.5	11777.4	11282.1	10627.4	10104.0	9444.7	7635.4	5790.6	4305.1	3157.9
35°	11864.0	11855.7	11564.8	11129.9	10298.3	9682.6	8851.9	6969.7	5234.4	3788.0	2754.0
37.5°	11619.6	11570.3	11360.6	10770.6	9682.6	8895.7	8001.1	6155.4	4549.5	3250.0	2340.0
40°	11270.3	11208.3	10867.2	10021.0	8630.3	7752.2	6863.1	5233.5	3832.8	2714.7	1878.5
42.5°	10554.5	10452.3	9935.2	8812.7	7275.2	6458.2	5721.3	4310.6	3133.3	2204.1	1442.7
45°	9268.7	9101.7	8386.0	7213.2	5872.7	5231.7	4608.8	3455.3	2508.7	1641.4	979.4
47.5°	7442.2	7259.8	6610.5	5668.4	4597.9	4078.1	3549.2	2544.3	1697.1	956.6	491.6
50°	5411.3	5285.4	4711.8	3917.6	3040.3	2604.5	2198.7	1418.9	814.4	462.3	201.6
52.5°	3117.8	3027.5	2628.1	2061.8	1495.6	1252.1	1006.8	619.2	414.9	183.3	64.7
55°	1271.2	1219.2	1044.2	884.6	663.9	573.6	478.8	309.2	139.5	43.7	25.6
57.5°	622.0	615.5	513.4	411.3	302.8	244.4	184.2	62.0	33.8	21.9	16.5
60°	247.1	238.0	163.3	94.8	52.9	42.9	36.4	25.6	19.1	14.6	11.8
62.5°	42.9	41.9	35.6	30.1	24.6	21.9	20.1	15.5	12.8	10.0	9.1
65°	20.1	20.1	18.3	16.5	13.6	12.8	11.8	10.0	8.2	7.3	7.3
67.5°	10.0	10.0	9.1	8.2	7.3	7.3	6.3	6.3	5.5	5.5	5.5
70°	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5	3.7	4.5	4.5
72.5°	3.7	3.7	3.7	2.7	1.8	2.7	2.7	2.7	3.7	4.5	4.5
75°	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5	4.5
77.5°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
80°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3
2.5°	1184.6	1137.2	1106.1	1051.4	1028.6	1018.6	968.4	920.1	873.6	839.8	787.9
5°	1520.2	1444.5	1328.6	1220.2	1172.8	1142.7	1044.2	952.9	866.3	790.6	700.3
7.5°	1881.2	1725.4	1543.8	1369.7	1287.7	1232.9	1080.6	947.4	823.5	708.6	585.4
10°	2227.8	1982.5	1718.1	1469.1	1357.9	1275.7	1077.0	906.5	745.0	596.4	464.2
12.5°	2523.3	2205.9	1854.8	1532.0	1387.0	1282.2	1043.2	835.3	639.3	479.6	364.7
15°	2772.2	2377.3	1945.1	1552.9	1378.8	1254.8	977.5	737.7	523.5	380.3	294.5
17.5°	2947.4	2460.3	1966.0	1517.4	1321.4	1178.2	878.2	612.8	411.3	307.3	232.5
20°	3049.5	2471.3	1915.0	1430.8	1221.0	1069.7	753.2	481.5	333.8	251.6	180.6
22.5°	3064.9	2417.5	1814.7	1314.1	1105.2	959.4	627.4	403.1	303.7	235.3	176.9
25°	2990.1	2310.8	1684.3	1200.0	1000.3	850.8	542.6	407.6	341.1	302.8	314.6
27.5°	2845.1	2134.8	1534.8	1083.3	890.9	739.6	512.5	426.7	372.0	378.5	400.3
30°	2622.6	1886.7	1319.6	885.4	682.2	563.6	407.6	307.3	255.3	241.6	242.6
32.5°	2295.3	1575.7	1035.9	614.6	458.7	380.3	258.1	171.5	172.3	159.6	158.7
35°	1921.4	1268.4	775.1	412.2	317.3	264.4	152.3	120.4	115.8	111.3	104.9
37.5°	1551.1	980.3	516.2	281.7	202.4	146.8	76.6	62.9	58.4	54.7	54.7
40°	1180.9	685.8	319.1	147.7	82.1	60.2	45.6	38.3	37.4	37.4	36.4
42.5°	857.1	404.9	173.3	58.4	45.6	40.1	31.9	28.3	28.3	28.3	28.3
45°	456.0	206.1	66.5	36.4	30.1	28.3	23.8	21.9	21.9	22.8	22.8
47.5°	210.7	77.5	33.8	24.6	21.0	21.0	18.3	17.3	17.3	18.3	18.3
50°	75.7	31.9	21.9	17.3	15.5	16.5	14.6	13.6	14.6	14.6	14.6
52.5°	29.1	20.1	15.5	13.6	11.8	12.8	11.0	11.0	11.8	11.8	11.8
55°	18.3	14.6	11.8	10.0	9.1	10.0	9.1	9.1	9.1	9.1	9.1
57.5°	12.8	11.0	9.1	8.2	7.3	8.2	8.2	8.2	8.2	8.2	8.2
60°	10.0	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2
62.5°	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2
65°	7.3	6.3	7.3	7.3	6.3	7.3	7.3	7.3	8.2	8.2	9.1
67.5°	5.5	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2
70°	5.5	5.5	6.3	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2
72.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2
75°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	7.3	8.2	8.2	8.2
77.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2	8.2
80°	5.5	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	9.1	9.1
82.5°	5.5	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	9.1	9.1
85°	5.5	6.3	6.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
87.5°	5.5	6.3	6.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3
2.5°	753.2	708.6	663.9	641.9	622.8	595.5	560.8	532.5	502.4	486.9	451.4
5°	629.3	552.6	487.9	456.8	433.2	400.3	364.7	339.2	316.5	303.7	280.9
7.5°	486.9	413.9	357.5	333.8	316.5	283.6	257.1	230.7	207.0	189.7	166.8
10°	376.7	320.1	273.6	250.8	231.7	196.9	165.1	140.4	114.9	97.6	90.3
12.5°	299.2	246.3	198.7	176.0	156.0	120.4	96.6	92.1	87.5	85.7	83.0
15°	229.8	181.4	131.4	108.6	100.3	95.8	90.3	89.3	85.7	85.7	83.0
17.5°	172.3	118.6	100.3	98.5	97.6	95.8	93.0	92.1	91.1	91.1	90.3
20°	124.1	114.9	112.1	113.9	114.9	116.7	115.8	115.8	119.4	127.7	125.9
22.5°	174.1	188.8	204.2	209.7	229.8	249.8	268.1	290.9	344.7	406.8	421.3
25°	344.7	388.5	428.6	450.5	483.3	528.0	570.9	623.8	661.2	692.1	727.7
27.5°	428.6	445.0	438.7	441.4	437.7	431.4	433.2	444.0	438.7	422.2	428.6
30°	253.5	266.3	258.9	262.6	252.6	252.6	249.8	255.3	251.6	245.3	243.5
32.5°	165.1	172.3	171.5	171.5	167.8	166.0	159.6	157.8	151.3	139.5	136.8
35°	99.4	94.8	90.3	87.5	85.7	85.7	84.8	84.8	82.1	79.3	78.5
37.5°	53.9	54.7	54.7	54.7	54.7	56.5	55.6	55.6	55.6	53.9	53.9
40°	37.4	39.2	39.2	39.2	40.1	40.1	40.1	41.1	40.1	40.1	40.1
42.5°	29.1	30.1	29.1	29.1	30.1	30.1	30.1	31.0	31.0	31.0	30.1
45°	23.8	23.8	22.8	23.8	23.8	24.6	24.6	24.6	24.6	23.8	23.8
47.5°	19.1	19.1	19.1	19.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1
50°	15.5	15.5	15.5	16.5	16.5	16.5	15.5	16.5	16.5	16.5	15.5
52.5°	11.8	11.8	11.8	11.8	11.8	11.0	11.0	11.0	11.0	11.0	10.0
55°	9.1	9.1	9.1	9.1	9.1	10.0	9.1	10.0	9.1	9.1	8.2
57.5°	8.2	8.2	8.2	8.2	9.1	9.1	8.2	8.2	8.2	7.3	7.3
60°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	6.3	6.3
62.5°	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3	6.3
65°	9.1	9.1	8.2	9.1	9.1	8.2	8.2	7.3	7.3	6.3	6.3
67.5°	9.1	9.1	9.1	9.1	9.1	9.1	8.2	8.2	7.3	7.3	6.3
70°	9.1	9.1	9.1	9.1	9.1	9.1	8.2	8.2	7.3	7.3	6.3
72.5°	9.1	9.1	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	6.3
75°	9.1	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3
77.5°	9.1	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3
80°	9.1	9.1	9.1	9.1	9.1	9.1	8.2	8.2	7.3	7.3	6.3
82.5°	9.1	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3
85°	9.1	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3	5.5
87.5°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192516

CATALOG NUMBER: LDA6A60927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	856.3	856.3	856.3	856.3	856.3	856.3	856.3	856.3
2.5°	451.4	443.2	439.5	433.2	427.7	424.9	414.9	426.7
5°	276.2	266.3	263.6	258.1	251.6	248.1	240.8	247.1
7.5°	157.8	145.9	140.4	135.9	129.5	124.1	117.6	121.2
10°	88.5	84.8	85.7	83.0	82.1	81.2	80.3	82.1
12.5°	82.1	79.3	80.3	78.5	77.5	77.5	76.6	77.5
15°	83.0	80.3	82.1	80.3	79.3	79.3	78.5	80.3
17.5°	90.3	88.5	90.3	88.5	89.3	88.5	89.3	90.3
20°	126.7	129.5	135.0	131.4	134.0	137.7	142.2	142.2
22.5°	445.9	504.2	511.6	540.8	615.5	612.8	662.9	664.7
25°	778.8	782.4	815.2	804.3	805.2	843.5	839.8	861.8
27.5°	447.7	446.8	453.2	441.4	445.0	447.7	437.7	449.5
30°	249.8	245.3	248.1	241.6	241.6	243.5	240.8	246.3
32.5°	138.6	135.0	135.0	130.4	129.5	128.6	125.9	128.6
35°	79.3	76.6	77.5	75.7	73.8	73.0	72.0	73.0
37.5°	54.7	52.9	53.9	52.0	50.2	49.2	48.4	49.2
40°	40.1	39.2	39.2	37.4	36.4	35.6	34.6	34.6
42.5°	30.1	29.1	29.1	27.4	26.4	25.6	24.6	25.6
45°	22.8	21.9	21.9	21.0	20.1	19.1	19.1	19.1
47.5°	20.1	19.1	20.1	19.1	18.3	18.3	18.3	18.3
50°	15.5	15.5	15.5	14.6	13.6	13.6	12.8	11.8
52.5°	10.0	9.1	9.1	8.2	8.2	7.3	7.3	7.3
55°	8.2	7.3	7.3	6.3	6.3	5.5	5.5	5.5
57.5°	6.3	6.3	5.5	5.5	4.5	4.5	4.5	4.5
60°	5.5	5.5	5.5	4.5	4.5	3.7	3.7	3.7
62.5°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
65°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
67.5°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
70°	6.3	5.5	5.5	4.5	4.5	4.5	3.7	3.7
72.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
75°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
77.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
80°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
82.5°	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5
85°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
87.5°	3.7	3.7	2.7	2.7	2.7	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)