

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192520

Luminaire Tested: **LDA6A60927D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5274.3 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54190	54190	54190
5°	148739	49928	20372
10°	325935	40864	7765
15°	497875	31101	9109
20°	576833	23137	14153
25°	629244	19029	22834
30°	702678	17262	23320
35°	714926	11839	15995
40°	727492	5618	8094
45°	728680	2334	3535
50°	616022	1006	1092
55°	198368	698	172
60°	39383	800	0
65°	4021	947	0
70°	433	1314	0
75°	0	1737	0
80°	0	2873	284
85°	0	5724	566

TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.2	2.5
10°-20°	694.0	13.2
20°-30°	1328.8	25.2
30°-40°	1565.5	29.7
40°-50°	1229.7	23.3
50°-60°	299.6	5.7
60°-70°	12.8	0.2
70°-80°	4.8	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2157.0	40.9
0°-40°	3722.5	70.6
0°-60°	5251.8	99.6
0°-90°	5274.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5274.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	988	988	988	988	988	
5°	2703	1956	907	475	370	357
15°	8772	4506	548	157	160	2449
25°	10403	5479	315	329	378	4849
35°	10683	3463	177	228	239	6699
45°	9399	1070	30	42	46	7062
55°	2076	39	7	4	2	2470
65°	31	4	7	4	0	82
75°	0	4	8	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5
2.5°	1694.3	1690.6	1666.0	1688.8	1619.5	1616.8	1585.8	1572.1	1532.0	1493.7	1439.0
5°	2702.9	2643.6	2595.3	2597.1	2463.9	2439.3	2370.0	2299.8	2192.2	2091.9	1956.0
7.5°	4120.0	4049.7	3947.6	3904.8	3650.3	3575.5	3432.3	3245.4	3011.1	2777.6	2526.0
10°	5855.2	5866.2	5734.0	5611.8	5226.9	5075.6	4843.9	4475.6	4031.5	3592.8	3147.0
12.5°	7601.6	7594.3	7436.6	7251.3	6777.2	6563.8	6255.7	5796.0	5207.8	4527.6	3830.0
15°	8772.5	8824.4	8757.9	8610.2	8205.2	7960.8	7613.4	6989.7	6273.0	5446.8	4505.7
17.5°	9507.4	9556.6	9533.0	9417.1	9059.7	8798.9	8508.9	7998.2	7169.3	6130.6	5038.2
20°	9887.7	9965.2	9954.3	9828.4	9558.5	9342.4	9022.3	8549.0	7831.4	6605.7	5382.9
22.5°	10141.2	10200.5	10216.9	10074.7	9795.6	9590.4	9356.1	8876.4	8201.6	6895.8	5519.8
25°	10402.9	10507.7	10404.8	10229.7	9973.4	9776.5	9526.5	9067.0	8378.5	7014.3	5478.7
27.5°	10723.9	10774.1	10540.6	10381.0	10096.5	9883.1	9617.8	9177.3	8409.5	6919.5	5244.4
30°	11100.6	10892.6	10729.4	10412.9	10090.1	9882.2	9612.3	9108.0	8246.3	6604.9	4790.2
32.5°	11038.5	10848.0	10662.9	10328.1	10009.0	9802.9	9501.9	8877.3	7860.5	6078.7	4163.7
35°	10682.8	10723.9	10524.2	10247.0	9885.9	9673.4	9345.1	8549.0	7205.8	5352.8	3463.4
37.5°	10382.8	10473.1	10342.7	10086.5	9719.9	9432.7	8989.5	8022.0	6351.3	4431.8	2799.5
40°	10165.8	10195.0	10124.7	9837.5	9397.1	8982.2	8469.7	7075.4	5313.6	3478.9	2209.5
42.5°	9829.4	9906.9	9782.8	9469.1	8801.6	8332.0	7589.7	5982.1	4127.3	2657.2	1663.3
45°	9399.0	9472.8	9319.6	8798.0	7869.6	7181.2	6275.6	4664.3	3053.0	1958.7	1070.5
47.5°	8696.8	8742.4	8446.0	7724.6	6375.1	5726.7	4798.4	3251.9	1967.0	1095.1	520.7
50°	7223.1	7201.3	6590.3	5703.0	4264.0	3583.7	2856.1	1762.7	883.6	518.9	325.6
52.5°	4655.2	4605.1	4000.4	3193.5	2159.4	1647.8	1238.3	760.5	460.5	290.0	128.6
55°	2075.5	2056.3	1683.3	1307.6	883.6	760.5	580.9	373.0	245.3	101.3	39.2
57.5°	769.6	752.3	662.9	556.3	426.7	354.7	281.7	178.8	62.9	33.8	21.0
60°	359.2	358.4	315.5	259.9	180.6	136.7	79.3	41.9	26.4	18.3	11.8
62.5°	114.9	112.1	78.5	57.4	41.1	35.6	28.3	21.0	13.6	10.0	7.3
65°	31.0	31.0	28.3	23.8	19.1	16.5	13.6	10.0	6.3	5.5	4.5
67.5°	11.8	11.8	11.0	10.0	7.3	6.3	5.5	4.5	3.7	4.5	4.5
70°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.5
72.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
75°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
77.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
80°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
82.5°	0.0	0.0	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5	5.5
85°	0.0	0.0	0.9	1.8	1.8	2.7	2.7	3.7	3.7	4.5	5.5
87.5°	0.0	0.0	0.9	1.8	1.8	2.7	2.7	3.7	3.7	4.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5
2.5°	1398.8	1338.7	1255.7	1207.4	1195.5	1169.9	1125.2	1058.7	1004.0	951.1	920.1
5°	1841.1	1698.8	1539.3	1427.1	1381.5	1320.4	1211.9	1099.8	996.7	907.3	837.2
7.5°	2309.8	2075.5	1817.4	1609.5	1534.7	1438.0	1261.1	1094.3	952.9	828.9	735.0
10°	2775.8	2398.3	2048.2	1747.2	1625.0	1493.7	1260.2	1044.1	878.1	734.1	630.1
12.5°	3241.8	2699.3	2217.7	1830.2	1671.5	1505.5	1222.8	967.5	783.3	636.5	537.1
15°	3672.2	2939.1	2332.6	1858.4	1667.0	1470.9	1147.2	874.6	683.9	548.0	456.0
17.5°	3993.3	3064.8	2359.0	1815.5	1594.9	1377.8	1031.4	765.1	589.1	469.6	375.7
20°	4150.9	3084.9	2296.2	1693.4	1470.9	1245.6	904.5	660.2	507.9	396.6	317.3
22.5°	4150.9	2990.1	2159.4	1540.2	1315.8	1093.4	782.4	573.6	444.0	345.6	279.1
25°	3993.3	2801.4	1976.0	1363.3	1145.3	942.9	676.7	508.9	394.8	314.6	258.9
27.5°	3686.8	2540.6	1740.8	1166.3	977.5	808.9	592.7	449.5	357.4	283.6	284.5
30°	3265.5	2220.5	1470.9	958.4	805.2	664.7	498.8	376.7	286.4	272.7	280.9
32.5°	2778.6	1837.5	1165.4	743.2	623.8	523.4	379.3	266.3	228.0	229.8	239.0
35°	2278.8	1446.3	877.2	550.8	464.2	379.3	249.0	175.1	173.3	176.9	183.3
37.5°	1799.2	1082.5	634.6	403.1	311.8	233.5	134.0	120.4	120.4	124.1	127.7
40°	1347.7	767.8	436.9	239.0	151.3	106.7	84.8	78.5	77.5	78.5	83.0
42.5°	925.6	486.1	259.9	95.8	73.0	62.0	53.9	49.2	48.4	49.2	52.0
45°	519.7	299.2	101.3	51.1	43.7	39.2	33.8	31.0	30.1	30.1	31.9
47.5°	325.6	118.6	45.6	31.9	27.3	25.6	21.9	20.1	19.1	19.1	20.1
50°	124.9	46.5	28.3	21.0	18.3	16.5	14.6	12.8	11.8	11.8	12.8
52.5°	42.9	27.3	18.3	13.6	11.8	11.0	9.1	8.2	8.2	8.2	8.2
55°	23.8	16.5	11.0	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3
57.5°	14.6	10.0	7.3	6.3	6.3	6.3	6.3	6.3	6.3	7.3	7.3
60°	8.2	6.3	5.5	5.5	5.5	5.5	6.3	6.3	6.3	7.3	7.3
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	7.3	7.3	7.3
65°	4.5	4.5	4.5	5.5	5.5	5.5	6.3	6.3	7.3	7.3	7.3
67.5°	4.5	4.5	5.5	5.5	5.5	6.3	6.3	7.3	7.3	7.3	7.3
70°	4.5	5.5	5.5	6.3	6.3	6.3	7.3	7.3	7.3	8.2	8.2
72.5°	4.5	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2
75°	5.5	5.5	5.5	6.3	6.3	6.3	7.3	8.2	8.2	8.2	8.2
77.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2	8.2
80°	5.5	5.5	6.3	6.3	7.3	7.3	8.2	8.2	8.2	9.1	9.1
82.5°	5.5	5.5	6.3	7.3	7.3	7.3	8.2	8.2	9.1	9.1	9.1
85°	5.5	6.3	6.3	7.3	7.3	7.3	8.2	8.2	9.1	9.1	9.1
87.5°	5.5	6.3	6.3	7.3	7.3	7.3	8.2	8.2	9.1	9.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5
2.5°	879.1	840.8	802.4	774.2	760.5	746.9	716.8	677.5	661.1	637.4	623.8
5°	766.0	701.3	650.2	616.5	596.4	569.9	535.3	496.9	475.1	450.5	434.1
7.5°	649.3	573.6	524.4	493.3	473.3	440.4	396.6	351.1	324.6	297.3	278.1
10°	547.1	475.1	419.4	383.8	358.4	320.1	276.2	244.4	221.5	197.9	178.8
12.5°	456.8	379.3	320.1	290.0	272.7	236.2	199.7	164.1	150.5	145.9	145.9
15°	370.2	300.0	249.8	224.3	206.1	166.8	159.6	157.8	156.8	156.0	157.8
17.5°	301.8	242.6	189.7	176.9	175.1	174.1	175.1	175.1	176.0	178.8	183.3
20°	253.5	198.7	195.1	196.1	196.1	199.7	204.2	207.9	211.5	216.2	224.3
22.5°	225.2	224.3	230.7	231.7	236.2	241.6	249.8	255.3	264.4	269.1	280.9
25°	259.9	266.3	278.1	281.7	289.0	298.2	311.0	318.3	329.1	334.6	348.4
27.5°	294.5	304.5	319.1	323.8	330.1	344.7	353.9	360.2	365.7	369.3	377.5
30°	291.8	300.9	315.5	316.5	325.6	335.6	341.1	346.6	350.2	349.2	353.9
32.5°	247.1	255.3	269.1	269.1	279.1	287.2	290.0	294.5	294.5	294.5	296.4
35°	189.7	195.1	204.2	207.0	215.2	220.7	222.5	228.0	228.0	226.2	226.2
37.5°	131.4	138.6	145.0	146.8	152.3	156.0	160.5	161.5	159.6	160.5	160.5
40°	85.7	90.3	94.8	95.8	100.3	103.1	107.6	107.6	108.6	107.6	109.4
42.5°	52.9	56.5	59.2	61.1	62.9	64.7	67.5	68.4	69.3	68.4	70.2
45°	32.8	34.6	36.4	37.4	38.3	39.2	41.9	41.9	41.9	41.9	42.9
47.5°	20.1	21.0	21.9	21.9	22.8	23.8	24.6	24.6	24.6	24.6	25.6
50°	11.8	12.8	12.8	12.8	13.6	13.6	14.6	14.6	14.6	13.6	14.6
52.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	8.2
55°	7.3	7.3	6.3	6.3	6.3	6.3	6.3	5.5	4.5	4.5	3.7
57.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	4.5	3.7	2.7
60°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	3.7	2.7
62.5°	7.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	3.7	2.7
65°	7.3	7.3	6.3	6.3	6.3	5.5	5.5	4.5	4.5	3.7	2.7
67.5°	7.3	7.3	7.3	6.3	7.3	6.3	5.5	5.5	4.5	3.7	3.7
70°	8.2	7.3	7.3	7.3	7.3	6.3	6.3	5.5	4.5	3.7	3.7
72.5°	8.2	8.2	7.3	7.3	7.3	6.3	6.3	5.5	4.5	4.5	3.7
75°	8.2	8.2	7.3	7.3	7.3	6.3	6.3	5.5	5.5	4.5	3.7
77.5°	8.2	8.2	8.2	7.3	7.3	7.3	6.3	6.3	5.5	4.5	3.7
80°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	3.7
82.5°	9.1	8.2	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	4.5
85°	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3	5.5	5.5	4.5
87.5°	9.1	8.2	8.2	8.2	8.2	7.3	7.3	6.3	5.5	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192520

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	988.5	988.5	988.5	988.5	988.5	988.5	988.5	988.5
2.5°	610.0	602.7	602.7	590.0	588.2	578.1	586.4	580.9
5°	415.8	404.0	400.3	387.5	383.0	371.2	374.8	370.2
7.5°	261.7	249.8	246.2	237.1	231.7	222.5	223.4	220.7
10°	159.6	148.7	145.9	143.2	140.4	139.5	140.4	139.5
12.5°	145.0	144.0	142.2	143.2	141.4	142.2	143.2	142.2
15°	157.8	159.6	157.8	158.7	157.8	159.6	160.5	160.5
17.5°	185.1	188.8	186.9	189.7	188.8	193.3	193.3	193.3
20°	227.0	233.5	231.7	235.3	235.3	240.8	240.8	242.6
22.5°	285.4	293.7	292.7	300.9	299.2	305.5	305.5	307.3
25°	355.6	363.9	364.7	370.2	369.3	375.7	375.7	377.5
27.5°	384.8	389.3	388.5	391.2	392.1	395.8	398.5	396.6
30°	361.1	364.7	363.9	365.7	365.7	368.4	371.2	368.4
32.5°	303.7	306.3	306.3	310.0	307.3	308.2	312.8	310.0
35°	232.5	234.3	232.5	234.3	235.3	235.3	239.8	239.0
37.5°	166.0	166.8	166.8	169.6	166.8	166.8	171.5	172.3
40°	111.3	112.1	111.3	114.9	113.1	113.1	115.8	113.1
42.5°	71.2	72.0	71.2	73.8	72.0	73.8	74.8	75.7
45°	43.7	43.7	42.9	44.7	43.7	44.7	45.6	45.6
47.5°	25.6	25.6	24.6	26.4	25.6	25.6	25.6	26.4
50°	13.6	13.6	13.6	14.6	13.6	13.6	13.6	12.8
52.5°	7.3	7.3	6.3	7.3	6.3	6.3	6.3	6.3
55°	3.7	2.7	2.7	2.7	1.8	1.8	1.8	1.8
57.5°	2.7	1.8	1.8	0.9	0.9	0.9	0.0	0.0
60°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
65°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.7	1.8	1.8	0.9	0.9	0.0	0.0	0.0
70°	2.7	1.8	1.8	0.9	0.9	0.0	0.0	0.0
72.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
75°	2.7	2.7	1.8	1.8	0.9	0.9	0.0	0.0
77.5°	3.7	2.7	1.8	1.8	0.9	0.9	0.0	0.0
80°	3.7	2.7	1.8	1.8	1.8	0.9	0.9	0.9
82.5°	3.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
85°	3.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
87.5°	3.7	2.7	2.7	1.8	1.8	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)