

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192522

Luminaire Tested: **LDA6A60927D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4901.3 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	44	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52337	52337	52337
5°	138911	48531	18567
10°	303212	39239	5533
15°	457687	28672	4813
20°	532390	19683	7555
25°	587139	21237	50307
30°	649600	15990	15642
35°	659246	8178	5856
40°	674414	3328	2805
45°	680071	2047	1698
50°	572894	1407	1092
55°	189221	956	602
60°	37190	899	406
65°	4384	1180	480
70°	1170	1314	593
75°	191	1737	953
80°	0	2873	1421
85°	0	5724	2327



TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.1	2.6
10°-20°	641.6	13.1
20°-30°	1266.5	25.8
30°-40°	1428.5	29.1
40°-50°	1134.1	23.1
50°-60°	277.3	5.7
60°-70°	14.8	0.3
70°-80°	6.3	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2035.1	41.5
0°-40°	3463.7	70.7
0°-60°	4875.0	99.5
0°-90°	4901.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4901.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	955	955	955	955	955	
5°	2524	1891	882	443	337	333
15°	8064	4286	505	99	85	2262
25°	9707	5195	351	636	832	4496
35°	9851	3307	122	97	88	6195
45°	8772	1030	26	27	22	6575
55°	1980	45	10	10	6	2323
65°	34	8	9	7	4	82
75°	1	4	8	7	4	2
85°	0	4	9	6	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7
2.5°	1657.0	1625.1	1639.7	1616.9	1552.1	1532.1	1548.4	1523.8	1450.0	1421.7	1392.6
5°	2524.3	2496.0	2505.1	2453.1	2331.9	2289.9	2287.1	2212.4	2062.8	1979.0	1891.3
7.5°	3827.4	3788.2	3777.3	3652.3	3418.9	3331.3	3288.4	3104.3	2822.5	2622.7	2426.7
10°	5447.0	5485.4	5446.2	5243.6	4877.1	4712.9	4609.0	4260.6	3752.7	3372.4	3005.7
12.5°	7071.2	7094.9	7021.0	6769.4	6303.4	6106.4	5953.2	5507.2	4837.8	4192.2	3645.0
15°	8064.4	8176.5	8107.1	7931.2	7570.0	7331.2	7193.5	6642.5	5800.0	5090.5	4286.2
17.5°	8772.0	8875.9	8818.5	8674.4	8266.8	8074.4	7985.0	7531.7	6614.3	5712.4	4765.8
20°	9125.9	9252.6	9200.6	9037.4	8738.2	8577.8	8469.2	8027.0	7199.8	6174.7	5085.9
22.5°	9365.7	9506.1	9449.5	9301.0	8996.3	8809.4	8758.4	8339.8	7506.3	6452.0	5221.8
25°	9706.8	9824.4	9664.8	9481.5	9180.6	8983.5	8952.6	8524.9	7653.0	6556.9	5195.4
27.5°	9951.1	10090.6	9819.8	9633.8	9290.0	9083.0	9042.9	8640.6	7666.8	6473.9	4981.0
30°	10262.1	10171.9	9933.8	9663.9	9297.3	9076.6	9025.5	8573.3	7529.9	6168.4	4561.6
32.5°	10139.0	10117.1	9879.1	9561.8	9219.8	8997.2	8928.8	8365.2	7154.2	5641.2	3967.9
35°	9850.8	9920.1	9721.4	9524.3	9099.4	8867.8	8772.9	8058.9	6587.8	4962.7	3306.7
37.5°	9682.1	9725.9	9600.0	9359.4	8938.0	8633.3	8453.7	7543.6	5846.5	4107.4	2669.3
40°	9424.1	9535.3	9414.1	9137.7	8651.6	8234.0	7921.2	6612.6	4869.8	3238.4	2087.4
42.5°	9141.3	9240.8	9124.9	8793.9	8107.1	7547.2	7027.5	5518.2	3812.8	2474.1	1565.9
45°	8772.0	8861.3	8653.4	8138.2	7166.0	6393.6	5874.7	4333.6	2875.3	1817.5	1030.5
47.5°	8106.3	8082.5	7788.0	6987.3	5789.9	5097.8	4494.1	3104.3	1911.4	1029.6	512.5
50°	6717.4	6495.8	6062.6	5133.3	3885.8	3138.1	2725.8	1602.3	867.3	498.9	321.9
52.5°	4350.9	4103.8	3707.0	2848.9	1865.9	1497.4	1201.0	724.1	452.3	281.7	126.7
55°	1979.8	1804.7	1551.2	1150.8	800.7	665.7	563.6	366.5	242.6	104.9	44.7
57.5°	754.2	695.8	618.3	493.4	370.2	320.1	265.4	176.0	75.7	39.2	26.4
60°	339.2	314.6	289.0	226.2	158.7	113.9	86.6	47.4	31.9	22.8	17.3
62.5°	115.8	96.6	80.3	57.4	42.9	37.4	32.8	26.4	19.1	15.5	11.8
65°	33.8	32.8	31.0	27.4	21.9	20.1	19.1	15.5	11.8	10.0	8.2
67.5°	16.5	15.5	14.6	13.6	11.0	10.0	10.0	9.1	7.3	6.3	5.5
70°	7.3	7.3	6.3	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
72.5°	3.7	3.7	3.7	2.7	2.7	2.7	2.7	3.7	3.7	4.5	4.5
75°	0.9	1.8	1.8	1.8	1.8	2.7	2.7	3.7	3.7	4.5	4.5
77.5°	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5	4.5
80°	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5	4.5
82.5°	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5	4.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.7	2.7	3.7	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7
2.5°	1321.4	1302.3	1226.6	1168.2	1140.8	1139.0	1077.9	1040.5	974.9	923.8	875.4
5°	1737.3	1652.5	1499.2	1378.0	1319.6	1289.5	1169.1	1082.5	969.4	881.9	795.2
7.5°	2160.4	1998.9	1783.7	1553.1	1458.1	1399.9	1213.8	1075.1	924.8	802.6	695.0
10°	2593.6	2309.1	1988.1	1683.5	1546.6	1448.1	1209.2	1021.4	848.1	704.9	587.4
12.5°	3045.0	2596.3	2149.4	1768.3	1587.7	1458.1	1168.2	942.9	754.2	601.9	489.7
15°	3425.3	2818.8	2251.6	1788.4	1574.9	1418.1	1080.6	843.5	653.9	505.2	403.1
17.5°	3719.0	2943.7	2270.7	1739.0	1503.8	1328.7	967.5	734.1	548.1	416.8	315.5
20°	3866.6	2963.0	2210.6	1622.4	1375.2	1194.7	839.0	622.8	459.6	337.4	250.8
22.5°	3877.6	2873.5	2079.2	1471.9	1233.8	1050.5	733.2	537.1	403.1	302.8	238.0
25°	3735.3	2701.2	1903.3	1317.8	1088.9	923.8	657.5	515.2	405.8	351.1	322.8
27.5°	3465.4	2462.2	1709.9	1163.6	963.9	836.3	626.5	515.2	439.5	396.6	406.8
30°	3091.5	2157.7	1440.8	953.9	784.3	673.0	492.4	385.8	302.8	252.6	243.5
32.5°	2606.3	1765.5	1117.2	704.9	571.8	485.1	332.9	241.6	195.2	190.6	185.1
35°	2144.9	1394.4	848.1	520.7	421.3	342.9	212.5	142.2	129.5	122.2	116.7
37.5°	1694.4	1043.2	609.2	378.5	289.0	218.0	109.4	92.1	80.3	73.0	66.5
40°	1274.0	749.7	429.5	228.8	151.3	94.0	65.7	56.5	50.2	46.5	44.7
42.5°	901.0	498.9	266.3	96.6	72.0	59.2	45.6	40.1	36.4	34.6	32.8
45°	523.5	310.0	107.6	56.5	45.6	41.1	33.8	30.1	28.3	26.4	25.6
47.5°	327.4	124.9	55.7	36.4	31.9	29.1	24.6	23.8	21.9	21.0	21.0
50°	132.2	55.7	34.6	25.6	22.8	21.9	19.1	18.3	16.5	16.5	16.5
52.5°	50.2	32.8	23.8	18.3	16.5	15.5	13.6	13.6	12.8	12.8	12.8
55°	29.1	21.9	16.5	12.8	11.8	11.8	11.0	11.0	10.0	10.0	10.0
57.5°	19.1	14.6	11.8	9.1	9.1	9.1	8.2	8.2	8.2	8.2	8.2
60°	12.8	10.0	8.2	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
62.5°	9.1	8.2	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	9.1
65°	7.3	6.3	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1	9.1
67.5°	5.5	5.5	5.5	5.5	6.3	6.3	7.3	8.2	8.2	8.2	9.1
70°	4.5	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1
72.5°	4.5	5.5	5.5	6.3	6.3	6.3	7.3	8.2	8.2	8.2	9.1
75°	4.5	5.5	5.5	6.3	6.3	6.3	7.3	8.2	8.2	8.2	9.1
77.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1	9.1
80°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1	9.1
82.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1	9.1
85°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	9.1	9.1
87.5°	5.5	5.5	6.3	6.3	6.3	7.3	7.3	8.2	8.2	8.2	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7
2.5°	851.8	809.9	764.2	749.7	735.0	706.8	689.5	658.4	635.6	612.8	594.5
5°	737.7	671.2	615.6	591.9	569.1	529.8	502.5	469.6	443.2	420.4	399.4
7.5°	619.2	542.6	486.9	463.3	440.5	397.6	363.0	321.9	290.9	265.4	244.4
10°	509.7	436.9	376.7	348.4	321.9	277.2	244.4	211.5	185.1	163.3	144.0
12.5°	414.9	336.4	275.4	254.4	228.8	192.4	161.5	125.9	110.4	103.9	99.4
15°	321.9	251.8	200.6	181.4	158.7	124.1	110.4	103.9	99.4	96.6	93.0
17.5°	245.3	186.9	136.8	124.1	116.7	109.4	105.8	101.3	98.5	97.6	94.8
20°	192.4	141.4	128.6	124.9	124.9	123.1	120.4	120.4	119.4	122.2	122.2
22.5°	197.9	197.9	208.9	207.9	222.5	237.1	248.1	283.6	303.7	346.6	375.7
25°	345.6	378.5	416.8	428.6	456.8	498.9	542.6	597.3	635.6	676.7	693.1
27.5°	431.4	436.9	431.4	445.0	426.7	415.9	419.6	425.9	425.9	428.6	439.5
30°	255.3	268.1	280.0	289.0	284.5	280.0	278.2	264.4	264.4	258.9	254.4
32.5°	173.3	171.5	169.6	173.3	169.6	169.6	166.9	167.8	162.3	158.7	156.8
35°	118.6	113.1	106.7	107.6	103.9	103.1	100.3	100.3	96.6	94.8	94.0
37.5°	65.7	65.7	62.9	63.9	62.9	62.9	62.9	63.9	62.9	62.9	63.9
40°	44.7	44.7	43.7	44.7	43.7	44.7	45.6	45.6	45.6	45.6	44.7
42.5°	33.8	33.8	32.8	33.8	32.8	33.8	34.6	34.6	34.6	34.6	34.6
45°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	27.4	27.4	26.4	26.4
47.5°	21.0	21.9	21.0	21.0	21.0	21.0	21.9	21.9	21.0	21.0	21.0
50°	17.3	17.3	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
52.5°	13.6	12.8	12.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.0
55°	10.0	10.0	9.1	9.1	9.1	10.0	10.0	10.0	10.0	9.1	9.1
57.5°	9.1	9.1	9.1	8.2	8.2	9.1	9.1	8.2	8.2	8.2	7.3
60°	8.2	9.1	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3
62.5°	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3	6.3
65°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3
67.5°	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	7.3	7.3	6.3
70°	9.1	9.1	9.1	9.1	9.1	8.2	8.2	8.2	7.3	7.3	6.3
72.5°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.3
75°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3
77.5°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3
80°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3
82.5°	9.1	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3
85°	9.1	9.1	8.2	8.2	8.2	8.2	7.3	7.3	6.3	6.3	5.5
87.5°	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.3	5.5	5.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192522

CATALOG NUMBER: LDA6A60927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	954.7	954.7	954.7	954.7	954.7	954.7	954.7	954.7
2.5°	572.7	569.1	566.3	571.8	569.9	547.1	549.9	549.0
5°	375.7	367.5	361.2	363.9	356.6	346.6	339.2	337.4
7.5°	223.5	214.3	208.9	203.4	201.6	188.8	183.3	186.9
10°	123.1	110.4	109.4	106.7	103.1	100.3	98.5	99.4
12.5°	94.8	94.0	92.1	91.1	89.3	88.5	87.5	86.6
15°	90.3	89.3	88.5	87.5	86.6	85.7	84.8	84.8
17.5°	93.0	93.0	92.1	91.1	91.1	92.1	91.1	90.3
20°	121.2	121.2	123.1	125.9	125.9	128.6	132.2	129.5
22.5°	394.0	414.1	438.7	446.0	488.8	523.5	587.4	559.1
25°	720.4	766.0	777.0	792.4	816.2	828.0	816.2	831.7
27.5°	437.7	453.2	455.0	456.0	461.5	460.5	448.7	456.0
30°	254.4	259.9	258.1	257.1	255.3	245.3	243.5	247.1
32.5°	159.6	157.8	156.8	156.0	156.0	150.5	153.2	151.3
35°	91.1	94.0	93.0	92.1	89.3	88.5	88.5	87.5
37.5°	61.1	62.0	61.1	60.2	58.4	57.4	56.5	55.7
40°	43.7	44.7	43.7	42.9	41.9	41.1	40.1	39.2
42.5°	32.8	33.8	32.8	32.8	31.0	30.1	29.1	28.3
45°	25.6	24.6	24.6	24.6	23.8	22.8	21.9	21.9
47.5°	21.0	21.0	21.0	20.1	19.1	19.1	19.1	18.3
50°	15.5	16.5	15.5	15.5	14.6	13.6	13.6	12.8
52.5°	11.0	11.0	10.0	10.0	9.1	8.2	8.2	8.2
55°	8.2	8.2	8.2	7.3	7.3	6.3	6.3	6.3
57.5°	7.3	6.3	6.3	6.3	5.5	5.5	4.5	4.5
60°	6.3	5.5	5.5	4.5	4.5	3.7	3.7	3.7
62.5°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
65°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
67.5°	5.5	5.5	4.5	4.5	4.5	3.7	3.7	3.7
70°	5.5	5.5	5.5	4.5	4.5	4.5	3.7	3.7
72.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
75°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
77.5°	6.3	5.5	5.5	5.5	4.5	4.5	4.5	4.5
80°	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5
82.5°	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
85°	5.5	4.5	4.5	4.5	3.7	3.7	3.7	3.7
87.5°	4.5	3.7	3.7	2.7	2.7	2.7	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)