

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192526

Luminaire Tested: **LDA6A60930D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60930D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4912.9 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	76036	76036	76036
5°	147331	72457	24433
10°	250307	63403	10977
15°	385712	50574	17446
20°	558363	32915	30348
25°	819223	31762	39020
30°	952539	30093	29903
35°	964127	15934	15807
40°	798231	6011	6634
45°	602869	2039	2419
50°	412473	751	751
55°	57374	650	96
60°	1491	636	0
65°	376	882	0
70°	160	1090	0
75°	0	1440	0
80°	0	2462	316
85°	0	4906	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	3.0
10°-20°	615.1	12.5
20°-30°	1403.1	28.6
30°-40°	1623.7	33.1
40°-50°	979.2	19.9
50°-60°	133.0	2.7
60°-70°	4.3	0.1
70°-80°	4.6	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2163.7	44.0
0°-40°	3787.4	77.1
0°-60°	4899.7	99.7
0°-90°	4912.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4912.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1387	1387	1387	1387	1387	
5°	2677	2192	1317	720	444	312
15°	6796	3820	891	274	307	2012
25°	13544	4527	525	632	645	6129
35°	14406	3451	238	243	236	8682
45°	7776	940	26	32	31	6081
55°	600	7	7	5	1	1177
65°	3	4	7	4	0	4
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0
2.5°	2005.8	1987.2	1995.0	1974.6	1922.8	1912.1	1911.1	1897.4	1853.6	1819.3	1778.4
5°	2677.3	2676.3	2681.2	2637.4	2546.6	2518.2	2504.5	2471.4	2365.0	2283.0	2192.2
7.5°	3515.7	3509.8	3504.0	3423.9	3281.5	3226.8	3191.7	3071.7	2925.2	2779.8	2617.7
10°	4496.6	4493.7	4471.3	4330.8	4102.3	4001.8	3933.5	3743.2	3507.9	3301.0	3025.7
12.5°	5635.8	5609.3	5569.4	5363.4	5050.1	4940.8	4790.4	4488.8	4127.8	3810.5	3425.9
15°	6796.2	6758.2	6686.9	6422.5	6034.0	5847.6	5661.1	5263.9	4773.9	4313.1	3820.2
17.5°	7931.4	7889.4	7722.6	7273.5	6893.8	6666.4	6459.5	5913.8	5338.1	4745.6	4120.8
20°	9571.1	9418.9	9128.1	8420.4	7714.8	7304.7	7062.7	6485.8	5773.3	5083.3	4334.7
22.5°	11761.4	11423.7	10804.0	9654.1	8645.9	8054.4	7658.1	6890.9	6086.6	5303.8	4466.4
25°	13543.7	13390.5	12685.8	11049.9	9476.5	8779.6	8228.2	7213.1	6315.1	5451.3	4527.0
27.5°	14692.5	14654.4	13849.2	12205.6	10154.8	9240.3	8624.4	7425.8	6425.4	5482.5	4497.6
30°	15047.8	15107.3	14334.3	12597.9	10351.0	9333.0	8659.5	7428.8	6340.5	5341.0	4310.2
32.5°	15021.4	15024.4	14076.7	12259.2	10031.9	9063.6	8366.7	7181.8	6027.2	4986.6	3954.0
35°	14406.5	14255.2	13183.6	11218.8	9289.0	8435.1	7786.9	6703.5	5510.7	4453.8	3451.4
37.5°	13056.6	12858.5	11609.2	9886.4	8409.7	7620.1	7096.8	6075.9	4895.8	3884.7	2932.0
40°	11154.3	10873.2	9842.5	8647.8	7447.3	6853.8	6414.7	5374.1	4238.1	3326.3	2445.1
42.5°	9250.0	9112.5	8431.2	7460.0	6638.2	6079.8	5621.1	4639.2	3605.5	2775.9	1829.1
45°	7776.2	7658.1	7200.3	6560.1	5753.8	5244.4	4802.1	3873.0	2801.2	1862.3	939.9
47.5°	6702.5	6606.8	6168.6	5496.1	4611.8	4054.5	3598.7	2539.7	1587.1	804.3	235.2
50°	4836.4	4738.8	4309.2	3530.4	2731.9	2265.4	1937.4	1134.1	450.0	163.0	24.4
52.5°	2370.9	2290.8	1998.9	1496.3	1004.3	722.2	528.0	212.8	51.8	17.5	11.7
55°	600.3	551.5	459.8	288.9	141.5	84.9	54.7	19.5	12.7	9.7	6.8
57.5°	34.1	33.1	30.2	22.4	16.6	14.6	12.7	9.7	6.8	5.8	4.9
60°	13.6	12.7	11.7	9.7	7.8	6.8	6.8	4.9	3.9	3.9	3.9
62.5°	5.8	5.8	5.8	4.9	3.9	3.9	3.9	2.9	3.9	3.9	3.9
65°	2.9	2.9	2.9	1.9	1.9	1.9	2.9	2.9	2.9	3.9	3.9
67.5°	1.9	1.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	3.9
70°	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9
72.5°	0.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9
75°	0.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
77.5°	0.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
80°	0.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
82.5°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
85°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
87.5°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0
2.5°	1725.6	1690.5	1638.7	1604.6	1571.5	1540.2	1488.5	1459.2	1406.5	1357.7	1315.7
5°	2082.9	1995.0	1888.7	1797.9	1739.3	1681.7	1577.3	1500.2	1403.5	1316.7	1236.6
7.5°	2444.1	2288.8	2114.1	1964.8	1874.0	1785.2	1629.0	1504.1	1367.5	1243.6	1125.3
10°	2772.0	2538.8	2291.8	2078.0	1955.1	1839.9	1633.9	1468.0	1292.3	1139.0	990.7
12.5°	3076.5	2757.4	2435.2	2156.1	2003.8	1865.3	1613.4	1410.4	1201.5	1019.9	847.3
15°	3347.9	2938.0	2539.7	2201.0	2022.3	1858.4	1565.6	1329.3	1094.2	891.1	672.5
17.5°	3553.8	3050.2	2585.6	2194.2	1989.2	1806.7	1483.6	1227.8	980.0	733.9	487.1
20°	3678.7	3098.0	2575.8	2141.5	1917.9	1724.6	1386.0	1117.6	842.3	564.2	429.4
22.5°	3731.5	3094.1	2529.9	2062.4	1830.0	1634.8	1292.3	1010.2	697.9	510.5	448.1
25°	3740.3	3054.1	2465.5	1975.5	1743.3	1549.0	1197.6	888.2	606.1	525.1	501.7
27.5°	3672.9	2960.4	2344.5	1850.6	1621.2	1420.1	1056.1	705.7	569.1	523.1	538.7
30°	3473.8	2746.7	2130.7	1630.9	1409.4	1208.3	754.5	553.5	472.4	475.4	479.3
32.5°	3123.3	2391.3	1787.2	1309.8	1067.8	796.5	469.5	370.0	359.2	359.2	357.3
35°	2655.9	1957.0	1402.6	828.6	530.9	382.6	243.0	244.0	239.1	238.1	237.1
37.5°	2172.7	1544.2	888.2	342.5	230.3	160.1	143.4	145.4	143.4	146.4	144.4
40°	1712.9	953.7	324.0	109.3	81.0	78.1	80.1	82.0	82.0	84.0	84.0
42.5°	995.6	316.2	84.9	43.9	43.9	41.9	42.9	44.8	45.8	46.8	45.8
45°	295.7	65.4	27.3	24.4	24.4	23.4	23.4	24.4	25.3	26.3	26.3
47.5°	46.8	18.5	15.6	13.6	13.6	13.6	13.6	13.6	14.6	14.6	15.6
50°	14.6	11.7	9.7	8.8	8.8	7.8	7.8	8.8	8.8	8.8	9.7
52.5°	8.8	6.8	6.8	5.8	6.8	6.8	5.8	6.8	6.8	6.8	7.8
55°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	6.8	6.8	6.8
57.5°	4.9	4.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
60°	4.9	4.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	6.8
62.5°	4.9	4.9	5.8	5.8	5.8	5.8	5.8	5.8	6.8	6.8	6.8
65°	4.9	4.9	5.8	5.8	5.8	5.8	5.8	6.8	6.8	6.8	6.8
67.5°	4.9	5.8	5.8	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8
70°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
72.5°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
75°	5.8	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	7.8
77.5°	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8
80°	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
82.5°	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
85°	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
87.5°	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0
2.5°	1279.6	1234.7	1213.2	1183.0	1161.5	1113.7	1094.2	1061.0	1033.6	988.7	991.7
5°	1168.4	1083.4	1025.8	980.9	949.8	873.6	822.8	769.2	720.3	659.9	637.3
7.5°	1014.1	909.7	821.8	768.2	728.1	626.6	514.4	426.5	360.2	312.3	293.8
10°	859.9	724.2	584.7	501.7	444.0	346.4	296.7	273.3	251.9	225.4	207.9
12.5°	680.3	487.1	360.2	326.9	303.5	271.4	239.1	213.7	218.6	219.6	226.4
15°	464.6	350.5	310.4	287.9	262.6	244.0	254.8	261.6	274.3	275.3	284.0
17.5°	377.8	328.9	296.7	295.7	297.7	308.4	325.0	333.8	350.5	354.4	367.0
20°	377.8	349.5	376.8	376.8	381.7	396.3	417.7	430.4	449.0	455.9	471.5
22.5°	430.4	450.0	484.1	488.0	490.0	505.6	532.9	545.6	567.1	571.0	587.6
25°	525.1	542.6	573.9	576.9	577.8	589.5	610.0	616.8	631.5	623.7	633.4
27.5°	555.4	563.2	582.7	584.7	579.8	584.7	592.5	592.5	597.3	581.7	584.7
30°	488.0	490.0	499.7	500.7	490.0	491.9	492.9	491.9	491.0	474.4	474.4
32.5°	362.2	362.2	374.8	371.9	360.2	363.1	363.1	363.1	362.2	348.5	346.4
35°	240.1	241.0	251.9	249.9	241.0	243.0	243.0	245.9	243.0	235.2	233.2
37.5°	146.4	147.3	152.3	153.3	150.4	151.3	152.3	151.3	153.3	149.4	147.3
40°	84.9	86.9	90.8	91.8	90.8	90.8	91.8	92.7	96.6	91.8	89.8
42.5°	49.8	50.8	52.8	52.8	52.8	52.8	53.7	54.7	55.7	54.7	53.7
45°	28.3	29.2	30.2	30.2	31.2	30.2	31.2	31.2	32.2	31.2	31.2
47.5°	16.6	16.6	17.5	17.5	18.5	17.5	18.5	18.5	18.5	17.5	17.5
50°	9.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	9.7	9.7
52.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	6.8	6.8	5.8	5.8
55°	6.8	6.8	6.8	6.8	6.8	6.8	5.8	4.9	4.9	3.9	3.9
57.5°	5.8	6.8	6.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9	2.9
60°	6.8	6.8	6.8	6.8	5.8	5.8	5.8	4.9	3.9	2.9	2.9
62.5°	6.8	6.8	6.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9	2.9
65°	6.8	6.8	6.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9	2.9
67.5°	6.8	6.8	6.8	6.8	6.8	5.8	5.8	4.9	3.9	3.9	2.9
70°	6.8	7.8	7.8	6.8	6.8	6.8	5.8	4.9	4.9	3.9	2.9
72.5°	6.8	7.8	7.8	6.8	6.8	6.8	5.8	4.9	4.9	3.9	2.9
75°	7.8	7.8	7.8	7.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9
77.5°	7.8	7.8	7.8	7.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9
80°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.8	4.9	3.9	3.9
82.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.8	4.9	3.9	3.9
85°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.8	4.9	3.9	2.9
87.5°	7.8	7.8	7.8	7.8	6.8	6.8	5.8	5.8	4.9	3.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192526

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0	1387.0
2.5°	955.6	933.1	923.3	938.9	931.1	907.7	912.6	898.0
5°	570.0	535.8	514.4	524.1	492.9	464.6	464.6	444.0
7.5°	275.3	264.6	258.7	260.7	253.8	244.9	240.1	240.1
10°	193.3	189.4	190.3	190.3	196.2	195.2	198.1	197.2
12.5°	229.3	231.3	232.3	236.2	241.0	241.0	244.0	242.0
15°	293.8	291.8	297.7	298.7	306.5	307.4	311.3	307.4
17.5°	373.9	377.8	383.6	382.6	398.2	399.2	399.2	398.2
20°	481.2	484.1	490.0	491.9	510.5	512.4	519.2	520.2
22.5°	598.3	598.3	601.2	605.1	622.7	623.7	626.6	626.6
25°	638.3	632.4	633.4	638.3	648.2	644.1	647.2	645.1
27.5°	586.6	577.8	575.9	582.7	589.5	578.8	582.7	582.7
30°	476.3	468.5	466.6	473.4	478.3	466.6	470.5	472.4
32.5°	348.5	343.5	342.5	347.4	351.4	341.6	345.5	348.5
35°	235.2	233.2	231.3	232.3	238.1	230.3	234.2	236.2
37.5°	149.4	145.4	146.4	148.3	152.3	147.3	151.3	151.3
40°	91.8	89.8	89.8	91.8	93.7	89.8	91.8	92.7
42.5°	53.7	53.7	53.7	54.7	55.7	53.7	53.7	54.7
45°	31.2	30.2	30.2	31.2	32.2	30.2	31.2	31.2
47.5°	17.5	16.6	16.6	17.5	17.5	16.6	17.5	17.5
50°	9.7	8.8	8.8	9.7	9.7	8.8	8.8	8.8
52.5°	4.9	4.9	4.9	4.9	4.9	4.9	3.9	3.9
55°	2.9	2.9	1.9	1.9	1.9	1.9	1.9	1.0
57.5°	1.9	1.9	1.0	1.0	1.0	1.0	0.0	0.0
60°	1.9	1.9	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	1.9	1.9	1.0	1.0	1.0	0.0	0.0	0.0
65°	1.9	1.9	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	1.9	1.9	1.0	1.0	1.0	0.0	0.0	0.0
70°	2.9	1.9	1.9	1.0	1.0	1.0	0.0	0.0
72.5°	2.9	1.9	1.9	1.9	1.0	1.0	0.0	0.0
75°	2.9	1.9	1.9	1.9	1.0	1.0	0.0	0.0
77.5°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	0.0
80°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
82.5°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
85°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	0.0
87.5°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)