

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204573

Luminaire Tested: **LE_6B15D010 EC6B10209727 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209727 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1468.8 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204573

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204573

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204573

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	3.8
10°-20°	159.8	10.9
20°-30°	240.7	16.4
30°-40°	286.4	19.5
40°-50°	285.9	19.5
50°-60°	232.5	15.8
60°-70°	143.0	9.7
70°-80°	55.4	3.8
80°-90°	8.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.6	31.1
0°-40°	743.0	50.6
0°-60°	1261.4	85.9
0°-90°	1468.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	592	
5°	590	56
15°	567	160
25°	524	241
35°	459	286
45°	372	286
55°	260	233
65°	144	143
75°	50	55
85°	7	9
90°	0	



TEST NUMBER: P204573

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	591.8
2.5°	592.6
5°	590.0
7.5°	586.5
10°	582.1
12.5°	574.4
15°	567.4
17.5°	557.0
20°	545.6
22.5°	535.2
25°	523.9
27.5°	508.2
30°	492.5
32.5°	477.8
35°	458.6
37.5°	437.8
40°	418.6
42.5°	395.1
45°	371.6
47.5°	346.4
50°	319.4
52.5°	291.5
55°	260.2
57.5°	229.8
60°	200.1
62.5°	171.4
65°	143.6
67.5°	117.5
70°	93.1
72.5°	70.5
75°	50.5
77.5°	33.1
80°	20.0
82.5°	12.1
85°	7.0
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)