

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192548

Luminaire Tested: **LDA6A60935D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5729.9 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56662	56662	56662
5°	145339	51546	16052
10°	283317	39612	7715
15°	508584	26901	10346
20°	755097	20424	17081
25°	858285	16828	26784
30°	930390	18395	25194
35°	980008	11926	15620
40°	1001197	5296	7607
45°	904272	2023	2822
50°	595255	802	802
55°	163015	698	0
60°	32563	800	0
65°	2296	1077	0
70°	337	1330	0
75°	0	1991	0
80°	0	2968	347
85°	0	5913	692



TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	2.2
10°-20°	672.6	11.7
20°-30°	1524.5	26.6
30°-40°	1829.9	31.9
40°-50°	1289.7	22.5
50°-60°	266.1	4.6
60°-70°	9.4	0.2
70°-80°	5.6	0.1
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2323.7	40.6
0°-40°	4153.6	72.5
0°-60°	5709.4	99.6
0°-90°	5729.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5729.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1034	1034	1034	1034	1034	
5°	2641	1924	937	390	292	325
15°	8961	3943	474	169	182	2659
25°	14190	4769	278	390	443	6548
35°	14644	3339	178	233	233	9103
45°	11664	1145	26	36	36	8579
55°	1706	23	7	5	0	2248
65°	18	5	8	5	0	53
75°	0	5	9	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6
2.5°	1761.8	1708.7	1729.5	1668.1	1654.6	1643.1	1654.6	1587.8	1550.4	1502.4	1463.9
5°	2641.1	2577.6	2592.3	2484.9	2435.9	2402.7	2396.3	2258.9	2155.7	2042.1	1924.4
7.5°	3676.8	3616.4	3608.1	3441.4	3340.3	3283.0	3259.1	3062.1	2884.0	2681.8	2460.9
10°	5089.6	4952.1	4909.4	4667.6	4475.0	4353.0	4203.0	3888.3	3575.8	3270.5	2989.2
12.5°	6733.7	6658.8	6552.5	6126.4	5788.7	5615.8	5391.8	4900.0	4426.9	3922.7	3451.7
15°	8961.2	8694.6	8513.3	7897.6	7353.7	7087.0	6759.8	6007.6	5292.7	4654.1	3942.6
17.5°	11137.9	10998.2	10714.8	9915.6	9078.0	8657.1	8169.4	7147.4	6137.8	5229.3	4360.3
20°	12943.4	12812.2	12489.1	11735.8	10806.5	10185.5	9571.9	8169.4	6850.4	5687.7	4639.6
22.5°	13808.1	13724.8	13461.2	12816.3	12024.5	11433.7	10774.2	9039.5	7377.6	5987.7	4766.7
25°	14189.5	14150.9	13981.1	13472.6	12726.6	12225.5	11602.5	9655.2	7705.9	6127.3	4768.8
27.5°	14576.0	14583.4	14208.3	13806.0	13098.7	12617.3	12017.2	9928.2	7765.2	6049.2	4612.4
30°	14697.9	14620.9	14455.2	13877.9	13205.9	12694.3	12050.4	9802.1	7521.4	5728.3	4300.9
32.5°	14647.9	14617.7	14435.4	13824.8	13023.6	12460.0	11728.5	9302.0	7040.0	5269.8	3859.2
35°	14643.8	14587.5	14169.7	13645.7	12659.0	11962.9	10999.2	8493.4	6358.6	4665.5	3339.2
37.5°	14379.1	14239.5	13925.9	13219.5	11919.2	11036.7	9956.3	7505.8	5525.1	3987.3	2823.5
40°	13990.5	13803.0	13390.4	12321.3	10637.6	9620.9	8566.4	6383.6	4642.6	3318.4	2275.4
42.5°	13178.8	12895.5	12311.9	10841.9	8930.0	8013.2	7135.9	5246.9	3786.2	2703.8	1736.8
45°	11663.9	11276.4	10487.6	8873.8	7214.1	6466.0	5760.5	4221.7	3030.8	2005.6	1145.1
47.5°	9374.9	9015.5	8297.6	7064.1	5657.5	5025.0	4462.4	3140.3	2054.6	1161.7	547.0
50°	6979.6	6671.2	6110.6	4909.4	3797.7	3300.7	2819.4	1783.7	962.7	552.3	227.1
52.5°	4164.5	4011.3	3514.2	2722.4	1875.4	1615.9	1297.2	755.4	485.5	200.1	61.4
55°	1705.6	1574.3	1387.8	1113.8	815.8	691.8	591.7	373.0	151.1	41.7	22.9
57.5°	771.0	741.9	657.4	516.8	375.1	314.6	212.5	70.8	33.4	20.8	13.5
60°	297.0	267.7	229.2	123.9	53.1	44.8	36.4	24.0	16.7	11.5	8.3
62.5°	42.8	40.6	36.4	29.1	22.9	20.8	17.7	12.6	9.4	7.3	6.2
65°	17.7	17.7	15.6	12.6	10.5	9.4	8.3	6.2	5.2	5.2	5.2
67.5°	7.3	7.3	6.2	5.2	4.1	4.1	4.1	3.2	4.1	4.1	5.2
70°	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2	4.1	4.1	5.2
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
75°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.1	5.2	5.2
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	6.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	6.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	6.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6
2.5°	1430.5	1363.8	1345.1	1286.7	1237.8	1213.8	1183.6	1115.8	1064.8	997.0	956.5
5°	1842.1	1716.0	1615.9	1494.1	1413.8	1361.8	1280.5	1156.5	1056.5	936.7	851.2
7.5°	2286.9	2056.7	1876.5	1675.4	1559.6	1469.1	1330.4	1152.3	1005.4	846.1	713.7
10°	2716.2	2372.4	2089.0	1800.4	1648.2	1522.2	1331.5	1107.6	912.7	711.6	572.0
12.5°	3094.4	2650.5	2251.6	1880.6	1692.0	1534.7	1296.1	1027.3	791.8	585.5	462.6
15°	3410.0	2866.2	2366.1	1910.8	1695.2	1507.6	1222.1	912.7	657.4	474.0	387.6
17.5°	3649.7	2979.8	2401.6	1874.4	1634.7	1430.5	1108.5	767.8	533.5	402.1	326.1
20°	3773.7	3001.7	2350.5	1775.3	1523.2	1313.9	959.6	623.1	452.2	350.1	273.0
22.5°	3789.4	2940.2	2228.6	1633.7	1382.6	1172.1	795.0	519.8	403.2	309.4	240.7
25°	3696.7	2806.9	2054.6	1473.3	1228.4	1009.6	647.1	465.7	366.8	278.2	277.1
27.5°	3498.6	2577.6	1846.3	1286.7	1041.9	821.0	549.1	420.9	327.2	294.9	313.7
30°	3219.5	2283.8	1589.9	1051.3	813.8	631.3	462.6	346.9	287.6	290.6	306.3
32.5°	2841.2	1919.1	1288.8	770.0	582.5	475.1	346.9	236.5	238.6	239.7	253.2
35°	2366.1	1538.8	962.7	517.8	409.4	334.5	195.8	174.0	177.2	178.2	187.5
37.5°	1896.2	1182.5	639.7	344.9	257.4	176.1	121.9	116.7	118.8	117.7	128.2
40°	1452.4	824.1	383.4	170.8	98.9	82.3	75.1	71.9	73.0	74.0	80.2
42.5°	1028.4	447.0	189.6	64.6	52.2	47.9	44.8	42.8	43.7	43.7	47.9
45°	522.0	211.5	64.6	35.5	32.3	29.1	27.1	26.1	26.1	26.1	28.1
47.5°	226.0	69.8	30.2	21.9	19.7	18.8	16.7	15.6	15.6	15.6	16.7
50°	70.8	28.1	18.8	14.6	12.6	11.5	10.5	10.5	10.5	9.4	10.5
52.5°	26.1	17.7	12.6	9.4	8.3	8.3	8.3	7.3	8.3	7.3	8.3
55°	15.6	11.5	8.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
57.5°	10.5	8.3	7.3	7.3	6.2	6.2	7.3	7.3	7.3	7.3	7.3
60°	7.3	7.3	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3
62.5°	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3
65°	5.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
67.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
70°	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3	9.4
72.5°	6.2	6.2	7.3	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4
75°	6.2	7.3	7.3	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4
77.5°	6.2	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4
80°	6.2	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4	10.5
82.5°	6.2	7.3	7.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4	10.5
85°	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4	10.5
87.5°	7.3	7.3	8.3	8.3	8.3	8.3	9.4	9.4	10.5	9.4	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6
2.5°	902.2	841.8	800.1	784.5	754.3	706.4	678.3	652.2	603.3	592.8	565.8
5°	753.3	656.4	587.6	561.6	527.2	486.6	447.0	420.9	389.7	377.1	358.4
7.5°	593.9	496.9	437.6	416.8	392.7	359.5	324.0	297.9	265.6	249.0	233.4
10°	466.7	394.8	344.9	324.0	299.0	263.6	227.1	192.8	164.6	147.0	143.8
12.5°	379.2	319.9	266.7	244.8	215.7	180.2	154.1	153.2	151.1	150.0	152.1
15°	310.5	253.2	196.9	172.9	164.6	163.5	166.7	169.9	168.8	171.9	174.0
17.5°	255.3	193.8	181.3	182.3	183.4	186.4	191.7	200.1	201.1	206.3	210.4
20°	208.4	205.2	210.4	214.6	217.8	224.0	235.4	245.9	249.0	256.3	264.7
22.5°	236.5	245.9	257.4	262.6	266.7	278.2	290.6	307.3	313.7	323.0	334.5
25°	285.5	301.1	318.8	325.1	331.3	350.1	364.7	384.5	389.7	401.2	412.6
27.5°	326.1	342.8	361.5	369.8	375.1	393.8	406.4	418.8	418.8	425.0	433.4
30°	319.9	333.4	349.0	355.3	357.4	370.9	383.4	387.6	385.6	388.6	394.8
32.5°	265.6	276.1	288.6	293.8	295.9	305.3	315.7	315.7	314.6	314.6	318.8
35°	196.9	204.2	210.4	215.7	218.9	225.1	234.5	233.4	233.4	231.3	234.5
37.5°	132.3	136.5	143.8	145.9	147.0	151.1	158.4	158.4	156.3	157.3	159.4
40°	80.2	85.4	89.6	90.7	92.7	95.9	101.0	101.0	101.0	101.0	102.1
42.5°	47.9	51.1	54.2	54.2	55.2	59.3	61.4	61.4	61.4	61.4	62.5
45°	28.1	29.1	31.3	32.3	32.3	34.4	35.5	35.5	35.5	35.5	36.4
47.5°	16.7	17.7	17.7	18.8	18.8	19.7	20.8	20.8	19.7	19.7	19.7
50°	10.5	10.5	10.5	10.5	11.5	11.5	11.5	11.5	11.5	11.5	10.5
52.5°	8.3	8.3	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2
55°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	4.1	3.2
57.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.2
60°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.2
62.5°	8.3	8.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	3.2
65°	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	3.2
67.5°	8.3	8.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	4.1	3.2
70°	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.2	5.2	5.2	4.1
72.5°	9.4	9.4	8.3	8.3	8.3	8.3	7.3	6.2	6.2	5.2	4.1
75°	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3	6.2	5.2	4.1
77.5°	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3	6.2	5.2	4.1
80°	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	4.1
82.5°	10.5	10.5	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	5.2
85°	10.5	10.5	9.4	9.4	9.4	8.3	8.3	7.3	6.2	6.2	5.2
87.5°	10.5	10.5	9.4	9.4	9.4	8.3	8.3	7.3	6.2	6.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192548

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6	1033.6
2.5°	549.1	517.8	507.4	514.7	506.3	500.1	491.8	487.5
5°	343.9	320.8	313.7	315.7	308.4	302.2	293.8	291.7
7.5°	211.5	189.6	181.3	181.3	172.9	165.6	160.5	157.3
10°	141.7	137.6	138.6	139.6	138.6	139.6	136.5	138.6
12.5°	152.1	150.0	152.1	153.2	153.2	155.2	151.1	154.1
15°	177.2	175.0	178.2	180.2	180.2	183.4	179.3	182.3
17.5°	216.7	215.7	220.9	223.0	224.0	229.2	224.0	228.1
20°	274.1	273.0	280.3	283.4	282.3	292.8	285.5	292.8
22.5°	348.0	346.0	356.3	359.5	360.5	374.0	367.8	373.0
25°	422.0	424.1	429.3	434.4	435.5	447.0	437.6	442.8
27.5°	437.6	434.4	437.6	443.8	444.9	450.1	441.7	445.9
30°	395.9	390.7	391.8	399.1	401.2	403.2	395.9	398.0
32.5°	321.9	313.7	313.7	320.8	323.0	326.1	313.7	318.8
35°	237.5	230.3	230.3	235.4	236.5	238.6	229.2	233.4
37.5°	162.6	156.3	158.4	160.5	161.5	163.5	162.6	161.5
40°	104.2	100.0	103.1	103.1	104.2	105.3	105.3	106.3
42.5°	63.6	60.4	62.5	62.5	63.6	63.6	63.6	64.6
45°	36.4	35.5	35.5	36.4	36.4	36.4	35.5	36.4
47.5°	19.7	18.8	19.7	19.7	19.7	19.7	19.7	19.7
50°	10.5	9.4	9.4	9.4	9.4	9.4	9.4	9.4
52.5°	5.2	4.1	4.1	4.1	3.2	4.1	3.2	3.2
55°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
57.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.2	3.2	2.1	2.1	1.1	1.1	1.1	0.0
80°	4.1	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.1	3.2	2.1	2.1	2.1	1.1	1.1	1.1
85°	4.1	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.1	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)