

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192554

Luminaire Tested: **LDA6A60935D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6025.8 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61914	61914	61914
5°	169931	57044	23278
10°	372382	46681	8873
15°	568806	35534	10409
20°	659020	26439	16166
25°	718898	21745	26094
30°	802782	19718	26643
35°	816796	13532	18270
40°	831143	6412	9246
45°	832490	2667	4031
50°	703798	1151	1245
55°	226630	793	201
60°	45007	910	0
65°	4605	1077	0
70°	513	1507	0
75°	0	1991	0
80°	0	3283	347
85°	0	6542	692

TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.3	2.5
10°-20°	792.9	13.2
20°-30°	1518.1	25.2
30°-40°	1788.6	29.7
40°-50°	1404.9	23.3
50°-60°	342.4	5.7
60°-70°	14.7	0.2
70°-80°	5.5	0.1
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2464.3	40.9
0°-40°	4252.8	70.6
0°-60°	6000.1	99.6
0°-90°	6025.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6025.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1129	1129	1129	1129	1129	
5°	3088	2235	1037	543	423	408
15°	10022	5148	626	179	183	2798
25°	11885	6259	360	376	431	5540
35°	12205	3957	202	260	273	7653
45°	10738	1223	34	48	52	8068
55°	2371	45	8	5	2	2822
65°	36	5	8	5	0	94
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4
2.5°	1935.7	1931.6	1903.4	1929.5	1850.3	1847.1	1811.8	1796.1	1750.2	1706.5	1644.0
5°	3088.0	3020.2	2965.0	2967.1	2815.0	2786.9	2707.7	2627.5	2504.5	2390.0	2234.7
7.5°	4707.0	4626.7	4510.1	4461.1	4170.4	4085.0	3921.4	3707.9	3440.1	3173.4	2885.8
10°	6689.6	6702.0	6550.9	6411.4	5971.7	5798.8	5534.1	5113.2	4605.8	4104.8	3595.3
12.5°	8684.6	8676.2	8496.0	8284.6	7742.8	7499.0	7146.9	6621.8	5949.8	5172.6	4375.6
15°	10022.3	10081.7	10005.7	9836.9	9374.3	9095.0	8698.2	7985.5	7166.7	6222.8	5147.6
17.5°	10862.0	10918.3	10891.2	10758.9	10350.5	10052.5	9721.3	9137.8	8190.7	7004.1	5756.0
20°	11296.5	11385.0	11372.6	11228.8	10920.3	10673.5	10307.8	9767.1	8947.1	7547.0	6149.9
22.5°	11586.0	11653.8	11672.6	11510.0	11191.2	10956.8	10689.1	10141.1	9370.1	7878.3	6306.1
25°	11885.1	12004.9	11887.2	11687.2	11394.4	11169.3	10883.9	10358.8	9572.2	8013.7	6259.3
27.5°	12251.7	12309.1	12042.4	11860.1	11535.0	11291.3	10988.1	10484.8	9607.7	7905.4	5991.5
30°	12682.0	12444.5	12258.1	11896.5	11527.8	11290.2	10981.9	10405.7	9421.1	7545.9	5472.7
32.5°	12611.2	12393.5	12182.0	11799.7	11435.1	11199.5	10855.8	10142.2	8980.5	6944.8	4756.9
35°	12205.0	12251.7	12023.6	11706.9	11294.3	11051.6	10676.6	9767.1	8232.4	6115.5	3956.8
37.5°	11862.2	11965.3	11816.4	11523.5	11104.7	10776.5	10270.2	9164.9	7256.2	5063.3	3198.4
40°	11614.2	11647.6	11567.3	11239.1	10736.0	10261.9	9676.4	8083.5	6070.7	3974.5	2524.4
42.5°	11229.7	11318.3	11176.6	10818.2	10055.6	9519.1	8671.1	6834.4	4715.3	3035.8	1900.2
45°	10738.0	10822.4	10647.4	10051.5	8990.9	8204.4	7169.8	5328.9	3488.0	2237.8	1223.1
47.5°	9935.9	9987.9	9649.4	8825.3	7283.4	6542.6	5482.1	3715.2	2247.2	1251.2	594.9
50°	8252.3	8227.3	7529.2	6515.6	4871.6	4094.4	3263.0	2013.8	1009.5	592.8	371.9
52.5°	5318.4	5261.2	4570.5	3648.4	2467.0	1882.6	1414.8	868.8	526.2	331.3	146.8
55°	2371.2	2349.3	1923.1	1494.0	1009.5	868.8	663.6	426.1	280.3	115.6	44.8
57.5°	879.3	859.5	757.5	635.5	487.5	405.3	321.9	204.2	71.9	38.5	24.0
60°	410.5	409.4	360.5	297.0	206.3	156.2	90.7	47.9	30.2	20.8	13.5
62.5°	131.2	128.2	89.6	65.7	46.9	40.6	32.3	24.0	15.6	11.5	8.3
65°	35.5	35.5	32.3	27.1	21.9	18.8	15.6	11.5	7.3	6.2	5.2
67.5°	13.5	13.5	12.6	11.5	8.3	7.3	6.2	5.2	4.1	5.2	5.2
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.1	4.1	5.2
72.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
75°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
80°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
82.5°	0.0	0.0	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2	6.2
85°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.1	4.1	5.2	6.2
87.5°	0.0	0.0	1.1	2.1	2.1	3.2	3.2	4.1	4.1	5.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4
2.5°	1598.2	1529.4	1434.6	1379.4	1365.8	1336.6	1285.6	1209.6	1147.0	1086.6	1051.1
5°	2103.4	1940.9	1758.6	1630.4	1578.4	1508.6	1384.5	1256.5	1138.8	1036.6	956.3
7.5°	2638.9	2371.2	2076.3	1838.8	1753.4	1643.0	1440.8	1250.1	1088.7	947.1	839.7
10°	3171.3	2740.0	2339.9	1996.1	1856.5	1706.5	1439.7	1192.9	1003.2	838.6	719.9
12.5°	3703.7	3083.8	2533.7	2090.9	1909.6	1720.0	1397.1	1105.4	894.9	727.2	613.7
15°	4195.4	3357.8	2665.0	2123.2	1904.5	1680.4	1310.6	999.1	781.3	626.1	520.9
17.5°	4562.1	3501.6	2695.2	2074.3	1822.1	1574.1	1178.4	874.1	673.0	536.5	429.2
20°	4742.3	3524.5	2623.3	1934.6	1680.4	1423.2	1033.5	754.3	580.3	453.2	362.5
22.5°	4742.3	3416.1	2467.0	1759.6	1503.4	1249.2	893.8	655.3	507.4	394.8	318.8
25°	4562.1	3200.5	2257.6	1557.6	1308.5	1077.2	773.1	581.4	451.1	359.5	295.9
27.5°	4212.1	2902.5	1988.8	1332.5	1116.8	924.0	677.2	513.6	408.3	324.0	325.0
30°	3730.8	2536.8	1680.4	1095.0	919.9	759.5	569.9	430.3	327.2	311.5	320.8
32.5°	3174.4	2099.2	1331.4	849.1	712.6	598.0	433.4	304.2	260.4	262.5	273.0
35°	2603.5	1652.4	1002.3	629.3	530.3	433.4	284.4	200.1	197.9	202.2	209.4
37.5°	2055.5	1236.6	725.0	460.5	356.3	266.7	153.2	137.6	137.6	141.7	145.9
40°	1539.8	877.2	499.0	273.0	172.9	121.9	96.9	89.6	88.6	89.6	94.8
42.5°	1057.5	555.3	297.0	109.4	83.4	70.8	61.4	56.3	55.2	56.3	59.3
45°	593.8	341.7	115.6	58.4	50.0	44.8	38.5	35.5	34.4	34.4	36.4
47.5°	371.9	135.4	52.0	36.4	31.2	29.1	25.0	22.9	21.9	21.9	22.9
50°	142.7	53.1	32.3	24.0	20.8	18.8	16.7	14.6	13.5	13.5	14.6
52.5°	49.0	31.2	20.8	15.6	13.5	12.6	10.4	9.4	9.4	9.4	9.4
55°	27.1	18.8	12.6	9.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3
57.5°	16.7	11.5	8.3	7.3	7.3	7.3	7.3	7.3	7.3	8.3	8.3
60°	9.4	7.3	6.2	6.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3
62.5°	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
65°	5.2	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3
67.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.3	8.3	8.3	8.3
70°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	8.3	9.4	9.4
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4
75°	6.2	6.2	6.2	7.3	7.3	7.3	8.3	9.4	9.4	9.4	9.4
77.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4	9.4
80°	6.2	6.2	7.3	7.3	8.3	8.3	9.4	9.4	9.4	10.4	10.4
82.5°	6.2	6.2	7.3	8.3	8.3	8.3	9.4	9.4	10.4	10.4	10.4
85°	6.2	7.3	7.3	8.3	8.3	8.3	9.4	9.4	10.4	10.4	10.4
87.5°	6.2	7.3	7.3	8.3	8.3	8.3	9.4	9.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4
2.5°	1004.3	960.6	916.9	884.6	868.8	853.2	818.9	774.0	755.3	728.2	712.6
5°	875.2	801.2	742.8	704.2	681.3	651.1	611.6	567.7	542.8	514.6	496.0
7.5°	741.7	655.3	599.0	563.6	540.7	503.1	453.2	401.2	370.9	339.6	317.8
10°	625.1	542.8	479.3	438.6	409.4	365.7	315.7	279.2	253.2	226.0	204.2
12.5°	521.9	433.4	365.7	331.3	311.5	269.8	228.1	187.5	171.9	166.7	166.7
15°	423.0	342.8	285.5	256.3	235.4	190.7	182.3	180.2	179.3	178.2	180.2
17.5°	344.9	277.1	216.7	202.2	200.1	199.0	200.1	200.1	201.1	204.2	209.4
20°	289.7	227.1	223.0	224.0	224.0	228.1	233.4	237.5	241.6	246.9	256.3
22.5°	257.4	256.3	263.6	264.7	269.8	276.1	285.5	291.7	302.1	307.3	320.8
25°	297.0	304.2	317.8	321.9	330.2	340.7	355.2	363.6	376.1	382.4	398.0
27.5°	336.4	348.0	364.6	369.8	377.1	393.8	404.2	411.5	417.7	422.0	431.4
30°	333.4	343.8	360.5	361.5	371.9	383.4	389.7	395.9	400.1	399.0	404.2
32.5°	282.3	291.7	307.3	307.3	318.8	328.2	331.3	336.4	336.4	336.4	338.6
35°	216.7	223.0	233.4	236.5	245.9	252.1	254.2	260.4	260.4	258.3	258.3
37.5°	150.0	158.4	165.6	167.7	174.0	178.2	183.4	184.4	182.3	183.4	183.4
40°	98.0	103.1	108.3	109.4	114.5	117.7	123.0	123.0	123.9	123.0	125.0
42.5°	60.4	64.6	67.8	69.8	71.9	74.0	77.1	78.1	79.2	78.1	80.2
45°	37.5	39.6	41.7	42.8	43.7	44.8	47.9	47.9	47.9	47.9	49.0
47.5°	22.9	24.0	25.0	25.0	26.1	27.1	28.1	28.1	28.1	28.1	29.1
50°	13.5	14.6	14.6	14.6	15.6	15.6	16.7	16.7	16.7	15.6	16.7
52.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.3	9.4
55°	8.3	8.3	7.3	7.3	7.3	7.3	7.3	6.2	5.2	5.2	4.1
57.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	3.2
60°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.2
62.5°	8.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.2
65°	8.3	8.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2	4.1	3.2
67.5°	8.3	8.3	8.3	7.3	8.3	7.3	6.2	6.2	5.2	4.1	4.1
70°	9.4	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.1	4.1
72.5°	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.2	5.2	5.2	4.1
75°	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.1
77.5°	9.4	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.1
80°	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	4.1
82.5°	10.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	5.2
85°	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	6.2	5.2
87.5°	10.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	6.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192554

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4	1129.4
2.5°	697.0	688.6	688.6	674.1	671.9	660.5	669.8	663.6
5°	475.1	461.5	457.3	442.8	437.6	424.1	428.2	423.0
7.5°	299.0	285.5	281.2	270.9	264.7	254.2	255.3	252.1
10°	182.3	169.9	166.7	163.5	160.5	159.4	160.5	159.4
12.5°	165.6	164.6	162.6	163.5	161.5	162.6	163.5	162.6
15°	180.2	182.3	180.2	181.3	180.2	182.3	183.4	183.4
17.5°	211.5	215.7	213.6	216.7	215.7	220.8	220.8	220.8
20°	259.4	266.7	264.7	268.8	268.8	275.0	275.0	277.1
22.5°	326.1	335.5	334.4	343.8	341.7	349.0	349.0	351.1
25°	406.3	415.7	416.8	423.0	422.0	429.2	429.2	431.4
27.5°	439.7	444.9	443.8	447.0	447.9	452.1	455.3	453.2
30°	412.6	416.8	415.7	417.7	417.7	420.9	424.1	420.9
32.5°	346.9	350.1	350.1	354.2	351.1	352.2	357.3	354.2
35°	265.6	267.7	265.6	267.7	268.8	268.8	274.1	273.0
37.5°	189.6	190.7	190.7	193.8	190.7	190.7	195.8	196.9
40°	127.1	128.2	127.1	131.2	129.2	129.2	132.3	129.2
42.5°	81.3	82.3	81.3	84.4	82.3	84.4	85.4	86.5
45°	50.0	50.0	49.0	51.1	50.0	51.1	52.0	52.0
47.5°	29.1	29.1	28.1	30.2	29.1	29.1	29.1	30.2
50°	15.6	15.6	15.6	16.7	15.6	15.6	15.6	14.6
52.5°	8.3	8.3	7.3	8.3	7.3	7.3	7.3	7.3
55°	4.1	3.2	3.2	3.2	2.1	2.1	2.1	2.1
57.5°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	0.0	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	3.2	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	4.1	3.2	2.1	2.1	1.1	1.1	0.0	0.0
80°	4.1	3.2	2.1	2.1	2.1	1.1	1.1	1.1
82.5°	4.1	3.2	3.2	2.1	2.1	1.1	1.1	1.1
85°	4.1	3.2	3.2	2.1	2.1	1.1	1.1	1.1
87.5°	4.1	3.2	3.2	2.1	2.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)